

Artisans Asylum – Electronics and Robotics Parts Locator/Inventory

2024-Mar-01 DETAILED

| Line | Bench/Location | Top/Mid/Bottom | Item |
|------|----------------|----------------|---|
| 1 | Bench Alpha | Top | Heat Shrink |
| 2 | Bench Alpha | Top | Hot Glue Guns |
| 3 | Bench Alpha | Top | Cable Wrap |
| 4 | Bench Alpha | Top | Heat Guns |
| 5 | Bench Alpha | Middle | Photon |
| 6 | Bench Alpha | Middle | FTDI Adapters |
| 7 | Bench Alpha | Middle | DB9/DB15 adapters |
| 8 | Bench Alpha | Middle | Breadboard jumpers (specials) |
| 9 | Bench Alpha | Middle | IC Test clip/chip probe |
| 10 | Bench Alpha | Middle | RS485-Cricket |
| 11 | Bench Alpha | Middle | MicroUSB breakout |
| 12 | Bench Alpha | Middle | EMPTY |
| 13 | Bench Alpha | Middle | USB to WiFi |
| 14 | Bench Alpha | Middle | Arduino – Temp – Current – Hall – TMP37F temperature – INA169 Analog DC current sensor – hall sensor – tilt sensor – thermistor NTC 100K – MAX30100EFD oximeter/hearttrate |
| 15 | Bench Alpha | Middle | Arduino distance – 2Y0A21 – GP2D120 – GP2D150 – Hagisonic AniBat – ambient light sensors |
| 16 | Bench Alpha | Middle | Arduino ADC/DAC/GPS – Gas sensors – MQ-3, MQ-5, MQ-6, MQ135, MQ-2, MQ-8, MQ-9; TTL JPEG Camera (Adafruit 397) – Accelerometers |
| 17 | Bench Alpha | Middle | SENSORS – pressure – humidity – distance – CO; DHT22 humidity, Parallax 27920 humidity HS1101, AMP load cells (FX29, 0.5-4.5V output, 5V supply); ACF5799003 (IR?); Adafruit 157 IR sensor TSOP38238, bend sensors, SSCSRNN1.6BA7A3 1.6 Bar absolute 3.3V pressure sensor, MPXV7002G pressure sensor, I2C MCP23017 input/output port expander; RepRap SD Ramp; water sensor |
| 18 | Bench Alpha | Middle | Arduino distance – 2Y0A21 – GP2D120 – GP2D150 – Hagisonic AniBat – ambient light sensors |
| 19 | Bench Alpha | Middle | 1 MB Memory and logic shift |
| 20 | Bench Alpha | Lower | Project boxes, large |
| 21 | Bench Alpha | Lower | Automotive |
| 22 | Bench Alpha | Lower | Car 12V plugs |
| 23 | Bench Alpha | Lower | Laptop power supplies |
| 24 | Bench Alpha | Lower | Small DC motors |
| 25 | Bench Alpha | Lower | Bunsen burners and lab strut |
| 26 | Bench Alpha | Lower | Matched 3C/4C connectors |
| 27 | Bench Alpha | Lower | RCA cables and plugs |
| 28 | Bench Bravo | Top | Arduino/RPI displays; polarizing films |
| 29 | Bench Bravo | Top | Small HDMI screen |
| 30 | Bench Bravo | Top | Remote control/RC 4 channel |
| 31 | Bench Bravo | Top | IR remotes |
| 32 | Bench Bravo | Top | Game controllers |
| 33 | Bench Bravo | Top | Flight simulator yoke for PC |
| 34 | Bench Bravo | Top | Electret microphone |
| 35 | Bench Bravo | Top | Borescope |
| 36 | Bench Bravo | Top | Stethoscope |
| 37 | Bench Bravo | Top | Touchscreen |
| 38 | Bench Bravo | Top | Heat sinks |
| 39 | Bench Bravo | Middle | Arduino power connectors |
| 40 | Bench Bravo | Middle | Arduino shields |
| 41 | Bench Bravo | Middle | Arduino stepper drivers |
| 42 | Bench Bravo | Middle | Smaller stepper motors and linear slides |
| 43 | Bench Bravo | Middle | Arduino power via battery |
| 44 | Bench Bravo | Middle | Arduino sensors |
| 45 | Bench Bravo | Middle | Conductive fabric |
| 46 | Bench Bravo | Middle | Level shifters |
| 47 | Bench Bravo | Middle | Feather/Huzzah/Stemma connectors |
| 48 | Bench Bravo | Middle | Raspberry Pi |
| 49 | Bench Bravo | Middle | Soldering practice |
| 50 | Bench Bravo | Middle | Signal generator board |
| 51 | Bench Bravo | Middle | Arduino Uno/Duemilenove |
| 52 | Bench Bravo | Middle | RPI breadboard |
| 53 | Bench Bravo | Middle | BNC connectors and Tees |
| 54 | Bench Bravo | Middle | Rascal and Galileo |
| 55 | Bench Bravo | Middle | Mega/Leonardo |
| 56 | Bench Bravo | Middle | Arduino Ethernet shield |
| 57 | Bench Bravo | Middle | Arduino demo |
| 58 | Bench Bravo | Middle | Digital playground |
| 59 | Bench Bravo | Middle | Neopixel |
| 60 | Bench Bravo | Middle | Raspberry Pi 4 station |
| 61 | Bench Bravo | Middle | HDMI converters |
| 62 | Bench Bravo | Middle | Pogo pins |
| 63 | Bench Bravo | Middle | Pi Zero |
| 64 | Bench Bravo | Middle | SD cards |
| 65 | Bench Bravo | Middle | SD readers |
| 66 | Bench Bravo | Middle | USB storage |
| 67 | Bench Bravo | Middle | House USB micro |
| 68 | Bench Bravo | Middle | DVD-R |

| | | | | |
|-----|-------------|---------------|--|---|
| 69 | Bench Bravo | Middle | Grove connectors | |
| 70 | Bench Bravo | Middle | PIC Programmer; melabs.com U2 programmer | |
| 71 | Bench Bravo | Lower | Industrial Controls 5 | fuse blocks (DIN mount), knife disconnect (DIN) large power blocks, lockout-tagout, PLC controller |
| 72 | Bench Bravo | Lower | Industrial Controls 6 | Feed throughs, 5V, 24V, 120 VAC, 240 VAC indicator lights, DIN rail, DIN mounting plates |
| 73 | Bench Bravo | Lower | Industrial Controls 7 | Estop, buzzer, lights, circuit breakers (2,3,4,5,10,25,32 Amp), safety relays, Mitsubishi L61P, TimeR Power 20R-14C, DPM75 motor surge protector SH04 AEG power auxiliary contactor |
| 74 | Bench Bravo | Lower | Limit switches and pushbuttons | |
| 75 | Bench Bravo | Lower | Network gear | |
| 76 | Bench Bravo | Lower | Panda and Beagleboards | |
| 77 | Bench Bravo | Lower | 15V and +/-15V power | |
| 78 | Bench Bravo | Lower | 18-36V power supplies, 9-36V power supplies | |
| 79 | Bench Bravo | Lower | Computer parts, USB C docking station | |
| 80 | Bench Bravo | Lower | 3C shielded cables | |
| 81 | Bench Bravo | Lower | Ethernet jacks | |
| 82 | Bench Bravo | Lower | Phone jacks | |
| 83 | Bench Bravo | Lower | Photovoltaic charger | |
| 84 | Bench Bravo | Lower | X10 house control | |
| 85 | Bench Bravo | Lower | Tube of DIN rail | |
| 86 | Bench Bravo | Lower | DIN rail, large power connectors and power feeds | |
| 87 | Bench Bravo | Lower | EMPTY | |
| 88 | Toolbox | Box | Hand tools | |
| 89 | Toolbox | Box | Screwdrivers | |
| 90 | Toolbox | Box | Cordless drill | |
| 91 | Toolbox | Box | Motorized drivers | |
| 92 | Toolbox | Box | Torx and sockets | |
| 93 | Toolbox | Box | ¼ bits | |
| 94 | Toolbox | Box | 4mm bits | |
| 95 | Toolbox | Box | Small screwdrivers | |
| 96 | Toolbox | Box | Hex tools | |
| 97 | Toolbox | Box | Pliers | |
| 98 | Toolbox | Box | Fuse Pullers | |
| 99 | Toolbox | Box | Crimp tools | |
| 100 | Toolbox | Box | Soldering tools | |
| 101 | Toolbox | Below | Industrial vacuum | |
| 102 | Toolbox | Below | 180 kg floor scale | |
| 103 | Shelf Alpha | Shelf 7 | Empty | |
| 104 | Shelf Alpha | Shelf 6 | 3300uF 25V capacitors | |
| 105 | Shelf Alpha | Shelf 6 | 4700uF 16V capacitors | |
| 106 | Shelf Alpha | Shelf 6 | Remote control build kit | |
| 107 | Shelf Alpha | Shelf 5 | IDC headers, 40 and 50 pin | |
| 108 | Shelf Alpha | Shelf 5 | 100 uF, 400V; 3300uF, 35V capacitors | |
| 109 | Shelf Alpha | Shelf 5 | Coax crimp, Coax cable | |
| 110 | Shelf Alpha | Shelf 5 | Coax splitters | |
| 111 | Shelf Alpha | Shelf 5 | Wire wrap; headsets; Plantronics CS520 | |
| 112 | Shelf Alpha | Shelf 4 | NiMH Batteries | |
| 113 | Shelf Alpha | Shelf 4 | LiPO Batteries | |
| 114 | Shelf Alpha | Shelf 4 | LiPO /NiMH battery chargers | |
| 115 | Shelf Alpha | Shelf 4 | AC to USB power | |
| 116 | Shelf Alpha | Shelf 4 | Drill bits and cordless drivers | |
| 117 | Shelf Alpha | Shelf 4 | small spool wire | |
| 118 | Shelf Alpha | Shelf 4 | magnet wire | |
| 119 | Shelf Alpha | Shelf 4 | JST connectors | |
| 120 | Shelf Alpha | Shelf 4 | BNC cables and post | |
| 121 | Shelf Alpha | Shelf 4 | USB exotics | |
| 122 | Shelf Alpha | Shelf 4 | USB barcode scanner | |
| 123 | Shelf Alpha | Shelf 4 | Measuring tools/distance | |
| 124 | Shelf Alpha | Shelf 4 | Magnifiers/Precision Resistors/Digital caliper | |
| 125 | Shelf Alpha | Shelf 4 | Tweezers – Q-tips – Cleaning tips | |
| 126 | Shelf Alpha | Shelf 4 | Flush cutters | |
| 127 | Shelf Alpha | Shelf 4 | Small wire strippers | |
| 128 | Shelf Alpha | Shelf 4 | Large wire strippers | |
| 129 | Shelf Alpha | Shelf 3 | USB widgets – cameras | |
| 130 | Shelf Alpha | Shelf 3 | USB widgets – sound recorders | |
| 131 | Shelf Alpha | Shelf 3 | USB widgets – portable scanners | |
| 132 | Shelf Alpha | Shelf 3 | Breadboard jumpers – Box 1 | |
| 133 | Shelf Alpha | Shelf 3 | Breadboard jumpers – Box 2 | |
| 134 | Shelf Alpha | Shelf 3 | Breadboard jumpers – Box 3 | |
| 135 | Shelf Alpha | Shelf 3 | Breadboards | |
| 136 | Shelf Alpha | Shelf 2 | 5V SSR power relays | |
| 137 | Shelf Alpha | Shelf 2 | Solid state relays | |
| 138 | Shelf Alpha | Shelf 2 | 5V and 12V fans | |
| 139 | Shelf Alpha | Shelf 2 | Industrial controls 3 | Pressure sensors, 0-30 psia, 0-10 psig, pressure switch, SICK RE11-DA; M8/M12 cables; immersion heater |
| 140 | Shelf Alpha | Shelf 2 | Industrial controls 4 | Industrial counters, meters, timers, time delay relays |
| 141 | Shelf Alpha | Shelf 2 | Speakers | |
| 142 | Shelf Alpha | Shelf 1/Floor | VI-B51-02 ; 150V to 12V DC to DC converter | VICOR |

| | | | | |
|-----|---------------|---------------|---|--|
| 143 | Shelf Alpha | Shelf 1/Floor | Industrial controls 2 | DIN Rail connectors/terminal blocks (Automation Direct and others) |
| 144 | Shelf Alpha | Shelf 1/Floor | Industrial controls 1 | Large solenoid LEV200A4ANF, solenoids 12VDC, 24VDC |
| 145 | Shelf Bravo | Shelf 7 | EMPTY | |
| 146 | Shelf Bravo | Shelf 6 | Soldering irons (old) | |
| 147 | Shelf Bravo | Shelf 6 | 7 segment displays, large | |
| 148 | Shelf Bravo | Shelf 5 | Photodiodes | |
| 149 | Shelf Bravo | Shelf 5 | lasers | |
| 150 | Shelf Bravo | Shelf 5 | Molex connectors, Peltier coolers, 12V heaters | |
| 151 | Shelf Bravo | Shelf 5 | AMP connectors | |
| 152 | Shelf Bravo | Shelf 5 | Audio ¼ and 1/8 | |
| 153 | Shelf Bravo | Shelf 5 | XLR and DIN | |
| 154 | Shelf Bravo | Shelf 5 | Cassette adapter to ¼ jack | |
| 155 | Shelf Bravo | Shelf 4 | Ipod USB – USB Universal – USB C | |
| 156 | Shelf Bravo | Shelf 4 | USB Micro A | |
| 157 | Shelf Bravo | Shelf 4 | USB B end | |
| 158 | Shelf Bravo | Shelf 4 | USB Mini A | |
| 159 | Shelf Bravo | Shelf 4 | LED 3 – Bipolar LEDs | |
| 160 | Shelf Bravo | Shelf 4 | LED 2 – Reflectors | |
| 161 | Shelf Bravo | Shelf 4 | LED 1 Generic LEDs, FyreWyre | |
| 162 | Shelf Bravo | Shelf 4 | Xbee and Bluetooth | |
| 163 | Shelf Bravo | Shelf 4 | IR transmitters and receivers; optoisolators | |
| 164 | Shelf Bravo | Shelf 4 | NiCD/Lithium batteries | |
| 165 | Shelf Bravo | Shelf 4 | Alkaline batteries, battery test | |
| 166 | Shelf Bravo | Shelf 4 | Mini vacuums | |
| 167 | Shelf Bravo | Shelf 4 | Free widgets | |
| 168 | Shelf Bravo | Shelf 3 | 24 VDC supplies | |
| 169 | Shelf Bravo | Shelf 3 | 50 nF 100V capacitors | |
| 170 | Shelf Bravo | Shelf 3 | 1500 uF 300V capacitors | |
| 171 | Shelf Bravo | Shelf 3 | Variable voltage power supplies | |
| 172 | Shelf Bravo | Shelf 2 | 6V and below power supplies except 5V | |
| 173 | Shelf Bravo | Shelf 2 | Below 12V and above 6V power supplies | |
| 174 | Shelf Bravo | Shelf 2 | 12V power supplies | |
| 175 | Shelf Bravo | Shelf 2 | Greater than 24V power supplies | |
| 176 | Shelf Bravo | Shelf 2 | 5V power supplies, mini and micro 5V | |
| 177 | Shelf Bravo | Shelf 2 | Power supplies greater than 12 V less than 24V | |
| 178 | Shelf Bravo | Shelf 1/Floor | Power resistors | |
| 179 | Shelf Bravo | Shelf 1/Floor | Power resistors | |
| 180 | Shelf Bravo | Shelf 1/Floor | Power resistors | |
| 181 | Shelf Bravo | Shelf 1/Floor | Fans, 12V, 24V, 120VAC | |
| 182 | Shelf Charlie | Shelf 7 | 48V DC 8.3A supplies; 60V DC 6A supplies | |
| 183 | Shelf Charlie | Shelf 6 | Empty boxes | |
| 184 | Shelf Charlie | Shelf 5 | Molex connectors | |
| 185 | Shelf Charlie | Shelf 5 | IDC headers; 10, 16, 20, 26, 34, 40, 50, 60 pin | |
| 186 | Shelf Charlie | Shelf 5 | Old development boards of various vintages; Stellaris launchpad | |
| 187 | Shelf Charlie | Shelf 5 | SPARE | |
| 188 | Shelf Charlie | Shelf 5 | Old multimeters and multimeter parts | |
| 189 | Shelf Charlie | Shelf 5 | Wire ferrules and crimper | |
| 190 | Shelf Charlie | Shelf 5 | P-clips and sticky mounts | |
| 191 | Shelf Charlie | Shelf 5 | Molex modular jacks and plugs, Molex drawers | |
| 192 | Shelf Charlie | Shelf 5 | Aviation connectors, 2,3,4,6 pin | |
| 193 | Shelf Charlie | Shelf 4 | keypads | |
| 194 | Shelf Charlie | Shelf 4 | AC control from Arduino | |
| 195 | Shelf Charlie | Shelf 4 | Rubber feet and cable clips, edge protectors | |
| 196 | Shelf Charlie | Shelf 4 | Basic multimeters (cheap) | |
| 197 | Shelf Charlie | Shelf 4 | Parallax and Beagle; Boron/Particle IOT; OpenCR | |
| 198 | Shelf Charlie | Shelf 4 | PCB mount terminal strips | |
| 199 | Shelf Charlie | Shelf 4 | USB with free ends | |
| 200 | Shelf Charlie | Shelf 4 | Battery rechargers | |
| 201 | Shelf Charlie | Shelf 4 | Inductors | |
| 202 | Shelf Charlie | Shelf 4 | Massive coils | |
| 203 | Shelf Charlie | Shelf 4 | RS232 and RS485 converters | |
| 204 | Shelf Charlie | Shelf 4 | Wire ferrules and crimper | |
| 205 | Shelf Charlie | Shelf 4 | Xacto | |
| 206 | Shelf Charlie | Shelf 4 | Office supplies, dry erase, pins, post-its | |
| 207 | Shelf Charlie | Shelf 4 | Resistor and capacitor boxes | |
| 208 | Shelf Charlie | Shelf 3 | LDT-028K piezo/vibration | |
| 209 | Shelf Charlie | Shelf 3 | Capacitors < 1 uF | |
| 210 | Shelf Charlie | Shelf 3 | Resistor sets | |
| 211 | Shelf Charlie | Shelf 2 | Phoenix contact – small | |
| 212 | Shelf Charlie | Shelf 2 | Phoenix contact – large | |
| 213 | Shelf Charlie | Shelf 2 | Uncommon connectors | |
| 214 | Shelf Charlie | Shelf 2 | Walabot/Lytro | |
| 215 | Shelf Charlie | Shelf 2 | Capacitors, 100 uF + | |
| 216 | Shelf Charlie | Shelf 2 | EMPTY | |
| 217 | Shelf Charlie | Shelf 1/Floor | Oscilloscope storage bag | |
| 218 | Corner | Shelf 1/Floor | White board | |
| 219 | Corner | Shelf 1/Floor | Arduino based robots | |
| 220 | Corner | Shelf 1/Floor | Robot tank frame | |
| 221 | Corner | Shelf 1/Floor | Dry erase markers | |
| 222 | Corner | Shelf 1/Floor | Wireless public address systems | |
| 223 | Corner | Shelf 1/Floor | Wood (2x4s) | |

| | | | |
|-----|--------------------|---------------|---|
| 224 | Corner | Shelf 1/Floor | Silicon single wafers |
| 225 | XYZ Table | Top | XYZ table |
| 226 | XYZ Table | Top | Arduino based robots |
| 227 | XYZ Table | Bottom | Stepper motor slides |
| 228 | XYZ Table | Bottom | XY Arduino based sensor moving system |
| 229 | XYZ Table | Bottom | 4 channel RC system |
| 230 | XYZ Table | Bottom | Roomba and Roomba power |
| 231 | Rolling Cart | Bottom | PC and driver software for XYZ table |
| 232 | Rolling Cart | Bottom | Speaker system for PC |
| 233 | Bookshelf | Top | Cable Wrap |
| 234 | Bookshelf | Top | Air solder system (in box) |
| 235 | Bookshelf | Shelf 6 | Tape |
| 236 | Bookshelf | Shelf 6 | Electrical tape |
| 237 | Bookshelf | Shelf 6 | EMPTY |
| 238 | Bookshelf | Shelf 6 | Conductive tape |
| 239 | Bookshelf | Shelf 6 | thread and string |
| 240 | Bookshelf | Shelf 6 | votive lights (battery powered) |
| 241 | Bookshelf | Shelf 6 | Velcro |
| 242 | Bookshelf | Shelf 5 | aluminum foil |
| 243 | Bookshelf | Shelf 5 | First aid kit |
| 244 | Bookshelf | Shelf 5 | latex gloves |
| 245 | Bookshelf | Shelf 5 | GPS unit |
| 246 | Bookshelf | Shelf 5 | Pulse O2 |
| 247 | Bookshelf | Shelf 5 | Books |
| 248 | Bookshelf | Shelf 5 | Paper bags for votives |
| 249 | Bookshelf | Shelf 5 | Books |
| 250 | Bookshelf | Shelf 4 | Light pucks |
| 251 | Bookshelf | Shelf 4 | EMPTY |
| 252 | Bookshelf | Shelf 4 | Books |
| 253 | Bookshelf | Shelf 3 | Books |
| 254 | Bookshelf | Shelf 3 | Make Magazine |
| 255 | Bookshelf | Shelf 2 | Books |
| 256 | Bookshelf | Shelf 2 | Glass break sensor and tester |
| 257 | Bookshelf | Shelf 2 | Sirens |
| 258 | Bookshelf | Shelf 1 | RJ-12 wire and crimper |
| 259 | Bookshelf | Shelf 1 | Old phone |
| 260 | Bookshelf | Shelf 1 | Books |
| 261 | Bookshelf | Shelf 1 | McMaster catalog |
| 262 | Bookshelf | Shelf 1 | Allied catalog |
| 263 | Fireproof Cabinet | Middle | Paint for marking E&R components (pink/green) |
| 264 | Fireproof Cabinet | Middle | Isopropyl alcohol |
| 265 | Fireproof Cabinet | Top | Printers |
| 266 | PrintMonster Bench | Top | Pencil sharpeners |
| 267 | PrintMonster Bench | Top | Hole punch |
| 268 | PrintMonster Bench | Top | Staplers |
| 269 | PrintMonster Bench | Top | Pens/Pencils/Scissors |
| 270 | PrintMonster Bench | Top | Architect's scale |
| 271 | PrintMonster Bench | Top | Binder clips |
| 272 | PrintMonster Bench | Top | Screen cleaner, 409 cleaner |
| 273 | PrintMonster Bench | Bottom | Paper, 11x17, 8.5x11 |
| 274 | PrintMonster Bench | Bottom | Paper, 8.5x14 |
| 275 | PrintMonster Bench | Bottom | DVD-RW, 3.5 inch floppies, DVD reader |
| 276 | PrintMonster Bench | Bottom | floppy reader, 100 MB Zip drive reader |
| 277 | PrintMonster Bench | Bottom | 8.5x11 glossy |
| 278 | PrintMonster Bench | Bottom | Staples |
| 279 | PrintMonster Bench | Bottom | Pens, pencils, staples, binder clips, dry erase |
| 280 | PrintMonster Bench | Bottom | Paper clips |
| 281 | PrintMonster Bench | Bottom | Stencil kit |
| 282 | PrintMonster Bench | Side | Computer |
| 283 | PrintMonster Bench | Side | Shredder |
| 284 | Bench Charlie | Top | Drift Bin |
| 285 | Bench Charlie | Top | 120/240 VAC power supplies; European plugs |
| 286 | Bench Charlie | Top | AC dongles and Edison AC plugs |
| 287 | Bench Charlie | Top | Heat Shrink |
| 288 | Bench Charlie | Top | Tape |
| 289 | Bench Charlie | Bottom | AC bulbs |
| 290 | Bench Charlie | Bottom | AC power strips |
| 291 | Bench Charlie | Bottom | Industrial contactors |
| 292 | Bench Delta | Top | 13.8 VDC 10 Amp power supply |
| 293 | Bench Delta | Top | 3-15 VAC variable output |
| 294 | Bench Delta | Top | Variac |
| 295 | Bench Delta | Middle | Desoldering tool |
| 296 | Bench Delta | Bottom | AC Extension cords |
| 297 | Bench Delta | Bottom | AC cable |
| 298 | Bench Delta | Bottom | UPS (w/o battery) |
| 299 | Bench Delta | Bottom | AC junction box and outlets |
| 300 | Bench Delta | Bottom | heavy gage 12VDC jumper cables |
| 301 | Bench Echo | Top | |
| 302 | Bench Echo | Bottom | Car jumper packs and compressors |
| 303 | Bench Echo | Bottom | IEC cables |
| 304 | Bench Foxtrot | Top | |
| 305 | Bench Foxtrot | Bottom | Plastic bags and packing material |
| 306 | Bench Foxtrot | Bottom | Signal analyzer (Agilent) |

| | | | | |
|-----|-------------------|------------|---|-------------------------|
| 307 | Bench Foxtrot | Bottom | Travel box | |
| 308 | Bench Foxtrot | Bottom | Thermocouples | |
| 309 | Bench Golf | Top | Projector | |
| 310 | Bench Golf | Bottom | Coax cable | |
| 311 | Bench Golf | Bottom | Travel box | |
| 312 | Bench Hotel | Top | | |
| 313 | Bench Hotel | Bottom | Network cables and wireless | |
| 314 | Bench Hotel | Bottom | Keyboards and mice | |
| 315 | Bench Hotel | Bottom | Old soldering stations | |
| 316 | Bench Hotel | Bottom | Dual monitor mounts (x2) | |
| 317 | Back Wall Storage | Top | Metric hardware; M2, M3, M4, M5; some M2.5 | |
| 318 | Back Wall Storage | Top | sheet metal screws – tips – wood screws – large sheet metal – tiny machine screws – screws for plastic – furniture -bolts (1-4) – long bolts – springs – wingnuts – plastic washers – metal washers – nuts – anchors – eye hooks – cotter pins | In green drawer cabinet |
| 319 | Back Wall Storage | Top | PC screws – bolts – sheet metal screws – shaft collar – badge clips – 3D inserts – heavy bolts – random parts – PIC nails – clevis pins – vector pins – test points – small washers – test points 2 – tiny nuts – step bolts – furniture pulls – rack mount M6 – OpenBuilds parts – long bolts – brackets | In red drawer cabinet |
| 320 | Back Wall Storage | Top | Spade/ring/quick connects | |
| 321 | Back Wall Storage | Top | Vampire connectors | |
| 322 | Back Wall Storage | Top | Wireblocks, general | |
| 323 | Back Wall Storage | Top | Wireblocks, 2, 3, and 5 pin (Wago) | |
| 324 | Back Wall Storage | Top | Strain relief | |
| 325 | Back Wall Storage | Top | 2mm headers | |
| 326 | Back Wall Storage | Top | Twist on | |
| 327 | Back Wall Storage | Top | Epoxy – super glue loctite – greases | |
| 328 | Back Wall Storage | Top | Dielectric grease – silicon sealant | |
| 329 | Back Wall Storage | Top | Grommets, cord grips | |
| 330 | Back Wall Storage | Top | Heat shrink connectors | |
| 331 | Back Wall Storage | Top | Sparki robots | |
| 332 | Back Wall Storage | Cubbies | Demo box | |
| 333 | Back Wall Storage | Cubbies | Standoffs | |
| 334 | Back Wall Storage | Cubbies | Vacuum cleaner | |
| 335 | Back Wall Storage | Cubbies | Circuit Hacking kits; spare CD4017 for kits; 9V and 9V clips for kits | |
| 336 | Back Wall Storage | Cubbies | MTA 100 connectors | |
| 337 | Back Wall Storage | Cubbies | Storage bags (snack, sandwich, quart, gallon) | |
| 338 | Back Wall Storage | Cubbies | Vacuum tubes | |
| 339 | Back Wall Storage | Cubbies | Heavy soldering tools | |
| 340 | Back Wall Storage | Cubbies | Additional hardware | |
| 341 | Back Wall Storage | Cubbies | Wire lugs and crimper | |
| 342 | Back Wall Storage | Cubbies | Genmitsu ProverXL 4030 | |
| 343 | Back Wall Storage | Cubbies | Anderson power pole | |
| 344 | COWWCHNT | Above | HOBE class kits | |
| 345 | COWWCHNT | Above | Measurement tools, air speed, weight Ph | |
| 346 | COWWCHNT | Above | Measurement tools, compass, time | |
| 347 | COWWCHNT | Above | Temperature measurement tools | |
| 348 | COWWCHNT | Above | USB Borescope | |
| 349 | COWWCHNT | Above | USB webcams | |
| 350 | COWWCHNT | Above | USB data acquisition; analog meters, digital panel meters | |
| 351 | COWWCHNT | Back Side | Tripod with USB camera | |
| 352 | COWWCHNT | Back Side | Tripod for posters | |
| 353 | COWWCHNT | Back Side | Projection screens | |
| 354 | COWWCHNT | Front Side | DIN cables | |
| 355 | COWWCHNT | Front Side | RCA converters | |
| 356 | COWWCHNT | Front Side | Firewire | |
| 357 | COWWCHNT | Front Side | ATA Serial hard drive cables | |
| 358 | COWWCHNT | Front Side | DIN converters | |
| 359 | COWWCHNT | Front Side | Display port adapters | |
| 360 | COWWCHNT | Front Side | VGA adapters, USB C, | |
| 361 | COWWCHNT | Front Side | DVI cable | |
| 362 | COWWCHNT | Front Side | DVI to VGA | |
| 363 | COWWCHNT | Front Side | exotic video | |
| 364 | COWWCHNT | Front Side | Nikon to RCA | |
| 365 | COWWCHNT | Front Side | DB9 to RJ11 | |
| 366 | COWWCHNT | Front Side | DIN cable (small) | |
| 367 | COWWCHNT | Front Side | RJ-11 | |
| 368 | COWWCHNT | Front Side | Wire | |
| 369 | COWWCHNT | Front Side | E-SATA cable | |
| 370 | COWWCHNT | Front Side | VGA Cable | |
| 371 | COWWCHNT | Front Side | DB25 cable/parallel port | |
| 372 | Bench Indigo | Top | Network gear | |
| 373 | Bench Indigo | Top | Speakers, PC microphones (1/8" jack) | |
| 374 | Bench Indigo | Top | Powered speakers | |
| 375 | Bench Indigo | Top | PC Speakers | |
| 376 | Bench Indigo | Middle | AMScope microscope with USB camera | |
| 377 | Bench Indigo | Bottom | Pneumatics; Hobbybots 3V110-06 | |
| 378 | Bench Indigo | Bottom | Tygon tubing | |
| 379 | Bench Indigo | Bottom | Pneumatic gages | |
| 380 | Bench Indigo | Bottom | Pneumatic pumps, AC Air blower | |
| 381 | Bench Indigo | Bottom | Thin plastic tubing | |
| 382 | Bench Indigo | Bottom | Larger stepper motors | |
| 383 | Bench Indigo | Bottom | AC Rope Lights | |

| | | | |
|-----|-----------------|---------------------|---|
| 384 | Bench Juliet | Top | Multimeters for classes |
| 385 | Bench Juliet | Top | LED tester |
| 386 | Bench Juliet | Top | Component testers (x3) |
| 387 | Bench Juliet | Top | LCR tester; scientific calculator (TI-30Xa) |
| 388 | Bench Juliet | Top | Dremel stand |
| 389 | Bench Juliet | Top | light box, head wearable magnifier |
| 390 | Bench Juliet | Bottom | Power resistors |
| 391 | Bench Juliet | Bottom | DB9 parts |
| 392 | Bench Juliet | Bottom | Thermocouples and temperature controllers |
| 393 | Bench Kilo | Top | Photo developer AC timer |
| 394 | Bench Kilo | Top | Desoldering tool |
| 395 | Bench Kilo | Top | Antistatic straps |
| 396 | Bench Kilo | Top | Stereo microscope |
| 397 | Bench Kilo | Top | Digital scale |
| 398 | Bench Kilo | Top | Toaster oven for SMT |
| 399 | Bench Kilo | Below | VGA video cables |
| 400 | Bench Kilo | Below | End stops |
| 401 | Bench Kilo | Below | thermal switches |
| 402 | Bench Kilo | Below | Solid state relays |
| 403 | Bench Kilo | Below | 24VDC DPDT relays and sockets |
| 404 | Bench Kilo | Below | 65A interconnects |
| 405 | Bench Kilo | Below | Relay, thin, single pole 24 VDC |
| 406 | Bench Kilo | Below | Potentiometers |
| 407 | Bench Kilo | Below | Buttons |
| 408 | Bench Kilo | Below | DIN mounted relay bases, Octal and Automation Direct |
| 409 | Bench Kilo | Below | Bezels |
| 410 | Bench Kilo | Below | Bus Bars |
| 411 | Bench Kilo | Below | Relays for DIN mounted bases, 12/24 VDC, 24/120/240 VAC |
| 412 | Bench Kilo | Below | IEC sockets |
| 413 | Bench Kilo | Below | Contact blocks |
| 414 | Bench Kilo | Below | Lights |
| 415 | Bench Kilo | Below | Relays and sockets single pole |
| 416 | Bench Lima | Above | Extra signal generators |
| 417 | Bench Lima | Above | High precision digital scale |
| 418 | Bench Lima | Middle | Fine tweezers |
| 419 | Bench Lima | Middle | Aoyue tips |
| 420 | Bench Lima | Middle | Microscope tools |
| 421 | Bench Lima | Middle | MTR 3000 series SMT rework |
| 422 | Bench Lima | Middle | Stereo microscope |
| 423 | Bench Lima | Bottom | Optical lenses |
| 424 | Bench Lima | Bottom | Metal soldering stations (need soldering ends) |
| 425 | Bench Mike | Top | Notepads |
| 426 | Bench Mike | Top | Chalk speedline |
| 427 | Bench Mike | Middle | Othermill and tools |
| 428 | Bench Mike | Middle | USB microscope |
| 429 | Bench Mike | Middle | Sandpaper |
| 430 | Bench Mike | Bottom | Socket set |
| 431 | Bench Mike | Bottom | AC powered drill |
| 432 | Bench Mike | Bottom | Heavy toolbox |
| 433 | Bench November | Top | RF station |
| 434 | Front Wire Rack | Top | Blinky cube |
| 435 | Front Wire Rack | Top | Envelopes |
| 436 | Front Wire Rack | Top | Luggage tag laminates |
| 437 | Front Wire Rack | Middle | Paper, Donations for E&R, flashlights, AC blacklight |
| 438 | Front Wire Rack | Middle | Clipboards for note taking |
| 439 | Front Wire Rack | Middle | Tags for marking projects |
| 440 | Front Wire Rack | Middle | Scissors, pens, pencils |
| 441 | Front Wire Rack | Middle | Safety glasses |
| 442 | Front Wire Rack | Bottom | Labels, envelopes |
| 443 | Front Wire Rack | Bottom | Clear report covers |
| 444 | Front Wire Rack | Bottom | DVDs, CDs. |
| 445 | REAR PARTS AREA | Bottom RadioShack 1 | Arduino sockets and plugs |
| 446 | REAR PARTS AREA | Bottom RadioShack 1 | Battery holders |
| 447 | REAR PARTS AREA | Bottom RadioShack 1 | Battery holders and coin cells |
| 448 | REAR PARTS AREA | Bottom RadioShack 1 | Fuses |
| 449 | REAR PARTS AREA | Bottom RadioShack 1 | Relays |
| 450 | REAR PARTS AREA | Bottom RadioShack 1 | Potentiometers, photocells |
| 451 | REAR PARTS AREA | Bottom RadioShack 1 | 2D potentiometers, condensor mics |
| 452 | REAR PARTS AREA | Bottom RadioShack 1 | Thermal paste, heat sinks |
| 453 | REAR PARTS AREA | Bottom RadioShack 2 | LEDs – blue – red – yellow – green |
| 454 | REAR PARTS AREA | Bottom RadioShack 2 | Segment displays, dot matrices |
| 455 | REAR PARTS AREA | Bottom RadioShack 2 | Small screens, LED mounting |
| 456 | REAR PARTS AREA | Bottom RadioShack 2 | LEDs and panel lights |
| 457 | REAR PARTS AREA | Bottom RadioShack 2 | Large switches and buttons |
| 458 | REAR PARTS AREA | Bottom RadioShack 2 | Molex connectors, RJ11, RJ45, speaker connectors |
| 459 | REAR PARTS AREA | Bottom RadioShack 2 | 1/8" and 1/4" plugs jacks for microphones/speakers |
| 460 | REAR PARTS AREA | Bottom RadioShack 2 | RCA, USB to serial |
| 461 | REAR PARTS AREA | Bottom MIDDLE OPEN | D-sub connectors |
| 462 | REAR PARTS AREA | Bottom MIDDLE OPEN | D-sub hardware |
| 463 | REAR PARTS AREA | Bottom MIDDLE OPEN | D-sub pins |
| 464 | REAR PARTS AREA | Bottom RadioShack 3 | Hobby servos, stepper drivers |
| 465 | REAR PARTS AREA | Bottom RadioShack 3 | Misc small DC motors, ceramic disks, large switches |
| 466 | REAR PARTS AREA | Bottom RadioShack 3 | AC lamps, zip ties, zip tie tiedowns, transformers |

| | | | | |
|-----|-----------------|---------------------|--|--|
| 467 | REAR PARTS AREA | Bottom RadioShack 3 | inductors, flashlamps, heat sinks, matches | |
| 468 | REAR PARTS AREA | Bottom RadioShack 3 | Transformers, alroids tins, tea lights | |
| 469 | REAR PARTS AREA | Bottom RadioShack 3 | DRAWER DIVIDERS | |
| 470 | REAR PARTS AREA | Bottom RadioShack 3 | AC motors, digital sandbox, picoboard | |
| 471 | REAR PARTS AREA | Bottom RadioShack 3 | DC motors, large zip ties | |
| 472 | REAR PARTS AREA | Bottom RadioShack 4 | Speakers and switches, optical slot switches | |
| 473 | REAR PARTS AREA | Bottom RadioShack 4 | Switches and rotary DIP switches | |
| 474 | REAR PARTS AREA | Bottom RadioShack 4 | DIP switches | |
| 475 | REAR PARTS AREA | Bottom RadioShack 4 | Rotary switches, alligator clips, banana plugs | |
| 476 | REAR PARTS AREA | Bottom RadioShack 4 | Knobs, buttons, terminal strips, PCB terminal strips | |
| 477 | REAR PARTS AREA | Bottom RadioShack 4 | DB-9, DB-25 connectors, terminal strips | |
| 478 | REAR PARTS AREA | Bottom RadioShack 4 | Solar cells, googly eyes, finger condoms, thermostat | |
| 479 | REAR PARTS AREA | Shelf 1 | Small drawers – diode kit, MOSFETS | |
| 480 | REAR PARTS AREA | Shelf 1 | Small drawers – Zener diodes, optoisolators | |
| 481 | REAR PARTS AREA | Shelf 1 | Small drawers – diodes, op-amps | |
| 482 | REAR PARTS AREA | Shelf 1 | Small drawers – Capacitors | |
| 483 | REAR PARTS AREA | Shelf 1 | Small drawers – Capacitors | |
| 484 | REAR PARTS AREA | Shelf 1 | Small drawers – Resistors | |
| 485 | REAR PARTS AREA | Shelf 1 | Small drawers – Resistors | |
| 486 | REAR PARTS AREA | Shelf 2 | Small drawers – TTL | |
| 487 | REAR PARTS AREA | Shelf 2 | Small drawers – TTL | |
| 488 | REAR PARTS AREA | Shelf 2 | Small drawers – TTL | |
| 489 | REAR PARTS AREA | Shelf 2 | Small drawers – TTL | |
| 490 | REAR PARTS AREA | Shelf 2 | Small drawers – Op-amps, ATMEGA, phototransistors | |
| 491 | REAR PARTS AREA | Shelf 2 | Small drawers – Crystals, headers, voltage regulators | |
| 492 | REAR PARTS AREA | Shelf 2 | Small drawers – Op-amps, voltage regulators, diodes | |
| 493 | REAR PARTS AREA | Shelf 2 | Small drawers – Transistors, TO-92, TO-220, relays, 555 | |
| 494 | REAR PARTS AREA | Shelf 3 | Connectors | |
| 495 | REAR PARTS AREA | Shelf 3 | Circuit breakers | |
| 496 | REAR PARTS AREA | Shelf 3 | Ham radio | |
| 497 | REAR PARTS AREA | Shelf 3 | Digital cameras | |
| 498 | REAR PARTS AREA | Shelf 3 | KK connectors and pins; 1xN Molex | |
| 499 | REAR PARTS AREA | Shelf 3 | Thermocouple conditioners | |
| 500 | REAR PARTS AREA | Shelf 3 | Signal conditioners | |
| 501 | REAR PARTS AREA | Shelf 3 | Pinewood Derby timer | |
| 502 | REAR PARTS AREA | Shelf 3 | DB-9 and DB-25 cables and breakout | |
| 503 | REAR PARTS AREA | Shelf 3 | Tablet holders | |
| 504 | REAR PARTS AREA | Shelf 3 | Resistors, gray case | |
| 505 | REAR PARTS AREA | Shelf 3 | Capacitors, gray case | |
| 506 | REAR PARTS AREA | Shelf 3 | 0.5 Watt Resistors, ½ Watt Resistors | |
| 507 | REAR PARTS AREA | Shelf 3 | DVI, Displayport, HDMI cables; Displayport to HDMI; HDMI to DVI; USB C to DVI Displayport to DVI | |
| 508 | BAKER RACKS | End | Wood scraps | |
| 509 | BAKER RACKS | End | Excess resistors; 150k to 22M resistors | |
| 510 | BAKER RACKS | End | Ribbon cable (cable only) | |
| 511 | BAKER RACK A | Shelf 1 | Unsorted parts, IC sockets | |
| 512 | BAKER RACK A | Shelf 2 | Unsorted parts, IC sockets | |
| 513 | BAKER RACK A | Shelf 3 | Ribbon cable connectors | |
| 514 | BAKER RACK A | Shelf 3 | Ribbon cable connectors | |
| 515 | BAKER RACK A | Shelf 4 | Ceramic heaters | |
| 516 | BAKER RACK A | Shelf 4 | Unsorted parts | |
| 517 | BAKER RACK A | Shelf 5 | Mass flow controllers | |
| 518 | BAKER RACK A | Shelf 5 | Load cells | |
| 519 | BAKER RACK A | Shelf 5 | MIDI keyboard | |
| 520 | BAKER RACK A | Shelf 5 | LED reels | |
| 521 | BAKER RACK A | Shelf 5 | USB A part reel | |
| 522 | BAKER RACK A | Shelf 5 | Diode reel 1N4148 | |
| 523 | BAKER RACK B | Shelf 1 | Odd connectors | |
| 524 | BAKER RACK B | Shelf 1 | Breadboard parts | |
| 525 | BAKER RACK B | Shelf 1 | Third hand parts | |
| 526 | BAKER RACK B | Shelf 1 | IC sockets with long leads | |
| 527 | BAKER RACK B | Shelf 1 | Extra fuses | |
| 528 | BAKER RACK B | Shelf 1 | Flash bulbs | |
| 529 | BAKER RACK B | Shelf 2 | Perf boards, SMT to PTH converters | |
| 530 | BAKER RACK B | Shelf 2 | SMT tooling | |
| 531 | BAKER RACK B | Shelf 2 | SMT and PTH LEDs | |
| 532 | BAKER RACK B | Shelf 2 | SMT crystals | |
| 533 | BAKER RACK B | Shelf 2 | SMT and PTH LEDs (sample books) | |
| 534 | REAR PARTS AREA | Shelf 1 – Column A | IXTH8P50 – Mosfet P-CH | |
| 535 | REAR PARTS AREA | Shelf 1 – Column A | IXTH10P50 – Mosfet P-CH | |
| 536 | REAR PARTS AREA | Shelf 1 – Column A | ITXTH11P50 – Mosfet P-CH | |
| 537 | REAR PARTS AREA | Shelf 1 – Column A | IXFH16N50P – Mosfet N-CH | |
| 538 | REAR PARTS AREA | Shelf 1 – Column A | IRFB3207PBF – Mosfet N-CH | |
| 539 | REAR PARTS AREA | Shelf 1 – Column A | IRF740 IRL7833 | |
| 540 | REAR PARTS AREA | Shelf 1 – Column A | IRFB16N50K – Mosfet N-CH | |
| 541 | REAR PARTS AREA | Shelf 1 – Column A | IRL2703 – HEX/MOS N-CH | |
| 542 | REAR PARTS AREA | Shelf 1 – Column A | TC427CP – Mosfet driver | |
| 543 | REAR PARTS AREA | Shelf 1 – Column A | TC4432CPA – Mosfet driver | |
| 544 | REAR PARTS AREA | Shelf 1 – Column A | IRF9540 – Mosfet P-CH | |
| 545 | REAR PARTS AREA | Shelf 1 – Column A | IRF1324PBF – HEX/MOS N-CH | |
| 546 | REAR PARTS AREA | Shelf 1 – Column A | IRFB4212PBF – Mosfet N-CH | |
| 547 | REAR PARTS AREA | Shelf 1 – Column A | IRFB110GPBF – Mosfet N-CH | |
| 548 | REAR PARTS AREA | Shelf 1 – Column A | AT30D60BHBG Diode Array | |
| 549 | REAR PARTS AREA | Shelf 1 – Column A | APT30M75BLL – Power MOSFET 300V 44A | |

| | | | |
|-----|-----------------|--------------------|--|
| 550 | REAR PARTS AREA | Shelf 1 – Column A | APT30D40BG Rectifier Diode 400V 30A |
| 551 | REAR PARTS AREA | Shelf 1 – Column A | 1N4002 rectifier diode |
| 552 | REAR PARTS AREA | Shelf 1 – Column A | 1N2326 temperature compensating diode |
| 553 | REAR PARTS AREA | Shelf 1 – Column A | 1N4004 – 1N4007 |
| 554 | REAR PARTS AREA | Shelf 1 – Column A | 1N3600 – 1N4001 |
| 555 | REAR PARTS AREA | Shelf 1 – Column A | 1N4148 – 1N4733 |
| 556 | REAR PARTS AREA | Shelf 1 – Column A | 1N4735 – 1N4742 |
| 557 | REAR PARTS AREA | Shelf 1 – Column A | 3.3V Zener |
| 558 | REAR PARTS AREA | Shelf 1 – Column A | 4.3V Zener |
| 559 | REAR PARTS AREA | Shelf 1 – Column A | 1N5232 5.6V Zener |
| 560 | REAR PARTS AREA | Shelf 1 – Column A | 6.8V – 7.2V – 8.2V Zener |
| 561 | REAR PARTS AREA | Shelf 1 – Column A | 1N5238 8.1V Zener – 9.1V 10V |
| 562 | REAR PARTS AREA | Shelf 1 – Column A | 1N5741 11V Zener – 1N5742 12V Zener – 1N5743 Zener |
| 563 | REAR PARTS AREA | Shelf 1 – Column A | 1N5244 14V Zener – 1N5245 15V Zener – 1N5246 16V Zener |
| 564 | REAR PARTS AREA | Shelf 1 – Column A | 1N5747 17V Zener – 1N5248 18V Zener – 1N5249 19V Zener |
| 565 | REAR PARTS AREA | Shelf 1 – Column A | 1N5250 20V Zener – 1N5251 22V Zener – 1N5254 24V Zener |
| 566 | REAR PARTS AREA | Shelf 1 – Column A | 1N5253 25V Zener – 26V Zener |
| 567 | REAR PARTS AREA | Shelf 1 – Column A | 1N5258B-TR 36V Zener |
| 568 | REAR PARTS AREA | Shelf 1 – Column A | 1N5401 Zener – 1N5404 Zener – EMPTY |
| 569 | REAR PARTS AREA | Shelf 1 – Column A | 1N5408 Zener – EMPTY |
| 570 | REAR PARTS AREA | Shelf 1 – Column B | 4N26 OPTO – 6N137 |
| 571 | REAR PARTS AREA | Shelf 1 – Column B | 4N33 OPTO – 4N25 |
| 572 | REAR PARTS AREA | Shelf 1 – Column B | 4N36 OPTO |
| 573 | REAR PARTS AREA | Shelf 1 – Column B | OPT101 |
| 574 | REAR PARTS AREA | Shelf 1 – Column B | PGA205BP IC PROG GAIN AMP |
| 575 | REAR PARTS AREA | Shelf 1 – Column B | 1N5231 – 5.1V Zener |
| 576 | REAR PARTS AREA | Shelf 1 – Column B | 1N914A |
| 577 | REAR PARTS AREA | Shelf 1 – Column B | 1N4005 |
| 578 | REAR PARTS AREA | Shelf 1 – Column B | RC4136 OPAMP |
| 579 | REAR PARTS AREA | Shelf 1 – Column B | NTE3040 OPTO NPN |
| 580 | REAR PARTS AREA | Shelf 1 – Column B | FGH80N60FD2 IGBT |
| 581 | REAR PARTS AREA | Shelf 1 – Column B | FB260N |
| 582 | REAR PARTS AREA | Shelf 1 – Column B | 1N5230 Zener 4.7V |
| 583 | REAR PARTS AREA | Shelf 1 – Column B | 458AG3 |
| 584 | REAR PARTS AREA | Shelf 1 – Column B | 1N4151 |
| 585 | REAR PARTS AREA | Shelf 1 – Column B | LM2575HV Step down regulator |
| 586 | REAR PARTS AREA | Shelf 1 – Column B | 1N4744A Zener 15V |
| 587 | REAR PARTS AREA | Shelf 1 – Column B | 1N5234B 6.2V Zener |
| 588 | REAR PARTS AREA | Shelf 1 – Column B | 1N964B 11.7V Zener |
| 589 | REAR PARTS AREA | Shelf 1 – Column B | 1N5350B 13V 1A 5W Zener |
| 590 | REAR PARTS AREA | Shelf 1 – Column B | 2E28 8.2V 2W Zener |
| 591 | REAR PARTS AREA | Shelf 1 – Column B | ZRC330A03 – IC REF 3.3V 3% |
| 592 | REAR PARTS AREA | Shelf 1 – Column B | LM2940S-10 12V 1.5A LDO REG |
| 593 | REAR PARTS AREA | Shelf 1 – Column B | 1N5399 |
| 594 | REAR PARTS AREA | Shelf 1 – Column B | 1N4728 3.3V Zener |
| 595 | REAR PARTS AREA | Shelf 1 – Column B | 1N4735 6.2V Zener |
| 596 | REAR PARTS AREA | Shelf 1 – Column B | 1N4742 12V Zener |
| 597 | REAR PARTS AREA | Shelf 1 – Column B | 1N4743 13V Zener |
| 598 | REAR PARTS AREA | Shelf 1 – Column B | 1N4746 18V Zener |
| 599 | REAR PARTS AREA | Shelf 1 – Column B | 1N4747A 20V Zener |
| 600 | REAR PARTS AREA | Shelf 1 – Column B | GP10Y DIODE 1.6kV 1A |
| 601 | REAR PARTS AREA | Shelf 1 – Column B | 1N5819 |
| 602 | REAR PARTS AREA | Shelf 1 – Column B | 1N4729 3.6V Zener |
| 603 | REAR PARTS AREA | Shelf 1 – Column B | 1N4743 5.6V Zener |
| 604 | REAR PARTS AREA | Shelf 1 – Column B | 1N5232B 5.6V Zener |
| 605 | REAR PARTS AREA | Shelf 1 – Column B | 1N961B 10V Zener |
| 606 | REAR PARTS AREA | Shelf 1 – Column B | 1N4750 27V Zener |
| 607 | REAR PARTS AREA | Shelf 1 – Column B | 1N4751 30V Zener |
| 608 | REAR PARTS AREA | Shelf 1 – Column B | 1N746A 3.3V Zener |
| 609 | REAR PARTS AREA | Shelf 1 – Column B | 1N5266 |
| 610 | REAR PARTS AREA | Shelf 1 – Column B | 1N9598 8.2V Zener |
| 611 | REAR PARTS AREA | Shelf 1 – Column B | 1N5338 5.1V 5W Zener |
| 612 | REAR PARTS AREA | Shelf 1 – Column B | 2E26,2D5 6.2V Zener |
| 613 | REAR PARTS AREA | Shelf 1 – Column B | 1N5349 12V Zener |
| 614 | REAR PARTS AREA | Shelf 1 – Column B | 1N5256B |
| 615 | REAR PARTS AREA | Shelf 1 – Column B | Step down to USB power |
| 616 | REAR PARTS AREA | Shelf 1 – Column B | LM317 |
| 617 | REAR PARTS AREA | Shelf 1 – Column B | Pololu 3.3V Voltage regulator |
| 618 | REAR PARTS AREA | Shelf 1 – Column B | STTH8L06D ultrafast diode |
| 619 | REAR PARTS AREA | Shelf 1 – Column B | 1N4733 5.1V Zener 1W 1% |
| 620 | REAR PARTS AREA | Shelf 1 – Column B | ULN2003AN |
| 621 | REAR PARTS AREA | Shelf 1 – Column B | MLT04 4 QUAD ANALOG MULT |
| 622 | REAR PARTS AREA | Shelf 1 – Column B | Pololu 3.3V Step up/down #2122 |
| 623 | REAR PARTS AREA | Shelf 1 – Column B | Pololu 5V Step up #2562 |
| 624 | REAR PARTS AREA | Shelf 1 – Column B | HFA08TB60 Diode 600V 8A |
| 625 | REAR PARTS AREA | Shelf 1 – Column B | 20L15T Schottky Rectifier 20A Low V drop |
| 626 | REAR PARTS AREA | Shelf 1 – Column B | DIODE UNKNOWN |
| 627 | REAR PARTS AREA | Shelf 1 – Column B | MBR160 Schottky diode 60V 1A |
| 628 | REAR PARTS AREA | Shelf 1 – Column B | 1N5817G |
| 629 | REAR PARTS AREA | Shelf 1 – Column B | STPS10L25D Schottky 25V 10A |
| 630 | REAR PARTS AREA | Shelf 1 – Column B | SA33CA TVS Diode 33V |
| 631 | REAR PARTS AREA | Shelf 1 – Column B | SA24CA |
| 632 | REAR PARTS AREA | Shelf 1 – Column B | V30100S-E3/45 – Schottky 30A 100V |

| | | | |
|-----|-----------------|--------------------|---|
| 633 | REAR PARTS AREA | Shelf 1 – Column B | SK5050C Schottky barrier 50A 50V |
| 634 | REAR PARTS AREA | Shelf 1 – Column C | UA7810CKC 10V 1.5A Voltage regulator |
| 635 | REAR PARTS AREA | Shelf 1 – Column C | PSMN070 FET |
| 636 | REAR PARTS AREA | Shelf 1 – Column C | TLV2404IN |
| 637 | REAR PARTS AREA | Shelf 1 – Column C | OPA241PA |
| 638 | REAR PARTS AREA | Shelf 1 – Column C | LM324 QUAD OP AMP |
| 639 | REAR PARTS AREA | Shelf 1 – Column C | LM358 |
| 640 | REAR PARTS AREA | Shelf 1 – Column C | UA741N |
| 641 | REAR PARTS AREA | Shelf 1 – Column C | UA741CP |
| 642 | REAR PARTS AREA | Shelf 1 – Column C | LM7809 |
| 643 | REAR PARTS AREA | Shelf 1 – Column C | OPA347 – OPA137P |
| 644 | REAR PARTS AREA | Shelf 1 – Column C | LM348 |
| 645 | REAR PARTS AREA | Shelf 1 – Column C | LM340 |
| 646 | REAR PARTS AREA | Shelf 1 – Column C | LM395 |
| 647 | REAR PARTS AREA | Shelf 1 – Column C | LT1073 Voltage regulator |
| 648 | REAR PARTS AREA | Shelf 1 – Column C | LM7805 |
| 649 | REAR PARTS AREA | Shelf 1 – Column C | LM7812 Voltage regulator |
| 650 | REAR PARTS AREA | Shelf 1 – Column C | LT1077CN8 IC precision OPAMP Micpwr Single |
| 651 | REAR PARTS AREA | Shelf 1 – Column C | PT78ST115H 15V 1.5A Voltage regulator |
| 652 | REAR PARTS AREA | Shelf 1 – Column C | TLC3702IP IC voltage comparator |
| 653 | REAR PARTS AREA | Shelf 1 – Column C | OPA445AP IC OPAMP 2 MHz |
| 654 | REAR PARTS AREA | Shelf 1 – Column C | LT1496IN IC OPAMP Rail-Rail In/out Quad |
| 655 | REAR PARTS AREA | Shelf 1 – Column C | UA747CN IC OPAMP Dual |
| 656 | REAR PARTS AREA | Shelf 1 – Column C | TLV3701IP |
| 657 | REAR PARTS AREA | Shelf 1 – Column C | LM78L12ACZ 12V 0.1A voltage regulator |
| 658 | REAR PARTS AREA | Shelf 1 – Column C | UA7815 15V 1.5A voltage regulator |
| 659 | REAR PARTS AREA | Shelf 1 – Column C | CL210 inrush limiter 1.5A 30 Ohm |
| 660 | REAR PARTS AREA | Shelf 1 – Column C | LT1173CS8 MAX666CPA IC voltage regulator dual mode 5V |
| 661 | REAR PARTS AREA | Shelf 1 – Column C | 74F675APC IC Reg serial in serial-parallel out |
| 662 | REAR PARTS AREA | Shelf 1 – Column C | TLE2426IP ½ rail virtual ground |
| 663 | REAR PARTS AREA | Shelf 1 – Column C | TL2352IP IC differential comparator |
| 664 | REAR PARTS AREA | Shelf 1 – Column C | LM3916 Dot bar driver |
| 665 | REAR PARTS AREA | Shelf 1 – Column C | 1N4148 100V 200mA Diode |
| 666 | REAR PARTS AREA | Shelf 1 – Column C | 1N4007 |
| 667 | REAR PARTS AREA | Shelf 1 – Column C | 1N914A |
| 668 | REAR PARTS AREA | Shelf 1 – Column C | 1N752A 5.6V Zener |
| 669 | REAR PARTS AREA | Shelf 1 – Column C | RPG10M 1000V |
| 670 | REAR PARTS AREA | Shelf 1 – Column C | 1N4448 100V |
| 671 | REAR PARTS AREA | Shelf 1 – Column C | HER305 3A 400V Diode |
| 672 | REAR PARTS AREA | Shelf 1 – Column C | 1N4001 |
| 673 | REAR PARTS AREA | Shelf 1 – Column C | Zener diode kit |
| 674 | REAR PARTS AREA | Shelf 1 – Column C | Diode kit |
| 675 | REAR PARTS AREA | Shelf 1 – Column C | HER303 2A 300V |
| 676 | REAR PARTS AREA | Shelf 1 – Column C | ECG198 |
| 677 | REAR PARTS AREA | Shelf 1 – Column D | 1000uF 6.3V |
| 678 | REAR PARTS AREA | Shelf 1 – Column D | 2200uF 6.3V |
| 679 | REAR PARTS AREA | Shelf 1 – Column D | 4700uF 6.3V |
| 680 | REAR PARTS AREA | Shelf 1 – Column D | 33uF 16V |
| 681 | REAR PARTS AREA | Shelf 1 – Column D | 10uF 16V |
| 682 | REAR PARTS AREA | Shelf 1 – Column D | 220uF 16V |
| 683 | REAR PARTS AREA | Shelf 1 – Column D | 470uF 16V |
| 684 | REAR PARTS AREA | Shelf 1 – Column D | 22uF 25V |
| 685 | REAR PARTS AREA | Shelf 1 – Column D | 100uF 25V |
| 686 | REAR PARTS AREA | Shelf 1 – Column D | 220uF 25V |
| 687 | REAR PARTS AREA | Shelf 1 – Column D | 1000uF 25V |
| 688 | REAR PARTS AREA | Shelf 1 – Column D | 2000uF 25V |
| 689 | REAR PARTS AREA | Shelf 1 – Column D | 0.33uF 35V |
| 690 | REAR PARTS AREA | Shelf 1 – Column D | 10uF 35V |
| 691 | REAR PARTS AREA | Shelf 1 – Column D | 33uF 35V |
| 692 | REAR PARTS AREA | Shelf 1 – Column D | 47uF 35V |
| 693 | REAR PARTS AREA | Shelf 1 – Column D | 100uF 35V |
| 694 | REAR PARTS AREA | Shelf 1 – Column D | 220uF 35V |
| 695 | REAR PARTS AREA | Shelf 1 – Column D | 1000uF 35V |
| 696 | REAR PARTS AREA | Shelf 1 – Column D | 0.22uF 50V aluminum |
| 697 | REAR PARTS AREA | Shelf 1 – Column D | 0.47uF 50V |
| 698 | REAR PARTS AREA | Shelf 1 – Column D | 1uF 50V aluminum |
| 699 | REAR PARTS AREA | Shelf 1 – Column D | 2.2uF 50V |
| 700 | REAR PARTS AREA | Shelf 1 – Column D | 3.3uF 50V |
| 701 | REAR PARTS AREA | Shelf 1 – Column D | 1800uF 6.3V |
| 702 | REAR PARTS AREA | Shelf 1 – Column D | 4.7uF 50V aluminum |
| 703 | REAR PARTS AREA | Shelf 1 – Column D | 10uF 50V |
| 704 | REAR PARTS AREA | Shelf 1 – Column D | 47uF 50V |
| 705 | REAR PARTS AREA | Shelf 1 – Column D | 100uF 50V |
| 706 | REAR PARTS AREA | Shelf 1 – Column D | 330uF 50V |
| 707 | REAR PARTS AREA | Shelf 1 – Column D | 470uF 50V |
| 708 | REAR PARTS AREA | Shelf 1 – Column D | 2200uF 50V |
| 709 | REAR PARTS AREA | Shelf 1 – Column D | 220uF 63V |
| 710 | REAR PARTS AREA | Shelf 1 – Column D | 100uF 16V |
| 711 | REAR PARTS AREA | Shelf 1 – Column D | 1000uF 16V |
| 712 | REAR PARTS AREA | Shelf 1 – Column D | 470uF 35V |
| 713 | REAR PARTS AREA | Shelf 1 – Column D | 1900uF 40V |
| 714 | REAR PARTS AREA | Shelf 1 – Column D | 0.01uF 100V |
| 715 | REAR PARTS AREA | Shelf 1 – Column D | 220uF 100V |

| | | | |
|-----|-----------------|--------------------|-----------------------------|
| 716 | REAR PARTS AREA | Shelf 1 – Column D | 320pF |
| 717 | REAR PARTS AREA | Shelf 1 – Column D | 0.22uF |
| 718 | REAR PARTS AREA | Shelf 1 – Column D | UNKNOWN |
| 719 | REAR PARTS AREA | Shelf 1 – Column D | 0.047uF 80V |
| 720 | REAR PARTS AREA | Shelf 1 – Column D | 150uF 385V |
| 721 | REAR PARTS AREA | Shelf 1 – Column D | 3300uF 10V |
| 722 | REAR PARTS AREA | Shelf 1 – Column D | 0.0033uF |
| 723 | REAR PARTS AREA | Shelf 1 – Column D | 0.033uF |
| 724 | REAR PARTS AREA | Shelf 1 – Column D | 2.2uF 400V |
| 725 | REAR PARTS AREA | Shelf 1 – Column D | 1000uF 50V |
| 726 | REAR PARTS AREA | Shelf 1 – Column D | 150uF 385V |
| 727 | REAR PARTS AREA | Shelf 1 – Column D | 1500uF 16V |
| 728 | REAR PARTS AREA | Shelf 1 – Column D | 0.0047uF |
| 729 | REAR PARTS AREA | Shelf 1 – Column D | 650pF |
| 730 | REAR PARTS AREA | Shelf 1 – Column D | 470pF |
| 731 | REAR PARTS AREA | Shelf 1 – Column D | 8200uF 10V |
| 732 | REAR PARTS AREA | Shelf 1 – Column D | 1200uF 10V |
| 733 | REAR PARTS AREA | Shelf 1 – Column D | TO SORT |
| 734 | REAR PARTS AREA | Shelf 1 – Column D | 0.0068uF |
| 735 | REAR PARTS AREA | Shelf 1 – Column D | 0.047uF |
| 736 | REAR PARTS AREA | Shelf 1 – Column D | 0.1uF 50V |
| 737 | REAR PARTS AREA | Shelf 1 – Column D | UNKNOWN |
| 738 | REAR PARTS AREA | Shelf 1 – Column D | 0.01uF JAMECO |
| 739 | REAR PARTS AREA | Shelf 1 – Column D | 0.001uF |
| 740 | REAR PARTS AREA | Shelf 1 – Column D | 0.0015uF |
| 741 | REAR PARTS AREA | Shelf 1 – Column D | 0.01uF 50V |
| 742 | REAR PARTS AREA | Shelf 1 – Column D | 2200pF 250V |
| 743 | REAR PARTS AREA | Shelf 1 – Column D | 68pF |
| 744 | REAR PARTS AREA | Shelf 1 – Column D | 220pF |
| 745 | REAR PARTS AREA | Shelf 1 – Column D | EMPTY |
| 746 | REAR PARTS AREA | Shelf 1 – Column D | UNKNOWN |
| 747 | REAR PARTS AREA | Shelf 1 – Column D | UNKNOWN |
| 748 | REAR PARTS AREA | Shelf 1 – Column D | UNKNOWN |
| 749 | REAR PARTS AREA | Shelf 1 – Column E | 100uF 6.3V |
| 750 | REAR PARTS AREA | Shelf 1 – Column E | 0.047uF 80V poly film |
| 751 | REAR PARTS AREA | Shelf 1 – Column E | 1000uF 100V |
| 752 | REAR PARTS AREA | Shelf 1 – Column E | 0.15uF 100V |
| 753 | REAR PARTS AREA | Shelf 1 – Column E | 0.039uF 100V |
| 754 | REAR PARTS AREA | Shelf 1 – Column E | 47uF 6.3V |
| 755 | REAR PARTS AREA | Shelf 1 – Column E | 0.001uF 50V |
| 756 | REAR PARTS AREA | Shelf 1 – Column E | 0.00056uF 50V 0.0047uF 50V |
| 757 | REAR PARTS AREA | Shelf 1 – Column E | 47 uF 25V |
| 758 | REAR PARTS AREA | Shelf 1 – Column E | 0.22uF 63V metal film |
| 759 | REAR PARTS AREA | Shelf 1 – Column E | 0.33uF 100V 0.33uF 50V |
| 760 | REAR PARTS AREA | Shelf 1 – Column E | 470pF |
| 761 | REAR PARTS AREA | Shelf 1 – Column E | 3.3uF tantalum |
| 762 | REAR PARTS AREA | Shelf 1 – Column E | 10uF 10V, 16V, 25V tantalum |
| 763 | REAR PARTS AREA | Shelf 1 – Column E | 47pF |
| 764 | REAR PARTS AREA | Shelf 1 – Column E | 1uF 50V |
| 765 | REAR PARTS AREA | Shelf 1 – Column E | 470pF axial |
| 766 | REAR PARTS AREA | Shelf 1 – Column E | 1uF 63V |
| 767 | REAR PARTS AREA | Shelf 1 – Column E | 2pF ceramic |
| 768 | REAR PARTS AREA | Shelf 1 – Column E | 3pF ceramic |
| 769 | REAR PARTS AREA | Shelf 1 – Column E | 5pF ceramic |
| 770 | REAR PARTS AREA | Shelf 1 – Column E | 10pF ceramic |
| 771 | REAR PARTS AREA | Shelf 1 – Column E | 15pF ceramic |
| 772 | REAR PARTS AREA | Shelf 1 – Column E | 22pF ceramic |
| 773 | REAR PARTS AREA | Shelf 1 – Column E | 30pF ceramic |
| 774 | REAR PARTS AREA | Shelf 1 – Column E | 33pF ceramic |
| 775 | REAR PARTS AREA | Shelf 1 – Column E | 47pF ceramic |
| 776 | REAR PARTS AREA | Shelf 1 – Column E | 68pF ceramic |
| 777 | REAR PARTS AREA | Shelf 1 – Column E | 75pF ceramic |
| 778 | REAR PARTS AREA | Shelf 1 – Column E | 82pF ceramic |
| 779 | REAR PARTS AREA | Shelf 1 – Column E | 100pF ceramic |
| 780 | REAR PARTS AREA | Shelf 1 – Column E | 150pF ceramic |
| 781 | REAR PARTS AREA | Shelf 1 – Column E | 220pF ceramic |
| 782 | REAR PARTS AREA | Shelf 1 – Column E | 330pF ceramic |
| 783 | REAR PARTS AREA | Shelf 1 – Column E | 470pF ceramic |
| 784 | REAR PARTS AREA | Shelf 1 – Column E | 680pF ceramic |
| 785 | REAR PARTS AREA | Shelf 1 – Column E | 1.0nF ceramic 1000pF 50V |
| 786 | REAR PARTS AREA | Shelf 1 – Column E | 1.5nF ceramic |
| 787 | REAR PARTS AREA | Shelf 1 – Column E | 2.2nF ceramic |
| 788 | REAR PARTS AREA | Shelf 1 – Column E | 3.3nF ceramic |
| 789 | REAR PARTS AREA | Shelf 1 – Column E | 4.7nF ceramic |
| 790 | REAR PARTS AREA | Shelf 1 – Column E | 6.8nF ceramic |
| 791 | REAR PARTS AREA | Shelf 1 – Column E | 10nF ceramic |
| 792 | REAR PARTS AREA | Shelf 1 – Column E | 15nF ceramic – EMPTY |
| 793 | REAR PARTS AREA | Shelf 1 – Column E | 22nF ceramic– EMPTY |
| 794 | REAR PARTS AREA | Shelf 1 – Column E | 47nF ceramic |
| 795 | REAR PARTS AREA | Shelf 1 – Column E | 68nF ceramic– EMPTY |
| 796 | REAR PARTS AREA | Shelf 1 – Column E | 100nF ceramic– EMPTY |
| 797 | REAR PARTS AREA | Shelf 1 – Column E | 470pF 5V |
| 798 | REAR PARTS AREA | Shelf 1 – Column E | 2200uF 10V aluminum |

| | | | |
|-----|-----------------|--------------------|--------------------------------|
| 799 | REAR PARTS AREA | Shelf 1 – Column E | 0.1uF unknown V |
| 800 | REAR PARTS AREA | Shelf 1 – Column E | 3.3uF 35V |
| 801 | REAR PARTS AREA | Shelf 1 – Column E | Variable capacitor |
| 802 | REAR PARTS AREA | Shelf 1 – Column E | Trim capacitor |
| 803 | REAR PARTS AREA | Shelf 1 – Column E | 10uF 35V |
| 804 | REAR PARTS AREA | Shelf 1 – Column E | 0.1uF 35V Jameco 33486 |
| 805 | REAR PARTS AREA | Shelf 1 – Column E | 1uF 35V Jameco 33662 |
| 806 | REAR PARTS AREA | Shelf 1 – Column E | 0.47uF 35V Jameco 33531 |
| 807 | REAR PARTS AREA | Shelf 1 – Column E | 33uF 25V |
| 808 | REAR PARTS AREA | Shelf 1 – Column E | 4.7uF 25V |
| 809 | REAR PARTS AREA | Shelf 1 – Column F | 0 Ohm, 1 Ohm |
| 810 | REAR PARTS AREA | Shelf 1 – Column F | 2 Ohm |
| 811 | REAR PARTS AREA | Shelf 1 – Column F | 4.3 Ohm, 4.7 Ohm |
| 812 | REAR PARTS AREA | Shelf 1 – Column F | 100 Ohm, 13 Ohm |
| 813 | REAR PARTS AREA | Shelf 1 – Column F | 38.3 Ohm, 40.2 Ohm |
| 814 | REAR PARTS AREA | Shelf 1 – Column F | 46.4 Ohm, 51.1 Ohm |
| 815 | REAR PARTS AREA | Shelf 1 – Column F | 62 Ohm, 68 Ohm |
| 816 | REAR PARTS AREA | Shelf 1 – Column F | 100 Ohm, 120 Ohm |
| 817 | REAR PARTS AREA | Shelf 1 – Column F | 133 Ohm, 147 Ohm |
| 818 | REAR PARTS AREA | Shelf 1 – Column F | 150 Ohm, 196 Ohm |
| 819 | REAR PARTS AREA | Shelf 1 – Column F | 200 Ohm, 237 Ohm |
| 820 | REAR PARTS AREA | Shelf 1 – Column F | 240 Ohm, 261 Ohm |
| 821 | REAR PARTS AREA | Shelf 1 – Column F | 287 Ohm, 294 Ohm |
| 822 | REAR PARTS AREA | Shelf 1 – Column F | 316 Ohm, 330 Ohm |
| 823 | REAR PARTS AREA | Shelf 1 – Column F | 383 Ohm, 390 Ohm |
| 824 | REAR PARTS AREA | Shelf 1 – Column F | 464 Ohm, 470 Ohm |
| 825 | REAR PARTS AREA | Shelf 1 – Column F | 475 Ohm, 499 Ohm |
| 826 | REAR PARTS AREA | Shelf 1 – Column F | 511 Ohm, 562 Ohm |
| 827 | REAR PARTS AREA | Shelf 1 – Column F | 750 Ohm, 909 Ohm |
| 828 | REAR PARTS AREA | Shelf 1 – Column F | 1K Ohm |
| 829 | REAR PARTS AREA | Shelf 1 – Column F | 1.13 kOhm, 1.2 kOhm |
| 830 | REAR PARTS AREA | Shelf 1 – Column F | 1.3 kOhm, 1.47 kOhm |
| 831 | REAR PARTS AREA | Shelf 1 – Column F | 1.91 kOhm, 1.96 kOhm |
| 832 | REAR PARTS AREA | Shelf 1 – Column F | 2 kOhm, 2.15 kOhm |
| 833 | REAR PARTS AREA | Shelf 1 – Column F | 2.2 kOhm, 2.4 kOhm |
| 834 | REAR PARTS AREA | Shelf 1 – Column F | 2.43 kOhm, 2.49 k Ohm |
| 835 | REAR PARTS AREA | Shelf 1 – Column F | 2.61 kOhm, 2.8 kOhm |
| 836 | REAR PARTS AREA | Shelf 1 – Column F | 3.3 kOhm, 3.92 kOhm |
| 837 | REAR PARTS AREA | Shelf 1 – Column F | 4.64 kOhm, 4.7 kOhm |
| 838 | REAR PARTS AREA | Shelf 1 – Column F | 4.99 kOhm, 5.1 kOhm |
| 839 | REAR PARTS AREA | Shelf 1 – Column F | 5.1 kOhm, 6.19 kOhm |
| 840 | REAR PARTS AREA | Shelf 1 – Column F | 6.81 kOhm, 6.98 kOhm |
| 841 | REAR PARTS AREA | Shelf 1 – Column F | 8.06 kOhm, 8.25 kOhm |
| 842 | REAR PARTS AREA | Shelf 1 – Column F | 9.09 kOhm, 12.1 kOhm |
| 843 | REAR PARTS AREA | Shelf 1 – Column F | 10 kOhm |
| 844 | REAR PARTS AREA | Shelf 1 – Column F | 12.7 kOhm, 14 kOhm |
| 845 | REAR PARTS AREA | Shelf 1 – Column F | 14.3 kOhm, 14.7 kOhm |
| 846 | REAR PARTS AREA | Shelf 1 – Column F | 16.9 kOhm |
| 847 | REAR PARTS AREA | Shelf 1 – Column F | 19.1 kOhm, 19.6 kOhm |
| 848 | REAR PARTS AREA | Shelf 1 – Column F | 20 kOhm, 20.5 kOhm |
| 849 | REAR PARTS AREA | Shelf 1 – Column F | 21.5 kOhm, 22kOhm |
| 850 | REAR PARTS AREA | Shelf 1 – Column F | 22.1 kOhm, 23 kOhm |
| 851 | REAR PARTS AREA | Shelf 1 – Column F | 24.3 kOhm, 25.5 kOhm |
| 852 | REAR PARTS AREA | Shelf 1 – Column F | 26.1 kOhm, 28 kOhm |
| 853 | REAR PARTS AREA | Shelf 1 – Column F | 27 kOhm, 28.7 kOhm |
| 854 | REAR PARTS AREA | Shelf 1 – Column F | 30 kOhm, 33 kOhm |
| 855 | REAR PARTS AREA | Shelf 1 – Column F | 34 kOhm, 34.8 kOhm |
| 856 | REAR PARTS AREA | Shelf 1 – Column F | 36 kOhm 38.3 kOhm |
| 857 | REAR PARTS AREA | Shelf 1 – Column F | 39 kOhm, 39.2 kOhm |
| 858 | REAR PARTS AREA | Shelf 1 – Column F | 46.4 kOhm, 47 kOhm |
| 859 | REAR PARTS AREA | Shelf 1 – Column F | 47.5 kOhm, 49.9 kOhm |
| 860 | REAR PARTS AREA | Shelf 1 – Column F | 51.1 kOhm, 56.2 kOhm |
| 861 | REAR PARTS AREA | Shelf 1 – Column F | 60.4 kOhm, 61.9 kOhm |
| 862 | REAR PARTS AREA | Shelf 1 – Column F | 68 kOhm, 68.1 kOhm |
| 863 | REAR PARTS AREA | Shelf 1 – Column F | 73.2 kOhm, 75 kOhm |
| 864 | REAR PARTS AREA | Shelf 1 – Column F | 82 kOhm, 100 kOhm |
| 865 | REAR PARTS AREA | Shelf 1 – Column F | 100 kOhm |
| 866 | REAR PARTS AREA | Shelf 1 – Column F | 120 kOhm, 137 kOhm |
| 867 | REAR PARTS AREA | Shelf 1 – Column F | 150 kOhm, 470 kOhm |
| 868 | REAR PARTS AREA | Shelf 1 – Column F | 10 kOhm 9 pin, 330 Ohm 8 pin |
| 869 | REAR PARTS AREA | Shelf 1 – Column F | 330 Ohm 10 pin |
| 870 | REAR PARTS AREA | Shelf 1 – Column F | 1 kOhm 10 pin |
| 871 | REAR PARTS AREA | Shelf 1 – Column F | 10 kOhm 10 pin |
| 872 | REAR PARTS AREA | Shelf 1 – Column F | Assorted multipin resistors |
| 873 | REAR PARTS AREA | Shelf 1 – Column F | Resistor kit 1 Ohm – 470 Ohm |
| 874 | REAR PARTS AREA | Shelf 1 – Column F | Resistor kit 510 Ohm – 12 kOhm |
| 875 | REAR PARTS AREA | Shelf 1 – Column G | 22 Ohm |
| 876 | REAR PARTS AREA | Shelf 1 – Column G | 220 Ohm |
| 877 | REAR PARTS AREA | Shelf 1 – Column G | 220 Ohm |
| 878 | REAR PARTS AREA | Shelf 1 – Column G | 226 Ohm |
| 879 | REAR PARTS AREA | Shelf 1 – Column G | 270 Ohm |
| 880 | REAR PARTS AREA | Shelf 1 – Column G | 301 Ohm |
| 881 | REAR PARTS AREA | Shelf 1 – Column G | 510 Ohm |

| | | | | |
|-----|-----------------|--------------------|----------------------------------|---|
| 882 | REAR PARTS AREA | Shelf 1 – Column G | 910 Ohm | |
| 883 | REAR PARTS AREA | Shelf 1 – Column G | 1 kOhm | |
| 884 | REAR PARTS AREA | Shelf 1 – Column G | 6.65 kOhm | |
| 885 | REAR PARTS AREA | Shelf 1 – Column G | 6.81 kOhm | |
| 886 | REAR PARTS AREA | Shelf 1 – Column G | 12 kOhm | |
| 887 | REAR PARTS AREA | Shelf 1 – Column G | 13 kOhm | |
| 888 | REAR PARTS AREA | Shelf 1 – Column G | 15 kOhm | |
| 889 | REAR PARTS AREA | Shelf 1 – Column G | 26.7 kOhm | |
| 890 | REAR PARTS AREA | Shelf 1 – Column G | 35.7 kOhm | |
| 891 | REAR PARTS AREA | Shelf 1 – Column G | 47.5 kOhm | |
| 892 | REAR PARTS AREA | Shelf 1 – Column G | 51 kOhm | |
| 893 | REAR PARTS AREA | Shelf 1 – Column G | 66.5 kOhm | |
| 894 | REAR PARTS AREA | Shelf 1 – Column G | 71.5 kOhm | |
| 895 | REAR PARTS AREA | Shelf 1 – Column G | 82 kOhm | |
| 896 | REAR PARTS AREA | Shelf 1 – Column G | 130 kOhm | |
| 897 | REAR PARTS AREA | Shelf 1 – Column G | 143 kOhm | |
| 898 | REAR PARTS AREA | Shelf 1 – Column G | 150 kOhm | |
| 899 | REAR PARTS AREA | Shelf 1 – Column G | 158 kOhm | |
| 900 | REAR PARTS AREA | Shelf 1 – Column G | 169 kOhm | |
| 901 | REAR PARTS AREA | Shelf 1 – Column G | 174 kOhm | |
| 902 | REAR PARTS AREA | Shelf 1 – Column G | 180 kOhm | |
| 903 | REAR PARTS AREA | Shelf 1 – Column G | 191 kOhm | |
| 904 | REAR PARTS AREA | Shelf 1 – Column G | 200 kOhm | |
| 905 | REAR PARTS AREA | Shelf 1 – Column G | 216 kOhm | |
| 906 | REAR PARTS AREA | Shelf 1 – Column G | 221 kOhm | |
| 907 | REAR PARTS AREA | Shelf 1 – Column G | 240 kOhm | |
| 908 | REAR PARTS AREA | Shelf 1 – Column G | 261 kOhm | |
| 909 | REAR PARTS AREA | Shelf 1 – Column G | EMPTY | |
| 910 | REAR PARTS AREA | Shelf 1 – Column G | 301 kOhm | |
| 911 | REAR PARTS AREA | Shelf 1 – Column G | 316 kOhm | |
| 912 | REAR PARTS AREA | Shelf 1 – Column G | 393 kOhm | |
| 913 | REAR PARTS AREA | Shelf 1 – Column G | 415 kOhm | |
| 914 | REAR PARTS AREA | Shelf 1 – Column G | EMPTY | |
| 915 | REAR PARTS AREA | Shelf 1 – Column G | 430 kOhm | |
| 916 | REAR PARTS AREA | Shelf 1 – Column G | 474 kOhm | |
| 917 | REAR PARTS AREA | Shelf 1 – Column G | 750 kOhm | |
| 918 | REAR PARTS AREA | Shelf 1 – Column G | 820 kOhm | |
| 919 | REAR PARTS AREA | Shelf 1 – Column G | 909 kOhm – EMPTY | |
| 920 | REAR PARTS AREA | Shelf 1 – Column G | 1 Mohm | |
| 921 | REAR PARTS AREA | Shelf 1 – Column G | 1.5 Mohm | |
| 922 | REAR PARTS AREA | Shelf 1 – Column G | 2 Mohm | |
| 923 | REAR PARTS AREA | Shelf 1 – Column G | 2.2 Mohm | |
| 924 | REAR PARTS AREA | Shelf 1 – Column G | EMPTY | |
| 925 | REAR PARTS AREA | Shelf 1 – Column G | 3.3 Mohm | |
| 926 | REAR PARTS AREA | Shelf 1 – Column G | 3.9 Mohm | |
| 927 | REAR PARTS AREA | Shelf 1 – Column G | 4.7 Mohm | |
| 928 | REAR PARTS AREA | Shelf 1 – Column G | 10 Mohm | |
| 929 | REAR PARTS AREA | Shelf 1 – Column G | EMPTY | |
| 930 | REAR PARTS AREA | Shelf 1 – Column G | 20 Mohm | |
| 931 | REAR PARTS AREA | Shelf 1 – Column G | 22 Mohm | |
| 932 | REAR PARTS AREA | Shelf 1 – Column G | EMPTY | |
| 933 | REAR PARTS AREA | Shelf 1 – Column G | EMPTY | |
| 934 | REAR PARTS AREA | Shelf 1 – Column G | EMPTY | |
| 935 | REAR PARTS AREA | Shelf 1 – Column G | Resistor kit – 15 kOhm – 10 Mohm | |
| 936 | REAR PARTS AREA | Shelf 2 – Column A | 7400 | Quad 2 input NAND gate |
| 937 | REAR PARTS AREA | Shelf 2 – Column A | 7401 | Single 2-input NAD gate |
| 938 | REAR PARTS AREA | Shelf 2 – Column A | 7402 | quad 2-input NOR gate |
| 939 | REAR PARTS AREA | Shelf 2 – Column A | 7403 | quad 2-input NAND gate |
| 940 | REAR PARTS AREA | Shelf 2 – Column A | 7404 | hex inverter gate |
| 941 | REAR PARTS AREA | Shelf 2 – Column A | 7405 | hex inverter gate |
| 942 | REAR PARTS AREA | Shelf 2 – Column A | 7406 | hex inverter gate |
| 943 | REAR PARTS AREA | Shelf 2 – Column A | 7407 | hex Buffer gate |
| 944 | REAR PARTS AREA | Shelf 2 – Column A | 7408 | quad 2-input AND gate |
| 945 | REAR PARTS AREA | Shelf 2 – Column A | 7409 | quad 2-input AND gate |
| 946 | REAR PARTS AREA | Shelf 2 – Column A | 7410 | triple 3-input NAND gate |
| 947 | REAR PARTS AREA | Shelf 2 – Column A | 7411 | triple 3-input NAND gate |
| 948 | REAR PARTS AREA | Shelf 2 – Column A | 7413 | dual 4-input NAND gate |
| 949 | REAR PARTS AREA | Shelf 2 – Column A | 7414 | Hex inverter gate |
| 950 | REAR PARTS AREA | Shelf 2 – Column A | 7416 | Hex inverter gate |
| 951 | REAR PARTS AREA | Shelf 2 – Column A | 7418 | dual 4-input NAND gate |
| 952 | REAR PARTS AREA | Shelf 2 – Column A | 7420 | dual 4-input NAND gate |
| 953 | REAR PARTS AREA | Shelf 2 – Column A | 7421 | dual 4-input AND gate |
| 954 | REAR PARTS AREA | Shelf 2 – Column A | 7426 | quad 2-input NAND gate |
| 955 | REAR PARTS AREA | Shelf 2 – Column A | 7427 | triple 3-input NOR gate |
| 956 | REAR PARTS AREA | Shelf 2 – Column A | 74LS30 | Single 2-input NAD gate |
| 957 | REAR PARTS AREA | Shelf 2 – Column A | 74LS32 | quad 2-input OR gate |
| 958 | REAR PARTS AREA | Shelf 2 – Column A | 7437 | quad 2-input NOR gate |
| 959 | REAR PARTS AREA | Shelf 2 – Column A | 74LS38 | quad 2-input NAND gate |
| 960 | REAR PARTS AREA | Shelf 2 – Column A | 74LS42 | BCD to decimal decoder |
| 961 | REAR PARTS AREA | Shelf 2 – Column A | 7451 | 3-3-input AND-OR-Invert gate and 2-2-input AND-OR-Invert gate |
| 962 | REAR PARTS AREA | Shelf 2 – Column A | 74LS54 | 2-2-2-2-input AND-OR-Invert gate |
| 963 | REAR PARTS AREA | Shelf 2 – Column A | 7464 | 4-3-2-2-input AND-OR-Invert gate |

| | | | | |
|------|-----------------|--------------------|--|--|
| 964 | REAR PARTS AREA | Shelf 2 – Column A | 74LS68 | dual J-K flip-flop, asynchronous clear (improved 74L73) |
| 965 | REAR PARTS AREA | Shelf 2 – Column A | 7472 | AND gated J-K master-slave flip-flop, asynchronous preset and clear |
| 966 | REAR PARTS AREA | Shelf 2 – Column A | 7473 | dual J-K flip-flop, asynchronous clear |
| 967 | REAR PARTS AREA | Shelf 2 – Column A | 7474 | dual D positive edge triggered flip-flop, asynchronous preset and clear |
| 968 | REAR PARTS AREA | Shelf 2 – Column A | 74LS75 | 4-bit bistable latch, complementary outputs |
| 969 | REAR PARTS AREA | Shelf 2 – Column A | 7476 | dual J-K flip-flop, asynchronous preset and clear |
| 970 | REAR PARTS AREA | Shelf 2 – Column A | 74LS83 | 4-bit binary full adder |
| 971 | REAR PARTS AREA | Shelf 2 – Column A | 74LS85 | 4-bit binary full adder |
| 972 | REAR PARTS AREA | Shelf 2 – Column A | 7486 | quad 2-input XOR gate |
| 973 | REAR PARTS AREA | Shelf 2 – Column A | 7489 | 64-bit RAM (16x4), 4 data inputs, 4 inverted data outputs |
| 974 | REAR PARTS AREA | Shelf 2 – Column A | 7490 | decade counter (separate divide-by-2 and divide-by-5 sections) |
| 975 | REAR PARTS AREA | Shelf 2 – Column A | 74190 COUNTER | synchronous presettable up/down 4-bit decade counter |
| 976 | REAR PARTS AREA | Shelf 2 – Column A | 74192 COUNTER | synchronous presettable up/down 4-bit decade counter, clear |
| 977 | REAR PARTS AREA | Shelf 2 – Column A | 7493 | 4-bit binary counter (separate divide-by-2 and divide-by-8 sections); |
| 978 | REAR PARTS AREA | Shelf 2 – Column A | 7417 | hex Buffer gate |
| 979 | REAR PARTS AREA | Shelf 2 – Column A | 74LS95 | 4-bit shift register, parallel in, parallel out, serial input |
| 980 | REAR PARTS AREA | Shelf 2 – Column A | 7496 | 5-bit parallel-in/parallel-out shift register, asynchronous preset |
| 981 | REAR PARTS AREA | Shelf 2 – Column B | 74LS107 | Dual J-K flip flops with clear |
| 982 | REAR PARTS AREA | Shelf 2 – Column B | 74F109 | dual J-NotK positive-edge-triggered flip-flop, clear and preset |
| 983 | REAR PARTS AREA | Shelf 2 – Column B | 74LS112 Dual J/K Flip Flop with preset and clear | dual J-K negative-edge-triggered flip-flop, clear and preset |
| 984 | REAR PARTS AREA | Shelf 2 – Column B | 74L113 Dual J/K Flip Flop negative edge triggered | dual J-K negative-edge-triggered flip-flop, preset |
| 985 | REAR PARTS AREA | Shelf 2 – Column B | 74121 monostable multivibrator | monostable multivibrator |
| 986 | REAR PARTS AREA | Shelf 2 – Column B | 74LS123 | dual retriggerable monostable multivibrator, clear |
| 987 | REAR PARTS AREA | Shelf 2 – Column B | 74LS132 Quad NAND Schmidt Trigger | quad 2-input NAND gate |
| 988 | REAR PARTS AREA | Shelf 2 – Column B | 74133 13 Input NAND | single 13-input NAND gate |
| 989 | REAR PARTS AREA | Shelf 2 – Column B | 74LS138 3-to-8 decoder/demultiplexer | 3-to-8 decoder/demultiplexer |
| 990 | REAR PARTS AREA | Shelf 2 – Column B | 74LS139 4-to-1 decoder/demultiplexer | 4-to-1 decoder/demultiplexer |
| 991 | REAR PARTS AREA | Shelf 2 – Column B | 74148 8-line to 3-line priority encoder | 8-line to 3-line priority encoder |
| 992 | REAR PARTS AREA | Shelf 2 – Column B | 74LS148 | 8-line to 3-line priority encoder |
| 993 | REAR PARTS AREA | Shelf 2 – Column B | 74150 | 16-line to 1-line data selector/multiplexer |
| 994 | REAR PARTS AREA | Shelf 2 – Column B | 74151 | 8-line to 1-line data selector/multiplexer |
| 995 | REAR PARTS AREA | Shelf 2 – Column B | 74LS153 Dual 4-to-1 data selector/multiplexor | Dual 4-to-1 data selector/multiplexor |
| 996 | REAR PARTS AREA | Shelf 2 – Column B | 74154 4-line to 16-line decoder/demux | 4-line to 16-line decoder/demux |
| 997 | REAR PARTS AREA | Shelf 2 – Column B | 74155 Dual 2-to-4 decoder/demux | Dual 2-to-4 decoder/demux |
| 998 | REAR PARTS AREA | Shelf 2 – Column B | 74LS157 Quad 2-to-1 selector/multiplexer non-inverting | Quad 2-to-1 selector/multiplexer non-inverting |
| 999 | REAR PARTS AREA | Shelf 2 – Column B | 74LS158 2-to-1 selector, multiplexer, inverting | 2-to-1 selector, multiplexer, inverting |
| 1000 | REAR PARTS AREA | Shelf 2 – Column B | 74161 | synchronous presettable 4-bit binary counter, asynchronous clear |
| 1001 | REAR PARTS AREA | Shelf 2 – Column B | 74LS163 | synchronous presettable 4-bit binary counter, synchronous clear |
| 1002 | REAR PARTS AREA | Shelf 2 – Column B | 74164 | 8-bit serial-in parallel-out (SIPO) shift register, asynchronous clear, not output latch |
| 1003 | REAR PARTS AREA | Shelf 2 – Column B | 74165 | 8-bit parallel-in serial-out (PISO) shift register, parallel load, complementary outputs |
| 1004 | REAR PARTS AREA | Shelf 2 – Column B | 74LS166 | parallel-load 8-bit shift register |
| 1005 | REAR PARTS AREA | Shelf 2 – Column B | 74LS168 8 b serial out parallel shift register | 8 b serial out parallel shift register |
| 1006 | REAR PARTS AREA | Shelf 2 – Column B | 74170 | 16-bit register file (4x4) |
| 1007 | REAR PARTS AREA | Shelf 2 – Column B | 74173 | quad D flip-flop, asynchronous clear |
| 1008 | REAR PARTS AREA | Shelf 2 – Column B | 74174 | hex D flip-flop, common asynchronous clear |
| 1009 | REAR PARTS AREA | Shelf 2 – Column B | 74LS175 | quad D edge-triggered flip-flop, complementary outputs and asynchronous clear |
| 1010 | REAR PARTS AREA | Shelf 2 – Column B | 74177 | presettable binary counter/latch |
| 1011 | REAR PARTS AREA | Shelf 2 – Column B | 74181 | 4-bit arithmetic logic unit and function generator |
| 1012 | REAR PARTS AREA | Shelf 2 – Column B | 74182 | lookahead carry generator |
| 1013 | REAR PARTS AREA | Shelf 2 – Column B | 74LS189 | 64-bit RAM (16x4), 4 data inputs, 4 inverted data outputs |
| 1014 | REAR PARTS AREA | Shelf 2 – Column B | 74LS191 | synchronous presettable up/down 4-bit binary counter |
| 1015 | REAR PARTS AREA | Shelf 2 – Column B | 74LS194 | 4-bit bidirectional universal shift register |
| 1016 | REAR PARTS AREA | Shelf 2 – Column B | 74198 | 8-bit bidirectional universal shift register |
| 1017 | REAR PARTS AREA | Shelf 2 – Column B | 74221 | dual monostable multivibrator |
| 1018 | REAR PARTS AREA | Shelf 2 – Column B | 74240 | octal buffer, inverting outputs |
| 1019 | REAR PARTS AREA | Shelf 2 – Column B | 74LS245 | octal bus transceiver, non-inverting outputs |
| 1020 | REAR PARTS AREA | Shelf 2 – Column B | 74LS253 | dual 4-line to 1-line data selector/multiplexer |
| 1021 | REAR PARTS AREA | Shelf 2 – Column B | 74257 | quad 2-line to 1-line data selector/multiplexer, non-inverting outputs |
| 1022 | REAR PARTS AREA | Shelf 2 – Column B | 74LS258 | quad 2-line to 1-line data selector/multiplexer, inverting outputs |
| 1023 | REAR PARTS AREA | Shelf 2 – Column B | 74LS259 | 8-bit bit addressable input latch with clr |

| | | | | |
|------|-----------------|--------------------|---|---|
| 1024 | REAR PARTS AREA | Shelf 2 – Column B | DP8304BN 8 bit BIXCVR | 8 bit BIXCVR |
| 1025 | REAR PARTS AREA | Shelf 2 – Column B | 7497 | synchronous 6-bit binary rate multiplier |
| 1026 | REAR PARTS AREA | Shelf 2 – Column C | 74260 | dual 5-input NOR gate |
| 1027 | REAR PARTS AREA | Shelf 2 – Column C | 74265 | quad complementary output elements |
| 1028 | REAR PARTS AREA | Shelf 2 – Column C | 74LS266 | quad 2-input XNOR gate |
| 1029 | REAR PARTS AREA | Shelf 2 – Column C | 74LS273 | 8-bit register, asynchronous clear |
| 1030 | REAR PARTS AREA | Shelf 2 – Column C | 74LS279 | quad set-reset latch |
| 1031 | REAR PARTS AREA | Shelf 2 – Column C | 74280 | 9-bit odd/even parity bit generator/checker |
| 1032 | REAR PARTS AREA | Shelf 2 – Column C | 74283 | 4-bit binary full adder (has carry in function) |
| 1033 | REAR PARTS AREA | Shelf 2 – Column C | 74284 | 4-bit by 4-bit parallel binary multiplier (high order 4 bits of product) |
| 1034 | REAR PARTS AREA | Shelf 2 – Column C | 74285 | 4-bit by 4-bit parallel binary multiplier (low order 4 bits of product) |
| 1035 | REAR PARTS AREA | Shelf 2 – Column C | 74287 | 1024-bit PROM (256x4) |
| 1036 | REAR PARTS AREA | Shelf 2 – Column C | 74293 4 b binary counter | 4-bit binary counter (separate divide-by-2 and divide-by-8 sections) |
| 1037 | REAR PARTS AREA | Shelf 2 – Column C | 74LS298 Quad 2-input mux w/storage | quad 2-input multiplexer, storage |
| 1038 | REAR PARTS AREA | Shelf 2 – Column C | 74367 | hex buffer, non-inverting outputs |
| 1039 | REAR PARTS AREA | Shelf 2 – Column C | 74LS368 | hex buffer, inverting outputs |
| 1040 | REAR PARTS AREA | Shelf 2 – Column C | 74LS373 | octal transparent latch |
| 1041 | REAR PARTS AREA | Shelf 2 – Column C | 74LS374 octal register | octal register |
| 1042 | REAR PARTS AREA | Shelf 2 – Column C | 74LS377 8b register with clock enable | 8-bit register, clock enable |
| 1043 | REAR PARTS AREA | Shelf 2 – Column C | 74LS379 | 4-bit register, clock enable and complementary outputs |
| 1044 | REAR PARTS AREA | Shelf 2 – Column C | 74LS393 | dual 4-bit binary counter, asynchronous clear |
| 1045 | REAR PARTS AREA | Shelf 2 – Column C | 74500 | 6-bit flash analog-to-digital converter (ADC) |
| 1046 | REAR PARTS AREA | Shelf 2 – Column C | 74573 | octal D-type transparent latch |
| 1047 | REAR PARTS AREA | Shelf 2 – Column C | 74HC595N shift register | 8-bit shift registers, serial-in, parallel-out, output latches, output enable |
| 1048 | REAR PARTS AREA | Shelf 2 – Column C | 74LS670 | 16-bit register file (4x4) |
| 1049 | REAR PARTS AREA | Shelf 2 – Column C | 4001 | |
| 1050 | REAR PARTS AREA | Shelf 2 – Column C | 4008 | |
| 1051 | REAR PARTS AREA | Shelf 2 – Column C | 4011 | |
| 1052 | REAR PARTS AREA | Shelf 2 – Column C | 4012 | |
| 1053 | REAR PARTS AREA | Shelf 2 – Column C | 4013/4014 | |
| 1054 | REAR PARTS AREA | Shelf 2 – Column C | 4014 | |
| 1055 | REAR PARTS AREA | Shelf 2 – Column C | 4016 | |
| 1056 | REAR PARTS AREA | Shelf 2 – Column C | 4017 | |
| 1057 | REAR PARTS AREA | Shelf 2 – Column C | 4023 | |
| 1058 | REAR PARTS AREA | Shelf 2 – Column C | 4024 | |
| 1059 | REAR PARTS AREA | Shelf 2 – Column C | 4028 | |
| 1060 | REAR PARTS AREA | Shelf 2 – Column C | 4041 | |
| 1061 | REAR PARTS AREA | Shelf 2 – Column C | 4049 | |
| 1062 | REAR PARTS AREA | Shelf 2 – Column C | 4061 | |
| 1063 | REAR PARTS AREA | Shelf 2 – Column C | 4066 | |
| 1064 | REAR PARTS AREA | Shelf 2 – Column C | 4081 | |
| 1065 | REAR PARTS AREA | Shelf 2 – Column C | 4093 | |
| 1066 | REAR PARTS AREA | Shelf 2 – Column C | ULN2003A 7 Channel Darlington | |
| 1067 | REAR PARTS AREA | Shelf 2 – Column C | CD4070BE | |
| 1068 | REAR PARTS AREA | Shelf 2 – Column C | CD40107BE | |
| 1069 | REAR PARTS AREA | Shelf 2 – Column C | 4027 | |
| 1070 | REAR PARTS AREA | Shelf 2 – Column C | TL780-12CKC 12V regulator TO-220 | |
| 1071 | REAR PARTS AREA | Shelf 2 – Column C | DSA2-16A-ND – diode avalanche 1600V 7A axial | |
| 1072 | REAR PARTS AREA | Shelf 2 – Column C | 74LS624 voltage controlled oscillator | |
| 1073 | REAR PARTS AREA | Shelf 2 – Column D | NJM7912FA-ND -12V Regulator TO-220 | |
| 1074 | REAR PARTS AREA | Shelf 2 – Column D | 7905 -5V linear voltage regulator | |
| 1075 | REAR PARTS AREA | Shelf 2 – Column D | LM7805-TO-92 +5V linear voltage regulator | |
| 1076 | REAR PARTS AREA | Shelf 2 – Column D | LM7915 -15V linear voltage regulator | |
| 1077 | REAR PARTS AREA | Shelf 2 – Column D | LM7815 +15V linear voltage regulator | |
| 1078 | REAR PARTS AREA | Shelf 2 – Column D | 74LS125 | |
| 1079 | REAR PARTS AREA | Shelf 2 – Column D | 74LS169 | |
| 1080 | REAR PARTS AREA | Shelf 2 – Column D | 7447-74LS114 | |
| 1081 | REAR PARTS AREA | Shelf 2 – Column D | 74244 | |
| 1082 | REAR PARTS AREA | Shelf 2 – Column D | 7440 | |
| 1083 | REAR PARTS AREA | Shelf 2 – Column D | 74160 | |
| 1084 | REAR PARTS AREA | Shelf 2 – Column D | 74122 | |
| 1085 | REAR PARTS AREA | Shelf 2 – Column D | 2206CP function gen – 2207CP voltage control oscillator | |
| 1086 | REAR PARTS AREA | Shelf 2 – Column D | 7412 | |
| 1087 | REAR PARTS AREA | Shelf 2 – Column D | UA775-LF353 | |
| 1088 | REAR PARTS AREA | Shelf 2 – Column D | V7805-1000 DC-DC 5V 5W – LM381 | |
| 1089 | REAR PARTS AREA | Shelf 2 – Column D | LM566 – LM723 | |
| 1090 | REAR PARTS AREA | Shelf 2 – Column D | TL083CN-TL080 | |
| 1091 | REAR PARTS AREA | Shelf 2 – Column D | UA308-LM301 | |
| 1092 | REAR PARTS AREA | Shelf 2 – Column D | LF347 – LF351N | |
| 1093 | REAR PARTS AREA | Shelf 2 – Column D | 2N3494 PNP Small signal transistor | |
| 1094 | REAR PARTS AREA | Shelf 2 – Column D | SMP50N06 N-Channel MOSFET | |
| 1095 | REAR PARTS AREA | Shelf 2 – Column D | 2N5769 | |
| 1096 | REAR PARTS AREA | Shelf 2 – Column D | LM336 2.5V reference source | |
| 1097 | REAR PARTS AREA | Shelf 2 – Column D | LM339 Quad voltage comparator | |
| 1098 | REAR PARTS AREA | Shelf 2 – Column D | LM380N audio power amplifier | |
| 1099 | REAR PARTS AREA | Shelf 2 – Column D | LM393 Low offset voltage dual comparators | |
| 1100 | REAR PARTS AREA | Shelf 2 – Column D | CP567 phase locked loop | |
| 1101 | REAR PARTS AREA | Shelf 2 – Column D | LM3914 dot bar display driver | |
| 1102 | REAR PARTS AREA | Shelf 2 – Column D | TIP30 PNP 1 Amp Darlington power transistor | |

| | | | |
|------|-----------------|--------------------------|---|
| 1103 | REAR PARTS AREA | Shelf 2 – Column D | 6.3V trans voltage clamp |
| 1104 | REAR PARTS AREA | Shelf 2 – Column D | 330uH inductors |
| 1105 | REAR PARTS AREA | Shelf 2 – Column D | 1Kx6 resistor network |
| 1106 | REAR PARTS AREA | Shelf 2 – Column D | 330 Ohm x 10 resistor network |
| 1107 | REAR PARTS AREA | Shelf 2 – Column D | X9C102P Digital potentiometer |
| 1108 | REAR PARTS AREA | Shelf 2 – Column D | EMPTY |
| 1109 | REAR PARTS AREA | Shelf 2 – Column D | APQ2369 |
| 1110 | REAR PARTS AREA | Shelf 2 – Column D | MPQ2369 |
| 1111 | REAR PARTS AREA | Shelf 2 – Column D | LTC1062 |
| 1112 | REAR PARTS AREA | Shelf 2 – Column D | MC14514B |
| 1113 | REAR PARTS AREA | Shelf 2 – Column D | AIRD-02-151K 150uH inductor |
| 1114 | REAR PARTS AREA | Shelf 2 – Column D | MUR3020 |
| 1115 | REAR PARTS AREA | Shelf 2 – Column D | MT8888 |
| 1116 | REAR PARTS AREA | Shelf 2 – Column D | LF442CN JFET Amp |
| 1117 | REAR PARTS AREA | Shelf 2 – Column D | TL084CN |
| 1118 | REAR PARTS AREA | Shelf 2 – Column D – TOP | Polyswitch resettable fuses (in case) |
| 1119 | REAR PARTS AREA | Shelf 2 | TTL Data book, Texas Instruments |
| 1120 | REAR PARTS AREA | Shelf 2 | TTL data sheets, assorted |
| 1121 | REAR PARTS AREA | Shelf 2 – Column E | IRLB8721PBF MOSFET 30V 62A 9mOhm |
| 1122 | REAR PARTS AREA | Shelf 2 – Column E | GP1U501QS IR Detector |
| 1123 | REAR PARTS AREA | Shelf 2 – Column E | Rectifier Bridge 1.5A 50V |
| 1124 | REAR PARTS AREA | Shelf 2 – Column E | 100V 4 Amp full bridge rectifier |
| 1125 | REAR PARTS AREA | Shelf 2 – Column E | LMC6484 Quad op amp Rail to Rail |
| 1126 | REAR PARTS AREA | Shelf 2 – Column E | LM311N comparator |
| 1127 | REAR PARTS AREA | Shelf 2 – Column E | LM393P dual comparators |
| 1128 | REAR PARTS AREA | Shelf 2 – Column E | LM339N quad comparators |
| 1129 | REAR PARTS AREA | Shelf 2 – Column E | ATTINY13A |
| 1130 | REAR PARTS AREA | Shelf 2 – Column E | ATMEGA8-16 |
| 1131 | REAR PARTS AREA | Shelf 2 – Column E | ATMEGA16 |
| 1132 | REAR PARTS AREA | Shelf 2 – Column E | SI-3240G 24V 1.5A regulator |
| 1133 | REAR PARTS AREA | Shelf 2 – Column E | TL082CP FET Op amp |
| 1134 | REAR PARTS AREA | Shelf 2 – Column E | LM6361N high speed op amp 50 MHz |
| 1135 | REAR PARTS AREA | Shelf 2 – Column E | 8L01-05-001 Reed relay 0.5A 5V |
| 1136 | REAR PARTS AREA | Shelf 2 – Column E | MOC3023 Triac photocoupler |
| 1137 | REAR PARTS AREA | Shelf 2 – Column E | TL494IN PWM controller |
| 1138 | REAR PARTS AREA | Shelf 2 – Column E | 78L18 Linear regulator +18V |
| 1139 | REAR PARTS AREA | Shelf 2 – Column E | DF10M bridge rectifier 1kV 1A |
| 1140 | REAR PARTS AREA | Shelf 2 – Column E | DF02M bridge rectifier 200V 1A |
| 1141 | REAR PARTS AREA | Shelf 2 – Column E | MF4CN-50 low pass filter |
| 1142 | REAR PARTS AREA | Shelf 2 – Column E | ZNRV10431U Varistor |
| 1143 | REAR PARTS AREA | Shelf 2 – Column E | TLV2462CP dual op amp |
| 1144 | REAR PARTS AREA | Shelf 2 – Column E | TV2462AQDRQ1 dual op amp |
| 1145 | REAR PARTS AREA | Shelf 2 – Column E | TK4436-ND inductor 10 uH |
| 1146 | REAR PARTS AREA | Shelf 2 – Column E | L298N dual full bridge driver |
| 1147 | REAR PARTS AREA | Shelf 2 – Column E | TK40E6N1.S1X MOSFET N-ch 60V 40A |
| 1148 | REAR PARTS AREA | Shelf 2 – Column E | 1.5KE150CA DICT-ND TVS diode 1500W 150V |
| 1149 | REAR PARTS AREA | Shelf 2 – Column E | STGW30N120KD IGBT 30A 1200V |
| 1150 | REAR PARTS AREA | Shelf 2 – Column E | LF156H JFET op amp |
| 1151 | REAR PARTS AREA | Shelf 2 – Column E | QSE156 photosensor |
| 1152 | REAR PARTS AREA | Shelf 2 – Column E | INA122PA instrumentation op amp |
| 1153 | REAR PARTS AREA | Shelf 2 – Column E | BD-A515RI 7 segment dual digit display; ATMEGA8515L |
| 1154 | REAR PARTS AREA | Shelf 2 – Column E | FQP30N06L 60V Power MOSFET |
| 1155 | REAR PARTS AREA | Shelf 2 – Column E | 50V 4 Amp full bridge rectifier |
| 1156 | REAR PARTS AREA | Shelf 2 – Column E | 1N4007 diode |
| 1157 | REAR PARTS AREA | Shelf 2 – Column E | 1 Mohm 0.1% precision resistor |
| 1158 | REAR PARTS AREA | Shelf 2 – Column E | IRFP150 Power MOSFET; L6203 full IC bridge |
| 1159 | REAR PARTS AREA | Shelf 2 – Column E | Phototransistors |
| 1160 | REAR PARTS AREA | Shelf 2 – Column E | GAL16V8-25LNC general array logic; TMS62256 TI SRAM 32K x 8 bit |
| 1161 | REAR PARTS AREA | Shelf 2 – Column E | Single Female Headers 40 pin |
| 1162 | REAR PARTS AREA | Shelf 2 – Column E | 4 digit 7 segment display |
| 1163 | REAR PARTS AREA | Shelf 2 – Column E | 4 digit 7 segment display |
| 1164 | REAR PARTS AREA | Shelf 2 – Column E | 1N4004 diode |
| 1165 | REAR PARTS AREA | Shelf 2 – Column E | Assorted diodes |
| 1166 | REAR PARTS AREA | Shelf 2 – Column E – TOP | Dupont connectors |
| 1167 | REAR PARTS AREA | Shelf 2 – Column E – TOP | Dupont connectors 2 |
| 1168 | REAR PARTS AREA | Shelf 2 – Column F | <=10MHz crystals |
| 1169 | REAR PARTS AREA | Shelf 2 – Column F | 10 MHz crystals |
| 1170 | REAR PARTS AREA | Shelf 2 – Column F | 16 MHz crystals |
| 1171 | REAR PARTS AREA | Shelf 2 – Column F | 20 MHz oscillators |
| 1172 | REAR PARTS AREA | Shelf 2 – Column F | 40 MHz oscillators, CMOS and TTL |
| 1173 | REAR PARTS AREA | Shelf 2 – Column F | JUMPERS (0.1" for board) |
| 1174 | REAR PARTS AREA | Shelf 2 – Column F | 32.768 kHz crystals |
| 1175 | REAR PARTS AREA | Shelf 2 – Column F | 16 MHz resonators |
| 1176 | REAR PARTS AREA | Shelf 2 – Column F | 18 MHz crystals |
| 1177 | REAR PARTS AREA | Shelf 2 – Column F | 20 MHz crystals |
| 1178 | REAR PARTS AREA | Shelf 2 – Column F | 2N3819 RF JFET |
| 1179 | REAR PARTS AREA | Shelf 2 – Column F | Arduino stack kits |
| 1180 | REAR PARTS AREA | Shelf 2 – Column F | 50 MHz crystals |
| 1181 | REAR PARTS AREA | Shelf 2 – Column F | 48 MHz crystals |
| 1182 | REAR PARTS AREA | Shelf 2 – Column F | 55.8 MHz crystals; 55.125 MHz crystals |
| 1183 | REAR PARTS AREA | Shelf 2 – Column F | 16 pin (2x8) sockets |
| 1184 | REAR PARTS AREA | Shelf 2 – Column F | NE565A phase lock loop – 2N3441 BJT NPN 140V 3A |

| | | | | |
|------|-----------------|--------------------------|---|--|
| 1185 | REAR PARTS AREA | Shelf 2 – Column F | 6 pin stackable (Arduino, 2x3) | |
| 1186 | REAR PARTS AREA | Shelf 2 – Column F | 32.000 MHz crystals | |
| 1187 | REAR PARTS AREA | Shelf 2 – Column F | IRF740 IRL7833 | |
| 1188 | REAR PARTS AREA | Shelf 2 – Column F | LMC6001 current amp | |
| 1189 | REAR PARTS AREA | Shelf 2 – Column F | TL071 op amps | |
| 1190 | REAR PARTS AREA | Shelf 2 – Column F | ICL7660 voltage converters | |
| 1191 | REAR PARTS AREA | Shelf 2 – Column F | 8 pin stackable (Arduino, 1x8) | |
| 1192 | REAR PARTS AREA | Shelf 2 – Column F | 0.1 Ohm 2W 1% resistor, 0.2 Ohm 1% resistor | |
| 1193 | REAR PARTS AREA | Shelf 2 – Column F | 7905 -5V 1A regulator | |
| 1194 | REAR PARTS AREA | Shelf 2 – Column F | LH0002CN unity gain buffer | |
| 1195 | REAR PARTS AREA | Shelf 2 – Column F | Dual stackable 0.1" headers (special) | |
| 1196 | REAR PARTS AREA | Shelf 2 – Column F | Dual stackable 0.1" headers (female) | |
| 1197 | REAR PARTS AREA | Shelf 2 – Column F | 10 pin stackable (Arduino, 1x10) | |
| 1198 | REAR PARTS AREA | Shelf 2 – Column F | MOSFETS NDP7050L-IRF710-IRF510-2N7000-IRLB8721 | |
| 1199 | REAR PARTS AREA | Shelf 2 – Column F | IRF610 | |
| 1200 | REAR PARTS AREA | Shelf 2 – Column F | 16 MHz crystals | |
| 1201 | REAR PARTS AREA | Shelf 2 – Column F | 1 MHz crystals | |
| 1202 | REAR PARTS AREA | Shelf 2 – Column F | 1 MHz crystals | |
| 1203 | REAR PARTS AREA | Shelf 2 – Column F | Single female headers, 0.1" <40pin | |
| 1204 | REAR PARTS AREA | Shelf 2 – Column F | Long male headers, 0.1" | |
| 1205 | REAR PARTS AREA | Shelf 2 – Column F | Single male headers, 0.1" | |
| 1206 | REAR PARTS AREA | Shelf 2 – Column F | Single male headers, 0.1" | |
| 1207 | REAR PARTS AREA | Shelf 2 – Column F | Double female headers, 0.1" | |
| 1208 | REAR PARTS AREA | Shelf 2 – Column F | Double male headers, 0.1" | |
| 1209 | REAR PARTS AREA | Shelf 2 – Column G | LM350T, LM342P | |
| 1210 | REAR PARTS AREA | Shelf 2 – Column G | LMC64442 op amp | |
| 1211 | REAR PARTS AREA | Shelf 2 – Column G | TL084 op amp | |
| 1212 | REAR PARTS AREA | Shelf 2 – Column G | LF356 JFET op amp | |
| 1213 | REAR PARTS AREA | Shelf 2 – Column G | NE5532 dual op amp | |
| 1214 | REAR PARTS AREA | Shelf 2 – Column G | G201E1 5V-5V converter, R-78E5.0-1.0 5V supply | |
| 1215 | REAR PARTS AREA | Shelf 2 – Column G | 2N6027 PUT 40V | |
| 1216 | REAR PARTS AREA | Shelf 2 – Column G | ZTX658 NPN Hi V Trans | |
| 1217 | REAR PARTS AREA | Shelf 2 – Column G | LM329DZ 6.9V precision reference | |
| 1218 | REAR PARTS AREA | Shelf 2 – Column G | LM385 voltage regulator | |
| 1219 | REAR PARTS AREA | Shelf 2 – Column G | MIC29310 LDO 3.3V | |
| 1220 | REAR PARTS AREA | Shelf 2 – Column G | Old transistors | |
| 1221 | REAR PARTS AREA | Shelf 2 – Column G | MAX483 RS485/422 transceiver7812 12V 1A regulator | |
| 1222 | REAR PARTS AREA | Shelf 2 – Column G | LM337 | |
| 1223 | REAR PARTS AREA | Shelf 2 – Column G | 2N4410 NPN 80V 0.2A | |
| 1224 | REAR PARTS AREA | Shelf 2 – Column G | Schottky diode 30V 200 mA | |
| 1225 | REAR PARTS AREA | Shelf 2 – Column G | LM395T transistor | |
| 1226 | REAR PARTS AREA | Shelf 2 – Column G | KY5050 voltage regulator | |
| 1227 | REAR PARTS AREA | Shelf 2 – Column G | LT1529 variable voltage regulator | |
| 1228 | REAR PARTS AREA | Shelf 2 – Column G | MAX726 switch voltage regulator | |
| 1229 | REAR PARTS AREA | Shelf 2 – Column G | LM317 adjustable voltage regulator | |
| 1230 | REAR PARTS AREA | Shelf 2 – Column G | LM334 current source | |
| 1231 | REAR PARTS AREA | Shelf 2 – Column G | IRFS3806 power MOSFET | |
| 1232 | REAR PARTS AREA | Shelf 2 – Column G | LD29300V80 3A LDO 8V regulator | |
| 1233 | REAR PARTS AREA | Shelf 2 – Column G | MAX600 voltage inverter/doubler | |
| 1234 | REAR PARTS AREA | Shelf 2 – Column G | 2N2907A transistors | |
| 1235 | REAR PARTS AREA | Shelf 2 – Column G | TS992 op amp | |
| 1236 | REAR PARTS AREA | Shelf 2 – Column G | NJM2396F33 3.3V LDO voltage regulator | |
| 1237 | REAR PARTS AREA | Shelf 2 – Column G | LM1086CT-5.0 voltage regulator 1.5A | |
| 1238 | REAR PARTS AREA | Shelf 2 – Column G | 7815 CT 15V 1A voltage regulator | |
| 1239 | REAR PARTS AREA | Shelf 2 – Column G | AS1114 low pass filter | |
| 1240 | REAR PARTS AREA | Shelf 2 – Column G | LM2902-MAX232N | |
| 1241 | REAR PARTS AREA | Shelf 2 – Column G | TIP3055 NPN Transistor | |
| 1242 | REAR PARTS AREA | Shelf 2 – Column G | TVS Diodes | |
| 1243 | REAR PARTS AREA | Shelf 2 – Column G | 2N2221, 2N2222A | |
| 1244 | REAR PARTS AREA | Shelf 2 – Column G | Photodiodes | |
| 1245 | REAR PARTS AREA | Shelf 2 – Column G | LM3914-LM3915 LED Bar displays | |
| 1246 | REAR PARTS AREA | Shelf 2 – Column G | PCB HD ribbon cable | |
| 1247 | REAR PARTS AREA | Shelf 2 – Column G | IR LEDs | |
| 1248 | REAR PARTS AREA | Shelf 2 – Column G – TOP | LED case – red, green, yellow, orange, IR, UV (?) | |
| 1249 | REAR PARTS AREA | Shelf 2 – Column H | MBR745 7.5A Schottky | |
| 1250 | REAR PARTS AREA | Shelf 2 – Column H | TIP120 Darlington | |
| 1251 | REAR PARTS AREA | Shelf 2 – Column H | 2N2907-2N3906-2N4403 PNP | |
| 1252 | REAR PARTS AREA | Shelf 2 – Column H | IXGP20N50 MOSFET 50 Amps 200V 0.06 Rds | |
| 1253 | REAR PARTS AREA | Shelf 2 – Column H | 20N60 MOSFET | |
| 1254 | REAR PARTS AREA | Shelf 2 – Column H | Motorola WW-62 NPN | |
| 1255 | REAR PARTS AREA | Shelf 2 – Column H | 2N5089 NPN | |
| 1256 | REAR PARTS AREA | Shelf 2 – Column H | 2N3904 | |
| 1257 | REAR PARTS AREA | Shelf 2 – Column H | NTE262 PNP | |
| 1258 | REAR PARTS AREA | Shelf 2 – Column H | MPF102 | |
| 1259 | REAR PARTS AREA | Shelf 2 – Column H | A92 PNP 0.5A | |
| 1260 | REAR PARTS AREA | Shelf 2 – Column H | ZSCT555 | |
| 1261 | REAR PARTS AREA | Shelf 2 – Column H | 2N4403 PNP – PN2907 PNP 800mA | |
| 1262 | REAR PARTS AREA | Shelf 2 – Column H | 2N3019 | |
| 1263 | REAR PARTS AREA | Shelf 2 – Column H | 2N3906 | |
| 1264 | REAR PARTS AREA | Shelf 2 – Column H | NTE197 PNP | |
| 1265 | REAR PARTS AREA | Shelf 2 – Column H | 2N6028 300mW 40V SCR | |
| 1266 | REAR PARTS AREA | Shelf 2 – Column H | NE555N, NE5534 | |
| 1267 | REAR PARTS AREA | Shelf 2 – Column H | 2N4401 NPN | |

| | | | |
|------|-----------------|--------------------|---|
| 1268 | REAR PARTS AREA | Shelf 2 – Column H | PN2907 PNP |
| 1269 | REAR PARTS AREA | Shelf 2 – Column H | BC546 NPN 65V 0.1A |
| 1270 | REAR PARTS AREA | Shelf 2 – Column H | TIP112 NPN Darlington |
| 1271 | REAR PARTS AREA | Shelf 2 – Column H | TIP32A NPN |
| 1272 | REAR PARTS AREA | Shelf 2 – Column H | LM555 |
| 1273 | REAR PARTS AREA | Shelf 2 – Column H | 2N5484 JFET |
| 1274 | REAR PARTS AREA | Shelf 2 – Column H | BC337-BC557-BD139-BD140 NPN PNP |
| 1275 | REAR PARTS AREA | Shelf 2 – Column H | 2N5485 |
| 1276 | REAR PARTS AREA | Shelf 2 – Column H | 2N5485 N JFET |
| 1277 | REAR PARTS AREA | Shelf 2 – Column H | 1N4250 |
| 1278 | REAR PARTS AREA | Shelf 2 – Column H | 556 Timers |
| 1279 | REAR PARTS AREA | Shelf 2 – Column H | 2N2219A-A92-2N3904-2N2222-2N5551-2N3906 |
| 1280 | REAR PARTS AREA | Shelf 2 – Column H | S8850-S8050-S9012-S9013-S9014-S9015-S9018 |
| 1281 | REAR PARTS AREA | Shelf 2 – Column H | A42-A733-A1015-C945-C1815-2N5401 |
| 1282 | REAR PARTS AREA | Shelf 2 – Column H | BDX34A PNP 60V |
| 1283 | REAR PARTS AREA | Shelf 2 – Column H | ZIF Headers |
| 1284 | REAR PARTS AREA | Shelf 2 – Column H | 0.0047uF 50V |
| 1285 | REAR PARTS AREA | Shelf 2 – Column H | Precision thermistors |
| 1286 | REAR PARTS AREA | Shelf 2 – Column H | W172DIP-7 12V Reed Relay |
| 1287 | REAR PARTS AREA | Shelf 2 – Column H | Transistors, TO-220 |
| 1288 | REAR PARTS AREA | Shelf 2 – Column H | Transistors, TO-92 |
| 1289 | REAR PARTS AREA | Shelf 2 – Column H | TDA2003V Audio amp |
| 1290 | BAKER RACK B | Shelf 2 | 0.03uF 500V |
| 1291 | BAKER RACK B | Shelf 2 | 0.01uF 1000V |
| 1292 | BAKER RACK B | Shelf 2 | 0.005uF 1000V |
| 1293 | BAKER RACK B | Shelf 2 | Varistor 130V |
| 1294 | BAKER RACK B | Shelf 2 | Varistor 387V; Varistor 430V |
| 1295 | BAKER RACK B | Shelf 2 | 68pF 100V/300V |
| 1296 | BAKER RACK B | Shelf 2 | 1F 5.5V Ultracapacitor |
| 1297 | BAKER RACK B | Shelf 2 | 0.05uF 8000V |
| 1298 | BAKER RACK B | Shelf 2 | 4.0uF 600V |
| 1299 | BAKER RACK B | Shelf 2 | 0.001uF 1000V |
| 1300 | BAKER RACK B | Shelf 2 | 0.68uF 400V |
| 1301 | BAKER RACK B | Shelf 2 | 25uF 500V |
| 1302 | BAKER RACK B | Shelf 2 | 50uF 500V |
| 1303 | BAKER RACK B | Shelf 2 | 3.3F 5.5V Ultracapacitor |
| 1304 | BAKER RACK B | Shelf 2 | 0.005uF 8000V |
| 1305 | BAKER RACK B | Shelf 2 | 33uF 10V |
| 1306 | BAKER RACK B | Shelf 2 | 10uF 15V |
| 1307 | BAKER RACK B | Shelf 2 | 22uF 16V |
| 1308 | BAKER RACK B | Shelf 2 | 47uF 16V |
| 1309 | BAKER RACK B | Shelf 2 | 0.01uF 25V |
| 1310 | BAKER RACK B | Shelf 2 | 15uF 50V |
| 1311 | BAKER RACK B | Shelf 2 | 100uF 63V |
| 1312 | BAKER RACK B | Shelf 2 | 3300uF 63V |
| 1313 | BAKER RACK B | Shelf 2 | 47uF 10V |
| 1314 | BAKER RACK B | Shelf 2 | 0.047uF 80V/0.01uF 80V |
| 1315 | BAKER RACK B | Shelf 2 | 0.022uF 100V |
| 1316 | BAKER RACK B | Shelf 2 | 1uF 100V |
| 1317 | BAKER RACK B | Shelf 2 | 2.2uF 100V |
| 1318 | BAKER RACK B | Shelf 2 | 33uF 100V |
| 1319 | BAKER RACK B | Shelf 2 | 47uF 100V |
| 1320 | BAKER RACK B | Shelf 2 | 22uF 250V |
| 1321 | BAKER RACK B | Shelf 2 | 47uF 35V |
| 1322 | BAKER RACK B | Shelf 2 | 100uF 63V |
| 1323 | BAKER RACK B | Shelf 2 | 100uF 63V (second bin) |
| 1324 | BAKER RACK B | Shelf 2 | 0.08uF 300V |
| 1325 | BAKER RACK B | Shelf 2 | 3uF 400V |
| 1326 | BAKER RACK B | Shelf 2 | UNSORTED ASSORTED <100uF capacitors |
| 1327 | BAKER RACK B | Shelf 2 | 7.5uF 450V |
| 1328 | BAKER RACK B | Shelf 2 | 10uF 450V |
| 1329 | BAKER RACK B | Shelf 2 | 1uF 63V |
| 1330 | BAKER RACK B | Shelf 2 | 47uF 35V |
| 1331 | BAKER RACK B | Shelf 2 | 1uF 50V |
| 1332 | BAKER RACK B | Shelf 2 | 1uF 50V metal film |