


Artisans Asylum – Electronics and Robotics Parts Locator/Inventory

2026-Mar-28 Detailed

Number of Indexed Elements: 3173
 To be cataloged = parts inside, not labeled/indexed
 Drawers not labeled may have items listed here

To be cataloged: 64
 EMPTY: 55
 Index count check: 3173



Note that there are BENCHES and SHELVES

Bench Alpha
 Bench Bravo
 Bench Charlie

Shelf Alpha
 Shelf Bravo
 Shelf Charlie

Shop layout from 2025-Aug-24

HINTS FOR FINDING PARTS AND EQUIVALENTS

- HINT 1** Search for part of part number; WM-1234 might be under WM1234 or WM-1234, so search for 1234; Molex parts may be 03-123-ZZZZ or 03123ZZZZ
- HINT 2** Many of the donated parts have Digikey part numbers; "WM-2015 6 position with ramp" is a Molex 0022012067 so if you are looking for that Molex part, use the Digikey part number
- HINT 3** Most of the parts are grouped; (sensors, pins, power supplies, wire)
- HINT 4** Look for synonyms; knives/X-Acto blades
- TO FIND EQUIVALENT PARTS, YOU CAN POINT AN LLM TO THIS LIST;** https://wiki.artisansasylum.com/images/1/1f/ENR_Inventory.pdf
- Looking for a specific type of connector? Check out: <https://connectorbook.com/identification.html>
- Have a surface mount part and are trying to know what it is? Check out: https://smd.yooneed.one/#google_vignette
- Looking to buy a part? You can search a large number of distributors with: <https://octopart.com>
- SOLDER (LEAD FREE)** is found in the front wire rack
- MULTIMETERS** should not leave the shop; they are located at Bench Juliet – Note there are 2-3 PORT and 4 PORT multimeter sections – especially don't remove the 4 PORT ones
- DO NOT CLIMB SHELVES** – use a step ladder (to the left of the cubbies in the back) or library step (near the rear shelves/Radio Shack shelves)

Line	Bench/Location	Top/Mid/Bottom	Item	
1	Bench Alpha	Top	Heat Shrink	
2	Bench Alpha	Top	Hot Glue Guns	
3	Bench Alpha	Top	Cable Wrap	
4	Bench Alpha	Top	Heat Guns	
5	Bench Alpha	Middle	Photon	
6	Bench Alpha	Middle	Ubuntu PC	
7	Bench Alpha	Middle	FTDI Adapters – USBASB programmer	
8	Bench Alpha	Middle	DB9/DB15 adapters	
9	Bench Alpha	Middle	Breadboard jumpers (specials)	
10	Bench Alpha	Middle	IC Test clip/chip probe	
11	Bench Alpha	Middle	RS485-Cricket	
12	Bench Alpha	Middle	MicroUSB – USB micro breakout	
13	Bench Alpha	Middle	EMPTY	
14	Bench Alpha	Middle	USB to WiFi	
15	Bench Alpha	Middle	ATMEL AVR Programmer; CodeWarrior USB TAP (Freescale)	
16	Bench Alpha	Middle – 8x8 drawer unit	HC-SR04 ultrasonic distance sensor and mounting bracket	R1 C1
17	Bench Alpha	Middle – 8x8 drawer unit	Adafruit flex/bend sensor	R1 C2
18	Bench Alpha	Middle – 8x8 drawer unit	SEN-09259 Sparkfun triple axis accelerometer	R1 C3
19	Bench Alpha	Middle – 8x8 drawer unit	Adafruit TLC59711 12-chan 16-bit constant sink current driver	R1 C4

20	Bench Alpha	Middle – 8x8 drawer unit	LIS3DH – triple axis accelerometer- LSM9DS1 – 9DOF sensor	R1 C5
21	Bench Alpha	Middle – 8x8 drawer unit	Meas-spec.com – sample piezo sensor	R1 C6
22	Bench Alpha	Middle – 8x8 drawer unit	KEYES 49E Hall Sensor; AH9246 omnipolar Hall sensor; AH9250-P-B magnetic switch; US4881EUA IC latch CMOS Hall sensor; US5881EUA hall sensor; US2881LUA IC latch Hall sensor; HLC2710-001 sensor logic out optic side view;	R1 C7
23	Bench Alpha	Middle – 8x8 drawer unit	Adafruit MCP4725 12-bit DAC I2C	R1 C8
24	Bench Alpha	Middle – 8x8 drawer unit	Grove light sensor v1.1; analog output 350 LUX	R2 C1
25	Bench Alpha	Middle – 8x8 drawer unit	RepRap SD ramps v1.0	R2 C2
26	Bench Alpha	Middle – 8x8 drawer unit	DHT11 – temperature/humidity sensor; AM2320 I2C humidity sensor	R2 C3
27	Bench Alpha	Middle – 8x8 drawer unit	MCP23017 16 bit I/O expander; I2C	R2 C4
28	Bench Alpha	Middle – 8x8 drawer unit	FX29 load cell 10 lb 0.5-4.5V output	R2 C5
29	Bench Alpha	Middle – 8x8 drawer unit	To be cataloged	R2 C6
30	Bench Alpha	Middle – 8x8 drawer unit	MPXV7002 pressure sensor	R2 C7
31	Bench Alpha	Middle – 8x8 drawer unit	Adafruit IR Sensor #157	R2 C8
32	Bench Alpha	Middle – 8x8 drawer unit	RJ-11/RJ11 breakout Sparkfun	R3 C1
33	Bench Alpha	Middle – 8x8 drawer unit	MX2125 Parallax dual axis accelerometer	R3 C2
34	Bench Alpha	Middle – 8x8 drawer unit	Photointerruptor (like GP2S40 – unknown model)	R3 C3
35	Bench Alpha	Middle – 8x8 drawer unit	Parallax HS1101 humidity sensor	R3 C4
36	Bench Alpha	Middle – 8x8 drawer unit	APDS9960 – Light/color/IR Proximity sensor	R3 C5
37	Bench Alpha	Middle – 8x8 drawer unit	Light/IR sensor VCNL4010	R3 C6
38	Bench Alpha	Middle – 8x8 drawer unit	Grove loudness/sound sensor	R3 C7
39	Bench Alpha	Middle – 8x8 drawer unit	MLX90614 dual zone IR – ACF579903	R3 C8
40	Bench Alpha	Middle – 8x8 drawer unit	AD22100AT – temperature sensor Vout TO-92	R4 C1
41	Bench Alpha	Middle – 8x8 drawer unit	LM335Z – IC precision temperature sensor TO-92	R4 C2
42	Bench Alpha	Middle – 8x8 drawer unit	Electronics Goldmine G951 – tilt switch	R4 C3
43	Bench Alpha	Middle – 8x8 drawer unit	TMP37F temperature sensor TO-92	R4 C4
44	Bench Alpha	Middle – 8x8 drawer unit	Electronics Goldmine G2005 – thermistor	R4 C5
45	Bench Alpha	Middle – 8x8 drawer unit	Stereo 20W Class D audio amplifier	R4 C6
46	Bench Alpha	Middle – 8x8 drawer unit	MAX30100EFD+ ; oximeter/heartate sensor	R4 C7
47	Bench Alpha	Middle – 8x8 drawer unit	TMP36GZ – temperature sensor TO-92	R4 C8
48	Bench Alpha	Middle – 8x8 drawer unit	Sparkfun R111/RJ45 breakout?	R5 C1
49	Bench Alpha	Middle – 8x8 drawer unit	Sparkfun ACS712 low current sensor board breakout SEN-08883	R5 C2
50	Bench Alpha	Middle – 8x8 drawer unit	sensor cable, 3 pin, polarized (unknown)	R5 C3
51	Bench Alpha	Middle – 8x8 drawer unit	LM35DT – precision temperature TO-220	R5 C4
52	Bench Alpha	Middle – 8x8 drawer unit	INA189 Analog DC current sensor Adafruit #1164	R5 C5
53	Bench Alpha	Middle – 8x8 drawer unit	H13B1 photointerruptor GE	R5 C6
54	Bench Alpha	Middle – 8x8 drawer unit	DS18B20 temperature sensor	R5 C7
55	Bench Alpha	Middle – 8x8 drawer unit	MF52A104J3950 – thermistor NTC 100K Ohm 5%	R5 C8
56	Bench Alpha	Middle – 8x8 drawer unit	OHNS120U Hall; OH360U Hall; US5881ESO Hall; HMC1512 sensor displacement rotary	R6 C1
57	Bench Alpha	Middle – 8x8 drawer unit	Keyes THDZ Piezo speaker	R6 C2
58	Bench Alpha	Middle – 8x8 drawer unit	Hall sensor – Radio Shack 276-1646 – OHS3140 Hall	R6 C3
59	Bench Alpha	Middle – 8x8 drawer unit	Pololu 2808 - Mini Pushbutton Power Switch with Reverse Voltage Protection, LV	R6 C4
60	Bench Alpha	Middle – 8x8 drawer unit	Visahy ambient light sensor TEPT5700	R6 C5
61	Bench Alpha	Middle – 8x8 drawer unit	Grove Dust Sensor	R6 C6
62	Bench Alpha	Middle – 8x8 drawer unit	Grove Dust Sensor	R6 C7
63	Bench Alpha	Middle – 8x8 drawer unit	Sharp GP2D120 distance sensor 4-30 cm	R6 C8
64	Bench Alpha	Middle – 8x8 drawer unit	Sharp 2Y0A21 distance sensor 10-80 cm	R7 C1
65	Bench Alpha	Middle – 8x8 drawer unit	Hagisonic AniBat HG-(L/M/U)40(T/R/D)A ultrasonic distance sensor	R7 C2
66	Bench Alpha	Middle – 8x8 drawer unit	Sharp GP2D150A distance sensor 4-30 cm; 15 deg	R7 C3
67	Bench Alpha	Middle – 8x8 drawer unit	Optical sensor – unknown details	R7 C4
68	Bench Alpha	Middle – 8x8 drawer unit	9 DOF MPU-9250	R7 C5
69	Bench Alpha	Middle – 8x8 drawer unit	RF11A034 3.3V 5V 433MHz 4Ch Receiver Timer Delay Board	R7 C6
70	Bench Alpha	Middle – 8x8 drawer unit	SPI Flash 1MB – Adafruit #1564	R7 C7
71	Bench Alpha	Middle – 8x8 drawer unit	Keyes sensors (IR, vibration)?	R7 C8
72	Bench Alpha	Middle – 8x8 drawer unit	Gas sensor – MQ-2 combustible gas – plus data sheet for gas sensors; heaters take 150mA	R8 C1
73	Bench Alpha	Middle – 8x8 drawer unit	Gas sensor – MQ-3 ethanol	R8 C2
74	Bench Alpha	Middle – 8x8 drawer unit	Gas sensor – MQ-5 natural gas	R8 C3
75	Bench Alpha	Middle – 8x8 drawer unit	Gas sensor – MQ-6 propane-butane	R8 C4
76	Bench Alpha	Middle – 8x8 drawer unit	Gas sensor – MQ-7 carbon monoxide (CO)	R8 C5
77	Bench Alpha	Middle – 8x8 drawer unit	Gas sensor – MQ-8 hydrogen gas (H2)	R8 C6
78	Bench Alpha	Middle – 8x8 drawer unit	Gas sensor – MQ-9 methane-propane	R8 C7
79	Bench Alpha	Middle – 8x8 drawer unit	Gas sensor – MQ-135 air quality;used in air quality control equipment for buildings/offices, are suitable for detecting of NH3,NOx, alcohol, Benzene, smoke,CO2 ,etc.	R8 C8
80	Bench Alpha	Middle	Calculator	
81	Bench Alpha	Middle	Arduino UNO sensors	
82	Bench Alpha	Lower	Project boxes, large	
83	Bench Alpha	Lower	Automotive	
84	Bench Alpha	Lower	Car 12V plugs	
85	Bench Alpha	Lower	Laptop power supplies	
86	Bench Alpha	Lower	Small DC motors, large AC motors	
87	Bench Alpha	Lower	Bunsen burners and lab strut	
88	Bench Alpha	Lower	Matched 3C/4C connectors	
89	Bench Alpha	Lower	Lego	
90	Bench Alpha	Lower	Nylon cable clamps; 5/16" and 1/8"; electrical cable hangers	
91	Bench Alpha	Lower	RCA cables and plugs	
92	Bench Bravo	Top	Arduino/RPI displays; polarizing films; cell phone glass	
93	Bench Bravo	Top	Small HDMI screen	
94	Bench Bravo	Top	Remote control/RC 4 channel	
95	Bench Bravo	Top	IR remotes	
96	Bench Bravo	Top	Game controllers	
97	Bench Bravo	Top	Flight simulator yoke for PC	
98	Bench Bravo	Top	Electret microphone	
99	Bench Bravo	Top	Borescope	
100	Bench Bravo	Top	Stethoscope	
101	Bench Bravo	Top	Touchscreen	
102	Bench Bravo	Top	Heat sinks	
103	Bench Bravo	Middle – Drawers Left	Arduino sensors; temperature, pressure, vibration, tilt, GPS antennas (SMA), UVF GPS to RPI; RTL-SDR software defined radio; Sparkfun Bus Pirate; debugger for 1-wire, 2-wire, 3-wire, UART, I2C, SPI	
104	Bench Bravo	Middle – Drawers Left	Arduino shields	
105	Bench Bravo	Middle – Drawers Left	Arduino-like: Arduino MKR Wifi 1010; Adafruit DC Boarduino; DRF0321 Wido; Flora Neopixel;Adafruit Gemma; Adafruit KB2040; Adafruit Circuit Playground Express; Adafruit Mini-Metal Speaker w/wires; Digispark; Arduino Nano; Arduino Pro Mini; Arduino Pro Mini 5V; Arduino Pro; Adafruit Trinket 5V; Adafruit Trinket 3V; Adafruit Pro Trinket 3V; Adafruit Pro Trinket Li-Ion Backpack; Adafruit Pro Trinket 5V; Biobot Analytics; microDuino; Arduino Pro Mini V2; LCP82x Xpresso v2/mbed; USB Bitwackker (schmalzhaus.com) – Windows only; Random boards; ATSM21	
106	Bench Bravo	Middle – Drawers Left	Smaller stepper motors and linear slides	
107	Bench Bravo	Middle – Drawers Left	Arduino power via battery	
108	Bench Bravo	Middle – Drawers Right	Xbee and Bluetooth	
109	Bench Bravo	Middle – Drawers Right	IR transmitters and receivers; optoisolators	
110	Bench Bravo	Middle – Drawers Right	NiCD/Lithium batteries	
111	Bench Bravo	Middle – Drawers Right	Alkaline batteries, battery test (AA, AAA, 12V)	
112	Bench Bravo	Middle – Drawers Right	Mini vacuums	

113	Bench Bravo	Middle – Drawers Right	Free widgets	
114	Bench Bravo	Middle – small drawers left	Rascal and Galileo	
115	Bench Bravo	Middle – small drawers left	Mega/Leonardo	
116	Bench Bravo	Middle – small drawers left	Arduino Ethernet shield	
117	Bench Bravo	Middle – small drawers left	Arduino demo	
118	Bench Bravo	Middle – small drawers left	Digital playground	
119	Bench Bravo	Middle – small drawers left	Neopixel	
120	Bench Bravo	Next to middle drawers	ATMEGA 328P-AUS SMT chips	
121	Bench Bravo	Middle – small drawers – right	HDMI converters	
122	Bench Bravo	Middle – small drawers – right	Pogo pins	
123	Bench Bravo	Middle – small drawers – right	Raspberry Pi Zero; Raspberry Pi Pico	
124	Bench Bravo	Middle – small drawers – right	SD cards / adapters	
125	Bench Bravo	Middle – small drawers – right	USB storage	
126	Bench Bravo	Middle – small drawers – right	Smart card reader	
127	Bench Bravo	Middle	Raspberry Pi 4 station	
128	Bench Bravo	Middle	RPI breadboard	
129	Bench Bravo	Middle	Raspberry Pi Station 1	
130	Bench Bravo	Middle	BNC connectors and Tees	
131	Bench Bravo	Middle	C and D batteries	
132	Bench Bravo	Middle	BNC to RCA; S-Video/RCA to USB; BNC/BNC breakout; BNC to dual banana jack input	
133	Bench Bravo	Middle	TinyISP programmers; ST-LINK/V2	
134	Bench Bravo	Middle – TOP LEFT	Heavy socket set, ¼ and ½; metric and Imperial	
135	Bench Bravo	Lower	Industrial Controls 5	fuse blocks (DIN mount), knife disconnect (DIN) large power blocks, lockout-tagout, PLC controller; Click PLC; HMI; Banner SC10-2roe safety controller
136	Bench Bravo	Lower	Industrial Controls 6	Feed throughs, 5V, 24V, 120 VAC, 240 VAC indicator lights, DIN rail, DIN mounting plates
137	Bench Bravo	Lower	Industrial Controls 7	Estop, buzzer, lights, circuit breakers (2,3,4,5,10,25,32 Amp), safety relays, Mitsubishi L61P, TimeR Power 20R-14C, DPM75 motor surge protector SH04 AEG power auxiliary contactor
138	Bench Bravo	Lower	Limit switches and pushbuttons	
139	Bench Bravo	Lower	Network gear	
140	Bench Bravo	Lower	Panda and Beagleboards	
141	Bench Bravo	Lower	15V and +/-15V power	
142	Bench Bravo	Lower	18-36V power supplies, 9-36V power supplies	
143	Bench Bravo	Lower	Computer parts, USB C docking station	
144	Bench Bravo	Lower	3C shielded cables	
145	Bench Bravo	Lower	Ethernet jacks	
146	Bench Bravo	Lower	Phone jacks	
147	Bench Bravo	Lower	Photovoltaic charger	
148	Bench Bravo	Lower	X10 house control	
149	Bench Bravo	Lower	Tube of DIN rail	
150	Bench Bravo	Lower	DIN rail, large power connectors and power feeds; connectors; Connect-IT; DINNectors (Automation Direct)	
151	Bench Bravo	Lower	EMPTY	
152	Toolbox	Box	Hand tools	
153	Toolbox	Box	Screwdrivers	
154	Toolbox	Box	Cordless drill	
155	Toolbox	Box	Motorized drivers	
156	Toolbox	Box	Torx and sockets	
157	Toolbox	Box	¼ bits, DeWalt screwdriver bits	
158	Toolbox	Box	4mm bits	
159	Toolbox	Box	Small screwdrivers	
160	Toolbox	Box	Hex tools	
161	Toolbox	Box	Pliers	
162	Toolbox	Box	Fuse Pullers	
163	Toolbox	Box	Crimp tools	
164	Toolbox	Box	Soldering tools	
165	Toolbox	Below	Industrial vacuum	
166	Toolbox	Below	180 kg floor scale	
167	Shelf Alpha	Shelf 8	Resistor kits; ¼ Watt and ½ Watt	
168	Shelf Alpha	Shelf 7A	Single board computers (x10) with Ubuntu 18.04 LTS; 2 GB Ram Atom processor	
169	Shelf Alpha	Shelf 7A	Resistor sets	
170	Shelf Alpha	Shelf 7A	Uncommon connectors	
171	Shelf Alpha	Shelf 7	TTL assorted odd	
172	Shelf Alpha	Shelf 7	3300uF 25V capacitors	
173	Shelf Alpha	Shelf 7	4700uF 16V capacitors	
174	Shelf Alpha	Shelf 7	Remote control build kit	
175	Shelf Alpha	Shelf 6	remote control LED puck lights	
176	Shelf Alpha	Shelf 6	Coax splitters; TRIAX	
177	Shelf Alpha	Shelf 6	100 uF, 400V; 3300uF, 35V capacitors; 0.0068uF 400V; 600V 5A G1826 diode	
178	Shelf Alpha	Shelf 6	24VDC fans	
179	Shelf Alpha	Shelf 6	Cable clamps / strain relief	
180	Shelf Alpha	Shelf 6	Minimate IPD1 Samtec connectors 2x1 to 2x12; Powermate IPBD Samtec connectors 2,3,4,5,6,8,10 straight; 2,3,4,5,6 right angle WM4203 5 pos vertical; WM4303 5 pin right angle; WM4204 6 pin; WM4304 6 pin; WM4206 8 pin; WM4306 8 pin right angle; Molex series KK254, 6373	
181	Shelf Alpha	Shelf 6	Molex Mini-Fit Jr. WM1837, WM1841, WM2501,WM-2500,A25555,A1422,WM1783,WM2761,WM3700,WM3600,A1431,A1402,WM1784,WM2772,WM3701,WM3601,WM1848 – 2 and 4 position plugs and receptacles and pins	
182	Shelf Alpha	Shelf 6	Coax crimp, Coax cable; RF modulator for television	
183	Shelf Alpha	Shelf 6	IDC headers, 40 and 50 pin	
184	Shelf Alpha	Shelf 5	Audio ¼ and 1/8; cassette adapter; 1/8 to FM transmitter	
185	Shelf Alpha	Shelf 5	1/8 and ¼ patch cables	
186	Shelf Alpha	Shelf 5	Molex 0.062" pins and shells; WM1002-ND; 02-06-2103-P100	
187	Shelf Alpha	Shelf 5	Molex 0.093" pins and shells; pin part numbers: 02-08-1002-P100; 02-09-1104-P100; 02-09-2103-P100; 02-09-2118-P100	
188	Shelf Alpha	Shelf 5	Command stops for mounting	
189	Shelf Alpha	Shelf 5	Wire wrap; headsets; Plantronics CS520	
190	Shelf Alpha	Shelf 5	Longer grabber	
191	Shelf Alpha	Shelf 5/4 (PILLAR MOUNT)	NiMH Batteries	
192	Shelf Alpha	Shelf 4 – drawers	LIPO Batteries – XT30, XT60, XT90 connectors; 18650 hardware	
193	Shelf Alpha	Shelf 4 – drawers	LIPO /NiMH battery chargers – Adafruit MicroLipo (1904) with microUSB; Seeed Studio Lipo Rider Plus; LC709203F Lipoly battery fuel gage	
194	Shelf Alpha	Shelf 4 – drawers	AC to USB power	
195	Shelf Alpha	Shelf 4 – drawers	Drill bits and cordless drivers; tap and die elements	
196	Shelf Alpha	Shelf 4 – drawers	small spool wire	
197	Shelf Alpha	Shelf 4 – drawers	long driver bits for hex, torx, and phillips, metric and Imperial	
198	Shelf Alpha	Shelf 4 – drawers	USB extension cords	
199	Shelf Alpha	Shelf 4	JST connectors – kits – 1.25mm, 2.0mm, 2.5mm, 2.54mm (0.1")	
200	Shelf Alpha	Shelf 4	JST connectors – loose wire – 1.00mm	
201	Shelf Alpha	Shelf 5	BNC cables and post	
202	Shelf Alpha	Shelf 4	USB exotics	
203	Shelf Alpha	Shelf 4		

204	Shelf Alpha	Shelf 4	USB barcode scanner	
205	Shelf Alpha	Shelf 4 – drawers	Measuring tools/distance; tape measure; ruler; measuring tape -	
206	Shelf Alpha	Shelf 4 – drawers	Magnifiers/Precision Resistors/Digital caliper; PCB ruler (Adafrit) – inspection mirrors – magnetic grabber	
207	Shelf Alpha	Shelf 4 – drawers	Tweezers – Q-tips – Cleaning tips -	
208	Shelf Alpha	Shelf 4 – drawers	Flush cutters	
209	Shelf Alpha	Shelf 4 – drawers	Small wire strippers	
210	Shelf Alpha	Shelf 4 – drawers	Large wire strippers	
211	Shelf Alpha	Shelf 3	USB widgets – cameras – bar code scanners	
212	Shelf Alpha	Shelf 3	USB widgets – sound recorders	
213	Shelf Alpha	Shelf 3	USB widgets – portable scanners	
214	Shelf Alpha	Shelf 3	Breadboard jumpers – Box 1	
215	Shelf Alpha	Shelf 3	Breadboard jumpers – Box 2	
216	Shelf Alpha	Shelf 3	Breadboard jumpers – Box 3	
217	Shelf Alpha	Shelf 3	Breadboards	
218	Shelf Alpha	Shelf 2	5V SSR power relays	
219	Shelf Alpha	Shelf 2	Solid state relays	
220	Shelf Alpha	Shelf 2	5V and 12V fans	
221	Shelf Alpha	Shelf 2	Industrial controls 3	Pressure sensors, 0-30 psia, 0-10 psig, pressure switch, SICK RE11-DA; M8/M12 cables; immersion heater; flow sensors
222	Shelf Alpha	Shelf 2	Industrial controls 4	Industrial counters, meters, timers, time delay relays; Hall sensors 5S140-3H-02-A South Pole 2.7-24V
223	Shelf Alpha	Shelf 2	M8 and M12 cables and connectors – 1	
224	Shelf Alpha	Shelf 2	M8 and M12 cables and connectors – 2	
225	Shelf Alpha	Shelf 2	M8 and M12 cables and connectors – 3	
226	Shelf Alpha	Shelf 2	Speakers	
227	Shelf Alpha	Shelf 1/Floor	VI-B51-02 ; 150V to 12V DC to DC converter	VICOR
228	Shelf Alpha	Shelf 1/Floor	Industrial controls 2	DIN Rail connectors/terminal blocks (Automation Direct and others)
229	Shelf Alpha	Shelf 1/Floor	Industrial controls 1	Large solenoid LEV200A4ANF, solenoids 12VDC, 24VDC
230	Shelf Bravo	Shelf 8	Old multimeters and multimeter parts	
231	Shelf Bravo	Shelf 8	Resistor kits; 0.22 Ohm to 442 Ohm; 44 Ohm to 3.9K; 6.98K to 442K	
232	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged – VARIOUS PIC CHIPS	R1 C1
233	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R1 C2
234	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R1 C3
235	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R1 C4
236	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R1 C5
237	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R1 C6
238	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R1 C7
239	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R1 C8
240	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R2 C1
241	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R2 C2
242	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R2 C3
243	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R2 C4
244	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R2 C5
245	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R2 C6
246	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R2 C7
247	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R2 C8
248	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R3 C1
249	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R3 C2
250	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R3 C3
251	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R3 C4
252	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R3 C5
253	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R3 C6
254	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R3 C7
255	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R3 C8
256	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R4 C1
257	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R4 C2
258	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R4 C3
259	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R4 C4
260	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R4 C5
261	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R4 C6
262	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R4 C7
263	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R4 C8
264	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R5 C1
265	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R5 C2
266	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R5 C3
267	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R5 C4
268	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R5 C5
269	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R5 C6
270	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R5 C7
271	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R5 C8
272	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R6 C1
273	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R6 C2
274	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R6 C3
275	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R6 C4
276	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R6 C5
277	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R6 C6
278	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R6 C7
279	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R6 C8
280	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R7 C1
281	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R7 C2
282	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R7 C3
283	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R7 C4
284	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R7 C5
285	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R7 C6
286	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R7 C7
287	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R7 C8
288	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R8 C1
289	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R8 C2
290	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R8 C3
291	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R8 C4
292	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R8 C5
293	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R8 C6
294	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R8 C7
295	Shelf Bravo	Shelf 8-8x8 drawer unit left	To be cataloged	R8 C8
296	Shelf Bravo	Shelf 7	P13420-ND 12V fans (x50)	
297	Shelf Bravo	Shelf 7	Soldering irons (old)	
298	Shelf Bravo	Shelf 6	Lasers and photodiodes	
299	Shelf Bravo	Shelf 6	XLR and DIN connectors	
300	Shelf Bravo	Shelf 6	1500uF 300V capacitors	
301	Shelf Bravo	Shelf 6	large capacitors – 68000uF 63V; 32000uF 350V; 270000uF 63V	

302	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	WM9154 – Molex 39-00-0078 – 16 AWG crimp Mini-Fit Jr	R1 C1
303	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	Samtec CC79R-2630-01-L - Socket Contact Gold 26-30 AWG Crimp Stamped – for MiniMate	R1 C2
304	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	WM16142-ND – Molex 39-00-0125	R1 C3
305	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	Molex 39-31-0040 – 4 position 2 row 4.2mm	R1 C4
306	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	Molex 39-01-2046 4 position housing	R1 C5
307	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	Molex 39-01-2066 6 position plug 2 row MiniFit Jr	R1 C6
308	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	Molex 39-01-2045 4 pos receptacle	R1 C7
309	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	Molex 39-21-0060 6 pos header	R1 C8
310	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	AMP 4C receptacle 0.093	R2 C1
311	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	AMP 3C plug 0.093	R2 C2
312	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	Adafruit 4936 – 4 pin molex cable 20 cm	R2 C3
313	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	Samtec T1M74-L-02-L CONN PIN 20-24AWG CRIMP GOLD for MiniMate	R2 C4
314	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	Molex connector receptacle WM3701-ND 39-01-2040 – 4 position dual	R2 C5
315	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	Molex connector housing 2 pos w/o ramp WM1575-ND 22-01-2021	R2 C6
316	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	WM-2015 6 position with ramp	R2 C7
317	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	A25347CT-ND conn socket 14-20 AWG	R2 C8
318	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	1-480702-0 – 4 circuit plug	R3 C1
319	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	WM-2503CT-ND conn socket 22-28 AWG	R3 C2
320	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	AMP 3C plug 0.093	R3 C3
321	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	AMP 2C plug T 0.093	R3 C4
322	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	AMP 2C recept T 0.093	R3 C5
323	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	AMP 2C plug 0.093	R3 C6
324	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	AMP 2C recept 0.093	R3 C7
325	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	EMPTY	R3 C8
326	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	AMP 94V 4 position 0.25 350780-1 (AMP-0-0350780-1)	R4 C1
327	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	AMP 94V 3 position 0.25	R4 C2
328	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	AMP 94V 2 position 0.25	R4 C3
329	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	09-50-8033-P 156KK 3 Pos	R4 C4
330	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	EMPTY	R4 C5
331	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	WM-6391 22-20 AWG gold pins	R4 C6
332	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	350705-1 (A1440-ND) Brass/Pre-tin (M) pins	R4 C7
333	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	350705-1 (A1440-ND) Brass/Pre-tin (F) sockets (presumed)	R4 C8
334	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	AMP 4C plug 0.093	R5 C1
335	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	AMP 3C receptacle 0.093	R5 C2
336	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	2C Molex 50-84-2020	R5 C3
337	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	3 conductor Molex 50-84-2030 and 50-84-1030	R5 C4
338	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	4 conductor Molex	R6 C1
339	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	2 conductor Molex (Radio Shack 274-222)	R6 C2
340	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	6 conductor Molex 50-84-2060 and 50-84-1060	R6 C3
341	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	9C Molex 03-09-1091 and Radio Shack 274-239 – Series 1292	R6 C4
342	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	12C Molex 03-09-2121; 03-09-1126; 03-09-2121; Molex 03-09-2092	R7 C1
343	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	Radio Shack 274-232 or WM1320-ND 12 position connector and pins	R7 C2
344	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	WM18434-ND MOLEX 39-01-4030 3 pos vertical	R7 C3
345	Shelf Bravo	Shelf 6 -Mixed unit (4x8 and 3x4)	Molex pins 02-09-2118; 02-06-2132; 02-06-1132	R7 C4
346	Shelf Bravo	Shelf 5-8x8 drawer unit	Switch toggle sealed SPDT CKN1061-ND E101SD1ABE	R1 C1
347	Shelf Bravo	Shelf 5-8x8 drawer unit	02-06-2103 – male term connector 18-24 AWG	R1 C2
348	Shelf Bravo	Shelf 5-8x8 drawer unit	C20S – stamped D-sub socket pins	R1 C3
349	Shelf Bravo	Shelf 5-8x8 drawer unit	T09S7-00; 9 pin female crimp connector	R1 C4
350	Shelf Bravo	Shelf 5-8x8 drawer unit	03HR-4K – HR 3-pin 2.5mm black connector	R1 C5
351	Shelf Bravo	Shelf 5-8x8 drawer unit	100 mil (0.1 in) header/jumper	R1 C6
352	Shelf Bravo	Shelf 5-8x8 drawer unit	WM2555-ND 24-30 AWG 16-02-1109 F terminal	R1 C7
353	Shelf Bravo	Shelf 5-8x8 drawer unit	WM2312 22-30 AWG 08-55-0102 F terminal	R1 C8
354	Shelf Bravo	Shelf 5-8x8 drawer unit	RJ-45 connectors	R2 C1
355	Shelf Bravo	Shelf 5-8x8 drawer unit	CP-1050-ND circular DIN 5-pin	R2 C2
356	Shelf Bravo	Shelf 5-8x8 drawer unit	03-06-2023 2 pos connector plug 0.062	R2 C3
357	Shelf Bravo	Shelf 5-8x8 drawer unit	03-06-2023 2 pos connector plug 0.062	R2 C4
358	Shelf Bravo	Shelf 5-8x8 drawer unit	2POS connector plug	R2 C5
359	Shelf Bravo	Shelf 5-8x8 drawer unit	S-Video connectors female (4 pin)	R2 C6
360	Shelf Bravo	Shelf 5-8x8 drawer unit	53462-0611 – right angle flat firewire connector header WM17300-ND	R2 C7
361	Shelf Bravo	Shelf 5-8x8 drawer unit	WM1837-ND F 20-24 AWG; WM1838-ND F 26-30 AWG	R2 C8
362	Shelf Bravo	Shelf 5-8x8 drawer unit	MHB14K-ND shrouded header 14 pos	R3 C1
363	Shelf Bravo	Shelf 5-8x8 drawer unit	WM2904-ND – 6 pos 0.100" with latch 50-57-9406	R3 C2
364	Shelf Bravo	Shelf 5-8x8 drawer unit	281-1882-ND terminal block PCB 2 POS and 3 POS	R3 C3
365	Shelf Bravo	Shelf 5-8x8 drawer unit	105-0754-001 STC insulated horizontal green connector jack	R3 C4
366	Shelf Bravo	Shelf 5-8x8 drawer unit	Mini DIN recept right angle 6 pin MDJ-004-6P	R3 C5
367	Shelf Bravo	Shelf 5-8x8 drawer unit	EVQ-PUM02K LT switch side with boss J lead SMD	R3 C6
368	Shelf Bravo	Shelf 5-8x8 drawer unit	PJ-003A male power jack open	R3 C7
369	Shelf Bravo	Shelf 5-8x8 drawer unit	S-Video connectors male (6 pin)	R3 C8
370	Shelf Bravo	Shelf 5-8x8 drawer unit	103308-6 LOPRO ST 26-pin 15 Au header connector	R4 C1
371	Shelf Bravo	Shelf 5-8x8 drawer unit	3505-3 ejector connectors long	R4 C2
372	Shelf Bravo	Shelf 5-8x8 drawer unit	SMA plug straight cable mount connector 901-9808	R4 C3
373	Shelf Bravo	Shelf 5-8x8 drawer unit	USB receptacle (USB-A) PCB	R4 C4
374	Shelf Bravo	Shelf 5-8x8 drawer unit	NO_TEC1-100 RJ-11 modular plugs 4C	R4 C5
375	Shelf Bravo	Shelf 5-8x8 drawer unit	RJ11 6-6 flag plug 6C	R4 C6
376	Shelf Bravo	Shelf 5-8x8 drawer unit	WM-1577 4 pos receptacles	R4 C7
377	Shelf Bravo	Shelf 5-8x8 drawer unit	S-video connectors (male) 4-pin	R4 C8
378	Shelf Bravo	Shelf 5-8x8 drawer unit	54142-1440 Connectors SODIMM socket 144 POS	R5 C1
379	Shelf Bravo	Shelf 5-8x8 drawer unit	WM3001-ND 3-pos	R5 C2
380	Shelf Bravo	Shelf 5-8x8 drawer unit	853-93-100-20-001000 right angle socket connector 2x50	R5 C3
381	Shelf Bravo	Shelf 5-8x8 drawer unit	641215-3 vertical header connector 3 pin 30 Au	R5 C4
382	Shelf Bravo	Shelf 5-8x8 drawer unit	BNC plug (misc connector)	R5 C5
383	Shelf Bravo	Shelf 5-8x8 drawer unit	AC plug blades	R5 C6
384	Shelf Bravo	Shelf 5-8x8 drawer unit	DIN 5-pin female PCB Conn	R5 C7
385	Shelf Bravo	Shelf 5-8x8 drawer unit	WM2300-ND 0.156 crimp 08-50-0106	R5 C8
386	Shelf Bravo	Shelf 5-8x8 drawer unit	WM4300 – connector header 2 pos 0.100" right angle	R6 C1
387	Shelf Bravo	Shelf 5-8x8 drawer unit	WM4301 – connector header 3 pos 0.100" right angle	R6 C2
388	Shelf Bravo	Shelf 5-8x8 drawer unit	WM4302 – connector header 4 pos 0.100" right angle	R6 C3
389	Shelf Bravo	Shelf 5-8x8 drawer unit	WM4303 – connector header 5 pos 0.100" right angle	R6 C4
390	Shelf Bravo	Shelf 5-8x8 drawer unit	WM4304 – connector header 6 pos 0.100" right angle	R6 C5
391	Shelf Bravo	Shelf 5-8x8 drawer unit	WM4306 – connector header 8 pos 0.100" right angle	R6 C6
392	Shelf Bravo	Shelf 5-8x8 drawer unit	WM4308 – connector header 10 pos 0.100" right angle	R6 C7
393	Shelf Bravo	Shelf 5-8x8 drawer unit	WM4310 – connector header 12 pos 0.100" right angle	R6 C8
394	Shelf Bravo	Shelf 5-8x8 drawer unit	WM4200 – connector header 2 pos 0.100"	R7 C1
395	Shelf Bravo	Shelf 5-8x8 drawer unit	WM4201 – connector header 3 pos 0.100"	R7 C2
396	Shelf Bravo	Shelf 5-8x8 drawer unit	WM4202 – connector header 4 pos 0.100"	R7 C3
397	Shelf Bravo	Shelf 5-8x8 drawer unit	WM4203 – connector header 5 pos 0.100"	R7 C4
398	Shelf Bravo	Shelf 5-8x8 drawer unit	WM4204 – connector header 6 pos 0.100"	R7 C5
399	Shelf Bravo	Shelf 5-8x8 drawer unit	WM4206 – connector header 8 pos 0.100"	R7 C6
400	Shelf Bravo	Shelf 5-8x8 drawer unit	WM4208 – connector header 10 pos 0.100"	R7 C7
401	Shelf Bravo	Shelf 5-8x8 drawer unit	WM4210 – connector header 12 pos 0.100"	R7 C8
402	Shelf Bravo	Shelf 5-8x8 drawer unit	WM2000 – connector housing 2 pos 0.100"	R8 C1
403	Shelf Bravo	Shelf 5-8x8 drawer unit	WM2001 – connector housing 3 pos 0.100"	R8 C2
404	Shelf Bravo	Shelf 5-8x8 drawer unit	WM2002 – connector housing 4 pos 0.100"	R8 C3

405	Shelf Bravo	Shelf 5-8x8 drawer unit	WM2003 – connector housing 5 pos 0.100"	R8 C4
406	Shelf Bravo	Shelf 5-8x8 drawer unit	WM2004 – connector housing 6 pos 0.100"	R8 C5
407	Shelf Bravo	Shelf 5-8x8 drawer unit	WM2006 – connector housing 8 pos 0.100"	R8 C6
408	Shelf Bravo	Shelf 5-8x8 drawer unit	WM2008 – connector housing 10 pos 0.100"	R8 C7
409	Shelf Bravo	Shelf 5-8x8 drawer unit	WM2010 – connector housing 12 pos 0.100"	R8 C8
410	Shelf Bravo	Shelf 5	Audio 1/4 and 1/8 cables	
411	Shelf Bravo	Shelf 5	Firewire IEEE 1394	
412	Shelf Bravo	Shelf 6	Pomona test leads and parts; banana plugs	
413	Shelf Bravo	Shelf 5	Peltier cooler heaters 24V 30W	
414	Shelf Bravo	Shelf 5	RFID reader	
415	Shelf Bravo	Shelf 5	Cord grips (large)	
416	Shelf Bravo	Shelf 5	Cord grips	
417	Shelf Bravo	Shelf 5	Cord grips	
418	Shelf Bravo	Shelf 5	Cord grips (IP67 – waterproof/washdown)	
419	Shelf Bravo	Shelf 4A	Ipod USB – USB Universal – USB C – USB C downstream adafru.it/4090	
420	Shelf Bravo	Shelf 4A	RFDuino – Arduino power connectors – NRLF24L01 (single-chip radio transceiver that operates in the 2.4 GHz ISM band) for Arduino-Arduino transmission	
421	Shelf Bravo	Shelf 4A	Grove Connectors	
422	Shelf Bravo	Shelf 4A	Level shifters;Stemma connectors; Stemma to JST; Adafruit I2C terminator; Feather Headers; Featherwing breakout; Featherwing 4MB M0 WiFi Ultimate GPS; Featherwing logger; SWD 2x5 breakouts; HELTEC HT1T-WB32; Makey Makey; Sparkfun Thing Plus ESP32; ESP8266 WiFi; Adafruit QtPy SAM21; Adafruit FadeCandy; PIC 10F206; Node ESP32; Sparkfun ATSAM21G R3 breakout; Adafruit ESP8266 Huzzah; ESP32;ATMega328P; ATTINY85; STM32; RedBear Labs MK20 v1.5; ESP8266 SparkFun Blynk	
423	Shelf Bravo	Shelf 4	USB Micro A end	
424	Shelf Bravo	Shelf 4	USB B end	
425	Shelf Bravo	Shelf 4	USB Mini A end	
426	Shelf Bravo	Shelf 4	SENSORS A – SENSORS A – SENSORS A – sensor boards:PCT2075 temperature sensor; VERTER 5V buck-boost; Toggle cap touch AT42QT1012;GT-7U GPS; Adafruit Ultimate GPS breakout V3; VLS3LOX TOP Distance; MLX90393 magnetometer;PCF8523 real time clock (RTC); DS3231 RTC; SparkX serial flash breakout; LSM6DS33 accelerometer and gyro; BNO055 9 DOF accelerometer+gyro+magnetometer; MSA301 3 DOF accelerometer; BMI270 6DOF IMU; Adafruit TLF493D 3D magnetometer; 6 axis gyro (MPU92/65); Gyro/Accelerometer GY-521; flex sensors/FlexiForce and driver boards; BNO008 (9 DOF); VMA301/DS1302 RTC; LM2596 step-down; 805M1-0020 accelerometer single axis 8kHz; DFRobot SEN0295 RP-C18.3LT Thin film pressure sensor; ADXL335 3 axis accelerometer; HASS 50-S SENSOR CURRENT HALL 50A AC/DC; BME280 temp/humidity/pressure I2C/SPI; H3LIS33DL high range accelerometer; BMP388 temperature/pressure sensor; Adafruit Bonsai Buckaroo (for plants)	
427	Shelf Bravo	Shelf 4	SENSORS B – SENSORS B – SENSORS B – sensor boards: HC-SR505 mini PIR sensors; ADXL345 3 axis accelerometer (I2C and SPI); LM386 audio amplifier boards; Catalex touch sensor TTP223B; VMA03 Velleman water sensor; DFPlayer Mini MP3 player; KY-022 IR receiver and KY-005 IR transmitter; LM293 digital IR sensor module (potentiometer sets sensitivity); LIDAR and LIDAR controller getsureal.com V1.2; MDS-40-MK-SR7-U10 magneto-inductive sensor – US5881 hall sensor unipolar – capacitive touch sensor I2C MPR121 (Adafruit adafru.it/1928); OPB606A reflective sensor	
428	Shelf Bravo	Shelf 4	Arduino power connectors	
429	Shelf Bravo	Shelf 4	Arduino-like: Arduino MKR Wifi 1010; Adafruit DC Boarduino; DRF0321 Wido; Flora Neopixel;Adafruit Gemma; Adafruit KB2040; Adafruit Circuit Playground Express; Adafruit Mini-Metal Speaker w/wires; Digispark; Arduino Nano; Arduino Pro Mini; Arduino Pro Mini 5V; Arduino Pro; Adafruit Trinket 5V; Adafruit Trinket 3V; Adafruit Pro Trinket 3V; Adafruit Pro Trinket Li-Ion Backpack; Adafruit Pro Trinket 5V; Biobot Analytics; microDuino; Arduino Pro Mini V2; LCP24; Xpresso v2/rnbed; USB Bitwacker (schmalzhaus.com) – Windows only; Random boards: ATSM21	
430	Shelf Bravo	Shelf 4	Feather/Huzzah/Stemma connectors	
431	Shelf Bravo	Shelf 4	Arduino breakout boards, Arduino Nano breakout boards	
432	Shelf Bravo	Shelf 4	Signal generator board	
433	Shelf Bravo	Shelf 4	Arduino Uno / DuemilenoVe / Arduino DUE (note 3.3V limits)	
434	Shelf Bravo	Shelf 4	PIC Programmer, melabs.com U2 programmer	
435	Shelf Bravo	Shelf 4	SD Readers (USB); also board level SD card reader hardware (SD and microSD)	
436	Shelf Bravo	Shelf 3	24 VDC supplies	
437	Shelf Bravo	Shelf 3	Mixed power supplies	
438	Shelf Bravo	Shelf 3	50 nF 100V capacitors	
439	Shelf Bravo	Shelf 3	1500 uF 300V capacitors	
440	Shelf Bravo	Shelf 2	Variable voltage power supplies	
441	Shelf Bravo	Shelf 2	6V and below power supplies except 5V	
442	Shelf Bravo	Shelf 2	Below 12V and above 6V power supplies	
443	Shelf Bravo	Shelf 2	12V power supplies	
444	Shelf Bravo	Shelf 2	Greater than 24V power supplies	
445	Shelf Bravo	Shelf 2	5V power supplies, mini and micro 5V	
446	Shelf Bravo	Shelf 2	Power supplies greater than 12 V less than 24V	
447	Shelf Bravo	Shelf 1/Floor	Power resistors	
448	Shelf Bravo	Shelf 1/Floor	Power resistors	
449	Shelf Bravo	Shelf 1/Floor	Power resistors	
450	Shelf Bravo	Shelf 1/Floor	Fans, 12V, 24V, 120VAC	
451	Shelf Charlie	Shelf 8	Reels of LEDs; WM3983TR-ND (0480372200) connector plug USB A 4 POS SMD R/A	
452	Shelf Charlie	Shelf 7	12 VDC Fans (50x) P1699-ND	
453	Shelf Charlie	Shelf 7	48V DC 8.3A supplies; 60V DC 6A supplies; 48VDC 10 A DIN rail supply	
454	Shelf Charlie	Shelf 6	Aviation connectors, 2,3,4,6 pin	
455	Shelf Charlie	Shelf 6	Magnet wire – 12, 22, 24, 26, 28, 30, 32 AWG	
456	Shelf Charlie	Shelf 6	Old development boards of various vintages; Stellaris launchpad	
457	Shelf Charlie	Shelf 5	EMPTY BINS	
458	Shelf Charlie	Shelf 5	IDC headers; 10, 16, 20, 26, 34, 40, 50, 60 pin	
459	Shelf Charlie	Shelf 5	SOLDERNG PRACTICE – SURFACE MOUNT BOARDS	
460	Shelf Charlie	Shelf 5	Wire ferrules and crimper	
461	Shelf Charlie	Shelf 5	P-clips and sticky mounts	
462	Shelf Charlie	Shelf 5	Molex modular jacks and plugs, Molex drawers WM-2700 series	
463	Shelf Charlie	Shelf 4	keypads	
464	Shelf Charlie	Shelf 4	AC control from Arduino	
465	Shelf Charlie	Shelf 4	Rubber feet and cable clips, edge protectors	
466	Shelf Charlie	Shelf 4	Basic multimeters (cheap)	
467	Shelf Charlie	Shelf 4	Parallax and Beagle; Boron/Particle IOT; OpenCR; Electron IOT	
468	Shelf Charlie	Shelf 4	PCB mount terminal strips	
469	Shelf Charlie	Shelf 4	USB with free ends	
470	Shelf Charlie	Shelf 4	Battery rechargers for AA/AAA NiMH and NiCd	
471	Shelf Charlie	Shelf 4	Inductors	
472	Shelf Charlie	Shelf 4	Conductive Fabric	
473	Shelf Charlie	Shelf 4	Massive coils	
474	Shelf Charlie	Shelf 4	RS232 and RS485 converters; USB to TTL; USB to CAN; USB to Ethernet; RS-232 to TTL	
475	Shelf Charlie	Shelf 4	Wire ferrules and crimper	
476	Shelf Charlie	Shelf 4	Xacto	
477	Shelf Charlie	Shelf 4	Office supplies, dry erase, pins, post-its	
478	Shelf Charlie	Shelf 4	Resistor and capacitor boxes	
479	Shelf Charlie	Shelf 3	LDT-028K piezo/vibration	
480	Shelf Charlie	Shelf 3	Capacitors < 1 uF	

481	Shelf Charlie	Shelf 4	LED 1 Generic LEDs, FyreWyre / EL Wire / Electroluminescent wire	
482	Shelf Charlie	Shelf 3	LED 2 – Reflectors	
483	Shelf Charlie	Shelf 2	Phoenix contact – small	
484	Shelf Charlie	Shelf 2	Phoenix contact – large	
485	Shelf Charlie	Shelf 2	AC timer (for photography development); turns on AC power for X time with switch closure	
486	Shelf Charlie	Shelf 2	Walabot/Lytro	
487	Shelf Charlie	Shelf 2	Capacitors, 100 uF +	
488	Shelf Charlie	Shelf 2	Shelf brackets – same as ones in Fiber Arts	
489	Shelf Charlie	Shelf 1/Floor	Oscilloscope storage bag; 36 VDC power supplies – 12V/24V/36V/48V/60V power supplies; 24V DIN rail supplies	
490	Corner	Shelf 2 – wire rack	LED 3 – Bipolar LEDs	
491	Corner	Shelf 2 – wire rack	12 V LED strips and LED drivers	
492	Corner	Shelf 2 – wire rack	Arduino based robots	
493	Corner	Shelf 1/Floor	Conductive fabric	
494	Corner	Shelf 1/Floor	Robot tank frame	
495	Corner	Shelf 1/Floor	Dry erase markers	
496	Corner	Shelf 1/Floor	Wireless public address systems	
497	Corner	Shelf 1/Floor	Wood (2x4s)	
498	Corner	Shelf 1/Floor	Silicon single wafers	
499	XYZ Table	Top	XYZ table and laptop to control system	
500	XYZ Table	Top	Arduino based robots	
501	XYZ Table	Bottom	Stepper motor slides	
502	XYZ Table	Bottom	XY Arduino based sensor moving system	
503	XYZ Table	Bottom	CNC and 3D printer control boards – multi-axis stepper motor control	
504	XYZ Table	Bottom	4 channel RC system	
505	XYZ Table	Bottom	Roomba and Roomba power; Infrared Camera for circuit analysis	
506	Rolling Cart	Bottom	PC connected to projector	
507	Rolling Cart	Bottom	Spare keyboard and mouse for general use	
508	Rolling Cart	Bottom	Speaker system for PC	
509	Bookshelf	Top	Cable Wrap	
510	Bookshelf	Top	Air solder system (in box)	
511	Bookshelf	Top-8x8 drawer unit	LVR008S – polyswitch 240VAC 0.0A Hold	R1 C1
512	Bookshelf	Top-8x8 drawer unit	RXE250 – polyswitch RXE 2.50A Hold	R1 C2
513	Bookshelf	Top-8x8 drawer unit	RXE110 – polyswitch RXE 1.10A hold	R1 C3
514	Bookshelf	Top-8x8 drawer unit	RXE020 – polyswitch RXE 0.20A hold	R1 C4
515	Bookshelf	Top-8x8 drawer unit	RXE010 – polyswitch RXE 0.10A hold	R1 C5
516	Bookshelf	Top-8x8 drawer unit	RXE005 – polyswitch RXE 0.05A hold	R1 C6
517	Bookshelf	Top-8x8 drawer unit	LVR012S – polyswitch 240VAC 0.12A hold	R1 C7
518	Bookshelf	Top-8x8 drawer unit	LVR005S – polyswitch 240VAC 0.05A hold	R1 C8
519	Bookshelf	Top-8x8 drawer unit	MC14050BCPG – IC buffer hex non invert 16-DIP	R2 C1
520	Bookshelf	Top-8x8 drawer unit	4017BPC – decade counter/divider with conde converter	R2 C2
521	Bookshelf	Top-8x8 drawer unit	MC14049UBCPG – IC buffer hex inverting 16-DIP	R2 C3
522	Bookshelf	Top-8x8 drawer unit	CM3P-67203L-35 FIFO	R2 C4
523	Bookshelf	Top-8x8 drawer unit	CD4070BCM quad exclusive OR gate	R2 C5
524	Bookshelf	Top-8x8 drawer unit	MA488CSA – RS485/422 transceiver	R2 C6
525	Bookshelf	Top-8x8 drawer unit	EMPTY	R2 C7
526	Bookshelf	Top-8x8 drawer unit	EMPTY	R2 C8
527	Bookshelf	Top-8x8 drawer unit	RF TAG – radiofrequency tag	R3 C1
528	Bookshelf	Top-8x8 drawer unit	MAX202E	R3 C2
529	Bookshelf	Top-8x8 drawer unit	74AS04 – hex inverter	R3 C3
530	Bookshelf	Top-8x8 drawer unit	MAX490CSA – RS485/422 transceiver	R3 C4
531	Bookshelf	Top-8x8 drawer unit	RXM-916-ES – RF Receiver 916MHz 16-pin	R3 C5
532	Bookshelf	Top-8x8 drawer unit	TXM-916-ES – RF Transmitter 916MHz 10-pin	R3 C6
533	Bookshelf	Top-8x8 drawer unit	TR-916-SC-2 RF Transceiver 916MHz 20-pin	R3 C7
534	Bookshelf	Top-8x8 drawer unit	Hex Inverter LSTTL Compatible SN74HCT04N	R3 C8
535	Bookshelf	Top-8x8 drawer unit	SN74LVC1G04DBVR – single inverter gate SOT-23-5	R4 C1
536	Bookshelf	Top-8x8 drawer unit	MAX490CSA – TX/RX RS485/RS422 low power	R4 C2
537	Bookshelf	Top-8x8 drawer unit	MAX3311ECUB RS-232 transceiver	R4 C3
538	Bookshelf	Top-8x8 drawer unit	MAX233CPP – 2DVR/2RCVR RS232 5V 20-DIP	R4 C4
539	Bookshelf	Top-8x8 drawer unit	MAX232ACWE – 2DVR/2RCVR RS232 5V 16-SOIC	R4 C5
540	Bookshelf	Top-8x8 drawer unit	EMPTY	R4 C6
541	Bookshelf	Top-8x8 drawer unit	A-9653-0139-02 Q limit magnet	R4 C7
542	Bookshelf	Top-8x8 drawer unit	EMPTY	R4 C8
543	Bookshelf	Top-8x8 drawer unit	EMPTY	R5 C1
544	Bookshelf	Top-8x8 drawer unit	EMPTY	R5 C2
545	Bookshelf	Top-8x8 drawer unit	EMPTY	R5 C3
546	Bookshelf	Top-8x8 drawer unit	EMPTY	R5 C4
547	Bookshelf	Top-8x8 drawer unit	EMPTY	R5 C5
548	Bookshelf	Top-8x8 drawer unit	EMPTY	R5 C6
549	Bookshelf	Top-8x8 drawer unit	EMPTY	R5 C7
550	Bookshelf	Top-8x8 drawer unit	EMPTY	R5 C8
551	Bookshelf	Top-8x8 drawer unit	138712 – mixed piezo buzzers	R6 C1
552	Bookshelf	Top-8x8 drawer unit	414337-1 SMB jack connector PCB rt angle gold	R6 C2
553	Bookshelf	Top-8x8 drawer unit	EMPTY	R6 C3
554	Bookshelf	Top-8x8 drawer unit	EFB-BD32B21 – 3 terminal ceramic buzzer piezo 12VDC 106dB	R6 C4
555	Bookshelf	Top-8x8 drawer unit	EFB-RD22C415 – 2 terminal ceramic buzzer piezo 15VPP 98dB	R6 C5
556	Bookshelf	Top-8x8 drawer unit	273-065B – 12VDC piezo buzzer	R6 C6
557	Bookshelf	Top-8x8 drawer unit	NC7SZ04M5X – IC inverter single signal SOT-23	R6 C7
558	Bookshelf	Top-8x8 drawer unit	EMPTY	R6 C8
559	Bookshelf	Top-8x8 drawer unit	GF0401M – 8 Ohm 0.2W 40mm round speaker	R7 C1
560	Bookshelf	Top-8x8 drawer unit	M3CA0208 – mic holder WM-52B/54B/55A/56A	R7 C2
561	Bookshelf	Top-8x8 drawer unit	P9949 – microphone cartridge 9.7mmx4.5mm	R7 C3
562	Bookshelf	Top-8x8 drawer unit	414338-1 SMB plug connector PCB right angle	R7 C4
563	Bookshelf	Top-8x8 drawer unit	ADXL203CE dual axis accelerometer 8CLCC (surface mount)	R7 C5
564	Bookshelf	Top-8x8 drawer unit	EMPTY	R7 C6
565	Bookshelf	Top-8x8 drawer unit	MP6802-ND – pressure sensor 15psia SMD	R7 C7
566	Bookshelf	Top-8x8 drawer unit	ISL29003IROZ-T7CT-ND – IC light sensor digital	R7 C8
567	Bookshelf	Top-8x8 drawer unit	PKM25-6A0 – piezo alarm 3-20VDC 6.8kHz +/- 0.7kHz	R8 C1
568	Bookshelf	Top-8x8 drawer unit	WM-R30B – 30mmx30mm flat speaker	R8 C2
569	Bookshelf	Top-8x8 drawer unit	EAS-2P113D – 20mm 7 ohm 0.2W round speaker	R8 C3
570	Bookshelf	Top-8x8 drawer unit	TMP102AIDRLT – IC digital temperature sensor – SOT-6	R8 C4
571	Bookshelf	Top-8x8 drawer unit	ultrasonic transducers	R8 C5
572	Bookshelf	Top-8x8 drawer unit	PKM22EPP-4001 – 2 terminal piezo alarm	R8 C6
573	Bookshelf	Top-8x8 drawer unit	EAF-20R01C – audio transducer 20x12.5mm straight pin	R8 C7
574	Bookshelf	Top-8x8 drawer unit	WM-57A – 57.5mmx56mm flat speaker	R8 C8
575	Bookshelf	Shelf 6	Tape	
576	Bookshelf	Shelf 6	Silicone flex wire – 22, 24, 26,30 AWG	
577	Bookshelf	Shelf 6	Electrical tape	
578	Bookshelf	Shelf 6	Aluminum foil	
579	Bookshelf	Shelf 6	Conductive tape	
580	Bookshelf	Shelf 6	thread and string	
581	Bookshelf	Shelf 6	votive lights (battery powered)	
582	Bookshelf	Shelf 6	Velcro	
583	Bookshelf	Shelf 5	First aid kit (small)	

584	Bookshelf	Shelf 5	First aid kit (small)	
585	Bookshelf	Shelf 5	latex gloves	
586	Bookshelf	Shelf 5	GPS unit	
587	Bookshelf	Shelf 5	Pulse oximeter O2	
588	Bookshelf	Shelf 5	Books	
589	Bookshelf	Shelf 5	Paper bags for votives	
590	Bookshelf	Shelf 5	Books	
591	Bookshelf	Shelf 4	Light pucks	
592	Bookshelf	Shelf 4	EMPTY	
593	Bookshelf	Shelf 4	Books	
594	Bookshelf	Shelf 3	Books	
595	Bookshelf	Shelf 3	Make Magazine	
596	Bookshelf	Shelf 2	Books	
597	Bookshelf	Shelf 2	Glass break sensor and tester	
598	Bookshelf	Shelf 2	Sirens	
599	Bookshelf	Shelf 1	RJ-12 wire and crimper	
600	Bookshelf	Shelf 1	Old phone	
601	Bookshelf	Shelf 1	Books	
602	Bookshelf	Shelf 1	McMaster catalog	
603	Bookshelf	Shelf 1	Allied catalog	
604	Fireproof Cabinet	Middle	Paint for marking E&R components (pink/green)	
605	Fireproof Cabinet	Middle	Isopropyl alcohol	
606	Fireproof Cabinet	Middle	LIPO 603465 3.7V 1300mAH	
607	Fireproof Cabinet	Middle	UN3840 LP552035 350mAH – Li Ion Polymer adafu.it/2750	
608	Fireproof Cabinet	Middle	Polymer Li-ion Rechargeable Battery DTP603450 3.7V 1000mAH	
609	Fireproof Cabinet	Middle	Polymer Li-ion Rechargeable Battery LP503562 3.7V 1200mAH	
610	PrintMonster Bench	Top	Printers	
611	PrintMonster Bench	Top	Pencil sharpeners	
612	PrintMonster Bench	Top	Hole punch	
613	PrintMonster Bench	Top	Staplers	
614	PrintMonster Bench	Top	Pens/Pencils/Scissors	
615	PrintMonster Bench	Top	Architect's scale	
616	PrintMonster Bench	Top	Binder clips	
617	PrintMonster Bench	Top	Screen cleaner, 409 cleaner	
618	PrintMonster Bench	Bottom	Paper, 11x17, 8.5x11	
619	PrintMonster Bench	Bottom	Paper, 8.5x14	
620	PrintMonster Bench	Bottom	DVD-RW, 3.5 inch floppies, DVD reader	
621	PrintMonster Bench	Bottom	floppy reader, 100 MB Zip drive reader	
622	PrintMonster Bench	Bottom	8.5x11 glossy	
623	PrintMonster Bench	Bottom	Staples	
624	PrintMonster Bench	Bottom	Pens, pencils, staples, binder clips, dry erase	
625	PrintMonster Bench	Bottom	Paper clips	
626	PrintMonster Bench	Bottom	Stencil kit	
627	PrintMonster Bench	Side	Computer	
628	PrintMonster Bench	Side	Shredder	
629	Bench Charlie	Top	Drift Bin	
630	Bench Charlie	Top	120/240 VAC power supplies; European plugs	
631	Bench Charlie	Top	AC dongles and Edison AC plugs	
632	Bench Charlie	Top	Heat Shrink	
633	Bench Charlie	Top	Tape	
634	Bench Charlie	Bottom	AC bulbs	
635	Bench Charlie	Bottom	AC power strips	
636	Bench Charlie	Bottom	Industrial contactors	
637	Bench Delta	Top	13.8 VDC 10 Amp power supply	
638	Bench Delta	Top	3-15 VAC variable output	
639	Bench Delta	Top	Variac	
640	Bench Delta	Middle		
641	Bench Delta	Bottom	AC Extension cords	
642	Bench Delta	Bottom	AC cable	
643	Bench Delta	Bottom	UPS (w/o battery)	
644	Bench Delta	Bottom	AC junction box and outlets	
645	Bench Delta	Bottom	heavy gage 12VDC jumper cables	
646	Bench Echo	Top	Benchtop multimeter BK Precision 2891E 4 ½ digits	
647	Bench Echo	Bottom	Car jumper packs and compressors	
648	Bench Echo	Bottom	IEC cables	
649	Bench Foxtrot	Top	Oscilloscopes, spectrum analyzer; 614 Electrometer	
650	Bench Foxtrot	Bottom	Plastic bags and packing material	
651	Bench Foxtrot	Bottom	Signal analyzer (Agilent)	
652	Bench Foxtrot	Bottom	Excess network gear (routers, cable)	
653	Bench Foxtrot	Bottom	Travel box	
654	Bench Foxtrot	Bottom	Thermocouples	
655	Bench Golf	Top	Projector	
656	Bench Golf	Bottom	Coax cable	
657	Bench Golf	Bottom	Travel box	
658	Bench Hotel	Top	Automatic desoldering devices and tools	
659	Bench Hotel	Top	Raspberry Pi Station 3	
660	Bench Hotel	Bottom	Network cables and wireless	
661	Bench Hotel	Bottom	Keyboards and mice	
662	Bench Hotel	Bottom	Old soldering stations	
663	Bench Hotel	Bottom	DB-9 and DB-25 cables; old printer cables	
664	Back Wall Storage	Top – above drawers	Metric hardware; M2, M3, M4, M5; some M2.5	
665	Back Wall Storage	Top – above drawers	Grommets	
666	Back Wall Storage	Top – above drawers	oil-WD40-glue-contact cleaner-vaseline-baking soda	
667	Back Wall Storage	Top – above drawers	Heat shrink wire taps	
668	Back Wall Storage	Top – Left	sheet metal screws – tips – wood screws – large sheet metal – tiny machine screws – screws for plastic – furniture -bolts (1-4) – long bolts – springs – wingnuts – plastic washers – metal washers – nuts – anchors – eye hooks – cotter pins	In green drawer cabinet
669	Back Wall Storage	Top – Left	PC screws – bolts – sheet metal screws – shaft collar – badge clips – 3D inserts – heavy bolts – random parts – PIC nails – clevis pins – vector pins – test points – small washers – test points 2 – tiny nuts – step bolts – furniture pulls – rack mount M6 – OpenBuilds parts – long bolts – brackets	In red drawer cabinet
670	Back Wall Storage	Top	Spade/ring/quick connects; silicon wafer bits (broken)	
671	Back Wall Storage	Top	Vampire connectors	
672	Back Wall Storage	Top	Wireblocks, general	
673	Back Wall Storage	Top	Wireblocks, 2, 3, and 5 pin (Wago)	
674	Back Wall Storage	Top	iPhone Projector; EVA-DRY mini-dehumidifier (plug in to set system up to dry; controls humidity passively)	
675	Back Wall Storage	Top	2mm headers	
676	Back Wall Storage	Top	Twist on	
677	Back Wall Storage	Top 3x3 box	Epoxy	R1 C1
678	Back Wall Storage	Top 3x3 box	Epoxy	R1 C2
679	Back Wall Storage	Top 3x3 box	Gasket maker	R1 C3
680	Back Wall Storage	Top 3x3 box	super glue	R2 C1
681	Back Wall Storage	Top 3x3 box	hot stuff adhesive	R2 C2
682	Back Wall Storage	Top 3x3 box	vacuum grease	R2 C3

683	Back Wall Storage	Top 3x3 box	loctite	R3 C1
684	Back Wall Storage	Top 3x3 box	other greases	R3 C2
685	Back Wall Storage	Top 3x3 box	silicone sealant	R3 C3
686	Back Wall Storage	Top	Dielectric grease – silicon sealant	
687	Back Wall Storage	Top	Grommets, cord grips; WD-40; anti-static; air duster; electronic cleaner	
688	Back Wall Storage	Top 8x8 drawer unit	Probe sleeves for multimeter probes	R1 C1
689	Back Wall Storage	Top 8x8 drawer unit	split key rings	R1 C2
690	Back Wall Storage	Top 8x8 drawer unit	90 DEG Quick connect F	R1 C3
691	Back Wall Storage	Top 8x8 drawer unit	keyrings	R1 C4
692	Back Wall Storage	Top 8x8 drawer unit	#18x5/8 brads	R1 C5
693	Back Wall Storage	Top 8x8 drawer unit	ball bearings	R1 C6
694	Back Wall Storage	Top 8x8 drawer unit	solar cell; 3.5V, 3.8mA in full sun	R1 C7
695	Back Wall Storage	Top 8x8 drawer unit	choke/ferrites	R1 C8
696	Back Wall Storage	Top 8x8 drawer unit	Vampire connectors red	R2 C1
697	Back Wall Storage	Top 8x8 drawer unit	Vampire connectors blue	R2 C2
698	Back Wall Storage	Top 8x8 drawer unit	Vampire connectors yellow	R2 C3
699	Back Wall Storage	Top 8x8 drawer unit	Ring connector bare metal	R2 C4
700	Back Wall Storage	Top 8x8 drawer unit	Assorted small bare ring connectors	R2 C5
701	Back Wall Storage	Top 8x8 drawer unit	Pushbutton latching multipole	R2 C6
702	Back Wall Storage	Top 8x8 drawer unit	Wago mounting carrier (221-505) 5 wire	R2 C7
703	Back Wall Storage	Top 8x8 drawer unit	Wood anchors	R2 C8
704	Back Wall Storage	Top 8x8 drawer unit	Pushbutton momentary	R3 C1
705	Back Wall Storage	Top 8x8 drawer unit	Wire blocks	R3 C2
706	Back Wall Storage	Top 8x8 drawer unit	2 wire block	R3 C3
707	Back Wall Storage	Top 8x8 drawer unit	3 wire block – 4 wire block	R3 C4
708	Back Wall Storage	Top 8x8 drawer unit	5 wire block	R3 C5
709	Back Wall Storage	Top 8x8 drawer unit	Brass solder tip holder	R3 C6
710	Back Wall Storage	Top 8x8 drawer unit	Circuit Stik – instant circuit board	R3 C7
711	Back Wall Storage	Top 8x8 drawer unit	¼" TAB	R3 C8
712	Back Wall Storage	Top 8x8 drawer unit	Odd jack parts – odd connectors	R4 C1
713	Back Wall Storage	Top 8x8 drawer unit	Blue LED SMT	R4 C2
714	Back Wall Storage	Top 8x8 drawer unit	Pan head 6-32 ½" long	R4 C3
715	Back Wall Storage	Top 8x8 drawer unit	10 pin 2x5 1.27mm IC socket – Adafruit part 1675	R4 C4
716	Back Wall Storage	Top 8x8 drawer unit	sample cups – Kibron	R4 C5
717	Back Wall Storage	Top 8x8 drawer unit	Cable mount	R4 C6
718	Back Wall Storage	Top 8x8 drawer unit	Special 2 pole	R4 C7
719	Back Wall Storage	Top 8x8 drawer unit	EMPTY	R4 C8
720	Back Wall Storage	Top 8x8 drawer unit	Red quick connect F w/M extension	R5 C1
721	Back Wall Storage	Top 8x8 drawer unit	Blue quick connect F w/M extension	R5 C2
722	Back Wall Storage	Top 8x8 drawer unit	Yellow quick connect F w/M extension	R5 C3
723	Back Wall Storage	Top 8x8 drawer unit	Red quick connect M	R5 C4
724	Back Wall Storage	Top 8x8 drawer unit	Red quick connect M insulated	R5 C5
725	Back Wall Storage	Top 8x8 drawer unit	Red quick connect F	R5 C6
726	Back Wall Storage	Top 8x8 drawer unit	Red quick connect F insulated	R5 C7
727	Back Wall Storage	Top 8x8 drawer unit	EMPTY	R5 C8
728	Back Wall Storage	Top 8x8 drawer unit	Red butt w/heat shrink; red no-crimp butt	R6 C1
729	Back Wall Storage	Top 8x8 drawer unit	Blue butt w/heat shrink; blue no-crimp butt	R6 C2
730	Back Wall Storage	Top 8x8 drawer unit	Yellow butt w/heat shrink; yellow no-crimp butt	R6 C3
731	Back Wall Storage	Top 8x8 drawer unit	Blue quick connect M w/heat shrink	R6 C4
732	Back Wall Storage	Top 8x8 drawer unit	Blue quick connect M insulated	R6 C5
733	Back Wall Storage	Top 8x8 drawer unit	Blue quick connect F	R6 C6
734	Back Wall Storage	Top 8x8 drawer unit	Blue quick connect F insulated	R6 C7
735	Back Wall Storage	Top 8x8 drawer unit	Blue quick connect F insulated	R6 C8
736	Back Wall Storage	Top 8x8 drawer unit	Red quick connect M w/heat shrink	R7 C1
737	Back Wall Storage	Top 8x8 drawer unit	Blue quick connect M w/heat shrink	R7 C2
738	Back Wall Storage	Top 8x8 drawer unit	Yellow quick connect M w/heat shrink	R7 C3
739	Back Wall Storage	Top 8x8 drawer unit	Yellow quick connect F w/heat shrink	R7 C4
740	Back Wall Storage	Top 8x8 drawer unit	Yellow quick connect M w/heat shrink	R7 C5
741	Back Wall Storage	Top 8x8 drawer unit	Yellow quick connect F	R7 C6
742	Back Wall Storage	Top 8x8 drawer unit	EMPTY	R7 C7
743	Back Wall Storage	Top 8x8 drawer unit	EMPTY	R7 C8
744	Back Wall Storage	Top 8x8 drawer unit	Red ring w/heat shrink	R8 C1
745	Back Wall Storage	Top 8x8 drawer unit	Blue ring w/heat shrink	R8 C2
746	Back Wall Storage	Top 8x8 drawer unit	Yellow ring w/heat shrink	R8 C3
747	Back Wall Storage	Top 8x8 drawer unit	Blue spade w/heat shrink	R8 C4
748	Back Wall Storage	Top 8x8 drawer unit	EMPTY	R8 C5
749	Back Wall Storage	Top 8x8 drawer unit	Join 18-10	R8 C6
750	Back Wall Storage	Top 8x8 drawer unit	Join 22-14	R8 C7
751	Back Wall Storage	Top 8x8 drawer unit	Join 22-14 small	R8 C8
752	Back Wall Storage	Bottom 8x8 drawer unit		R1 C1
753	Back Wall Storage	Bottom 8x8 drawer unit	Blue bullet	R1 C2
754	Back Wall Storage	Bottom 8x8 drawer unit	Yellow bullet	R1 C3
755	Back Wall Storage	Bottom 8x8 drawer unit	Red butt	R1 C4
756	Back Wall Storage	Bottom 8x8 drawer unit	Blue butt	R1 C5
757	Back Wall Storage	Bottom 8x8 drawer unit	Yellow butt	R1 C6
758	Back Wall Storage	Bottom 8x8 drawer unit	tiny butt splices; white no-crimp butt	R1 C7
759	Back Wall Storage	Bottom 8x8 drawer unit	Special tiny connectors; ring and quick connect	R1 C8
760	Back Wall Storage	Bottom 8x8 drawer unit	Red ring	R2 C1
761	Back Wall Storage	Bottom 8x8 drawer unit	Blue ring	R2 C2
762	Back Wall Storage	Bottom 8x8 drawer unit	Blue ring	R2 C3
763	Back Wall Storage	Bottom 8x8 drawer unit	Yellow ring L	R2 C4
764	Back Wall Storage	Bottom 8x8 drawer unit	Yellow ring	R2 C5
765	Back Wall Storage	Bottom 8x8 drawer unit	Big yellow ring	R2 C6
766	Back Wall Storage	Bottom 8x8 drawer unit	Big yellow ring	R2 C7
767	Back Wall Storage	Bottom 8x8 drawer unit	Chrome Quick Connect Female	R2 C8
768	Back Wall Storage	Bottom 8x8 drawer unit	Red 1/8" male quick connect	R3 C1
769	Back Wall Storage	Bottom 8x8 drawer unit	Red 1/8" female quick connect	R3 C2
770	Back Wall Storage	Bottom 8x8 drawer unit	Red 3/16" male quick connect	R3 C3
771	Back Wall Storage	Bottom 8x8 drawer unit	Red 3/16" female quick connect	R3 C4
772	Back Wall Storage	Bottom 8x8 drawer unit	Blue 3/16" male quick connect	R3 C5
773	Back Wall Storage	Bottom 8x8 drawer unit	Blue 3/16" female quick connect	R3 C6
774	Back Wall Storage	Bottom 8x8 drawer unit	Blue half side ring connector	R3 C7
775	Back Wall Storage	Bottom 8x8 drawer unit	Special universal	R3 C8
776	Back Wall Storage	Bottom 8x8 drawer unit	Red spade	R4 C1
777	Back Wall Storage	Bottom 8x8 drawer unit	Red spade	R4 C2
778	Back Wall Storage	Bottom 8x8 drawer unit	Blue spade 1	R4 C3
779	Back Wall Storage	Bottom 8x8 drawer unit	Blue spade 2	R4 C4
780	Back Wall Storage	Bottom 8x8 drawer unit	Blue spade 3	R4 C5
781	Back Wall Storage	Bottom 8x8 drawer unit	Yellow spade	R4 C6
782	Back Wall Storage	Bottom 8x8 drawer unit	plastic washers	R4 C7
783	Back Wall Storage	Bottom 8x8 drawer unit	Plastic washers	R4 C8
784	Back Wall Storage	Bottom 8x8 drawer unit	Extra ring terminals	R5 C1
785	Back Wall Storage	Bottom 8x8 drawer unit	Tiny thru pins	R5 C2
786	Back Wall Storage	Bottom 8x8 drawer unit	AMP male 1-66103-7	R5 C3

787	Back Wall Storage	Bottom 8x8 drawer unit	EMPTY	R5 C4
788	Back Wall Storage	Bottom 8x8 drawer unit	EMPTY	R6 C1
789	Back Wall Storage	Bottom 8x8 drawer unit	2 pin 0.1" male headers	R6 C2
790	Back Wall Storage	Bottom 8x8 drawer unit	606ZZ bearings; ball bearings	R6 C3
791	Back Wall Storage	Bottom 8x8 drawer unit	Red/black spade small	R6 C4
792	Back Wall Storage	Bottom 8x8 drawer unit	3 pin 0.1 male headers	R7 C1
793	Back Wall Storage	Bottom 8x8 drawer unit	3 pin 0.1 male headers	R7 C2
794	Back Wall Storage	Bottom 8x8 drawer unit	Blue ring connectors	R7 C3
795	Back Wall Storage	Bottom 8x8 drawer unit	Silicon wafer bits (P type)	R7 C4
796	Back Wall Storage	Top	Dremel press and Dremel bits	
797	Back Wall Storage	Cubbies	Demo box	R3 C1
798	Back Wall Storage	Cubbies	Standoffs	R2 C1
799	Back Wall Storage	Cubbies	Tiny hardware, medium hardware, insert (3D printing) hardware	R1 C1
800	Back Wall Storage	Cubbies	Circuit Hacking kits; spare CD4017 for kits; 9V and 9V clips for kits	R2 C2
801	Back Wall Storage	Cubbies	MTA 100 connectors and crimping tool	R2 C3
802	Back Wall Storage	Cubbies	Storage bags (snack, sandwich, quart, gallon)	R1 C2
803	Back Wall Storage	Cubbies	Vacuum tubes	R2 C2
804	Back Wall Storage	Cubbies	Heavy soldering tools	R3 C3
805	Back Wall Storage	Cubbies	Additional hardware	R1 C3
806	Back Wall Storage	Cubbies	Wire lugs and crimper	R3 C4
807	Back Wall Storage	Cubbies	Genmitsu ProverXL 4030 – for XYZ table – add-ons; drill/dremel attachment	R2 C4
808	Back Wall Storage	Cubbies	Anderson power pole	R1 C4
809	Back Wall Storage	LEFT HAND SIDE	Step ladder	
810	Back Wall Storage	LEFT HAND SIDE	Spare power strips for tables	
811	Blue Shelf B (Rear Wall)	Shelf 1	Spill mats (in bag) – overflow for COWWCHNT Live network hub; power for Circuit Hacking Night display; air blower and recharger; auto jumper; NiMH NiCd Li-Ion charger;	
812	Blue Shelf B (Rear Wall)	Shelf 2		
813	Blue Shelf B (Rear Wall)	Shelf 3	Parts to be sorted; spare Pomona rack	
814	Blue Shelf B (Rear Wall)	Shelf 3	Demo box; demos for circuit hacking and Hands On Basic Electronics; magnet/coil demo	
815	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	1N4148 SOD-323-2	R1 C1
816	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	1N5395 400V 1.5A	R1 C2
817	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	1N5060TR 400V 2A	R1 C3
818	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	2N4923 NPN 80V 3A 30W	R1 C4
819	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	1N734A Zener 3.9V 0.5W	R1 C5
820	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	2N5087 PNP 50mA 50V	R1 C6
821	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	BC547BG 100mA 50V NPN	R1 C7
822	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	BC548CG 100mV 30V NPN	R1 C8
823	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	1.8pF 200V ceramic; 3.9pF 50V ceramic	R2 C1
824	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	180pF 100V ceramic	R2 C2
825	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	MPSA8599 500mA 80V PNP	R2 C3
826	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	MPS8099 500mA 80V NPN	R2 C4
827	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	MPSA20 NPN	R2 C5
828	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	MPSA18 NPN	R2 C6
829	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	BC558BRL1G 100mA 30V PNP	R2 C7
830	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	BC556BG 100mA 80V PNP	R2 C8
831	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	1500pF 100V ceramic	R3 C1
832	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	0.01uF 50V ceramic	R3 C2
833	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	0.01uF 63V polyester	R3 C3
834	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	100uF 16V electrolytic	R3 C4
835	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	0.01uF 100V polyester	R3 C5
836	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	22uF 50V electrolytic	R3 C6
837	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	6.8uF 100V electrolytic	R3 C7
838	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	NTE100MP germanium matched	R3 C8
839	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	1uF 63V electrolytic	R4 C1
840	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	1uF 250V metal poly	R4 C2
841	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	0.047uF 100V ceramic	R4 C3
842	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	0.068uF 100V ceramic	R4 C4
843	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	0.22uF 100V and 200V	R4 C5
844	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	TOP227Y 3 terminal PWM SW	R4 C6
845	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	TF134 134C fusible link	R4 C7
846	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	Microtemp 167C fusible link	R4 C8
847	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	2.2uF 35V tantalum	R5 C1
848	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	0.47uF 100V polyester; 47uF 100V electrolytic	R5 C2
849	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	220uF 35V electrolytic; 220uF 100V electrolytic	R5 C3
850	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	1000uF 35V electrolytic; 6800uF 63V electrolytic	R5 C4
851	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	10pF 50V and 100V ceramic	R6 C1
852	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	22uF 35V tantalum	R6 C2
853	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	0.015uF 50V ceramic; 0.015uF 2kV polyester	R6 C3
854	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	580uF 35V electrolytic; 560uF 25V electrolytic	R6 C4
855	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	NTE5804 RECT 3A 400V	R7 C1
856	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	2N4920 PNP power 3A 80V; 220uF 63V; 220uF 100V	R7 C2
857	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	2N4923 NPN power 3A 80V; 33uF 50V; 33uF 63V; 56uF 63V	R7 C3
858	Blue Shelf B (Rear Wall)	Shelf 3 -Mixed unit (4x8 and 3x4)	68uF 50V; 68uF 63V; 82uF 50V; 220uF 50V	R7 C4
859	Blue Shelf B (Rear Wall)	Shelf 4	Parts to be sorted; spare Pomona rack	
860	Blue Shelf B (Rear Wall)	Shelf 5	Humidity controller – EMM-6 Electret measuring microphone	
861	Blue Shelf B (Rear Wall)	Shelf 5	Spare monitor; Molex parts	
862	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	0016020103 Conn Socket 22-24 AWG Crimp Gold	R1 C1
863	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	A1436 Conn Pin 24-18 AWG Male Brass	R1 C2
864	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	649457-8 Conn Header Rt Angle 8 Pos 0.100 Tin	R1 C3
865	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	640456-8 CONN HEADER VERT 8 Pos 0.100 Tin	R1 C4
866	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	0444761112 CONN SOCKET 18-20AWG CRIMP TIN	R1 C5
867	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	640389-2 CONN HEADER R/A 2POS 0.156 MM TIN	R1 C6
868	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	22-11-2042 CONN HEADER 4 POS 0.100 VERT GOLD	R2 C1
869	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	640456-4 CONN HEADER VERT 4 POS 0.100 TIN	R2 C2
870	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	1-640456-2 CONN HEADER VERT 12 POS 1.000/2.56MM	R2 C3
871	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	640456-3 CONN HEADER VERT 3 POS 0.100 TIN	R2 C4
872	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	22-11-2032 CONN HEADER 3 POS 0.100 VERT GOLD	R2 C5
873	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	640456-5 CONN HEADER VERT 5 POS 0.100 TIN	R2 C6
874	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	43645-0300 CONN RECEPT 3 POS 3MM SINGLE ROW	R3 C1
875	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	0430251200 CONN RECEPT 12 POS 3MM VERT DUAL	R3 C2
876	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	0050579405 CONN HOUSING 5 POS 0.100 W/LATCH	R3 C3
877	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	0430250800 CONN RECEPT 8 POS 3MM VERT DUAL	R3 C4
878	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	0430250600 CONN RECEPT 6 POS 3MM VERT DUAL	R3 C5
879	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	0430251400 CONN RECEPT 14 POS 3MM VERT DUAL	R3 C6
880	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	0430251600 CONN RECEPT 16 POS 3MM VERT DUAL	R4 C1
881	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	50-57-9003-P CONN RCPT HSG 3 POS 0.100 PITCH	R4 C2
882	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	0430250400 CONN RECEPT 4 POS 3MM VERT DUAL	R4 C3
883	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	39-28-9028 CONN HEADER 2 POS 4.2 MM STR GOLD	R4 C4
884	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	53047-0810 CONN HEADER 8 POS 1.25 MM VERT TIN	R4 C5
885	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	DIVIDERS	R4 C6
886	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	26-61-4060 CONN HEADER 6 POS 0.156 IN VERT GOLD	R5 C1
887	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	08-50-0114 CONN TERM FEMALE 22-30 AWG TIN	R5 C2
888	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	ELVH04100E .150"/3.81MM R/A HDR CLOSED ENDS	R5 C3
889	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	DF12(3.5)-20DP-0.5V(86) CONN HEADER 20 POS 3.5MM SMD 0.5MM	R5 C4

890	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	DF12-20DS-0.5V(86) CONN RECEPT 20 POS 0.5MM GOLD SMD	R5 C5
891	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	70553-0107 CONN HEADER 3 POS 0.100 R/A 30AU	R5 C6
892	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	08-55-0101 CONN TERM FEMALE 22-30 AWG GOLD – PIN/SOCKET	R6 C1
893	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	0430300006 CONN SOCKET 26-30 AWG GOLD CRIMP – PIN/SOCKET	R6 C1
894	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	0444763112 CONN TERM FEMALE 16 AWG TIN CRIMP – PIN/SOCKET	R6 C1
895	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	DF13-2630SCFA CONN SOCKET 26-30 AWG CRIMP GOLD – PIN/SOCKET	R6 C1
896	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	3-641210-2 2-position, right-angle, friction lock MTA-156 header, 30µin gold plating	R6 C2
897	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	640389-4 4-position, right-angle, friction lock MTA-156 header, tin plating	R6 C2
898	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	1-480698-0 2-position, single-row Universal MATE-N-LOK plug housing	R6 C2
899	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	H3BXG-10112-B2 12" (304.8mm) black jumper wire, 22 AWG, pre-crimped DF11 sockets, gold plating	R6 C3
900	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	640385-4 4-position, right-angle, unshrouded MTA-156 header, tin plating	R7 C1
901	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	0010321021 2-position, 5.08mm pitch SPOX wire-to-board vertical header, tin plating	R7 C1
902	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	70553-0110 6-position, 2.54mm pitch SL shrouded right-angle header, gold plating	R7 C1
903	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	640445-3 3-position, vertical, friction lock MTA-156 header, tin plating	R7 C2
904	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	1-640457-2 12-position, right-angle, unshrouded MTA-100 header, tin plating	R7 C3
905	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	5-103956-3 4-position, 2.54mm pitch AMPMODU MTE IDC receptacle housing, tin plating	R7 C3
906	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	3-640426-8 8-position, 3.96mm pitch MTA-156 IDC receptacle assembly (18 AWG), tin plating	R8 C1
907	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	270-1392 Radio Shack (Vector Electronics T42-1) Push-In Terminals For 0.042" holes	R8 C1
908	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	1-480701-0 3-position, single-row Universal MATE-N-LOK cap (receptacle) housing	R8 C2
909	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	1-480702-0 4-position, single-row Universal MATE-N-LOK plug housing	R8 C2
910	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	350706-1 Universal MATE-N-LOK split pin crimp terminal, 24-18 AWG, tin plating	R8 C3
911	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	770146-1 .093" Commercial Pin and Socket crimp terminal, 24-18 AWG, tin plating	R8 C3
912	Blue Shelf B (Rear Wall)	Shelf 5 – Mixed unit (5x6 and 3x3)	1971783-2-06-W9 6" (152.4mm) white jumper wire, 18 AWG, pre-crimped Power Triple Lock socket, tin plating	R8 C3
913	COWWCHNT	Above	Wireless baby monitor (can be web enabled); GoPro battery charger	
914	COWWCHNT	Above	Measurement tools, air speed, weight Ph	
915	COWWCHNT	Above	Measurement tools, compass, time	
916	COWWCHNT	Above	Temperature measurement tools	
917	COWWCHNT	Above	USB Borescope	
918	COWWCHNT	Above	USB webcams; wireless babycam	
919	COWWCHNT	Above	Radar detector, washing machine control boards	
920	COWWCHNT	Above	USB data acquisition; analog meters, digital panel meters; current transducers 0-5V from 0-10 Amps AC – JC10F-010-V; Phoenix Contact MCR-SL-CUC-200-U; 0-200A; 0-10V output with 20-30 VDC power supply	
921	COWWCHNT	Back Side	Tripod with USB camera	
922	COWWCHNT	Back Side	Tripod for posters	
923	COWWCHNT	Back Side	Projection screens	
924	COWWCHNT	Front Side	DIN cables	
925	COWWCHNT	Front Side	RCA converters	
926	COWWCHNT	Front Side	Firewire	
927	COWWCHNT	Front Side	ATA Serial hard drive cables	
928	COWWCHNT	Front Side	DIN converters	
929	COWWCHNT	Front Side	Display port adapters	
930	COWWCHNT	Front Side	VGA adapters, USB C,	
931	COWWCHNT	Front Side	DVI cable	
932	COWWCHNT	Front Side	DVI to VGA	
933	COWWCHNT	Front Side	exotic video; optical cable	
934	COWWCHNT	Front Side	Nikon to RCA	
935	COWWCHNT	Front Side	DB9 to RJ11	
936	COWWCHNT	Front Side	DIN cable (small)	
937	COWWCHNT	Front Side	RJ-11	
938	COWWCHNT	Front Side	Wire	
939	COWWCHNT	Front Side	E-SATA cable	
940	COWWCHNT	Front Side	VGA Cable	
941	COWWCHNT	Front Side	DB25 cable/parallel port	
942	Bench Indigo	Top	Network gear	
943	Bench Indigo	Top	Speakers, PC microphones (1/8" jack)	
944	Bench Indigo	Top	Powered speakers	
945	Bench Indigo	Top	PC Speakers	
946	Bench Indigo	Middle	AMScope microscope with USB camera; film projector	
947	Bench Indigo	Middle	Ubuntu PC	
948	Bench Indigo	Bottom	Pneumatics; Hobbybots 3V110-06	
949	Bench Indigo	Bottom	Tygon tubing	
950	Bench Indigo	Bottom	Pneumatic gages	
951	Bench Indigo	Bottom	Pneumatic pumps, AC Air blower	
952	Bench Indigo	Bottom	Thin plastic tubing	
953	Bench Indigo	Bottom	Larger stepper motors	
954	Bench Indigo	Bottom	AC Rope Lights	
955	Bench Indigo	Bottom Right	Pneumatic valves, pumps, and actuators; solenoid valves	
956	Bench Juliet	Top	Multimeters for classes; multimeters (four port) TEN LABELED 1-10	
957	Bench Juliet	Top	current clamps and probes; AC line splitters; back probes	
958	Bench Juliet	Top	Component testers; USB test / USB testing widgets; servo tester; capacitance/inductance meter, Behringer CT100 professional 6-in-1 cable tester	
959	Bench Juliet	Top	TM-902C temperature probes (K-type) -50C to 1300C (2)	
960	Bench Juliet	Top	LCR tester; scientific calculator (TI-30Xa)	
961	Bench Juliet	Top	Engraving tool	
962	Bench Juliet	Top	light box, head wearable magnifier	
963	Bench Juliet	Top	Raspberry Pi Station 2	
964	Bench Juliet	Top	Windows PC; Neat NM-1000 USB portable paper scanner	
965	Bench Juliet	Top	simple function generators XR2206 square/sine/triangle	
966	Bench Juliet	Bottom	Power resistors	
967	Bench Juliet	Bottom	DB9 parts	
968	Bench Juliet	Bottom	Thermocouples and temperature controllers; RTD Pt100; temperature indicators (50C hot yes/no; 90C-120C stickers)	
969	Bench Kilo	Top-8x8 drawer unit Col A	SD103C-TR Diode Schottky 20V DO-35	R1 C1
970	Bench Kilo	Top-8x8 drawer unit Col A	MMBT3904 – NPN – general purpose -40V 0.2A – SOT-23	R1 C2
971	Bench Kilo	Top-8x8 drawer unit Col A	TSMF3700 – Vishay IR emitter 160mW	R1 C3
972	Bench Kilo	Top-8x8 drawer unit Col A	TSML3710 – Vishay IR emitter 170mW	R1 C4
973	Bench Kilo	Top-8x8 drawer unit Col A	TSOP5700 Vishay IR Mod 455kHz	R1 C5
974	Bench Kilo	Top-8x8 drawer unit Col A	TAOS TSL230 light to frequency programmable	R1 C6
975	Bench Kilo	Top-8x8 drawer unit Col A	PD100MCOMP – photodiode IR 820nm side looking	R1 C7
976	Bench Kilo	Top-8x8 drawer unit Col A	SAA1101T Philips video sync generators	R1 C8
977	Bench Kilo	Top-8x8 drawer unit Col A	CD4044 – IC quad NAND R/S Latch 16-DIP	R2 C1
978	Bench Kilo	Top-8x8 drawer unit Col A	CE4046BCM – IC lock loop phase MPWR – 16-DIP	R2 C2
979	Bench Kilo	Top-8x8 drawer unit Col A	IR2301 High and low driver SOIC	R2 C3
980	Bench Kilo	Top-8x8 drawer unit Col A	BC846B-7-F NPN 65V SOT-23	R2 C4
981	Bench Kilo	Top-8x8 drawer unit Col A	STS6NF20V – MOSFET N-CH 20V 6A SOIC	R2 C5
982	Bench Kilo	Top-8x8 drawer unit Col A	SMAZ24-TP Diode Zener 24V 1A DO214AC	R2 C6
983	Bench Kilo	Top-8x8 drawer unit Col A	V30100S-E34W diode Schottky 30A 100V TO-220	R2 C7
984	Bench Kilo	Top-8x8 drawer unit Col A	TR-916-SC-PA – Transceiver RF 916 MHz 1/2-Duplex	R2 C8
985	Bench Kilo	Top-8x8 drawer unit Col A	PSMN070-200B NPN FET SOT-404	R3 C1

986	Bench Kilo	Top-8x8 drawer unit Col A	PSMN130-200D NPN FET SOT-428	R3 C2
987	Bench Kilo	Top-8x8 drawer unit Col A	ADG601BRTZ – IC Switch SPST SOT23-6	R3 C3
988	Bench Kilo	Top-8x8 drawer unit Col A	BA17805T – IC regulator 3 pin 5V TO220FP	R3 C4
989	Bench Kilo	Top-8x8 drawer unit Col A	LIS3LV02DL – 3 axis accelerometer 16-LGA	R3 C5
990	Bench Kilo	Top-8x8 drawer unit Col A	74HTC154 – high speed 4 to 16 decoder and multiplexer	R3 C6
991	Bench Kilo	Top-8x8 drawer unit Col A	LP311D – IC Diff comparator 8-SOIC	R3 C7
992	Bench Kilo	Top-8x8 drawer unit Col A	LM35DZ – IC sensor – temperature TO-92	R3 C8
993	Bench Kilo	Top-8x8 drawer unit Col A	LM3404HVMA – IC Reg CC BUCK 1A 6-75V 8-SOIC	R4 C1
994	Bench Kilo	Top-8x8 drawer unit Col A	LT1006S8 – IC precision op amp 5V single 8-SOIC	R4 C2
995	Bench Kilo	Top-8x8 drawer unit Col A	BZX8416 ZENER 16V SOT23	R4 C3
996	Bench Kilo	Top-8x8 drawer unit Col A	STR2550 – TRANS PNP 500V 0.5A SOT-23-3	R4 C4
997	Bench Kilo	Top-8x8 drawer unit Col A	KSP44TA – TRANS NPN 400V 0.3A TO-92-3	R4 C5
998	Bench Kilo	Top-8x8 drawer unit Col A	FDS6162N7 – MOSFET N-CH 20V 23A	R4 C6
999	Bench Kilo	Top-8x8 drawer unit Col A	22R224C – Inductor – radial 220uH 0.43A	R4 C7
1000	Bench Kilo	Top-8x8 drawer unit Col A	L78M05CDT-TR – IC regulator Post 5V DPAK	R4 C8
1001	Bench Kilo	Top-8x8 drawer unit Col A	LF356 JFET op amp – SOIC	R5 C1
1002	Bench Kilo	Top-8x8 drawer unit Col A	SN74ACT1284DW	R5 C2
1003	Bench Kilo	Top-8x8 drawer unit Col A	DS26C32ATM	R5 C3
1004	Bench Kilo	Top-8x8 drawer unit Col A	1SMB5918B73 Zener Diode 3W 5.1V SMB	R5 C4
1005	Bench Kilo	Top-8x8 drawer unit Col A	TC03C100A – trimmer capacitor 10pF	R5 C5
1006	Bench Kilo	Top-8x8 drawer unit Col A	712800320210 – trimmer capacitor 20pF	R5 C6
1007	Bench Kilo	Top-8x8 drawer unit Col A	1210 inductor 27nH to 56nH	R5 C7
1008	Bench Kilo	Top-8x8 drawer unit Col A	trimmer capacitor 30pF	R5 C8
1009	Bench Kilo	Top-8x8 drawer unit Col A	LM2907-8 frequency to voltage converter 8-SOIC	R6 C1
1010	Bench Kilo	Top-8x8 drawer unit Col A	ZXCL330E5TA – IC Reg LDO micropower 3.3V SOT23-5	R6 C2
1011	Bench Kilo	Top-8x8 drawer unit Col A	1SMB5943B73G – zener diode 56V 3W SMB	R6 C3
1012	Bench Kilo	Top-8x8 drawer unit Col A	Resistor 6.8 1/2W SMD 5%	R6 C4
1013	Bench Kilo	Top-8x8 drawer unit Col A	FDC6312P – Mosfet P-Ch Dual 20V SSOT-6	R6 C5
1014	Bench Kilo	Top-8x8 drawer unit Col A	RMLM2502TRPBF – Mosfet N-Ch 20V 4.2A SOT-23	R6 C6
1015	Bench Kilo	Top-8x8 drawer unit Col A	SHT15 – humidity sensor	R6 C7
1016	Bench Kilo	Top-8x8 drawer unit Col A	710600090000 – Ferrite core 2010	R6 C8
1017	Bench Kilo	Top-8x8 drawer unit Col A	LM2936M-5.0 – 5V regulator	R7 C1
1018	Bench Kilo	Top-8x8 drawer unit Col A	LT1521CST-3.3 – LDO 3.3V regulator with shutdown SOT223	R7 C2
1019	Bench Kilo	Top-8x8 drawer unit Col A	LM317LM – 3 term adjustable regulator 8-SOIC	R7 C3
1020	Bench Kilo	Top-8x8 drawer unit Col A	SR0365G – Supertex 120AC to 3VDC	R7 C4
1021	Bench Kilo	Top-8x8 drawer unit Col A	LP2985IM5-3.6 – Regulator LDO micropower 150mA 3.6V	R7 C5
1022	Bench Kilo	Top-8x8 drawer unit Col A	ZR78L033GTA – voltage regulator 200mA 3.3V SOT-223 SMD	R7 C6
1023	Bench Kilo	Top-8x8 drawer unit Col A	LTC1983E56-5 charge pump reg inv 3V SOT23-6	R7 C7
1024	Bench Kilo	Top-8x8 drawer unit Col A	LT1175CST-5 LDO reg negative 5V 500mA	R7 C8
1025	Bench Kilo	Top-8x8 drawer unit Col A	LM2397IMP-5.0 5V 400mA positive regulator	R8 C1
1026	Bench Kilo	Top-8x8 drawer unit Col A	UA78M33CDCYR – positive voltage regulator FX 3.3V	R8 C2
1027	Bench Kilo	Top-8x8 drawer unit Col A	SR036MG – inductorless dual output offline regular MSOP-8	R8 C3
1028	Bench Kilo	Top-8x8 drawer unit Col A	SN75189D – quad line receiver 14-SOP	R8 C4
1029	Bench Kilo	Top-8x8 drawer unit Col A	SR037MG – inductorless dual output offline regulator MSOP-8	R8 C5
1030	Bench Kilo	Top-8x8 drawer unit Col A	MCP 6002T-1/5N IC OPAMP 1MHz RRO	R8 C6
1031	Bench Kilo	Top-8x8 drawer unit Col A	SN75188D – quad line driver 14-SOP	R8 C7
1032	Bench Kilo	Top-8x8 drawer unit Col A	CL1N8 – constant current LED driver	R8 C8
1033	Bench Kilo	Top – between Col A/ColB	antistatic foam	
1034	Bench Kilo	Top – between Col A/ColB	RF Ferrite sheet 4.724"x4.724" 38M501AA1212	
1035	Bench Kilo	Top-8x8 drawer unit Col B	33pF – 0603	R1 C1
1036	Bench Kilo	Top-8x8 drawer unit Col B	15pF – 0603	R1 C2
1037	Bench Kilo	Top-8x8 drawer unit Col B	18pF – 0805	R1 C3
1038	Bench Kilo	Top-8x8 drawer unit Col B	12pF – 0805	R1 C4
1039	Bench Kilo	Top-8x8 drawer unit Col B	15pF – 0805	R1 C5
1040	Bench Kilo	Top-8x8 drawer unit Col B	2nF – 0805 – 50V	R1 C6
1041	Bench Kilo	Top-8x8 drawer unit Col B	100nF 50V 0603	R1 C7
1042	Bench Kilo	Top-8x8 drawer unit Col B	33nF – 0603 – 50V	R1 C8
1043	Bench Kilo	Top-8x8 drawer unit Col B	Ferrite pot cores	R2 C1
1044	Bench Kilo	Top-8x8 drawer unit Col B	Hi-Mu CH172128 – CH102125 u=125	R2 C2
1045	Bench Kilo	Top-8x8 drawer unit Col B	Hi-Mu CH229125 – CH203125 u=125	R2 C3
1046	Bench Kilo	Top-8x8 drawer unit Col B	Sendust CS102125 – CS172125	R2 C4
1047	Bench Kilo	Top-8x8 drawer unit Col B	Sendust CS224125 – CS 203125	R2 C5
1048	Bench Kilo	Top-8x8 drawer unit Col B	220pF – 0603	R2 C6
1049	Bench Kilo	Top-8x8 drawer unit Col B	30 pF 0805	R2 C7
1050	Bench Kilo	Top-8x8 drawer unit Col B	27pF 0805	R2 C8
1051	Bench Kilo	Top-8x8 drawer unit Col B	Misc Ferrites	R3 C1
1052	Bench Kilo	Top-8x8 drawer unit Col B	Ferrite pot cores	R3 C2
1053	Bench Kilo	Top-8x8 drawer unit Col B	MCP6041T-1/OT IC opamp 1uA 1.4V single rail	R3 C3
1054	Bench Kilo	Top-8x8 drawer unit Col B	MCP6022-1/5N IC opamp 2.5V dual	R3 C4
1055	Bench Kilo	Top-8x8 drawer unit Col B	OPA 211AIDGKT IC opamp 80MHz signal	R3 C5
1056	Bench Kilo	Top-8x8 drawer unit Col B	LM78M12ACDT-TR – IC Regulator 12V precision 500mA DPAK	R3 C6
1057	Bench Kilo	Top-8x8 drawer unit Col B	IRU1010-33CY – LDO regulator 3.3V 1.0A SOT-223	R3 C7
1058	Bench Kilo	Top-8x8 drawer unit Col B	IRU1010-18CY-ND – LDO regulator 1.8V 1.0A SOT-223	R3 C8
1059	Bench Kilo	Top-8x8 drawer unit Col B	ATF-551M4 E-PHEMT Pseudomorphic HEMT	R4 C1
1060	Bench Kilo	Top-8x8 drawer unit Col B	LM92CIM-ND – IC sensor therm comp dig 8-SOIC	R4 C2
1061	Bench Kilo	Top-8x8 drawer unit Col B	SN75C322DWR RS-232 line driver/receiver 20-SOIC	R4 C3
1062	Bench Kilo	Top-8x8 drawer unit Col B	LMH6559MANOPB – IC buffer H/S closed loop 8-SOIC	R4 C4
1063	Bench Kilo	Top-8x8 drawer unit Col B	100u 6.3V X5R 1210	R4 C5
1064	Bench Kilo	Top-8x8 drawer unit Col B	33000pF 16V 0805	R4 C6
1065	Bench Kilo	Top-8x8 drawer unit Col B	ADF410 76Hz synth	R4 C7
1066	Bench Kilo	Top-8x8 drawer unit Col B	AD8310 AM DEMOO	R4 C8
1067	Bench Kilo	Top-8x8 drawer unit Col B	L78L05ACD13TR – IC regulator LDO 5V 0.1A 8SO	R5 C1
1068	Bench Kilo	Top-8x8 drawer unit Col B	ZXCT1009FTA – IC simple current monitor	R5 C2
1069	Bench Kilo	Top-8x8 drawer unit Col B	LM317-KTTR IC regulator positive adj 1.5A DDPAK	R5 C3
1070	Bench Kilo	Top-8x8 drawer unit Col B	47uF 6.3V X5R 1210	R5 C4
1071	Bench Kilo	Top-8x8 drawer unit Col B	LT1086CM-3.3 – ultralow drop regulator 3.3V 1.5A	R5 C5
1072	Bench Kilo	Top-8x8 drawer unit Col B	Zener 9.1V SOT-23	R5 C6
1073	Bench Kilo	Top-8x8 drawer unit Col B	BAV235 diode pair	R5 C7
1074	Bench Kilo	Top-8x8 drawer unit Col B	LT3080EST – IC regulator LDO adju 1.1A SOT223	R5 C8
1075	Bench Kilo	Top-8x8 drawer unit Col B	ZXCT1010E5TA – IC enhanced offset current monitor SOT23	R6 C1
1076	Bench Kilo	Top-8x8 drawer unit Col B	TPS71533DCKR 3.3V Hi-In LDO voltage regulator	R6 C2
1077	Bench Kilo	Top-8x8 drawer unit Col B	LM78L05ACM voltage regulator 5V 100mA	R6 C3
1078	Bench Kilo	Top-8x8 drawer unit Col B	LM78L12ACM voltage regulator 12V 100mA	R6 C4
1079	Bench Kilo	Top-8x8 drawer unit Col B	LM358	R6 C5
1080	Bench Kilo	Top-8x8 drawer unit Col B	MCP6042 dual opamp	R6 C6
1081	Bench Kilo	Top-8x8 drawer unit Col B	MCP1700 3.3V regulator	R6 C7
1082	Bench Kilo	Top-8x8 drawer unit Col B	TL331 comparator	R6 C8
1083	Bench Kilo	Top-8x8 drawer unit Col B	ANT 2.4-CW-RCS – Antenna 2.4GH right angle ¼ wave whip	R7 C1
			Misc SMA: Taoglas PC104 Penta band cellular antenna 164.9mm Φ1.37 coaxial cable with IPEX connector, ANT-STUBR-433SM 433MHz whip antenna RA SMA 42mm	R7 C2
1084	Bench Kilo	Top-8x8 drawer unit Col B		R7 C3
1085	Bench Kilo	Top-8x8 drawer unit Col B	LM2936MP-3.3 regulator ultra low power 50mA 3.3V	R7 C4
1086	Bench Kilo	Top-8x8 drawer unit Col B	MC7805-BD-TRKG – IC regulator 5V 1A SMD	R7 C5
1087	Bench Kilo	Top-8x8 drawer unit Col B	UA78M05CDCYR – regulator 500mA 5V fixed	R7 C6
1088	Bench Kilo	Top-8x8 drawer unit Col B	CC2420 – ZigBee-ready RF Transceiver	R7 C8

1089	Bench Kilo	Top-8x8 drawer unit Col B	Right angle LEDs – 0805 green	R7 C7
1090	Bench Kilo	Top-8x8 drawer unit Col B	RP-SMA end – CONREVSM003.062 – card edge mount	R7 C8
1091	Bench Kilo	Top-8x8 drawer unit Col B	A761/LR-44 coin cell	R8 C1
1092	Bench Kilo	Top-8x8 drawer unit Col B	LM317S SMD voltage regulator adjustable	R8 C2
1093	Bench Kilo	Top-8x8 drawer unit Col B	UA78L05ACD 5V 100mA regulator	R8 C3
1094	Bench Kilo	Top-8x8 drawer unit Col B	LM79L05ACM -5V 100mA regulator (negative voltage)	R8 C4
1095	Bench Kilo	Top-8x8 drawer unit Col B	LM79L12ACM -12V 100mA regulator (negative voltage)	R8 C5
1096	Bench Kilo	Top-8x8 drawer unit Col B	ERJ-8GEYJ121V 120 Ohm 1/4W 5% 1206 SMD	R8 C6
1097	Bench Kilo	Top-8x8 drawer unit Col B	ERJ-8GEYJ151V 150 Ohm 1/4W 5% 1206 SMD	R8 C7
1098	Bench Kilo	Top-8x8 drawer unit Col B	RC0805FR-07590RL resistor 590 Ohm 1/8W 0805	R8 C8
1099	Bench Kilo	Top-CAPACITOR BOOKS	0.5pF-0.01uF capacitors 100V 0603	
1100	Bench Kilo	Top-CAPACITOR BOOKS	0.1-1000pF capacitors 25-50V 0201	
1101	Bench Kilo	Top-CAPACITOR BOOKS	0.1-1000pF capacitors 50V 0402	
1102	Bench Kilo	Top-CAPACITOR BOOKS	0.1-47pF capacitors 50V 1005M/0402	
1103	Bench Kilo	Top-CAPACITOR BOOKS	0.1-47pF capacitors 250V 0603	
1104	Bench Kilo	Top-CAPACITOR BOOKS	5.1-47pF capacitors 50V 0402	
1105	Bench Kilo	Top-8x8 drawer unit Col C	ECJ-2VC1H102J 1000pF 50V ceramic capacitor 0805	R1 C1
1106	Bench Kilo	Top-8x8 drawer unit Col C	251R14S120GV4T 12pF 250V ceramic capacitor 0805	R1 C2
1107	Bench Kilo	Top-8x8 drawer unit Col C	PCC101CGCT capacitor 100pF 50V ceramic 0805	R1 C3
1108	Bench Kilo	Top-8x8 drawer unit Col C	CC0805JRNPOBN150 15pF 50V ceramic capacitor 0805	R1 C4
1109	Bench Kilo	Top-8x8 drawer unit Col C	SR211A180JAA 18pF 100V 5% mono ceramic capacitor – radial	R1 C5
1110	Bench Kilo	Top-8x8 drawer unit Col C	251R14S200GV4T 20pF 250V ceramic capacitor 0603	R1 C6
1111	Bench Kilo	Top-8x8 drawer unit Col C	GRM2165C1H222JA01D 2200pF 50V 5% 0805	R1 C7
1112	Bench Kilo	Top-8x8 drawer unit Col C	0805N120J500NT – 12pF 40V NPO Ceramic cap 0805	R1 C8
1113	Bench Kilo	Top-8x8 drawer unit Col C	ECU-V1H1050CCV 5pF 50V ceramic capacitor 0603	R2 C1
1114	Bench Kilo	Top-8x8 drawer unit Col C	ECJ-1VC2A101J 100pF 100V NPO ceramic capacitor 0603	R2 C2
1115	Bench Kilo	Top-8x8 drawer unit Col C	PCC050CVCT-ND capacitor 5pF 50V 0603	R2 C3
1116	Bench Kilo	Top-8x8 drawer unit Col C	C3225V5V1C226Z capacitor 22uF 16V 1210	R2 C4
1117	Bench Kilo	Top-8x8 drawer unit Col C	251R14S300GV4T capacitor 30pF 250V 0603	R2 C5
1118	Bench Kilo	Top-8x8 drawer unit Col C	VJ0805A180JXACW1BC 18pF 50V NPO capacitor 0805	R2 C6
1119	Bench Kilo	Top-8x8 drawer unit Col C	0805N180J500NT 18pF 50V NPO ceramic capacitor 0805	R2 C7
1120	Bench Kilo	Top-8x8 drawer unit Col C	PC1898CT capacitor 2.2uF 16V 1206	R2 C8
1121	Bench Kilo	Top-8x8 drawer unit Col C	ceramic capacitor 100pF 50V 0805	R3 C1
1122	Bench Kilo	Top-8x8 drawer unit Col C	ceramic capacitor 12pF 250V 0603	R3 C2
1123	Bench Kilo	Top-8x8 drawer unit Col C	ceramic capacitor 10000pF 16V X7R 0603	R3 C3
1124	Bench Kilo	Top-8x8 drawer unit Col C	ceramic capacitor 1000pF 50V 0402	R3 C4
1125	Bench Kilo	Top-8x8 drawer unit Col C	ceramic capacitor 33000pF 16V X7R 0603	R3 C5
1126	Bench Kilo	Top-8x8 drawer unit Col C	ceramic capacitor 0.15uF 50V 0805	R3 C6
1127	Bench Kilo	Top-8x8 drawer unit Col C	ceramic capacitor 10uF 16V X7R 0603	R3 C7
1128	Bench Kilo	Top-8x8 drawer unit Col C	GKG70015 15-70pF trim cap through hole	R3 C8
1129	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 1uF 1206 unknown voltage	R4 C1
1130	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 10uF 10V SMD	R4 C2
1131	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 1uF 50V 0805	R4 C3
1132	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 1uF 35V tantalum radial (through hole)	R4 C4
1133	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 10uF 4V X5R 0603	R4 C5
1134	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 10uF 16V Y5V 1210	R4 C6
1135	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 100uF 16V SMD	R4 C7
1136	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 22uF 10V SMD	R4 C8
1137	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 15uF 35V tantalum SMD	R5 C1
1138	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 22uF 25V tantalum SMD	R5 C2
1139	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 10uF 35V tantalum SMD	R5 C3
1140	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 22uF 25V tantalum SMD	R5 C4
1141	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 0.01uF 630V X7R 1206 SMD	R5 C5
1142	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 1uF 35V Y5V tantalum SMD	R5 C6
1143	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 22uF 20V tantalum SMD	R5 C7
1144	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 1uF 16V Y5V ceramic 0805	R5 C8
1145	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 1uF 16V 0805	R6 C1
1146	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 10uF 10V X5R 0805	R6 C2
1147	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 0.22uF 25V X7R 0805	R6 C3
1148	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 4.7uF 25V 0805	R6 C4
1149	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 2.2uF 25V X5R 0805	R6 C5
1150	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 1000pF 50V X7R 0603	R6 C6
1151	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 22pF 100V 0805	R6 C7
1152	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 0.68uF 25V 1206	R6 C8
1153	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 47uF 10V 10% X5R 1210	R7 C1
1154	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 6800pF 50V 0805, 6800pF 16V 0805	R7 C2
1155	Bench Kilo	Top-8x8 drawer unit Col C	capacitor LYTH SMD 22uF 50V	R7 C3
1156	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 4.7uF 10V SMD	R7 C4
1157	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 10uF 4V X5R 0603	R7 C5
1158	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 100uF 6.3V SMD 1812; 100uF 35V SMD	R7 C6
1159	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 1uF 6.3V X5R 0603	R7 C7
1160	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 1uF 10V X7R 0805	R7 C8
1161	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 22uF 6.3V Y5V 0805	R8 C1
1162	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 100uF 16V SMD	R8 C2
1163	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 100pF 500V NPO 0805	R8 C3
1164	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 6800pF 50V 0805, 6800pF 16V 0805	R8 C4
1165	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 10000pF 50V X7R 0603	R8 C5
1166	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 27pF 50V NPO 0603	R8 C6
1167	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 0.1uF 25V Y5V 0805	R8 C7
1168	Bench Kilo	Top-8x8 drawer unit Col C	capacitor 33000pF 16V X7R 0603	R8 C8
1169	Bench Kilo	Middle	Desoldering tool	
1170	Bench Kilo	Middle	Antistatic straps	
1171	Bench Kilo	Middle	Stereo microscope	
1172	Bench Kilo	Middle	Toaster oven for SMT	
1173	Bench Kilo	Middle – Left Side	SMT trimmer kit (on 8x8 drawers)	
1174	Bench Kilo	Middle – Left Side – (8x8 drawers)	AD9054ABSTZ-135-ND 8 bit 135MSPS	R1 C1
1175	Bench Kilo	Middle – Left Side – (8x8 drawers)	MM74HC4046M – lock loop phase CMOS 16-SOIC	R1 C2
1176	Bench Kilo	Middle – Left Side – (8x8 drawers)	CD4046BNSR phase lock loop MCPWR 16-SOIP	R1 C3
1177	Bench Kilo	Middle – Left Side – (8x8 drawers)	LMC6482AIM quad dual rail op amp SO-8	R1 C4
1178	Bench Kilo	Middle – Left Side – (8x8 drawers)	ADG202AKR sw analog quad spst 16-SOIC	R1 C5
1179	Bench Kilo	Middle – Left Side – (8x8 drawers)	KM4170ISSTR3 I/O RR 5.3V 16mA opamp SC70-5	R1 C6
1180	Bench Kilo	Middle – Left Side – (8x8 drawers)	ADS1115IDGSR ADC 16bit 860SPS 10MSOP IC	R1 C7
1181	Bench Kilo	Middle – Left Side – (8x8 drawers)	LM4861M 1.1W power amp with shutdown	R1 C8
1182	Bench Kilo	Middle – Left Side – (8x8 drawers)	MAX4217 – opamp	R2 C1
1183	Bench Kilo	Middle – Left Side – (8x8 drawers)	MAX4123 – opamp	R2 C2
1184	Bench Kilo	Middle – Left Side – (8x8 drawers)	AD8605ART-REEL7 single rail-rail I/O LN opamp	R2 C3
1185	Bench Kilo	Middle – Left Side – (8x8 drawers)	LM8272M opamp rail-rail I/O HIOUT	R2 C4
1186	Bench Kilo	Middle – Left Side – (8x8 drawers)	HV57708 – high voltage shift register	R2 C5
1187	Bench Kilo	Middle – Left Side – (8x8 drawers)	3002 coin battery holder 20mm dia SMD	R2 C6
1188	Bench Kilo	Middle – Left Side – (8x8 drawers)	DF9-9S-1V(20) – 9POS 1mm vertical recept conn	R2 C7
1189	Bench Kilo	Middle – Left Side – (8x8 drawers)	3000 coin battery holder 12.5mm SMD	R2 C8
1190	Bench Kilo	Middle – Left Side – (8x8 drawers)	SN74AHC1G04DCKR IC single inverter gate	R3 C1
1191	Bench Kilo	Middle – Left Side – (8x8 drawers)	1060K – battery holder SMT 20mm cell	R3 C2
1192	Bench Kilo	Middle – Left Side – (8x8 drawers)	LTC1068-25CG filter building block 28-SSOP	R3 C3

1193	Bench Kilo	Middle – Left Side – (8x8 drawers)	TEMD5000 Vishay 215mW IR detector	R3 C4
1194	Bench Kilo	Middle – Left Side – (8x8 drawers)	63uF 6.3V SMT	R3 C5
1195	Bench Kilo	Middle – Left Side – (8x8 drawers)	R-78B12-2.0 – 2 AMP pin compatible drop in replacement for LM7812	R3 C6
1196	Bench Kilo	Middle – Left Side – (8x8 drawers)	R-78B12-2.0 – 2 AMP pin compatible drop in replacement for LM7812	R3 C7
1197	Bench Kilo	Middle – Left Side – (8x8 drawers)	R-78B5 0-2.0 – 1 AMP pin compatible drop in replacement for LM7805	R3 C8
1198	Bench Kilo	Middle – Left Side – (8x8 drawers)	FDA380-ND Mosfet N-CH 300V TO-3	R4 C1
1199	Bench Kilo	Middle – Left Side – (8x8 drawers)	FDC6401N Mosfet dual N-CH 2.5 SPEC	R4 C2
1200	Bench Kilo	Middle – Left Side – (8x8 drawers)	SI2342DS-T1-GE3 Mosfet N-CH 8V 6A SOT-23	R4 C3
1201	Bench Kilo	Middle – Left Side – (8x8 drawers)	IRF7488TRPBF Mostlet N-CH 80V 6.3A 8-SOIC	R4 C4
1202	Bench Kilo	Middle – Left Side – (8x8 drawers)	SN74HCT574DW Oct D Flip-flop 20-SOP	R4 C5
1203	Bench Kilo	Middle – Left Side – (8x8 drawers)	MAX3051CSE RS458/422 Quad 16-SOIC	R4 C6
1204	Bench Kilo	Middle – Left Side – (8x8 drawers)	MCP6042T-I/5N opamp 1uA 1.4V	R4 C7
1205	Bench Kilo	Middle – Left Side – (8x8 drawers)	74ACT574SC Oct D type flip-flop SO-20	R4 C8
1206	Bench Kilo	Middle – Left Side – (8x8 drawers)	TPIC6B273 – power oct D-latch 20-SOP	R5 C1
1207	Bench Kilo	Middle – Left Side – (8x8 drawers)	GN04017N0L MMIC switch spot 0.8GHz	R5 C2
1208	Bench Kilo	Middle – Left Side – (8x8 drawers)	UPG152TA-E3 MMIC Switch SPDT 2.5GHz	R5 C3
1209	Bench Kilo	Middle – Left Side – (8x8 drawers)	SN74ACH376DR hex buffer line driver 3ST SOIC-16	R5 C4
1210	Bench Kilo	Middle – Left Side – (8x8 drawers)	NTR4501NTG Mosfet N-CH 20V 3.2A	R5 C5
1211	Bench Kilo	Middle – Left Side – (8x8 drawers)	NE34018-T1 HJ-FET 2GHz SOT-343	R5 C6
1212	Bench Kilo	Middle – Left Side – (8x8 drawers)	P13159CT-ND /ELK-E333FA – digital noise filter 200KHz SMD	R5 C7
1213	Bench Kilo	Middle – Left Side – (8x8 drawers)	NE25139-T1 FET 900MHz	R5 C8
1214	Bench Kilo	Middle – Left Side – (8x8 drawers)	BAT545 – 30V 200mA Schottky diode	R6 C1
1215	Bench Kilo	Middle – Left Side – (8x8 drawers)	BAT54WSDIC – 30V 200mW Schottky diode	R6 C2
1216	Bench Kilo	Middle – Left Side – (8x8 drawers)	BAT54CTA dual schottky diode SOT-23	R6 C3
1217	Bench Kilo	Middle – Left Side – (8x8 drawers)	BAT54 30V 200mA Schottky diode	R6 C4
1218	Bench Kilo	Middle – Left Side – (8x8 drawers)	BAT54ATA dual Schottky diode CA SOT-23	R6 C5
1219	Bench Kilo	Middle – Left Side – (8x8 drawers)	1N6263T 15mA 60V D-Schottky Barr diode	R6 C6
1220	Bench Kilo	Middle – Left Side – (8x8 drawers)	SS2PH10-M3/84A diode Schottky 100V 2A DO220AA	R6 C7
1221	Bench Kilo	Middle – Left Side – (8x8 drawers)	NDS9942 Mosfet N-Ch and P-Ch 20V SO-8	R6 C8
1222	Bench Kilo	Middle – Left Side – (8x8 drawers)	11D003 1.1A 30V Schottky diode	R7 C1
1223	Bench Kilo	Middle – Left Side – (8x8 drawers)	BAV21WSDICT – Schottky diode 200V 200mW	R7 C2
1224	Bench Kilo	Middle – Left Side – (8x8 drawers)	MAX3X704AOLCT – Schottky diode 30V 30mA	R7 C3
1225	Bench Kilo	Middle – Left Side – (8x8 drawers)	MAX3X704AOL – Schottky diode 30V 30mA	R7 C4
1226	Bench Kilo	Middle – Left Side – (8x8 drawers)	PMEG20005EJ – Schottky rect 20V 0.5A	R7 C5
1227	Bench Kilo	Middle – Left Side – (8x8 drawers)	50SQ100 Schottky diode 100V 5A DO-204AR (through hole)	R7 C6
1228	Bench Kilo	Middle – Left Side – (8x8 drawers)	LLSD101A Schottky diode 60V 400mW	R7 C7
1229	Bench Kilo	Middle – Left Side – (8x8 drawers)	SK35A-LTPM3C-ND Schottky diode 50V 3A	R7 C8
1230	Bench Kilo	Middle – Left Side – (8x8 drawers)	10BQ100 Schottky diode 100V 1A SMD	R8 C1
1231	Bench Kilo	Middle – Left Side – (8x8 drawers)	1N5817MCT Schottky diode 20V 1A SMD	R8 C2
1232	Bench Kilo	Middle – Left Side – (8x8 drawers)	SDMG0340LA-7 Schottky diode 40V 200mW SOT-323	R8 C3
1233	Bench Kilo	Middle – Left Side – (8x8 drawers)	SDMG0340LC-7 – Schottky diode 40V 200mW SOT-323	R8 C4
1234	Bench Kilo	Middle – Left Side – (8x8 drawers)	MA716-(TX) Schottky diode 30V 20mA	R8 C5
1235	Bench Kilo	Middle – Left Side – (8x8 drawers)	MA704-(TX) Schottky diode 15V 30mA	R8 C6
1236	Bench Kilo	Middle – Left Side – (8x8 drawers)	FDC6401N Mosfet dual N-CH 20V SSOT-6	R8 C7
1237	Bench Kilo	Middle – Left Side – (8x8 drawers)	R-78K5.0-2.0 DC-DC converter	R8 C8
1238	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	LTST C190GKT LED GREEN CLEAR 0603 SMD	R1 C1
1239	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	7520A10-TRLF LED LIGHT PIPE 3mm RT ANG SMD	R1 C2
1240	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	LS E63B-BB8C-1-1-Z LED SUPRED 645nm 4-PLCC SMD	R1 C3
1241	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	HSMZ-A100-R001J LED 639nm RED CLR 2-PLCC	R1 C4
1242	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	LB E6SG-S2U1-35-Z LED TOP LED 469nm BLUE 4PLCC	R1 C5
1243	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	EMPTY	R2 C1
1244	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	150060RS75000 LED RED CLEAR 0603 SMD	R2 C2
1245	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	LRTB G6TG-TU7-VV7+ST7-IB LED MULTILED RGB DIFF 6PLCC	R2 C3
1246	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	SML-LX0603GW-TR LED 565nm GRN DIFF 0603 SMD	R2 C4
1247	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	OVSPRBCRA LED 525nm RED 1W SMD 6X6	R2 C5
1248	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	OPA4340UA IC QUAD SNGL SUPP OP AMP SO-14	R3 C1
1249	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	LF412CN Op Amp, 4Mhz 8-Pin MDIP	R3 C2
1250	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	OPA2344UA IC RAIL-TO-RAIL OP AMP 8-SOIC	R3 C3
1251	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	OPA4353UA IC HS CMOS OP AMP 14-SOIC	R3 C4
1252	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	OPA2340UA IC DUAL SNGL SUPPLY OP AMP SO-8	R3 C5
1253	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	OPA2397AIDCNR OP AMP GP R-R 90kHz SOT23-8	R4 C1
1254	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	LTC1540CMS8#PBF IC COMP NANOPOWER W/REF 8-MSOP	R4 C2
1255	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	OPA353UA IC HS CMOS OP AMP	R4 C3
1256	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	MCP6041T-I/OT IC OPAMP 1UA 1.4V SNGLR—R SOT235	R4 C4
1257	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	OPA340NA/250 IC SINGLE SUPPLY OPAMP SOT-23-5	R4 C5
1258	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	IRS21844SPBF IC DRIVER HALF-BRIDGE 14-SOIC	R5 C1
1259	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	2N5088 NPN LL LN HI GAIN AMP TRANS TO-92	R5 C2
1260	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	TLV2404IPWR IC OPAMP MCPWR QUAD 14-TSSOP	R5 C3
1261	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	LT1673CS8 IC OPAMP R-R IN/OUT DUAL 8-SOIC	R5 C4
1262	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	OPA2705UA IC 12V RRIO OPAMP 8-SOIC	R5 C5
1263	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	IRS2011STRPBF IC GATE DRVR HALF-BRIDGE 8-SOIC	R6 C1
1264	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	EMPTY	R6 C2
1265	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	EMPTY	R6 C3
1266	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	EMPTY	R6 C4
1267	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	EMPTY	R6 C5
1268	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	EVQ-PLHA15 LIGHT TOUCH SWITCH SMD 160GE 5mm	R7 C1
1269	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	TYN640RG SCR 600V 40A TO-220AB	R7 C2
1270	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	TCR22-3 SCR SENS GATE 1.5 AMP 100V TO-92	R7 C3
1271	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	S101E SCR NON SENSITIVE GATE 1.0A/100V TO-92	R7 C4
1272	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	TL1451ACN – IC PWM Controller dual channel 16-DIP	R7 C5
1273	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	ICM7555IPAZ IC OSC SINGLE TIMER 1MHZ 8-DIP	R8 C1
1274	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	FODM124 OPTOCOUPLER 100AP	R8 C2
1275	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	LTV-817S OPTOSIOLATOR 1CH SMD	R8 C3
1276	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	GP2L26 PHOTOINTERRUPTOR REFLEC 0.8 mm SMD	R8 C4
1277	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	GP2S60 PHOTOINTERRUPTOR REFLEC 1 mm SMD	R8 C5
1278	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	GP2S27T PHOTOINTERRUPTOR REFLEC 0.8 mm SMD	R9 C1
1279	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	HLW8S-2CT7L CONN FPC/FFC 8 POS 1mm VERT PCB	R9 C2
1280	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	TC913BCPA IC OPAMP DUAL AUTO ZERO 8DIP	R9 C3
1281	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	EMPTY	R9 C4
1282	Bench Kilo	Middle – Left Side – Gray (9x5 drawers)	EMPTY	R9 C5
1283	Bench Kilo	Below	VGA video cables	
1284	Bench Kilo	Below	End stops	
1285	Bench Kilo	Below	thermal switches; NTE8242 thermal cutoff	
1286	Bench Kilo	Below	Solid state relays; relays to 40A	
1287	Bench Kilo	Below	24VDC DPDT relays and sockets	
1288	Bench Kilo	Below	65A interconnects	
1289	Bench Kilo	Below	Relay, thin, single pole 24 VDC	
1290	Bench Kilo	Below	Potentiometers	
1291	Bench Kilo	Below	Buttons	
1292	Bench Kilo	Below	DIN mounted relay bases, Octal and Automation Direct	
1293	Bench Kilo	Below	Bezels	
1294	Bench Kilo	Below	Bus Bars	
1295	Bench Kilo	Below	Relays for DIN mounted bases, 12/24 VDC, 24/120/240 VAC	
1296	Bench Kilo	Below	IEC sockets	

1297	Bench Kilo	Below	Contact blocks	
1298	Bench Kilo	Below	Lights	
1299	Bench Kilo	Below	Relays and sockets single pole	
1300	Bench Kilo	Below	Digital scales, 0.01 g, 0.1 g, 2g (x2) resolution	
1301	Bench Kilo	Below	Pick and place system for SMD	
1302	Bench Kilo	Below	Symatrix dual mic preamp SX202 (3)	
1303	Blue Shelf A	Shelf 1	To fix / to donate shelf	
1304	Blue Shelf A	Shelf 2	Loaner laptops and charging station – Megohmmeter – TeleThermometer	
1305	Blue Shelf A	Shelf 3	Old soldering station – empty storage boxes; 3 channel PWM generators XY-LPWM3; Kindle; Android tablet – DMX controllers	
1306	Blue Shelf A	Shelf 3A	Light theremin – MIDI keyboard – MIDI cable (5 pin M-M) – Tone Port UX1 (mixer)	
1307	Blue Shelf A	Shelf 4	SMD pick and place – scale 2200g x 2g (2)	
1308	Blue Shelf A	Shelf 5	SX208 stereo compressor limiter – SX202 dual mic pre-amp – clear timer vault – heat plate – graduated cylinder (250 ml) – spare Metcal units	
1309	Bench Lima	Top – Column A	10 Ohm 0402	R1 C1
1310	Bench Lima	Top – Column A	15 Ohm 0402	R1 C2
1311	Bench Lima	Top – Column A	22 Ohm 0402	R1 C3
1312	Bench Lima	Top – Column A	22 Ohm (2010, 5025?)	R1 C4
1313	Bench Lima	Top – Column A	33 Ohm 0402	R1 C5
1314	Bench Lima	Top – Column A	47 Ohm 0402; 1206	R1 C6
1315	Bench Lima	Top – Column A	68 Ohm 0402	R1 C7
1316	Bench Lima	Top – Column A	82 Ohm 1206	R1 C8
1317	Bench Lima	Top – Column A	100 Ohm 0402 1206	R2 C1
1318	Bench Lima	Top – Column A	150 Ohm 0402 0603	R2 C2
1319	Bench Lima	Top – Column A	200 Ohm 1206	R2 C3
1320	Bench Lima	Top – Column A	220 Ohm	R2 C4
1321	Bench Lima	Top – Column A	330 Ohm	R2 C5
1322	Bench Lima	Top – Column A	470 Ohm	R2 C6
1323	Bench Lima	Top – Column A	680 Ohm	R2 C7
1324	Bench Lima	Top – Column A	18 Ohm 1/8W 0805	R2 C8
1325	Bench Lima	Top – Column A	1K 0402	R3 C1
1326	Bench Lima	Top – Column A	1.5K Ohm	R3 C2
1327	Bench Lima	Top – Column A	2.1K Ohm 0805; 2.2K Ohm 0402	R3 C3
1328	Bench Lima	Top – Column A	3.3K Ohm 0402 2512; 3.32K 1/10W 0606	R3 C4
1329	Bench Lima	Top – Column A	4.7K Ohm 0402; 1206	R3 C5
1330	Bench Lima	Top – Column A	6.8K Ohm 0402; 1210	R3 C6
1331	Bench Lima	Top – Column A	7.87K Ohm 0805; 5.6K Ohm 1206	R3 C7
1332	Bench Lima	Top – Column A	10K Ohm	R3 C8
1333	Bench Lima	Top – Column A	15K Ohm 0402; 0805	R4 C1
1334	Bench Lima	Top – Column A	22K Ohm	R4 C2
1335	Bench Lima	Top – Column A	25.5K Ohm 0805	R4 C3
1336	Bench Lima	Top – Column A	33K Ohm	R4 C4
1337	Bench Lima	Top – Column A	47K Ohm	R4 C5
1338	Bench Lima	Top – Column A	68K Ohm	R4 C6
1339	Bench Lima	Top – Column A	100K Ohm	R4 C7
1340	Bench Lima	Top – Column A	383K Ohm 0805	R4 C8
1341	Bench Lima	Top – Column A	1pF 0402	R5 C1
1342	Bench Lima	Top – Column A	1.2pF	R5 C2
1343	Bench Lima	Top – Column A	1.5pF	R5 C3
1344	Bench Lima	Top – Column A	1.8pF	R5 C4
1345	Bench Lima	Top – Column A	2.2pF	R5 C5
1346	Bench Lima	Top – Column A	2.7pF	R5 C6
1347	Bench Lima	Top – Column A	3.3pF	R5 C7
1348	Bench Lima	Top – Column A	3.9pF	R5 C8
1349	Bench Lima	Top – Column A	4.7pF	R6 C1
1350	Bench Lima	Top – Column A	5.6pF	R6 C2
1351	Bench Lima	Top – Column A	6.8pF	R6 C3
1352	Bench Lima	Top – Column A	9.0pF	R6 C4
1353	Bench Lima	Top – Column A	12pF	R6 C5
1354	Bench Lima	Top – Column A	MMBV3700LT1 diode tuningSS 200V SOT23	R6 C6
1355	Bench Lima	Top – Column A	Varactor 0.8pF to 2.5pF MA27V1900L 6V	R6 C7
1356	Bench Lima	Top – Column A	Resistor 22M Ohm SMD0805	R6 C8
1357	Bench Lima	Top – Column A	Varactor 2 to 4.5pF	R7 C1
1358	Bench Lima	Top – Column A	Varactor 5 to 10pF	R7 C2
1359	Bench Lima	Top – Column A	EMPTY	R7 C3
1360	Bench Lima	Top – Column A	Varactor 6 to 10pF	R7 C4
1361	Bench Lima	Top – Column A	Varactor 7 to 18pF	R7 C5
1362	Bench Lima	Top – Column A	Varactor 0.75 to 2pF	R7 C6
1363	Bench Lima	Top – Column A	Varactor 0.4 to 0.2pF	R7 C7
1364	Bench Lima	Top – Column A	Varactor 0.3 to 0.25pF	R7 C8
1365	Bench Lima	Top – Column A	ELJ-RF 1N52FB inductor 1.5nH 0402 SMD	R8 C1
1366	Bench Lima	Top – Column A	2.2nH	R8 C2
1367	Bench Lima	Top – Column A	3.3nH	R8 C3
1368	Bench Lima	Top – Column A	4.7nH	R8 C4
1369	Bench Lima	Top – Column A	6.8nH	R8 C5
1370	Bench Lima	Top – Column A	10nH	R8 C6
1371	Bench Lima	Top – Column A	15nH	R8 C7
1372	Bench Lima	Top – Column A	22nH	R8 C8
1373	Bench Lima	Top – Column B	1.2uH unshielded inductor	R1 C1
1374	Bench Lima	Top – Column B	33uH power inductor	R1 C2
1375	Bench Lima	Top – Column B	1.8uH	R1 C3
1376	Bench Lima	Top – Column B	22uH	R1 C4
1377	Bench Lima	Top – Column B	0 Ohm 1/8W 5% 1206	R1 C5
1378	Bench Lima	Top – Column B	330 Ohm 1/8W 5% 1206	R1 C6
1379	Bench Lima	Top – Column B	Trim potentiometer 20K Ohm 4 mm squared SMD	R1 C7
1380	Bench Lima	Top – Column B	DS276S low power RS232	R1 C8
1381	Bench Lima	Top – Column B	0.12 Ohm 1/8W 0805	R2 C1
1382	Bench Lima	Top – Column B	47 Ohm 1/8W 5% 0805	R2 C2
1383	Bench Lima	Top – Column B	39 Ohm 1/4W 0805 SMD	R2 C3
1384	Bench Lima	Top – Column B	4.87K 1/10 W 0805	R2 C4
1385	Bench Lima	Top – Column B	1K Ohm 1/8W 1206	R2 C5
1386	Bench Lima	Top – Column B	4.87K Ohm 0805	R2 C6
1387	Bench Lima	Top – Column B	68 Ohm 2512	R2 C7
1388	Bench Lima	Top – Column B	SDR1005-150ML – power inductor 15 uH – SMD	R2 C8
1389	Bench Lima	Top – Column B	47K Ohm 1/8W 1206	R3 C1
1390	Bench Lima	Top – Column B	1K Ohm 1206 SMD	R3 C2
1391	Bench Lima	Top – Column B	390 Ohm 1/8W 1206	R3 C3
1392	Bench Lima	Top – Column B	1M Ohm 1206 SMD	R3 C4
1393	Bench Lima	Top – Column B	1M Ohm 0805 SMD	R3 C5
1394	Bench Lima	Top – Column B	100K Ohm 1206 SMD	R3 C6
1395	Bench Lima	Top – Column B	100 Ohm 1206 SMD	R3 C7
1396	Bench Lima	Top – Column B	0.020 Ohm 1 W 2512 SMD	R3 C8
1397	Bench Lima	Top – Column B	19.1 Ohm 1/4W 0805	R4 C1
1398	Bench Lima	Top – Column B	10K Ohm 1206 SMD	R4 C2
1399	Bench Lima	Top – Column B	49.9 Ohm 1/10W 0805	R4 C3

1400	Bench Lima	Top - Column B	MMBT4403DICT PNP SMD Trans 40V 350mW	R4 C4
1401	Bench Lima	Top - Column B	LM385M3X-2.5 2.5V shunt ref diode SOT23	R4 C5
1402	Bench Lima	Top - Column B	LM404EIM3-2.5 2.5V shunt ref SOT23	R4 C6
1403	Bench Lima	Top - Column B	HD02-T 200V 0.8A bridge rectifier	R4 C7
1404	Bench Lima	Top - Column B	MB6SCT-ND - IC bridge rectifier 0.5A 600V 4SOIC	R4 C8
1405	Bench Lima	Top - Column B	MA8051 - Zener 5.1V 150mW	R5 C1
1406	Bench Lima	Top - Column B	Zener 5.1V 150mW	R5 C2
1407	Bench Lima	Top - Column B	Zener 5.1V 500mW	R5 C3
1408	Bench Lima	Top - Column B	Zener 5.1V 500mW	R5 C4
1409	Bench Lima	Top - Column B	Zener 5.1V 1W	R5 C5
1410	Bench Lima	Top - Column B	Zener 5.1V 500mW	R5 C6
1411	Bench Lima	Top - Column B	Dual USB Port TVS	R5 C7
1412	Bench Lima	Top - Column B	FMMT5179TA NPN RF Transistor	R5 C8
1413	Bench Lima	Top - Column B	MMBT2222A - NPN 40V 350mW	R6 C1
1414	Bench Lima	Top - Column B	LTC1516CS8 - 5V Chrd Pump DC/DC converter SO-8	R6 C2
1415	Bench Lima	Top - Column B	MAX 756CSA step up DC/DC converter	R6 C3
1416	Bench Lima	Top - Column B	FMMT3904TA - NPN trans 40V 200mA SOT23	R6 C4
1417	Bench Lima	Top - Column B	MMBT2907A - PNP SOT23	R6 C5
1418	Bench Lima	Top - Column B	DF1510S-T 1.5A 1000V rectifier bridge	R6 C6
1419	Bench Lima	Top - Column B	PZT651T1 - trans SS HC NPN 60V 2A SOT-223	R6 C7
1420	Bench Lima	Top - Column B	PZT751T1 - trans SS HC PNP 60V 5A	R6 C8
1421	Bench Lima	Top - Column B	GN2470R4 - insulated gate bipolar transistor	R7 C1
1422	Bench Lima	Top - Column B	F2587CT-ND Fuse 5A 125V Fast	R7 C2
1423	Bench Lima	Top - Column B	FMMT3906TA PNO 40V trans SOT23	R7 C3
1424	Bench Lima	Top - Column B	LM317EMPCT-ND - regulator adjustable 1A SOT223	R7 C4
1425	Bench Lima	Top - Column B	LM337-KTR IC reg neg adj 1.5 DDPACK	R7 C5
1426	Bench Lima	Top - Column B	LM390IMP-3.3 IC reg 3.3V	R7 C6
1427	Bench Lima	Top - Column B	OPA4343VA - quad single supply op amp 14-SOIC	R7 C7
1428	Bench Lima	Top - Column B	AD7746 - 24 bit CDC w/temp sensor	R7 C8
1429	Bench Lima	Top - Column B	FDV302PCT Mosfet P-Ch 25V SOT23	R8 C1
1430	Bench Lima	Top - Column B	LM339 SMT	R8 C2
1431	Bench Lima	Top - Column B	LM324AM opamp quad low power 14-SOIC	R8 C3
1432	Bench Lima	Top - Column B	PCF8574ADWR - remote 8 bit I/O expander I2C	R8 C4
1433	Bench Lima	Top - Column B	MCP604-1/SL - quad opamp 2.7V	R8 C5
1434	Bench Lima	Top - Column B	ADS1015/ADC I2C	R8 C6
1435	Bench Lima	Top - Column B	TL074CN - quad low noise J-FET opamp	R8 C7
1436	Bench Lima	Top - Column B	RTC-4553A2 - real time clock 5+/10 ppm	R8 C8
1437	Bench Lima	Top - Component Books	Murata - chip inductor LQW15AW 80 series 51 to 220nH	
1438	Bench Lima	Top - Component Books	Murata - chip inductor LQW15AN 80 series 1.3 to 7.8nH	
1439	Bench Lima	Top - Component Books	Murata - chip inductor LQW18AN 80 series 2.2 to 31nH	
1440	Bench Lima	Top - Component Books	Murata - chip inductor LQW18AN 80 series 7.9 to 75nH	
1441	Bench Lima	Top - Component Books	Murata - chip inductor LQW18AN 80 series 33 to 390nH	
1442	Bench Lima	Top - Column C	DDC101U 20-bit A/D converter	R1 C1
1443	Bench Lima	Top - Column C	2.5V reference diode 8-SOIC	R1 C2
1444	Bench Lima	Top - Column C	MAX232ID IC dual EIA-232 driver/receiver	R1 C3
1445	Bench Lima	Top - Column C	LM4864M-ND - LM4864 - I Amp audio power shutdown 8-SOIC; MCP6284 op-amp	R1 C4
1446	Bench Lima	Top - Column C	LM20BIM7 - IC SMD temp sensor SC-70-5	R1 C5
1447	Bench Lima	Top - Column C	ELTEC442 IR-EYE dual IR detector	R1 C6
1448	Bench Lima	Top - Column C	LTST-C150KYKT LED Amber yellow clear 1206 SMD	R1 C7
1449	Bench Lima	Top - Column C	LTST-C150KAKT LED red-orange clear 1206 SMD	R1 C8
1450	Bench Lima	Top - Column C	LTST-C930CBKT LED blue clear 1210 domed SMD	R2 C1
1451	Bench Lima	Top - Column C	PCA9306DCUR - IC volt level translator 8-VSSOP	R2 C2
1452	Bench Lima	Top - Column C	AD8067ART Fast FET opamp SOT23-5	R2 C3
1453	Bench Lima	Top - Column C	AD8065ARTZ Fast FET opamp SOT23-5	R2 C4
1454	Bench Lima	Top - Column C	AD8066ARZ dual fast FET opamp 8-SOIC	R2 C5
1455	Bench Lima	Top - Column C	AD8067ART Fast FET opamp SOT23-5	R2 C6
1456	Bench Lima	Top - Column C	LM394CH super matched NPN pairs TO-5	R2 C7
1457	Bench Lima	Top - Column C	PDB-C152SM - photodiode blue 0.74mm square SMD	R2 C8
1458	Bench Lima	Top - Column C	LTST-C930KGT LED green clear 1210 domed SMD	R3 C1
1459	Bench Lima	Top - Column C	LTST-C930KSKT LED yellow clear 1210 domed SMD	R3 C2
1460	Bench Lima	Top - Column C	DG5306X LED green clear high bright 5mm	R3 C3
1461	Bench Lima	Top - Column C	LY W57B-FYGY-26 LED yellow clear 594nm 1W SMD	R3 C4
1462	Bench Lima	Top - Column C	LTST-C190KAKT LED red orange clear LED 0603 SMD	R3 C5
1463	Bench Lima	Top - Column C	LTST-C150KGT LED green clear 1206 SMD	R3 C6
1464	Bench Lima	Top - Column C	LTST-C170KGT LED green clear 0805 SMD	R3 C7
1465	Bench Lima	Top - Column C	LA W578B-FYGY-24 LED amber clear 624nm 1W SMD	R3 C8
1466	Bench Lima	Top - Column C	G9491 LED red SMD	R4 C1
1467	Bench Lima	Top - Column C	LTST-C930KAKT LED domed red orange clear 1210 SMD	R4 C2
1468	Bench Lima	Top - Column C	LTST-C150CBKT LED blue clear 1206 SMD	R4 C3
1469	Bench Lima	Top - Column C	TIOPA 209A OBY J8 opamp low power 36V	R4 C4
1470	Bench Lima	Top - Column C	LTST-C150KSKT LED yellow clear 1206 SMD	R4 C5
1471	Bench Lima	Top - Column C	LTST-C155KGJRK LED green/red bicolor 1210 SMD	R4 C6
1472	Bench Lima	Top - Column C	0606LWCT white LED 0603 SMD	R4 C7
1473	Bench Lima	Top - Column C	SSF-LXH305GD-TR LED green diff right angle 7x4x5.5mm	R4 C8
1474	Bench Lima	Top - Column C	1206RGBCT-CA RGB LED 1206 SMD	R5 C1
1475	Bench Lima	Top - Column C	560MY8C yellow amber LED 5mm	R5 C2
1476	Bench Lima	Top - Column C	560PBG6 60 degree royal blue LED 5mm	R5 C3
1477	Bench Lima	Top - Column C	BAV99ZXCT dual diode in series SMD SOT-23	R5 C4
1478	Bench Lima	Top - Column C	BAV235-7-F diode switch 200V 350mW	R5 C5
1479	Bench Lima	Top - Column C	67-1375-1 LED green diffuse right angle	R5 C6
1480	Bench Lima	Top - Column C	GM5WA06260A LED RGB SMD	R5 C7
1481	Bench Lima	Top - Column C	SML-LX3632SISUGSBC LED RGB 3.2x3.6mm clear lens SMD	R5 C8
1482	Bench Lima	Top - Column C	0603KGCT green LED	R6 C1
1483	Bench Lima	Top - Column C	0603LGCT pure green LED	R6 C2
1484	Bench Lima	Top - Column C	0603LBCT blue LED 0603	R6 C3
1485	Bench Lima	Top - Column C	0603KRCT red LED 0603	R6 C4
1486	Bench Lima	Top - Column C	0603KYCT amber LED 0603	R6 C5
1487	Bench Lima	Top - Column C	365-1468-1-ND LED IR 940nm Clear PLCC-2 SMD	R6 C6
1488	Bench Lima	Top - Column C	GM5WA06250A LED RGB SMD	R6 C7
1489	Bench Lima	Top - Column C	MAX6957AAI+ IC driver LED port 20/28 28-SSOP	R6 C8
1490	Bench Lima	Top - Column C	Blue star with collimated batwing blue LED LXHL-NB98	R7 C1
1491	Bench Lima	Top - Column C	LM4929MM amp audio headphone 40mW 10MSOP	R7 C2
1492	Bench Lima	Top - Column C	LM4808M dual amp headphone 8-SOIC	R7 C3
1493	Bench Lima	Top - Column C	122-1285-ND XC2C128-7VQG100C CoolRunner-II 128-macrocell device	R7 C4
1494	Bench Lima	Top - Column C	445-1902-1-ND NLFV25T-1010K-PF inductor shield 100uH	R7 C5
1495	Bench Lima	Top - Column C	LMV324M quad op amp 14-SOIC	R7 C6
1496	Bench Lima	Top - Column C	QEB421 LED IR 880nm SMD	R7 C7
1497	Bench Lima	Top - Column C	BF1108R - IC RF switch SOT-143R	R7 C8
1498	Bench Lima	Top - Column C	MAX4312EEE - video mux 4/8ch 16QSOP	R8 C1
1499	Bench Lima	Top - Column C	OPAS52FA - high current/power opamp 7-DDPACK	R8 C2
1500	Bench Lima	Top - Column C	OPAS52UA - high current/power opamp 8-SOIC	R8 C3
1501	Bench Lima	Top - Column C	LMC7101 opamp	R8 C4
1502	Bench Lima	Top - Column C	MA2JP0200L - diode PIN 60V 100mA S Mini-2P	R8 C5
1503	Bench Lima	Top - Column C	Diode general purpose 1KV 1A SMA S1M-13-F	R8 C6

1504	Bench Lima	Top – Column C	LM6172IM-ND amplifier dual high speed low power	R8 C7
1505	Bench Lima	Top – Column C	MCP601T-I/OT op amp	R8 C8
1506	Bench Lima	Top – Top	Coilcraft designer kit – 0603CS SMT Inductors kit C324B	
1507	Bench Lima	Top – Top	Coilcraft designer kit – 0603HP SMT Inductors kit C406B	
1508	Bench Lima	Top – Top	Coilcraft designer kit – 0603CS SMT Inductors kit C324A	
1509	Bench Lima	Top – Top	Coilcraft designer kit – Square core inductors kit C457	
1510	Bench Lima	Top – Top	Coilcraft designer kit – Square core inductors 0806 0807 0908 SQ kit C424	
1511	Bench Lima	Top – Top	Coilcraft designer kit – 0402DF – SMT Inductors kit C462	
1512	Bench Lima	Top – Top	Coilcraft designer kit – 0402AF – SMT Inductors kit C397	
1513	Bench Lima	Top – Top	Coilcraft designer kit – 0402HP- SMT Inductors kit C403A	
1514	Bench Lima	Top – Top	Coilcraft designer kit – D0501OH – SMT power inductors kit C355	
1515	Bench Lima	Top – Top	Coilcraft designer kit – MIDI Spring Air core inductors – kit C318	
1516	Bench Lima	Middle	Fine tweezers	
1517	Bench Lima	Middle	Aoyue tips	
1518	Bench Lima	Middle	Microscope tools	
1519	Bench Lima	Middle	MTR 3000 series SMT rework	
1520	Bench Lima	Middle	Stereo microscope	
1521	Bench Lima	Bottom	Optical lenses	
1522	Bench Lima	Bottom	Shallow bin (24"x16"x4")	
1523	Bench Lima	Side Cart	SMT Semiconductors, SMT Actives, SMT 2512/2010	
1524	Bench Lima	Side Cart	SMT Capacitors, 0603, 1206, 1210, 0402, 0805, 0805, 0805	
1525	Bench Mike	Top – Column A	TLV2772 op amp; TLV2372 op amp	R1 C1
1526	Bench Mike	Top – Column A	Resonator 16MHz	R1 C2
1527	Bench Mike	Top – Column A	Oscillator 16 MHz	R1 C3
1528	Bench Mike	Top – Column A	1MHz 8FM ser clock oscillator	R1 C4
1529	Bench Mike	Top – Column A	32.768 kHz 12.5pF crystal	R1 C5
1530	Bench Mike	Top – Column A	16MHz 20pF crystal	R1 C6
1531	Bench Mike	Top – Column A	25MHz 18pF crystal	R1 C7
1532	Bench Mike	Top – Column A	Oscillator 12MHz 3.3V	R1 C8
1533	Bench Mike	Top – Column A	10 MHz crystal	R2 C1
1534	Bench Mike	Top – Column A	8 MHz crystal	R2 C2
1535	Bench Mike	Top – Column A	4MHz ceramic resonator	R2 C3
1536	Bench Mike	Top – Column A	4MHz 20pF quartz crystal	R2 C4
1537	Bench Mike	Top – Column A	16MHz ceramic resonator w/cap	R2 C5
1538	Bench Mike	Top – Column A	10MHz ceramic resonator w/cap	R2 C6
1539	Bench Mike	Top – Column A	4MHz ceramic resonator w/cap	R2 C7
1540	Bench Mike	Top – Column A	6MHz ceramic resonator w/cap	R2 C8
1541	Bench Mike	Top – Column A	15MHz crystal	R3 C1
1542	Bench Mike	Top – Column A	Oscillator 40.5MHz	R3 C2
1543	Bench Mike	Top – Column A	4MHz oscillator CMOS/TTL	R3 C3
1544	Bench Mike	Top – Column A	Crystal oscillators 16MHz	R3 C4
1545	Bench Mike	Top – Column A	Crystal oscillators 20MHz	R3 C5
1546	Bench Mike	Top – Column A	Crystal oscillators 20MHz CMOS/TTL	R3 C6
1547	Bench Mike	Top – Column A	Crystal oscillators 20MHz 20pF	R3 C7
1548	Bench Mike	Top – Column A	Ceramic resonator 6MHz	R3 C8
1549	Bench Mike	Top – Column A	Ceramic resonator 6MHz	R4 C1
1550	Bench Mike	Top – Column A	8MHz crystal	R4 C2
1551	Bench Mike	Top – Column A	11.0592MHz 18pF crystal	R4 C3
1552	Bench Mike	Top – Column A	16MHz 18pF crystal	R4 C4
1553	Bench Mike	Top – Column A	20MHz 18pF crystal	R4 C5
1554	Bench Mike	Top – Column A	20MHz oscillator	R4 C6
1555	Bench Mike	Top – Column A	16MHz crystal	R4 C7
1556	Bench Mike	Top – Column A	16MHz crystal	R4 C8
1557	Bench Mike	Top – Column A	10MHz 18pF crystal	R5 C1
1558	Bench Mike	Top – Column A	19.44 MHz crystal	R5 C2
1559	Bench Mike	Top – Column A	20MHz 18pF crystal	R5 C3
1560	Bench Mike	Top – Column A	32.768 kHz crystal	R5 C4
1561	Bench Mike	Top – Column A	32.768 kHz crystal	R5 C5
1562	Bench Mike	Top – Column A	6MHz crystal	R5 C6
1563	Bench Mike	Top – Column A	18.432MHz crystal	R5 C7
1564	Bench Mike	Top – Column A	1000kHz ceramic resonator	R5 C8
1565	Bench Mike	Top – Column A	32.768 kHz 6pF SMD crystal	R6 C1
1566	Bench Mike	Top – Column A	16MHz 18pF crystal	R6 C2
1567	Bench Mike	Top – Column A	1000kHz ceramic resonator	R6 C3
1568	Bench Mike	Top – Column A	500kHz ceramic resonator	R6 C4
1569	Bench Mike	Top – Column A	455kHz ceramic resonator	R6 C5
1570	Bench Mike	Top – Column A	400kHz ceramic resonator	R6 C6
1571	Bench Mike	Top – Column A	200kHz ceramic resonator	R6 C7
1572	Bench Mike	Top – Column A	24MHz 18pF crystal	R6 C8
1573	Bench Mike	Top – Column A	Oscillator socket 4 pin A462-ND	R7 C1
1574	Bench Mike	Top – Column A	ceramic resonator 20MHz	R7 C2
1575	Bench Mike	Top – Column A	Crystal 10MHz	R7 C3
1576	Bench Mike	Top – Column A	Crystal 49.86MHz	R7 C4
1577	Bench Mike	Top – Column A	20K 4mm potentiometer SMD	R7 C5
1578	Bench Mike	Top – Column A	Power resistor 1 Ohm 20W TO220	R7 C6
1579	Bench Mike	Top – Column A	Power resistor 0.1 Ohm 20W TO220	R7 C7
1580	Bench Mike	Top – Column A	Power resistor 0.5 Ohm 20W TO220	R7 C8
1581	Bench Mike	Top – Column A	32.768kHz SMD crystal	R8 C1
1582	Bench Mike	Top – Column A	EMPTY	R8 C2
1583	Bench Mike	Top – Column A	7025kHz Channel 324 WW-II vintage FM set	R8 C3
1584	Bench Mike	Top – Column A	47K Ohm 10 pin 9 resistor net	R8 C4
1585	Bench Mike	Top – Column A	470 Ohm 10 pin 9 resistor net	R8 C5
1586	Bench Mike	Top – Column A	1k Ohm 6 pin bussed	R8 C6
1587	Bench Mike	Top – Column A	1k Ohm 10 pin 9 resistor net	R8 C7
1588	Bench Mike	Top – Column A	4.7 kOhm 10 pin 9 resistor net	R8 C8
1589	Bench Mike	Top – Column B	WM1722-ND 4 pos 1.25 mm housing	R1 C1
1590	Bench Mike	Top – Column B	A100254CT-ND 24 pos 1mm right angle	R1 C2
1591	Bench Mike	Top – Column B	Philmore 86-1002 stereo FM transmitter 88MHz to 108MHz BA1404	R1 C3
1592	Bench Mike	Top – Column B	WM2533-ND – connector male 2 pos 0.100 (latching)	R1 C4
1593	Bench Mike	Top – Column B	280358 – rectangular housing 2 pos	R1 C5
1594	Bench Mike	Top – Column B	WM2900-ND connector housing 2 pos 0.100 (latching)	R1 C6
1595	Bench Mike	Top – Column B	WM2802-ND – connector housing 4 pos 0.100 single	R1 C7
1596	Bench Mike	Top – Column B	WM2535-ND connector housing male 4 pos 0.100	R1 C8
1597	Bench Mike	Top – Column B	WM2902-ND connector housing 4 pos 0.100	R2 C1
1598	Bench Mike	Top – Column B	WM2903-ND connector housing 5 pos 0.100	R2 C2
1599	Bench Mike	Top – Column B	WM4924-ND connector header right angle 2 pos 0.100	R2 C3
1600	Bench Mike	Top – Column B	S7108-ND connector header female 10 pos 0.100 (2 column; 2x5)	R2 C4
1601	Bench Mike	Top – Column B	S7018-ND connector header female 20 pos 0.100 (1 column)	R2 C5
1602	Bench Mike	Top – Column B	455-1706-ND – connector header top 4 pos 2mm	R2 C6
1603	Bench Mike	Top – Column B	Connector receptacle Mini-USB 5 POS	R2 C7
1604	Bench Mike	Top – Column B	IC FTDI FT232RL	R2 C8
1605	Bench Mike	Top – Column B	CH401-ND VN101501 switch magnet digital vane	R3 C1
1606	Bench Mike	Top – Column B	H22LTB – switch interrupt totem buff-out	R3 C2
1607	Bench Mike	Top – Column B	TL3315NF100Q – switch tactile LQPRO 100GF SMD	R3 C3

1608	Bench Mike	Top - Column B	WM2500-ND connector terminal male 18-24 AWG	R3 C4
1609	Bench Mike	Top - Column B	S216S02 - relay SSR 250 VAC 16A ZC 4-SIP	R3 C5
1610	Bench Mike	Top - Column B	Connector housing 2.5mm XH 12 pos	R3 C6
1611	Bench Mike	Top - Column B	AE7208-ND 8 pin gold IC socket	R3 C7
1612	Bench Mike	Top - Column B	Insulator BU45 45C	R3 C8
1613	Bench Mike	Top - Column B	DF9-9P-1V(32) connector header 9 pos 1mm SMD TIN	R4 C1
1614	Bench Mike	Top - Column B	171-009-103L001 connector DB9 Male solder cup nickel	R4 C2
1615	Bench Mike	Top - Column B	Connector jack 3.5mm SMD	R4 C3
1616	Bench Mike	Top - Column B	73251-1151 Molex 500 Ohm edgemount	R4 C4
1617	Bench Mike	Top - Column B	WM3603-ND plug and receptacle 8 pos	R4 C5
1618	Bench Mike	Top - Column B	Connector Molex 3P 09-50-3031	R4 C6
1619	Bench Mike	Top - Column B	Connector Molex 6P 09-50	R4 C7
1620	Bench Mike	Top - Column B	Connector Molex 8P 09-50-3081	R4 C8
1621	Bench Mike	Top - Column B	641214-4 Connector header 4 pos 30Au right angle	R5 C1
1622	Bench Mike	Top - Column B	DF9-9S-1V(20) connector receptacle 9 pos 1mm SMD TIN	R5 C2
1623	Bench Mike	Top - Column B	Fuseblock W3A Fuse SMD F1226CT-ND	R5 C3
1624	Bench Mike	Top - Column B	BAS70-05-7 - Diode Schottky CC 70V 200mW SOT-23	R5 C4
1625	Bench Mike	Top - Column B	2SA1162 - PNP transistor SMD	R5 C5
1626	Bench Mike	Top - Column B	DTA143ZUA - transistor PNP with built in bias resistors SOT	R5 C6
1627	Bench Mike	Top - Column B	2SC3356 R25 - transistor NPN - SMT	R5 C7
1628	Bench Mike	Top - Column B	DTC143ZUA - transistor NPN with built in bias resistors SOT	R5 C8
1629	Bench Mike	Top - Column B	2SC2954 NPN transistor SMD	R6 C1
1630	Bench Mike	Top - Column B	BFG540X - NPN transistor SMD	R6 C2
1631	Bench Mike	Top - Column B	1SV214 - variable capacitance diode SMD	R6 C3
1632	Bench Mike	Top - Column B	AT-30511-TR1 - NPN transistor SOT-23	R6 C4
1633	Bench Mike	Top - Column B	2SA1615-KZ - silicon power transistor 10A - SMD	R6 C5
1634	Bench Mike	Top - Column B	PBMT3904 Trans NPN 40V 0.2A TO-236AB	R6 C6
1635	Bench Mike	Top - Column B	BAS70-06-7 - Diode Schottky 70V 200mW SOT-23	R6 C7
1636	Bench Mike	Top - Column B	Variable 10K potentiometer SMT	R6 C8
1637	Bench Mike	Top - Column B	2SA1576 Trans PNP SO-323	R7 C1
1638	Bench Mike	Top - Column B	BSS138 - Mosfet N-CH 50V 220mA SOT-23	R7 C2
1639	Bench Mike	Top - Column B	2SA1213 Trans PNP 50V 2A SOT-89	R7 C3
1640	Bench Mike	Top - Column B	Tuning diode MV2105; tuning diode MV2109	R7 C4
1641	Bench Mike	Top - Column B	2SC3120 NPN Transistor for RF - SMD	R7 C5
1642	Bench Mike	Top - Column B	LM3480IM3-3.3 - IC voltage regulator LDO 100mA 3.3V SOT23-3	R7 C6
1643	Bench Mike	Top - Column B	Tuning diode MV209; tunable RF coil 0.270-0.33uH	R7 C7
1644	Bench Mike	Top - Column B	G6L-1F-TRDC12 - telecom relay SPST 1A 12VDC SMT	R7 C8
1645	Bench Mike	Top - Column B	CCV-084B16 - buzzer audio magnetic 3.6VDC SMD	R8 C1
1646	Bench Mike	Top - Column B	WM-64PNT - microphone Omni 6x2.2mm w/cap	R8 C2
1647	Bench Mike	Top - Column B	3214W-1-203E - trim potentiometer 20K 4mm top adjust	R8 C3
1648	Bench Mike	Top - Column B	LNJ717W83RAS - LED Blue/Green/Orange 3 color SMD	R8 C4
1649	Bench Mike	Top - Column B	5015 - PC test point - SMT	R8 C5
1650	Bench Mike	Top - Column B	Polyswitch 0.5A, 1.5A, PTC 24V 750mA SMD/1812 fuses	R8 C6
1651	Bench Mike	Top - Column B	20K B 3 SMD - trim potentiometer	R8 C7
1652	Bench Mike	Top - Column B	EE2-3NUH-L - relay general purpose DPDT 2A 3VDC SMT	R8 C8
1653	Bench Mike	Top - Column C	LM4070/4.1	R1 C1
1654	Bench Mike	Top - Column C	BAT54	R1 C2
1655	Bench Mike	Top - Column C	RFP30N06LE	R1 C3
1656	Bench Mike	Top - Column C	IRLL110 MOSFET N-CH 100V SOT23	R1 C4
1657	Bench Mike	Top - Column C	M25P20 Flash	R1 C5
1658	Bench Mike	Top - Column C	PA42-350V high voltage amp	R1 C6
1659	Bench Mike	Top - Column C	S4407-ND female connector 32 pos 0.100" right angle	R1 C7
1660	Bench Mike	Top - Column C	MHB20K-ND 20 pos straight	R1 C8
1661	Bench Mike	Top - Column C	10BQ100 Schottky diode 100V 1A SMB	R2 C1
1662	Bench Mike	Top - Column C	IRLML6402 - MOSFET P-CH 20V 3.7A SOT-23	R2 C2
1663	Bench Mike	Top - Column C	IRLML2502 - MOSFET N-CH 20V 4.2A SOT-23	R2 C3
1664	Bench Mike	Top - Column C	FDV304P - P-CH 25V 400mA SOT-23	R2 C4
1665	Bench Mike	Top - Column C	MAX3232	R2 C5
1666	Bench Mike	Top - Column C	LM235AH	R2 C6
1667	Bench Mike	Top - Column C	MSP430F SOIC	R2 C7
1668	Bench Mike	Top - Column C	MC78LC33	R2 C8
1669	Bench Mike	Top - Column C	AT91SAM7S128	R3 C1
1670	Bench Mike	Top - Column C	91SAM7X256	R3 C2
1671	Bench Mike	Top - Column C	DP83948	R3 C3
1672	Bench Mike	Top - Column C	H1102	R3 C4
1673	Bench Mike	Top - Column C	LR8N3 high voltage regulator 450V	R3 C5
1674	Bench Mike	Top - Column C	MSP430F SOIC	R3 C6
1675	Bench Mike	Top - Column C	MIC2920A - 3.3V regulator	R3 C7
1676	Bench Mike	Top - Column C	78LC50	R3 C8
1677	Bench Mike	Top - Column C	IN470A 10V Zener	R4 C1
1678	Bench Mike	Top - Column C	RJ-45 shielded	R4 C2
1679	Bench Mike	Top - Column C	7x2 shrouded key	R4 C3
1680	Bench Mike	Top - Column C	92K battery clips	R4 C4
1681	Bench Mike	Top - Column C	LM92 digital temp sensor SOIC	R4 C5
1682	Bench Mike	Top - Column C	MSP430F449	R4 C6
1683	Bench Mike	Top - Column C	TL431	R4 C7
1684	Bench Mike	Top - Column C	LM1117 3.3V regulator	R4 C8
1685	Bench Mike	Top - Column C	ERA-ISM amplifier	R5 C1
1686	Bench Mike	Top - Column C	GALI-566	R5 C2
1687	Bench Mike	Top - Column C	IR21834	R5 C3
1688	Bench Mike	Top - Column C	MOLD2027M 2-channel opto	R5 C4
1689	Bench Mike	Top - Column C	UCC3805	R5 C5
1690	Bench Mike	Top - Column C	160-1220-1-ND LTST-S220EKT - LED red/orange clear 0805 right angle SMD	R5 C6
1691	Bench Mike	Top - Column C	Compact Flash (CF) card holder - SMT	R5 C7
1692	Bench Mike	Top - Column C	(SD) card holder - SMT	R5 C8
1693	Bench Mike	Top - Column C	INA321 instrumentation amp	R6 C1
1694	Bench Mike	Top - Column C	OPA348 general purpose opamp; OPA349; TLV2401 low power op amp	R6 C2
1695	Bench Mike	Top - Column C	TLV3491 1.8V comparator; TLV2760 1.8V	R6 C3
1696	Bench Mike	Top - Column C	OPA 336 low power precision opamp; OPA363 fast opamp	R6 C4
1697	Bench Mike	Top - Column C	TMP101 digital temperature sensor	R6 C5
1698	Bench Mike	Top - Column C	REF3025, REF3033 micropower voltage reference (2.5V, 3.3V, 0.2% 20ppm)	R6 C6
1699	Bench Mike	Top - Column C	MAX2451	R6 C7
1700	Bench Mike	Top - Column C	MMBT3906-TP - transistor PNP 40V 0.2A SOT23	R6 C8
1701	Bench Mike	Top - Column C	LL4148 diode general purpose 100V 200mA SOD80	R7 C1
1702	Bench Mike	Top - Column C	RS1GB-13-F diode fast recovery 1A 400V SMB	R7 C2
1703	Bench Mike	Top - Column C	7914G-1-000E switch key 4mm square SMD gull wing	R7 C3
1704	Bench Mike	Top - Column C	EVQ-Q2U0W switch LT 6mm 260GF H=3.1mm SMD	R7 C4
1705	Bench Mike	Top - Column C	EVQ-PLHA15 switch LT SMD 160GE 5mm	R7 C5
1706	Bench Mike	Top - Column C	B3S-1002P - switch tactile 6mm 230GF H=4.3mm	R7 C6
1707	Bench Mike	Top - Column C	SMD switch; unknown model	R7 C7
1708	Bench Mike	Top - Column C	MMBT4401-7-F NPN transistor 350mW 40V SMD SOT23	R7 C8
1709	Bench Mike	Top - Column C	FQB22P10TM - Mosfet P-CH 100V 22A D2PAK	R8 C1
1710	Bench Mike	Top - Column C	SMBT3904E6327 NPN 40V SOT-23	R8 C2
1711	Bench Mike	Top - Column C	FDC6305M Mosfet N-CH dual 20V SSO26	R8 C3

1712	Bench Mike	Top – Column C	FDN304P Mosfet P-CH 20V 2.4A SSOT3	R8 C4
1713	Bench Mike	Top – Column C	FDN306P Mosfet P-CH 12V 2.6A SSOT3	R8 C5
1714	Bench Mike	Top – Column C	FMMT596TA PNP transistor SMD SOT23 200V	R8 C6
1715	Bench Mike	Top – Column C	MMBT5088 – transistor general purpose NPN amp SOT-23	R8 C7
1716	Bench Mike	Top – Column C	MMBT3906-7-F PNP 40V 300 mW SMD SOT-23	R8 C8
1717	Bench Mike	Top	Notebooks	
1718	Bench Mike	Top	Chalk speedline	
1719	Bench Mike	Middle	Othermill and tools	
1720	Bench Mike	Middle	USB microscope	
1721	Bench Mike	Middle	Sandpaper	
1722	Bench Mike	Bottom	EMPTY	
1723	Bench Mike	Bottom	AC powered drill	
1724	Bench Mike	Bottom	LARGE UPS unit, 120VAC, 15Amp output (1.8kW output)	
1725	Bench November	Top	RF station	
1726	Front Wire Rack	Top	Blinky cube	
1727	Front Wire Rack	Top	Envelopes	
1728	Front Wire Rack	Top	Luggage tag laminates	
1729	Front Wire Rack	Middle	Paper, Donations for E&R, flashlights, AC blacklight	
1730	Front Wire Rack	Middle	Clipboards for note taking	
1731	Front Wire Rack	Middle	Tags for marking projects	
1732	Front Wire Rack	Middle	Scissors, pens, pencils	
1733	Front Wire Rack	Middle	Safety glasses	
1734	Front Wire Rack	Bottom	Labels, envelopes	
1735	Front Wire Rack	Bottom	Clear report covers	
1736	Front Wire Rack	Bottom	DVDs, CDs.	
1737	REAR PARTS AREA	Bottom RadioShack 1	Arduino sockets and plugs	
1738	REAR PARTS AREA	Bottom RadioShack 1	Battery holders; AAAA, AAA, AA, C, D, 9V	
1739	REAR PARTS AREA	Bottom RadioShack 1	Battery holders and coin cells; CR1220; CR2032; CR2025; LR44	
1740	REAR PARTS AREA	Bottom RadioShack 1	Fuses	
1741	REAR PARTS AREA	Bottom RadioShack 1	Relays	
1742	REAR PARTS AREA	Bottom RadioShack 1	Potentiometers, photocells	
1743	REAR PARTS AREA	Bottom RadioShack 1	2D potentiometers, condenser mics	
1744	REAR PARTS AREA	Bottom RadioShack 1	Thermal paste, heat sinks	
1745	REAR PARTS AREA	Bottom RadioShack 2	LEDs – blue – red – yellow – green – white – orange – infrared (NTE3017) – red/green	
1746	REAR PARTS AREA	Bottom RadioShack 2	Segment displays, dot matrices	
1747	REAR PARTS AREA	Bottom RadioShack 2	Small screens, LED mounting; Edison bulbs and bases	
1748	REAR PARTS AREA	Bottom RadioShack 2	LEDs and panel lights; RGB LEDs	
1749	REAR PARTS AREA	Bottom RadioShack 2	Large switches and buttons	
1750	REAR PARTS AREA	Bottom RadioShack 2	RJ11, RJ45, speaker connectors; DIN 9 pin connectors	
1751	REAR PARTS AREA	Bottom RadioShack 2	1/8" and 1/4" plugs jacks for microphones/speakers	
1752	REAR PARTS AREA	Bottom RadioShack 2	RCA, USB to serial	
1753	REAR PARTS AREA	Bottom MIDDLE OPEN	D-sub connectors	
1754	REAR PARTS AREA	Bottom MIDDLE OPEN	D-sub hardware	
1755	REAR PARTS AREA	Bottom MIDDLE OPEN	D-sub pins	
1756	REAR PARTS AREA	Bottom RadioShack 3	Hobby servos, stepper drivers	
1757	REAR PARTS AREA	Bottom RadioShack 3	Misc small DC motors, ceramic disks, large switches	
1758	REAR PARTS AREA	Bottom RadioShack 3	AC lamps, zip ties, zip tie tie-downs, transformers	
1759	REAR PARTS AREA	Bottom RadioShack 3	Inductors, flashlamps, heat sinks, matches, magnets	
1760	REAR PARTS AREA	Bottom RadioShack 3	Transformers, alroids tins, tea lights	
1761	REAR PARTS AREA	Bottom RadioShack 3	DRAWER DIVIDERS	
1762	REAR PARTS AREA	Bottom RadioShack 3	AC motors, picoboard	
1763	REAR PARTS AREA	Bottom RadioShack 3	DC motors, large zip ties	
1764	REAR PARTS AREA	Bottom RadioShack 4	Speakers and switches, optical slot switches	
1765	REAR PARTS AREA	Bottom RadioShack 4	Switches and rotary DIP switches	
1766	REAR PARTS AREA	Bottom RadioShack 4	DIP switches	
1767	REAR PARTS AREA	Bottom RadioShack 4	alligator clips	
1768	REAR PARTS AREA	Bottom RadioShack 4	Knobs, buttons, terminal strips, PCB terminal strips	
1769	REAR PARTS AREA	Bottom RadioShack 4	DB-9, DB-25 connectors, terminal strips	
1770	REAR PARTS AREA	Bottom RadioShack 4	Solar cells, googly eyes, finger condoms, thermostat	
1771	REAR PARTS AREA	Shelf 1	Small drawers – diode kit, MOSFETS	
1772	REAR PARTS AREA	Shelf 1	Small drawers – Zener diodes, optoisolators	
1773	REAR PARTS AREA	Shelf 1	Small drawers – diodes, op-amps	
1774	REAR PARTS AREA	Shelf 1	Small drawers – Capacitors	
1775	REAR PARTS AREA	Shelf 1	Small drawers – Capacitors	
1776	REAR PARTS AREA	Shelf 1	Small drawers – Resistors	
1777	REAR PARTS AREA	Shelf 1	Small drawers – Resistors	
1778	REAR PARTS AREA	Shelf 2	Small drawers – TTL	
1779	REAR PARTS AREA	Shelf 2	Small drawers – TTL	
1780	REAR PARTS AREA	Shelf 2	Small drawers – TTL	
1781	REAR PARTS AREA	Shelf 2	Small drawers – TTL	
1782	REAR PARTS AREA	Shelf 2	Small drawers – Op-amps, ATMega, phototransistors	
1783	REAR PARTS AREA	Shelf 2	Small drawers – Crystals, headers, voltage regulators	
1784	REAR PARTS AREA	Shelf 2	Small drawers – Op-amps, voltage regulators, diodes	
1785	REAR PARTS AREA	Shelf 2	Small drawers – Transistors, TO-92, TO-220, relays, 555	
1786	REAR PARTS AREA	Shelf 3	Connectors	
1787	REAR PARTS AREA	Shelf 3	Circuit breakers; 1A to 25A, DC and AC; DIN rail mounted circuit breakers	
1788	REAR PARTS AREA	Shelf 3	Ham radio	
1789	REAR PARTS AREA	Shelf 3	Digital cameras	
1790	REAR PARTS AREA	Shelf 3 -10Rx6C	WM-2517 conn term male 22-24 AWG tin; 0016020114 – Molex	R1 C1
1791	REAR PARTS AREA	Shelf 3 -10Rx6C	Molex 0.1 in 1x6	R1 C2
1792	REAR PARTS AREA	Shelf 3 -10Rx6C	Molex 0.1 in 1x7	R1 C3
1793	REAR PARTS AREA	Shelf 3 -10Rx6C	Molex 0.1 in 1x8	R1 C4
1794	REAR PARTS AREA	Shelf 3 -10Rx6C	Molex 0.1 in 1x9	R1 C5
1795	REAR PARTS AREA	Shelf 3 -10Rx6C	Molex 0.1 in 1x10	R1 C6
1796	REAR PARTS AREA	Shelf 3 -10Rx6C	WM-2510 conn term female 22-24 AWG tin; 0016020102 – Molex	R2 C1
1797	REAR PARTS AREA	Shelf 3 -10Rx6C	Molex 0.1 in 1x1	R2 C2
1798	REAR PARTS AREA	Shelf 3 -10Rx6C	Molex 0.1 in 1x2	R2 C3
1799	REAR PARTS AREA	Shelf 3 -10Rx6C	Molex 0.1 in 1x3	R2 C4
1800	REAR PARTS AREA	Shelf 3 -10Rx6C	Molex 0.1 in 1x4	R2 C5
1801	REAR PARTS AREA	Shelf 3 -10Rx6C	Molex 0.1 in 1x5	R2 C6
1802	REAR PARTS AREA	Shelf 3 -10Rx6C	Molex male pin Molex B	R3 C1
1803	REAR PARTS AREA	Shelf 3 -10Rx6C	Molex female pin Molex B	R3 C2
1804	REAR PARTS AREA	Shelf 3 -10Rx6C	More Molex female pin Molex B	R3 C3
1805	REAR PARTS AREA	Shelf 3 -10Rx6C	Molex 0.1 in 1x2	R3 C4
1806	REAR PARTS AREA	Shelf 3 -10Rx6C	Molex 0.1 in 2x4	R3 C5
1807	REAR PARTS AREA	Shelf 3 -10Rx6C	Molex 0.1 in 2x5	R3 C6
1808	REAR PARTS AREA	Shelf 3 -10Rx6C	1772-36 PLUG and 1772-36R RECEPTACLE	R4 C1
1809	REAR PARTS AREA	Shelf 3 -10Rx6C	1625-15P Plug and 1625-15R Receptacle	R4 C2
1810	REAR PARTS AREA	Shelf 3 -10Rx6C	1625-12P Plug and 1625-12R Receptacle	R4 C3
1811	REAR PARTS AREA	Shelf 3 -10Rx6C	1625-9P Plug and 1625-9P Receptacle	R4 C4
1812	REAR PARTS AREA	Shelf 3 -10Rx6C	1649-8P Plug and 1649-8R Receptacle	R4 C5
1813	REAR PARTS AREA	Shelf 3 -10Rx6C	1625-6P Plug and 1625-6R Receptacle	R4 C6
1814	REAR PARTS AREA	Shelf 3 -10Rx6C	1561 0.062" female terminals	R5 C1
1815	REAR PARTS AREA	Shelf 3 -10Rx6C	1560 0.062" male terminals	R5 C2

1816	REAR PARTS AREA	Shelf 3 -10Rx6C	1625-1P Plug and 1625-1R Receptacle	R5 C3
1817	REAR PARTS AREA	Shelf 3 -10Rx6C	1625-3P Plug and 1625-3R Receptacle	R5 C4
1818	REAR PARTS AREA	Shelf 3 -10Rx6C	1625-4P Plug and 1625-4R Receptacle	R5 C5
1819	REAR PARTS AREA	Shelf 3 -10Rx6C	1625-5P Plug and 1625-5R Receptacle	R5 C6
1820	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 HDR-2 26-48-1021	R6 C1
1821	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 HDR-3 26-48-1031	R6 C2
1822	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 HDR-4 26-48-1041	R6 C3
1823	REAR PARTS AREA	Shelf 3 -10Rx6C	EMPTY	R6 C4
1824	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 HDR-6 26-48-1061	R6 C5
1825	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 HDR-10 26-48-1101	R6 C6
1826	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 RHDR-2 26-48-1022	R7 C1
1827	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 RHDR-3 26-48-1023	R7 C2
1828	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 RHDR-4 26-48-1042	R7 C3
1829	REAR PARTS AREA	Shelf 3 -10Rx6C	WM-2534 0701070002 conn housing 3 pin	R7 C4
1830	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 RHDR-6 26-48-1062	R7 C5
1831	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 RHDR-10 26-48-1102	R7 C6
1832	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 TRM-2 09-50-7021 housing 2 pos	R8 C1
1833	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 TRM-3 09-50-7031	R8 C2
1834	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 TRM-4 09-50-7041	R8 C3
1835	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 TRM-5 09-50-7051	R8 C4
1836	REAR PARTS AREA	Shelf 3 -10Rx6C	WM-2104-ND 0.156 housing 6 pos	R8 C5
1837	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 TRM-10 09-50-7101	R8 C6
1838	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 08-50-106 / 08-55-0104 and extractor	R9 C1
1839	REAR PARTS AREA	Shelf 3 -10Rx6C	Gold female pins	R9 C2
1840	REAR PARTS AREA	Shelf 3 -10Rx6C	MegaFit female pins	R9 C3
1841	REAR PARTS AREA	Shelf 3 -10Rx6C	LP-1001A connector	R9 C4
1842	REAR PARTS AREA	Shelf 3 -10Rx6C	EMPTY	R9 C5
1843	REAR PARTS AREA	Shelf 3 -10Rx6C	KK 0.156 TRM-R 09-50-8040 4 position	R9 C6
1844	REAR PARTS AREA	Shelf 3 -10Rx6C	Molex 0.1 in 2x13	R10 C1
1845	REAR PARTS AREA	Shelf 3 -10Rx6C	EMPTY	R10 C2
1846	REAR PARTS AREA	Shelf 3 -10Rx6C	EMPTY	R10 C3
1847	REAR PARTS AREA	Shelf 3 -10Rx6C	EMPTY	R10 C4
1848	REAR PARTS AREA	Shelf 3 -10Rx6C	EMPTY	R10 C5
1849	REAR PARTS AREA	Shelf 3 -10Rx6C	0039012180 conn receptacle HSG 18 pos 4.20mm	R10 C6
1850	REAR PARTS AREA	Shelf 3	Molex Mini-Fit Jr. Power Connector Kit – 76650-0014	
1851	REAR PARTS AREA	Shelf 3	Molex SMT off-the-board solution kit 76650-0236; 1.25mm and 1.5mm pitch	
1852	REAR PARTS AREA	Shelf 3	Molex off-the-board solution kit 76650-0237; 2 mm pitch	
1853	REAR PARTS AREA	Shelf 3	Samtec – Mini Mate 0.100" connector kit	
1854	REAR PARTS AREA	Shelf 3	Thermocouple conditioners – TMP006 thermocouple amplifiers	
1855	REAR PARTS AREA	Shelf 3	Signal conditioners	
1856	REAR PARTS AREA	Shelf 3	Pinewood Derby timer	
1857	REAR PARTS AREA	Shelf 3	DB-9 and DB-25 cables and breakouts	
1858	REAR PARTS AREA	Shelf 3	Tablet holders	
1859	REAR PARTS AREA	Shelf 3	DVI, Displayport, HDMI cables; Displayport to HDMI; HDMI to DVI; USB C to DVI Displayport to DVI	
1860	REAR PARTS AREA	Shelf 4	Mass flow controllers	
1861	REAR PARTS AREA	Shelf 4	Load cells; HX711 load cell amplifier	
1862	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	100K 10 pin 9 resistor net	R1 C1
1863	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	10K ¼ Watt 1%	R1 C2
1864	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	100k bussed resistor net	R1 C3
1865	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	470k 10 pin 9 resistor net	R1 C4
1866	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	4.7k resistor net	R1 C5
1867	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	1M 10 pin 9 resistor net	R1 C6
1868	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	10k 10 pin 9 resistor net	R1 C7
1869	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	100K resistor net	R1 C8
1870	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	1.3 Ohm 1W 5% resistor	R2 C1
1871	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	0.68 Ohm 1W 5% resistor	R2 C2
1872	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	4.7 Ohm 1W 5% resistor	R2 C3
1873	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	1 Ohm 1 Watt 5% resistor	R2 C4
1874	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	2.2 Ohm 1 Watt 5% resistor	R2 C5
1875	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	10 Ohm 1 Watt 5% resistor	R2 C6
1876	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	4.7 Ohm 5% resistor	R2 C7
1877	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	0.1 Ohm 5W current sense resistor	R2 C8
1878	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	0.010 Ohm 5W current sense resistor	R3 C1
1879	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	ZMR500C – IC Vreg mini 5V 50mA TO-92	R3 C2
1880	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	27 Ohm 1W 5% resistor	R3 C3
1881	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	1M Ohm 1/4W 1% resistor	R3 C4
1882	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	3W 0.003 Ohm resistor	R3 C5
1883	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	200K 1W 1% metal film resistor	R3 C6
1884	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	10 Ohm 1/2W resistor	R3 C7
1885	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	0.005 Ohm resistor	R3 C8
1886	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	1.5K Ohm ¼ 25 Watt resistor	R4 C1
1887	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	2K Ohm 1% 25 Watt resistor	R4 C2
1888	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	IC 5V 150mA LDO regulator TO-92 – TL750L05CLP	R4 C3
1889	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	IC 24V positive regulator TO220F – NJM7824FA	R4 C4
1890	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	IC 3.3V linear regulator 300mA SOT-23 – MIC5504-3.3YM5-TR	R4 C5
1891	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	2.7V Zener 0.5W 5%	R4 C6
1892	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	4.7K Ohm ¼ Watt 5%	R4 C7
1893	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	2K Ohm 1/2W 1% resistor	R4 C8
1894	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM317 500mA TO-220	R5 C1
1895	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	SR0375G – 120VAC to 5VDC	R5 C2
1896	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM334H – constant current source	R5 C3
1897	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM317LZ – adjustable regulator	R5 C4
1898	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	MIC39100-5.0WS – IC reg LDO 1A 5.0V SOT223	R5 C5
1899	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LP2950CZ-5.0/LFT3 – IC REG Linear 5V 100mA TO92-3	R5 C6
1900	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM337-SP 1.5A TO220	R5 C7
1901	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	NJM79L05A 5V negative regulator	R5 C8
1902	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM317T 1.5A adjustable regulator	R6 C1
1903	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM1086CT-5 – 5V 1.5A positive LDO reg	R6 C2
1904	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM320LZ-12 12V negative voltage regulator -12V 0.1A	R6 C3
1905	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM78L05ACZ – 5V 100mA reg	R6 C4
1906	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	REG1117-3.3 LDO regulator 3.3V; LM1117S-SMT	R6 C5
1907	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM4041IZ1.2 1.225V voltage ref; LM4041DIZ-ADJ	R6 C6
1908	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM2936Z-5.0 – ultra quiet 5V reg	R6 C7
1909	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM78L12ACZ 12V 0.1A reg	R6 C8
1910	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM7905CT -5V 4% regulator	R7 C1
1911	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	DC-DC 36Vin, 5V Out	R7 C2
1912	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM339D – Quad diff comparator	R7 C3
1913	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	MIC29300-5.0WDT IC LDO 3A 5.0V	R7 C4
1914	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	UA7808CKC 8V 1.5A regulator	R7 C5
1915	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM4040EIZ-2.52 5V shunt ref +/-2%; LM4040C25IBZR	R7 C6
1916	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM4040CIZ-4.1 4.1V ref +/-0.5%	R7 C7
1917	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	MPS651 TRANS	R7 C8
1918	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM385Z-2.5 2.5V shunt ref diode	R8 C1

1919	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LM3362-2.5 2.5V shunt ref	R8 C2
1920	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	MPS6515 Trans amp NPN SS GP	R8 C3
1921	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	LMD18200T – IC H bridge 3A 55V	R8 C4
1922	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	DF02 full wave bridge	R8 C5
1923	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	2N5963 BJT NPN transistor	R8 C6
1924	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	J310 JFET N-channel 25V 10 mA	R8 C7
1925	REAR PARTS AREA	Shelf 4-8x8 drawer unit LEFT	PN2907A PNP SML SIG amplifier	R8 C8
1926	REAR PARTS AREA	Shelf 4 – IN BETWEEN UNITS	1 W Resistors of various sizes	
1927	REAR PARTS AREA	Shelf 4 – IN BETWEEN UNITS	TY-145P 600 Ohm CT Audio transformer	
1928	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	LF441CN – JFET Op Amp	R1 C1
1929	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	TC-105 Phone transformer 600 Ohm 90mA	R1 C2
1930	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	4046BPC – phased locked loop	R1 C3
1931	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	LM324AN – low power quad op amp 14 pin	R1 C4
1932	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	ADG202AKN – sw analog quad spst	R1 C5
1933	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	LM4864N – 300 mW audio power amp	R1 C6
1934	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	TLC274CN quad cmos opamp	R1 C7
1935	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	LMC555CN	R1 C8
1936	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	TLO84CN quad jfet input opamp	R2 C1
1937	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	MCP604-IP quad op amp 2.7V	R2 C2
1938	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	LTC1043CN – switch cap building block	R2 C3
1939	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	LM34DZ – Fahrenheit temperature sensor	R2 C4
1940	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	LT1014DN – precision op amp quad 800V	R2 C5
1941	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	LM6134AIN – quad high speed op amp	R2 C6
1942	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	MAX518BCSA – dual bit serial DAC	R2 C7
1943	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	LTC1540ISB – nanopower comparator	R2 C8
1944	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	MAX335CN serial octal switch	R3 C1
1945	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	AD712JN – Hi speed BIFET	R3 C2
1946	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	LF444CN – quad power JFET opamp	R3 C3
1947	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	PCM1702 – DAC 20 bit	R3 C4
1948	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	OP467GP precision high speed quad opamp	R3 C5
1949	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	2322-691-90001 – capacitive humidity sensor	R3 C6
1950	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	OP27G – op amp	R3 C7
1951	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	OP37GP – ultra low offset op amp	R3 C8
1952	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	AD736JN – low power RMS to DC converter	R4 C1
1953	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	AD630AD – IC mod/demod	R4 C2
1954	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	OPA2350PA – dual op amp	R4 C3
1955	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	MAX319CPA – SPDT CMOS analog switch	R4 C4
1956	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	LM567CN – PLL tone decoder	R4 C5
1957	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	PTC 1A	R4 C6
1958	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	TVS 6.8V	R4 C7
1959	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	TVS 12V	R4 C8
1960	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	TVS 15V	R5 C1
1961	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	TVS 18V	R5 C2
1962	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	TVS 20V	R5 C3
1963	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	TVS 23.1-37.5V	R5 C4
1964	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	TVS 27V	R5 C5
1965	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	TVS 30V	R5 C6
1966	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	GP02-40 – diode – 4000V 0.25A	R5 C7
1967	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	GP02-40 – diode – 4000V 0.25A	R5 C8
1968	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	Zener diode 2.4V	R6 C1
1969	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	Zener diode – 3.9V	R6 C2
1970	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	Zener diode 5.6V 5W 1N5339B	R6 C3
1971	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	NTC CL11	R6 C4
1972	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	LF311H	R6 C5
1973	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	LM343H	R6 C6
1974	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	LM79M5CT	R6 C7
1975	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	LM79M5CT	R6 C8
1976	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	P7258ND	R7 C1
1977	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	WM-2539 8 position	R7 C2
1978	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	WM-2901 3 position with latch	R7 C3
1979	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	WM-8040 16 position (2x8)	R7 C4
1980	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	A14283-ND conn recep HSG 4 pos Uni-Mate	R7 C5
1981	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	A113189-ND conn pkg 4 pos	R7 C6
1982	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	BAS70XY – General-purpose quadruple Schottky diode	R7 C7
1983	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	LP2951CN – IC Reg linear pos adj 100mA 8-DIP	R7 C8
1984	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	EVQ-Q2Y02W – switch It 6mm 350GF H=2.5mm SMD	R8 C1
1985	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	EVQ-PLDA15 – switch It – SMD	R8 C2
1986	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	P12307SCT-ND – EVQ-P4M03K – switch – SMD	R8 C3
1987	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	CHP-Q21TB – switch DIP piano style 2-pos SMD	R8 C4
1988	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	Light touch switch SMD 5mm – EVQ-PLHA15	R8 C5
1989	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	7814G-1-023E – switch, 4mm sq SPDT SMD 2000 LIFE	R8 C6
1990	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	VFT2045BP diode – Trench MOS Barrier Schottky Rectifier for PV Solar Cell Bypass	R8 C7
1991	REAR PARTS AREA	Shelf 4-8x8 drawer unit RIGHT	Protection Ultra Low VF = 0.33 V at IF = 5 A	R8 C8
1992	BAKER RACKS	End	Wood scraps	
1993	BAKER RACKS	End	Excess resistors; 150k to 22M resistors	
1994	BAKER RACKS	End	Ribbon cable (cable only)	
1995	REAR PARTS AREA	Shelf 1 – Column A	IXTH8P50 – Mosfet P-CH	
1996	REAR PARTS AREA	Shelf 1 – Column A	IXTH10P50 – Mosfet P-CH	
1997	REAR PARTS AREA	Shelf 1 – Column A	IXTH11P50 – Mosfet P-CH	
1998	REAR PARTS AREA	Shelf 1 – Column A	IXFH16N50P – Mosfet N-CH	
1999	REAR PARTS AREA	Shelf 1 – Column A	IRFB3207PBF – Mosfet N-CH	
2000	REAR PARTS AREA	Shelf 1 – Column A	IRF740 IRL7833	
2001	REAR PARTS AREA	Shelf 1 – Column A	IRFB16N50K – Mosfet N-CH	
2002	REAR PARTS AREA	Shelf 1 – Column A	IRL2703 – HEX/MOS N-CH	
2003	REAR PARTS AREA	Shelf 1 – Column A	TC427CP – Mosfet driver	
2004	REAR PARTS AREA	Shelf 1 – Column A	TC4432CPA – Mosfet driver	
2005	REAR PARTS AREA	Shelf 1 – Column A	IRF9540 – Mosfet P-CH	
2006	REAR PARTS AREA	Shelf 1 – Column A	IRF1324PBF – HEX/MOS N-CH	
2007	REAR PARTS AREA	Shelf 1 – Column A	IRFB4212PBF – Mosfet N-CH	
2008	REAR PARTS AREA	Shelf 1 – Column A	IRFB110GPBF – Mosfet N-CH	
2009	REAR PARTS AREA	Shelf 1 – Column A	AT30D60BHBG Diode Array	
2010	REAR PARTS AREA	Shelf 1 – Column A	APT30M75BLL – Power MOSFET 300V 44A	
2011	REAR PARTS AREA	Shelf 1 – Column A	APT30D40BG Rectifier Diode 400V 30A	
2012	REAR PARTS AREA	Shelf 1 – Column A	1N4002 rectifier diode	
2013	REAR PARTS AREA	Shelf 1 – Column A	1N2326 temperature compensating diode	
2014	REAR PARTS AREA	Shelf 1 – Column A	1N4004 – 1N4007	
2015	REAR PARTS AREA	Shelf 1 – Column A	1N3600 – 1N4001	
2016	REAR PARTS AREA	Shelf 1 – Column A	1N4148 – 1N4733	
2017	REAR PARTS AREA	Shelf 1 – Column A	1N4735 – 1N4742	
2018	REAR PARTS AREA	Shelf 1 – Column A	3.3V Zener	
2019	REAR PARTS AREA	Shelf 1 – Column A	4.3V Zener	
2020	REAR PARTS AREA	Shelf 1 – Column A	1N5232 5.6V Zener	
2021	REAR PARTS AREA	Shelf 1 – Column A	6.8V – 7.2V – 8.2V Zener	

2022	REAR PARTS AREA	Shelf 1 – Column A	1N5238 8.1V Zener – 9.1V 10V	
2023	REAR PARTS AREA	Shelf 1 – Column A	1N5741 11V Zener - 1N5742 12V Zener – 1N5743 Zener	
2024	REAR PARTS AREA	Shelf 1 – Column A	1N5244 14V Zener – 1N5245 15V Zener – 1N5246 16V Zener	
2025	REAR PARTS AREA	Shelf 1 – Column A	1N5747 17V Zener – 1N5248 18V Zener – 1N5249 19V Zener	
2026	REAR PARTS AREA	Shelf 1 – Column A	1N5250 20V Zener – 1N5251 22V Zener – 1N5254 24V Zener	
2027	REAR PARTS AREA	Shelf 1 – Column A	1N5253 25V Zener – 26V Zener	
2028	REAR PARTS AREA	Shelf 1 – Column A	1N5258B-TR 36V Zener	
2029	REAR PARTS AREA	Shelf 1 – Column A	1N5401 Zener – 1N5404 Zener – EMPTY	
2030	REAR PARTS AREA	Shelf 1 – Column A	Zener 1N4730-3.9V;1N4732-4.7V;1N4733-5.1V;1N4736-6.8V; 1N4737-7.5V;1N4739-9.1V;1N4740-10V	
2031	REAR PARTS AREA	Shelf 1 – Column B	4N26 OPTO – 6N137	R1 C1
2032	REAR PARTS AREA	Shelf 1 – Column B	4N33 OPTO – 4N25	R1 C2
2033	REAR PARTS AREA	Shelf 1 – Column B	4N36 OPTO	R1 C3
2034	REAR PARTS AREA	Shelf 1 – Column B	OPT101	R1 C4
2035	REAR PARTS AREA	Shelf 1 – Column B	PGA205BP IC PROG GAIN AMP	R1 C5
2036	REAR PARTS AREA	Shelf 1 – Column B	1N5231 – 5.1V Zener	R1 C6
2037	REAR PARTS AREA	Shelf 1 – Column B	1N914A	R1 C7
2038	REAR PARTS AREA	Shelf 1 – Column B	1N4005	R1 C8
2039	REAR PARTS AREA	Shelf 1 – Column B	RC4136 OPAMP	R2 C1
2040	REAR PARTS AREA	Shelf 1 – Column B	NTE3040 OPTO NPN	R2 C2
2041	REAR PARTS AREA	Shelf 1 – Column B	FGH80N60F02 IGBT	R2 C3
2042	REAR PARTS AREA	Shelf 1 – Column B	FB260N	R2 C4
2043	REAR PARTS AREA	Shelf 1 – Column B	1N5230 Zener 4.7V	R2 C5
2044	REAR PARTS AREA	Shelf 1 – Column B	458AG3	R2 C6
2045	REAR PARTS AREA	Shelf 1 – Column B	1N4151	R2 C7
2046	REAR PARTS AREA	Shelf 1 – Column B	LM2575HV Step down regulator	R2 C8
2047	REAR PARTS AREA	Shelf 1 – Column B	1N4744A Zener 15V	R3 C1
2048	REAR PARTS AREA	Shelf 1 – Column B	1N5234B 6.2V Zener	R3 C2
2049	REAR PARTS AREA	Shelf 1 – Column B	1N964B 11.7V Zener	R3 C3
2050	REAR PARTS AREA	Shelf 1 – Column B	1N5350B 13V 1A 5W Zener	R3 C4
2051	REAR PARTS AREA	Shelf 1 – Column B	2E28 8.2V 2W Zener	R3 C5
2052	REAR PARTS AREA	Shelf 1 – Column B	ZRC330A03 – IC REF 3.3V 3%	R3 C6
2053	REAR PARTS AREA	Shelf 1 – Column B	LM2940S-10 12V 1.5A LDO REG	R3 C7
2054	REAR PARTS AREA	Shelf 1 – Column B	1N5399	R3 C8
2055	REAR PARTS AREA	Shelf 1 – Column B	1N4728 3.3V Zener	R4 C1
2056	REAR PARTS AREA	Shelf 1 – Column B	1N4735 6.2V Zener	R4 C2
2057	REAR PARTS AREA	Shelf 1 – Column B	1N4742 12V Zener	R4 C3
2058	REAR PARTS AREA	Shelf 1 – Column B	1N4743 13V Zener	R4 C4
2059	REAR PARTS AREA	Shelf 1 – Column B	1N4746 18V Zener	R4 C5
2060	REAR PARTS AREA	Shelf 1 – Column B	1N4747A 20V Zener	R4 C6
2061	REAR PARTS AREA	Shelf 1 – Column B	GP10Y DIODE 1.6kV 1A	R4 C7
2062	REAR PARTS AREA	Shelf 1 – Column B	1N5819	R4 C8
2063	REAR PARTS AREA	Shelf 1 – Column B	1N4729 3.6V Zener	R5 C1
2064	REAR PARTS AREA	Shelf 1 – Column B	1N4743 5.6V Zener	R5 C2
2065	REAR PARTS AREA	Shelf 1 – Column B	1N5232B 5.6V Zener	R5 C3
2066	REAR PARTS AREA	Shelf 1 – Column B	1N961B 10V Zener	R5 C4
2067	REAR PARTS AREA	Shelf 1 – Column B	1N4750 27V Zener	R5 C5
2068	REAR PARTS AREA	Shelf 1 – Column B	1N4751 30V Zener	R5 C6
2069	REAR PARTS AREA	Shelf 1 – Column B	1N746A 3.3V Zener	R5 C7
2070	REAR PARTS AREA	Shelf 1 – Column B	1N5266	R5 C8
2071	REAR PARTS AREA	Shelf 1 – Column B	1N9598 8.2V Zener	R6 C1
2072	REAR PARTS AREA	Shelf 1 – Column B	1N5338 5.1V 5W Zener	R6 C2
2073	REAR PARTS AREA	Shelf 1 – Column B	2E26.2D5 6.2V Zener	R6 C3
2074	REAR PARTS AREA	Shelf 1 – Column B	1N5349 12V Zener	R6 C4
2075	REAR PARTS AREA	Shelf 1 – Column B	1N5258B	R6 C5
2076	REAR PARTS AREA	Shelf 1 – Column B	Step down to USB power	R6 C6
2077	REAR PARTS AREA	Shelf 1 – Column B	LM317	R6 C7
2078	REAR PARTS AREA	Shelf 1 – Column B	Pololu 3.3V Voltage regulator	R6 C8
2079	REAR PARTS AREA	Shelf 1 – Column B	STTH8L06D ultrafast diode	R7 C1
2080	REAR PARTS AREA	Shelf 1 – Column B	1N4733 5.1V Zener 1W 1%	R7 C2
2081	REAR PARTS AREA	Shelf 1 – Column B	ULN2003AN	R7 C3
2082	REAR PARTS AREA	Shelf 1 – Column B	MLT04 4 QUAD ANALOG MULT	R7 C4
2083	REAR PARTS AREA	Shelf 1 – Column B	Pololu 3.3V Step up/down #2122	R7 C5
2084	REAR PARTS AREA	Shelf 1 – Column B	Pololu 5V Step up #2562	R7 C6
2085	REAR PARTS AREA	Shelf 1 – Column B	HFA08TB60 Diode 600V 8A; 60S1-TP 100V 6A diode	R7 C7
2086	REAR PARTS AREA	Shelf 1 – Column B	20L15T Schottky Rectifier 20A Low V drop	R7 C8
2087	REAR PARTS AREA	Shelf 1 – Column B	DIODE UNKNOWN; ULN2064B	R8 C1
2088	REAR PARTS AREA	Shelf 1 – Column B	MBR160 Schottky diode 60V 1A	R8 C2
2089	REAR PARTS AREA	Shelf 1 – Column B	1N5817G; 1N5817RLG	R8 C3
2090	REAR PARTS AREA	Shelf 1 – Column B	STPS10L25D Schottky 25V 10A; STPS5L40 Schottky 40V 5 A DO-201 diodes	R8 C4
2091	REAR PARTS AREA	Shelf 1 – Column B	SA33CA TVS Diode 33V	R8 C5
2092	REAR PARTS AREA	Shelf 1 – Column B	SA24CA	R8 C6
2093	REAR PARTS AREA	Shelf 1 – Column B	V30100S-E3/45 – Schottky 30A 100V	R8 C7
2094	REAR PARTS AREA	Shelf 1 – Column B	SK5050C Schottky barrier 50A 50V	R8 C8
2095	REAR PARTS AREA	Shelf 1 – Column C	UA7810CKC 10V 1.5A Voltage regulator	
2096	REAR PARTS AREA	Shelf 1 – Column C	PSMN070 FET; ZVN4206A N-CH FET	
2097	REAR PARTS AREA	Shelf 1 – Column C	TLV2404IN	
2098	REAR PARTS AREA	Shelf 1 – Column C	OPA241PA	
2099	REAR PARTS AREA	Shelf 1 – Column C	LM324 QUAD OP AMP	
2100	REAR PARTS AREA	Shelf 1 – Column C	LM358	
2101	REAR PARTS AREA	Shelf 1 – Column C	UA741N	
2102	REAR PARTS AREA	Shelf 1 – Column C	UA741CP	
2103	REAR PARTS AREA	Shelf 1 – Column C	LM7809	
2104	REAR PARTS AREA	Shelf 1 – Column C	OPA347 – OPA137P	
2105	REAR PARTS AREA	Shelf 1 – Column C	LM348	
2106	REAR PARTS AREA	Shelf 1 – Column C	LM340	
2107	REAR PARTS AREA	Shelf 1 – Column C	LM395	
2108	REAR PARTS AREA	Shelf 1 – Column C	LT1073 Voltage regulator	
2109	REAR PARTS AREA	Shelf 1 – Column C	LM7805	
2110	REAR PARTS AREA	Shelf 1 – Column C	LM7812 Voltage regulator	
2111	REAR PARTS AREA	Shelf 1 – Column C	LT1077CN8 IC precision OPAMP Micpwr Single	
2112	REAR PARTS AREA	Shelf 1 – Column C	PT78ST115H 15V 1.5A Voltage regulator	
2113	REAR PARTS AREA	Shelf 1 – Column C	TLC3702IP IC voltage comparator	
2114	REAR PARTS AREA	Shelf 1 – Column C	OPA445AP IC OPAMP 2 MHz	
2115	REAR PARTS AREA	Shelf 1 – Column C	LT1496IN IC OPAMP Rail-Rail In/out Quad	
2116	REAR PARTS AREA	Shelf 1 – Column C	UA747CN IC OPAMP Dual	
2117	REAR PARTS AREA	Shelf 1 – Column C	TLV3701IP	
2118	REAR PARTS AREA	Shelf 1 – Column C	LM78L12ACZ 12V 0.1A voltage regulator	
2119	REAR PARTS AREA	Shelf 1 – Column C	UA7815 15V 1.5A voltage regulator	
2120	REAR PARTS AREA	Shelf 1 – Column C	CL210 inrush limiter 1.5A 30 Ohm	
2121	REAR PARTS AREA	Shelf 1 – Column C	LT1173CS8 MAX666CPA IC voltage regulator dual mode 5V	
2122	REAR PARTS AREA	Shelf 1 – Column C	74F675APC IC Reg serial in serial-parallel out	
2123	REAR PARTS AREA	Shelf 1 – Column C	TLE2426IP ½ rail virtual ground	
2124	REAR PARTS AREA	Shelf 1 – Column C	TL2352IP IC differential comparator	

2125	REAR PARTS AREA	Shelf 1 – Column C	LM3916 Dot bar driver	
2126	REAR PARTS AREA	Shelf 1 – Column C	1N4148 100V 200mA Diode	
2127	REAR PARTS AREA	Shelf 1 – Column C	1N4007	
2128	REAR PARTS AREA	Shelf 1 – Column C	1N914A	
2129	REAR PARTS AREA	Shelf 1 – Column C	1N752A 5.6V Zener	
2130	REAR PARTS AREA	Shelf 1 – Column C	RPG10M 1000V; 1N5408G 1000V 3A diode	
2131	REAR PARTS AREA	Shelf 1 – Column C	1N4448 100V	
2132	REAR PARTS AREA	Shelf 1 – Column C	HER305 3A 400V Diode	
2133	REAR PARTS AREA	Shelf 1 – Column C	1N4001	
2134	REAR PARTS AREA	Shelf 1 – Column C	Zener diode kit; 3.3V; 4.7V; 5.1V; 6.2V; 7.5V; 8.2V; 9V; 10V; 12V; 15V; 18V; 24V; 27V; 30V;	
2135	REAR PARTS AREA	Shelf 1 – Column C	Schottky 100V 3A; 1N5229; 1N5223; 1N5221	
2136	REAR PARTS AREA	Shelf 1 – Column C	Diode kit	
2136	REAR PARTS AREA	Shelf 1 – Column C	HER303 2A 300V	
2137	REAR PARTS AREA	Shelf 1 – Column C	ECG198; ECG126; ECG123 Sylvania semiconductor	
2138	REAR PARTS AREA	Shelf 1 – Column D	1000uF 6.3V	R1 C1
2139	REAR PARTS AREA	Shelf 1 – Column D	2200uF 6.3V	R1 C2
2140	REAR PARTS AREA	Shelf 1 – Column D	4700uF 6.3V	R1 C3
2141	REAR PARTS AREA	Shelf 1 – Column D	33uF 16V	R1 C4
2142	REAR PARTS AREA	Shelf 1 – Column D	10uF 16V	R1 C5
2143	REAR PARTS AREA	Shelf 1 – Column D	220uF 16V	R1 C6
2144	REAR PARTS AREA	Shelf 1 – Column D	470uF 16V	R2 C1
2145	REAR PARTS AREA	Shelf 1 – Column D	22uF 25V; 47uF 25V	R2 C2
2146	REAR PARTS AREA	Shelf 1 – Column D	100uF 25V	R2 C3
2147	REAR PARTS AREA	Shelf 1 – Column D	220uF 25V; 470uF 25V	R2 C4
2148	REAR PARTS AREA	Shelf 1 – Column D	1000uF 25V	R2 C5
2149	REAR PARTS AREA	Shelf 1 – Column D	2000uF 25V	R2 C6
2150	REAR PARTS AREA	Shelf 1 – Column D	0.33uF 35V	R3 C1
2151	REAR PARTS AREA	Shelf 1 – Column D	10uF 35V	R3 C2
2152	REAR PARTS AREA	Shelf 1 – Column D	33uF 35V	R3 C3
2153	REAR PARTS AREA	Shelf 1 – Column D	47uF 35V	R3 C4
2154	REAR PARTS AREA	Shelf 1 – Column D	100uF 35V	R3 C5
2155	REAR PARTS AREA	Shelf 1 – Column D	220uF 35V	R3 C6
2156	REAR PARTS AREA	Shelf 1 – Column D	1000uF 35V	R4 C1
2157	REAR PARTS AREA	Shelf 1 – Column D	0.22uF 50V aluminum	R4 C2
2158	REAR PARTS AREA	Shelf 1 – Column D	0.47uF 50V; 0.47uF 100V	R4 C3
2159	REAR PARTS AREA	Shelf 1 – Column D	1uF 50V aluminum	R4 C4
2160	REAR PARTS AREA	Shelf 1 – Column D	2.2uF 50V	R4 C5
2161	REAR PARTS AREA	Shelf 1 – Column D	3.3uF 50V	R4 C6
2162	REAR PARTS AREA	Shelf 1 – Column D	1800uF 6.3V	R5 C1
2163	REAR PARTS AREA	Shelf 1 – Column D	4.7uF 50V aluminum	R5 C2
2164	REAR PARTS AREA	Shelf 1 – Column D	10uF 50V	R5 C3
2165	REAR PARTS AREA	Shelf 1 – Column D	47uF 50V	R5 C4
2166	REAR PARTS AREA	Shelf 1 – Column D	100uF 50V	R5 C5
2167	REAR PARTS AREA	Shelf 1 – Column D	330uF 50V	R5 C6
2168	REAR PARTS AREA	Shelf 1 – Column D	470uF 50V	R6 C1
2169	REAR PARTS AREA	Shelf 1 – Column D	2200uF 50V	R6 C2
2170	REAR PARTS AREA	Shelf 1 – Column D	220uF 63V	R6 C3
2171	REAR PARTS AREA	Shelf 1 – Column D	100uF 16V	R6 C4
2172	REAR PARTS AREA	Shelf 1 – Column D	1000uF 16V – 1000uF 63V	R6 C5
2173	REAR PARTS AREA	Shelf 1 – Column D	470uF 35V	R6 C6
2174	REAR PARTS AREA	Shelf 1 – Column D	1900uF 40V	R7 C1
2175	REAR PARTS AREA	Shelf 1 – Column D	0.01uF 100V	R7 C2
2176	REAR PARTS AREA	Shelf 1 – Column D	220uF 100V	R7 C3
2177	REAR PARTS AREA	Shelf 1 – Column D	320pF	R7 C4
2178	REAR PARTS AREA	Shelf 1 – Column D	0.22uF 25V	R7 C5
2179	REAR PARTS AREA	Shelf 1 – Column D	UNKNOWN	R7 C6
2180	REAR PARTS AREA	Shelf 1 – Column D	1000uF 50V	R8 C1
2181	REAR PARTS AREA	Shelf 1 – Column D	150uF 385V	R8 C2
2182	REAR PARTS AREA	Shelf 1 – Column D	3300uF 10V	R8 C3
2183	REAR PARTS AREA	Shelf 1 – Column D	0.0033uF	R8 C4
2184	REAR PARTS AREA	Shelf 1 – Column D	0.033uF 25V	R8 C5
2185	REAR PARTS AREA	Shelf 1 – Column D	100 pF	R8 C6
2186	REAR PARTS AREA	Shelf 1 – Column D	2.2uF 400V	R9 C1
2187	REAR PARTS AREA	Shelf 1 – Column D	150uF 385V	R9 C2
2188	REAR PARTS AREA	Shelf 1 – Column D	1500uF 16V	R9 C3
2189	REAR PARTS AREA	Shelf 1 – Column D	0.0047uF	R9 C4
2190	REAR PARTS AREA	Shelf 1 – Column D	650pF	R9 C5
2191	REAR PARTS AREA	Shelf 1 – Column D	470pF	R9 C6
2192	REAR PARTS AREA	Shelf 1 – Column D	8200uF 10V	R10 C1
2193	REAR PARTS AREA	Shelf 1 – Column D	1200uF 10V	R10 C2
2194	REAR PARTS AREA	Shelf 1 – Column D	TO SORT	R10 C3
2195	REAR PARTS AREA	Shelf 1 – Column D	0.0068uF	R10 C4
2196	REAR PARTS AREA	Shelf 1 – Column D	0.047uF 25V, 250V	R10 C5
2197	REAR PARTS AREA	Shelf 1 – Column D	0.1uF 50V; 0.1uF 100V	R10 C6
2198	REAR PARTS AREA	Shelf 1 – Column D	0.33uF	R11 C1
2199	REAR PARTS AREA	Shelf 1 – Column D	10nF = 0.01uF JAMECO	R11 C2
2200	REAR PARTS AREA	Shelf 1 – Column D	0.001uF	R11 C3
2201	REAR PARTS AREA	Shelf 1 – Column D	0.0015uF	R11 C4
2202	REAR PARTS AREA	Shelf 1 – Column D	0.01uF 50V	R11 C5
2203	REAR PARTS AREA	Shelf 1 – Column D	2200pF 250V	R11 C6
2204	REAR PARTS AREA	Shelf 1 – Column D	68pF	R12 C1
2205	REAR PARTS AREA	Shelf 1 – Column D	0.1uF 100V ceramic	R12 C2
2206	REAR PARTS AREA	Shelf 1 – Column D	15uF 350V	R12 C3
2207	REAR PARTS AREA	Shelf 1 – Column D	PTC C860 Thermistor	R12 C4
2208	REAR PARTS AREA	Shelf 1 – Column D	0.47uF-390pF-1000pF-2200pF-4700pF; 1000V	R12 C5
2209	REAR PARTS AREA	Shelf 1 – Column D	47pF, 1500pF-5600pF-6800pF; 100V	R12 C6
2210	REAR PARTS AREA	Shelf 1 – Column E	100uF 6.3V	
2211	REAR PARTS AREA	Shelf 1 – Column E	0.047uF 80V poly film	
2212	REAR PARTS AREA	Shelf 1 – Column E	1000uF 100V	
2213	REAR PARTS AREA	Shelf 1 – Column E	0.15uF 100V	
2214	REAR PARTS AREA	Shelf 1 – Column E	0.039uF 100V	
2215	REAR PARTS AREA	Shelf 1 – Column E	47uF 6.3V	
2216	REAR PARTS AREA	Shelf 1 – Column E	0.001uF 50V	
2217	REAR PARTS AREA	Shelf 1 – Column E	0.00056uF 50V 0.0047uF 50V	
2218	REAR PARTS AREA	Shelf 1 – Column E	47 uF 25V	
2219	REAR PARTS AREA	Shelf 1 – Column E	0.22uF 63V metal film	
2220	REAR PARTS AREA	Shelf 1 – Column E	0.33uF 100V 0.33uF 50V	
2221	REAR PARTS AREA	Shelf 1 – Column E	470pF	
2222	REAR PARTS AREA	Shelf 1 – Column E	3.3uF tantalum	
2223	REAR PARTS AREA	Shelf 1 – Column E	10uF 10V, 16V, 25V tantalum	
2224	REAR PARTS AREA	Shelf 1 – Column E	47pF	
2225	REAR PARTS AREA	Shelf 1 – Column E	1uF 50V	
2226	REAR PARTS AREA	Shelf 1 – Column E	470pF axial	
2227	REAR PARTS AREA	Shelf 1 – Column E	1uF 63V	

2228	REAR PARTS AREA	Shelf 1 – Column E	2pF ceramic
2229	REAR PARTS AREA	Shelf 1 – Column E	3pF ceramic
2230	REAR PARTS AREA	Shelf 1 – Column E	5pF ceramic; 4.7pF 50V
2231	REAR PARTS AREA	Shelf 1 – Column E	10pF ceramic
2232	REAR PARTS AREA	Shelf 1 – Column E	15pF ceramic
2233	REAR PARTS AREA	Shelf 1 – Column E	22pF ceramic
2234	REAR PARTS AREA	Shelf 1 – Column E	30pF ceramic
2235	REAR PARTS AREA	Shelf 1 – Column E	33pF ceramic
2236	REAR PARTS AREA	Shelf 1 – Column E	47pF ceramic
2237	REAR PARTS AREA	Shelf 1 – Column E	68pF ceramic
2238	REAR PARTS AREA	Shelf 1 – Column E	75pF ceramic
2239	REAR PARTS AREA	Shelf 1 – Column E	82pF ceramic
2240	REAR PARTS AREA	Shelf 1 – Column E	100pF ceramic
2241	REAR PARTS AREA	Shelf 1 – Column E	150pF ceramic
2242	REAR PARTS AREA	Shelf 1 – Column E	220pF ceramic
2243	REAR PARTS AREA	Shelf 1 – Column E	330pF ceramic
2244	REAR PARTS AREA	Shelf 1 – Column E	470pF ceramic
2245	REAR PARTS AREA	Shelf 1 – Column E	680pF ceramic
2246	REAR PARTS AREA	Shelf 1 – Column E	1.0nF ceramic 1000pF 50V
2247	REAR PARTS AREA	Shelf 1 – Column E	1.5nF ceramic
2248	REAR PARTS AREA	Shelf 1 – Column E	2.2nF ceramic
2249	REAR PARTS AREA	Shelf 1 – Column E	3.3nF ceramic
2250	REAR PARTS AREA	Shelf 1 – Column E	4.7nF ceramic
2251	REAR PARTS AREA	Shelf 1 – Column E	6.8nF ceramic
2252	REAR PARTS AREA	Shelf 1 – Column E	10nF ceramic
2253	REAR PARTS AREA	Shelf 1 – Column E	15nF ceramic – EMPTY
2254	REAR PARTS AREA	Shelf 1 – Column E	22nF ceramic– EMPTY
2255	REAR PARTS AREA	Shelf 1 – Column E	47nF ceramic
2256	REAR PARTS AREA	Shelf 1 – Column E	68nF ceramic– EMPTY
2257	REAR PARTS AREA	Shelf 1 – Column E	100nF ceramic– EMPTY
2258	REAR PARTS AREA	Shelf 1 – Column E	470pF5 0V
2259	REAR PARTS AREA	Shelf 1 – Column E	2200uF 10V aluminum
2260	REAR PARTS AREA	Shelf 1 – Column E	0.1uF unknown V
2261	REAR PARTS AREA	Shelf 1 – Column E	3.3uF 35V
2262	REAR PARTS AREA	Shelf 1 – Column E	Variable capacitor
2263	REAR PARTS AREA	Shelf 1 – Column E	Trim capacitor
2264	REAR PARTS AREA	Shelf 1 – Column E	10uF 35V
2265	REAR PARTS AREA	Shelf 1 – Column E	0.1uF 35V Jameco 33486
2266	REAR PARTS AREA	Shelf 1 – Column E	1uF 35V Jameco 33662
2267	REAR PARTS AREA	Shelf 1 – Column E	0.47uF 35V Jameco 33531
2268	REAR PARTS AREA	Shelf 1 – Column E	33uF 25V
2269	REAR PARTS AREA	Shelf 1 – Column E	4.7uF 25V
2270	REAR PARTS AREA	Shelf 1 – Column F	0 Ohm, 1 Ohm
2271	REAR PARTS AREA	Shelf 1 – Column F	2 Ohm
2272	REAR PARTS AREA	Shelf 1 – Column F	4.3 Ohm, 4.7 Ohm
2273	REAR PARTS AREA	Shelf 1 – Column F	100 Ohm, 13 Ohm
2274	REAR PARTS AREA	Shelf 1 – Column F	38.3 Ohm, 40.2 Ohm
2275	REAR PARTS AREA	Shelf 1 – Column F	46.4 Ohm, 51.1 Ohm
2276	REAR PARTS AREA	Shelf 1 – Column F	62 Ohm, 68 Ohm; 71.5 Ohm
2277	REAR PARTS AREA	Shelf 1 – Column F	100 Ohm, 120 Ohm
2278	REAR PARTS AREA	Shelf 1 – Column F	133 Ohm, 147 Ohm
2279	REAR PARTS AREA	Shelf 1 – Column F	150 Ohm, 196 Ohm
2280	REAR PARTS AREA	Shelf 1 – Column F	200 Ohm, 237 Ohm
2281	REAR PARTS AREA	Shelf 1 – Column F	240 Ohm, 261 Ohm
2282	REAR PARTS AREA	Shelf 1 – Column F	287 Ohm, 294 Ohm
2283	REAR PARTS AREA	Shelf 1 – Column F	316 Ohm, 330 Ohm
2284	REAR PARTS AREA	Shelf 1 – Column F	383 Ohm, 390 Ohm
2285	REAR PARTS AREA	Shelf 1 – Column F	464 Ohm, 470 Ohm
2286	REAR PARTS AREA	Shelf 1 – Column F	475 Ohm, 499 Ohm
2287	REAR PARTS AREA	Shelf 1 – Column F	511 Ohm, 562 Ohm
2288	REAR PARTS AREA	Shelf 1 – Column F	750 Ohm, 909 Ohm
2289	REAR PARTS AREA	Shelf 1 – Column F	1K Ohm
2290	REAR PARTS AREA	Shelf 1 – Column F	1.13 kOhm, 1.2 kOhm
2291	REAR PARTS AREA	Shelf 1 – Column F	1.3 kOhm, 1.47 kOhm
2292	REAR PARTS AREA	Shelf 1 – Column F	1.91 kOhm, 1.96 kOhm
2293	REAR PARTS AREA	Shelf 1 – Column F	2 kOhm, 2.15 kOhm
2294	REAR PARTS AREA	Shelf 1 – Column F	2.2 kOhm, 2.4 kOhm
2295	REAR PARTS AREA	Shelf 1 – Column F	2.43 kOhm, 2.49 k Ohm
2296	REAR PARTS AREA	Shelf 1 – Column F	2.61 kOhm, 2.8 kOhm
2297	REAR PARTS AREA	Shelf 1 – Column F	3.3 kOhm, 3.92 kOhm; 4kOhm
2298	REAR PARTS AREA	Shelf 1 – Column F	4.64 kOhm, 4.7 kOhm
2299	REAR PARTS AREA	Shelf 1 – Column F	4.99 kOhm, 5.1 kOhm
2300	REAR PARTS AREA	Shelf 1 – Column F	5.1 kOhm, 6.19 kOhm
2301	REAR PARTS AREA	Shelf 1 – Column F	6.81 kOhm, 6.98 kOhm
2302	REAR PARTS AREA	Shelf 1 – Column F	8.06 kOhm, 8.25 kOhm
2303	REAR PARTS AREA	Shelf 1 – Column F	9.09 kOhm, 12.1 kOhm
2304	REAR PARTS AREA	Shelf 1 – Column F	10 kOhm
2305	REAR PARTS AREA	Shelf 1 – Column F	12.7 kOhm, 14 kOhm
2306	REAR PARTS AREA	Shelf 1 – Column F	14.3 kOhm, 14.7 kOhm
2307	REAR PARTS AREA	Shelf 1 – Column F	16.9 kOhm
2308	REAR PARTS AREA	Shelf 1 – Column F	19.1 kOhm, 19.6 kOhm
2309	REAR PARTS AREA	Shelf 1 – Column F	20 kOhm, 20.5 kOhm
2310	REAR PARTS AREA	Shelf 1 – Column F	21.5 kOhm, 22kOhm
2311	REAR PARTS AREA	Shelf 1 – Column F	22.1 kOhm, 23 kOhm
2312	REAR PARTS AREA	Shelf 1 – Column F	24.3 kOhm, 25.5 kOhm
2313	REAR PARTS AREA	Shelf 1 – Column F	26.1 kOhm, 28 kOhm
2314	REAR PARTS AREA	Shelf 1 – Column F	27 kOhm, 28.7 kOhm
2315	REAR PARTS AREA	Shelf 1 – Column F	30 kOhm, 33 kOhm
2316	REAR PARTS AREA	Shelf 1 – Column F	34 kOhm, 34.8 kOhm
2317	REAR PARTS AREA	Shelf 1 – Column F	36 kOhm 38.3 kOhm
2318	REAR PARTS AREA	Shelf 1 – Column F	39 kOhm, 39.2 kOhm
2319	REAR PARTS AREA	Shelf 1 – Column F	46.4 kOhm, 47 kOhm
2320	REAR PARTS AREA	Shelf 1 – Column F	47.5 kOhm, 49.9 kOhm
2321	REAR PARTS AREA	Shelf 1 – Column F	51.1 kOhm, 56.2 kOhm
2322	REAR PARTS AREA	Shelf 1 – Column F	60.4 kOhm, 61.9 kOhm
2323	REAR PARTS AREA	Shelf 1 – Column F	68 kOhm, 68.1 kOhm
2324	REAR PARTS AREA	Shelf 1 – Column F	73.2 kOhm, 75 kOhm
2325	REAR PARTS AREA	Shelf 1 – Column F	82 kOhm, 100 kOhm
2326	REAR PARTS AREA	Shelf 1 – Column F	100 kOhm
2327	REAR PARTS AREA	Shelf 1 – Column F	120 kOhm, 137 kOhm
2328	REAR PARTS AREA	Shelf 1 – Column F	150 kOhm, 470 kOhm
2329	REAR PARTS AREA	Shelf 1 – Column F	10 kOhm 9 pin, 330 Ohm 8 pin
2330	REAR PARTS AREA	Shelf 1 – Column F	330 Ohm 10 pin
2331	REAR PARTS AREA	Shelf 1 – Column F	1 kOhm 10 pin

2332	REAR PARTS AREA	Shelf 1 – Column F	10 kOhm 10 pin	
2333	REAR PARTS AREA	Shelf 1 – Column F	Assorted multipin resistors	
2334	REAR PARTS AREA	Shelf 1 – Column F	Resistor kit 1 Ohm – 470 Ohm	
2335	REAR PARTS AREA	Shelf 1 – Column F	Resistor kit 510 Ohm – 12 kOhm	
2336	REAR PARTS AREA	Shelf 1 – Column G	18 Ohm; 22 Ohm	
2337	REAR PARTS AREA	Shelf 1 – Column G	220 Ohm	
2338	REAR PARTS AREA	Shelf 1 – Column G	78.7 Ohm; 220 Ohm	
2339	REAR PARTS AREA	Shelf 1 – Column G	226 Ohm	
2340	REAR PARTS AREA	Shelf 1 – Column G	270 Ohm	
2341	REAR PARTS AREA	Shelf 1 – Column G	301 Ohm	
2342	REAR PARTS AREA	Shelf 1 – Column G	510 Ohm	
2343	REAR PARTS AREA	Shelf 1 – Column G	910 Ohm	
2344	REAR PARTS AREA	Shelf 1 – Column G	1 kOhm	
2345	REAR PARTS AREA	Shelf 1 – Column G	6.65 kOhm	
2346	REAR PARTS AREA	Shelf 1 – Column G	6.81 kOhm	
2347	REAR PARTS AREA	Shelf 1 – Column G	12 kOhm	
2348	REAR PARTS AREA	Shelf 1 – Column G	13 kOhm	
2349	REAR PARTS AREA	Shelf 1 – Column G	15 kOhm; 16.2kOhm	
2350	REAR PARTS AREA	Shelf 1 – Column G	26.7 kOhm	
2351	REAR PARTS AREA	Shelf 1 – Column G	35.7 kOhm	
2352	REAR PARTS AREA	Shelf 1 – Column G	47.5 kOhm	
2353	REAR PARTS AREA	Shelf 1 – Column G	51 kOhm	
2354	REAR PARTS AREA	Shelf 1 – Column G	66.5 kOhm	
2355	REAR PARTS AREA	Shelf 1 – Column G	71.5 kOhm	
2356	REAR PARTS AREA	Shelf 1 – Column G	82 kOhm	
2357	REAR PARTS AREA	Shelf 1 – Column G	130 kOhm	
2358	REAR PARTS AREA	Shelf 1 – Column G	143 kOhm	
2359	REAR PARTS AREA	Shelf 1 – Column G	150 kOhm	
2360	REAR PARTS AREA	Shelf 1 – Column G	158 kOhm	
2361	REAR PARTS AREA	Shelf 1 – Column G	169 kOhm	
2362	REAR PARTS AREA	Shelf 1 – Column G	174 kOhm	
2363	REAR PARTS AREA	Shelf 1 – Column G	180 kOhm; 182 kOhm	
2364	REAR PARTS AREA	Shelf 1 – Column G	191 kOhm	
2365	REAR PARTS AREA	Shelf 1 – Column G	200 kOhm	
2366	REAR PARTS AREA	Shelf 1 – Column G	216 kOhm	
2367	REAR PARTS AREA	Shelf 1 – Column G	221 kOhm	
2368	REAR PARTS AREA	Shelf 1 – Column G	240 kOhm	
2369	REAR PARTS AREA	Shelf 1 – Column G	261 kOhm	
2370	REAR PARTS AREA	Shelf 1 – Column G	EMPTY	
2371	REAR PARTS AREA	Shelf 1 – Column G	301 kOhm	
2372	REAR PARTS AREA	Shelf 1 – Column G	316 kOhm	
2373	REAR PARTS AREA	Shelf 1 – Column G	393 kOhm	
2374	REAR PARTS AREA	Shelf 1 – Column G	415 kOhm	
2375	REAR PARTS AREA	Shelf 1 – Column G	EMPTY	
2376	REAR PARTS AREA	Shelf 1 – Column G	430 kOhm	
2377	REAR PARTS AREA	Shelf 1 – Column G	474 kOhm	
2378	REAR PARTS AREA	Shelf 1 – Column G	750 kOhm	
2379	REAR PARTS AREA	Shelf 1 – Column G	820 kOhm	
2380	REAR PARTS AREA	Shelf 1 – Column G	909 kOhm – EMPTY	
2381	REAR PARTS AREA	Shelf 1 – Column G	1 Mohm	
2382	REAR PARTS AREA	Shelf 1 – Column G	1.5 Mohm	
2383	REAR PARTS AREA	Shelf 1 – Column G	2 Mohm	
2384	REAR PARTS AREA	Shelf 1 – Column G	2.2 Mohm	
2385	REAR PARTS AREA	Shelf 1 – Column G	EMPTY	
2386	REAR PARTS AREA	Shelf 1 – Column G	3.3 Mohm	
2387	REAR PARTS AREA	Shelf 1 – Column G	3.9 Mohm	
2388	REAR PARTS AREA	Shelf 1 – Column G	4.7 Mohm	
2389	REAR PARTS AREA	Shelf 1 – Column G	10 Mohm	
2390	REAR PARTS AREA	Shelf 1 – Column G	EMPTY	
2391	REAR PARTS AREA	Shelf 1 – Column G	20 Mohm	
2392	REAR PARTS AREA	Shelf 1 – Column G	22 Mohm	
2393	REAR PARTS AREA	Shelf 1 – Column G	EMPTY	
2394	REAR PARTS AREA	Shelf 1 – Column G	EMPTY	
2395	REAR PARTS AREA	Shelf 1 – Column G	EMPTY	
2396	REAR PARTS AREA	Shelf 1 – Column G	Resistor kit – 15 kOhm – 10 Mohm	
2397	REAR PARTS AREA	Shelf 2 – Column A	7400	Quad 2 input NAND gate
2398	REAR PARTS AREA	Shelf 2 – Column A	7401	Single 2-input NAD gate
2399	REAR PARTS AREA	Shelf 2 – Column A	7402	quad 2-input NOR gate
2400	REAR PARTS AREA	Shelf 2 – Column A	7403	quad 2-input NAND gate
2401	REAR PARTS AREA	Shelf 2 – Column A	7404	hex inverter gate
2402	REAR PARTS AREA	Shelf 2 – Column A	7405	hex inverter gate
2403	REAR PARTS AREA	Shelf 2 – Column A	7406	hex inverter gate
2404	REAR PARTS AREA	Shelf 2 – Column A	7407	hex Buffer gate
2405	REAR PARTS AREA	Shelf 2 – Column A	7408	quad 2-input AND gate
2406	REAR PARTS AREA	Shelf 2 – Column A	7409	quad 2-input AND gate
2407	REAR PARTS AREA	Shelf 2 – Column A	7410	triple 3-input NAND gate
2408	REAR PARTS AREA	Shelf 2 – Column A	7411	triple 3-input NAND gate
2409	REAR PARTS AREA	Shelf 2 – Column A	7413	dual 4-input NAND gate
2410	REAR PARTS AREA	Shelf 2 – Column A	7414	Hex inverter gate
2411	REAR PARTS AREA	Shelf 2 – Column A	7416	Hex inverter gate
2412	REAR PARTS AREA	Shelf 2 – Column A	7418	dual 4-input NAND gate
2413	REAR PARTS AREA	Shelf 2 – Column A	7420	dual 4-input NAND gate
2414	REAR PARTS AREA	Shelf 2 – Column A	7421	dual 4-input AND gate
2415	REAR PARTS AREA	Shelf 2 – Column A	7426	quad 2-input NAND gate
2416	REAR PARTS AREA	Shelf 2 – Column A	7427	triple 3-input NOR gate
2417	REAR PARTS AREA	Shelf 2 – Column A	74LS30	Single 2-input NAD gate
2418	REAR PARTS AREA	Shelf 2 – Column A	74LS32	quad 2-input OR gate
2419	REAR PARTS AREA	Shelf 2 – Column A	7437	quad 2-input NOR gate
2420	REAR PARTS AREA	Shelf 2 – Column A	74LS38	quad 2-input NAND gate
2421	REAR PARTS AREA	Shelf 2 – Column A	74LS42	BCD to decimal decoder
2422	REAR PARTS AREA	Shelf 2 – Column A	7451	3-3-input AND-OR-Invert gate and 2-2-input AND-OR-Invert gate
2423	REAR PARTS AREA	Shelf 2 – Column A	74LS54	2-2-2-2-input AND-OR-Invert gate
2424	REAR PARTS AREA	Shelf 2 – Column A	7464	4-3-2-2-input AND-OR-Invert gate
2425	REAR PARTS AREA	Shelf 2 – Column A	74LS68	dual J-K flip-flop, asynchronous clear (improved 74L73)
2426	REAR PARTS AREA	Shelf 2 – Column A	7472	AND gated J-K master-slave flip-flop, asynchronous preset and clear
2427	REAR PARTS AREA	Shelf 2 – Column A	7473	dual J-K flip-flop, asynchronous clear
2428	REAR PARTS AREA	Shelf 2 – Column A	7474	dual D positive edge triggered flip-flop, asynchronous preset and clear
2429	REAR PARTS AREA	Shelf 2 – Column A	74LS75	4-bit bistable latch, complementary outputs
2430	REAR PARTS AREA	Shelf 2 – Column A	7476	dual J-K flip-flop, asynchronous preset and clear
2431	REAR PARTS AREA	Shelf 2 – Column A	74LS83	4-bit binary full adder

2432	REAR PARTS AREA	Shelf 2 – Column A	74LS85	4-bit binary full adder
2433	REAR PARTS AREA	Shelf 2 – Column A	7486	quad 2-input XOR gate
2434	REAR PARTS AREA	Shelf 2 – Column A	7489	64-bit RAM (16x4), 4 data inputs, 4 inverted data outputs
2435	REAR PARTS AREA	Shelf 2 – Column A	7490	decade counter (separate divide-by-2 and divide-by-5 sections)
2436	REAR PARTS AREA	Shelf 2 – Column A	74190 COUNTER	synchronous presettable up/down 4-bit decade counter
2437	REAR PARTS AREA	Shelf 2 – Column A	74192 COUNTER	synchronous presettable up/down 4-bit decade counter, clear
2438	REAR PARTS AREA	Shelf 2 – Column A	7493	4-bit binary counter (separate divide-by-2 and divide-by-8 sections);
2439	REAR PARTS AREA	Shelf 2 – Column A	7417	hex Buffer gate
2440	REAR PARTS AREA	Shelf 2 – Column A	74LS95	4-bit shift register, parallel in, parallel out, serial input
2441	REAR PARTS AREA	Shelf 2 – Column A	7496	5-bit parallel-in/parallel-out shift register, asynchronous preset
2442	REAR PARTS AREA	Shelf 2 – Column B	74LS107	Dual J-K flip flops with clear
2443	REAR PARTS AREA	Shelf 2 – Column B	74F109	dual J-NotK positive-edge-triggered flip-flop, clear and preset
2444	REAR PARTS AREA	Shelf 2 – Column B	74LS112 Dual J/K Flip Flop with preset and clear	dual J-K negative-edge-triggered flip-flop, clear and preset
2445	REAR PARTS AREA	Shelf 2 – Column B	74L113 Dual J/K Flip Flop negative edge triggered	dual J-K negative-edge-triggered flip-flop, preset
2446	REAR PARTS AREA	Shelf 2 – Column B	74121 monostable multivibrator	monostable multivibrator
2447	REAR PARTS AREA	Shelf 2 – Column B	74LS123	dual retriggerable monostable multivibrator, clear
2448	REAR PARTS AREA	Shelf 2 – Column B	74LS132 Quad NAND Schmidt Trigger	quad 2-input NAND gate
2449	REAR PARTS AREA	Shelf 2 – Column B	74133 13 Input NAND	single 13-input NAND gate
2450	REAR PARTS AREA	Shelf 2 – Column B	74LS138 3-to-8 decoder/demultiplexer	3-to-8 decoder/demultiplexer
2451	REAR PARTS AREA	Shelf 2 – Column B	74LS139 4-to-1 decoder/demultiplexer	4-to-1 decoder/demultiplexer
2452	REAR PARTS AREA	Shelf 2 – Column B	74148 8-line to 3-line priority encoder	8-line to 3-line priority encoder
2453	REAR PARTS AREA	Shelf 2 – Column B	74LS148	8-line to 3-line priority encoder
2454	REAR PARTS AREA	Shelf 2 – Column B	74150	16-line to 1-line data selector/multiplexer
2455	REAR PARTS AREA	Shelf 2 – Column B	74151	8-line to 1-line data selector/multiplexer
2456	REAR PARTS AREA	Shelf 2 – Column B	74LS153 Dual 4-to-1 data selector/multiplexer	Dual 4-to-1 data selector/multiplexer
2457	REAR PARTS AREA	Shelf 2 – Column B	74154 4-line to 16-line decoder/demux	4-line to 16-line decoder/demux
2458	REAR PARTS AREA	Shelf 2 – Column B	74155 Dual 2-to-4 decoder/demux	Dual 2-to-4 decoder/demux
2459	REAR PARTS AREA	Shelf 2 – Column B	74LS157 Quad 2-to-1 selector/multiplexer non-inverting	Quad 2-to-1 selector/multiplexer non-inverting
2460	REAR PARTS AREA	Shelf 2 – Column B	74LS158 2-to-1 selector, multiplexer, inverting	2-to-1 selector, multiplexer, inverting
2461	REAR PARTS AREA	Shelf 2 – Column B	74161	synchronous presettable 4-bit binary counter, asynchronous clear
2462	REAR PARTS AREA	Shelf 2 – Column B	74LS163	synchronous presettable 4-bit binary counter, synchronous clear
2463	REAR PARTS AREA	Shelf 2 – Column B	74164	8-bit serial-in parallel-out (SIPO) shift register, asynchronous clear, not output latch
2464	REAR PARTS AREA	Shelf 2 – Column B	74165	8-bit parallel-in serial-out (PISO) shift register, parallel load, complementary outputs
2465	REAR PARTS AREA	Shelf 2 – Column B	74LS166	parallel-load 8-bit shift register
2466	REAR PARTS AREA	Shelf 2 – Column B	74LS168 8 b serial out parallel shift register	8 b serial out parallel shift register
2467	REAR PARTS AREA	Shelf 2 – Column B	74170	16-bit register file (4x4)
2468	REAR PARTS AREA	Shelf 2 – Column B	74173	quad D flip-flop, asynchronous clear
2469	REAR PARTS AREA	Shelf 2 – Column B	74174	hex D flip-flop, common asynchronous clear
2470	REAR PARTS AREA	Shelf 2 – Column B	74LS175	quad D edge-triggered flip-flop, complementary outputs and asynchronous clear
2471	REAR PARTS AREA	Shelf 2 – Column B	74177	presettable binary counter/latch
2472	REAR PARTS AREA	Shelf 2 – Column B	74181	4-bit arithmetic logic unit and function generator
2473	REAR PARTS AREA	Shelf 2 – Column B	74182	lookahead carry generator
2474	REAR PARTS AREA	Shelf 2 – Column B	74LS189	64-bit RAM (16x4), 4 data inputs, 4 inverted data outputs
2475	REAR PARTS AREA	Shelf 2 – Column B	74LS191	synchronous presettable up/down 4-bit binary counter
2476	REAR PARTS AREA	Shelf 2 – Column B	74LS194; 74LS195	4-bit bidirectional universal shift register; 4-bit parallel access shift register
2477	REAR PARTS AREA	Shelf 2 – Column B	74198	8-bit bidirectional universal shift register
2478	REAR PARTS AREA	Shelf 2 – Column B	74221	dual monostable multivibrator
2479	REAR PARTS AREA	Shelf 2 – Column B	74240	octal buffer, inverting outputs
2480	REAR PARTS AREA	Shelf 2 – Column B	74LS245; 74LVC245 logic shifter; 74245	octal bus transceiver, non-inverting outputs
2481	REAR PARTS AREA	Shelf 2 – Column B	74LS253	dual 4-line to 1-line data selector/multiplexer
2482	REAR PARTS AREA	Shelf 2 – Column B	74257	quad 2-line to 1-line data selector/multiplexer, non-inverting outputs
2483	REAR PARTS AREA	Shelf 2 – Column B	74LS258	quad 2-line to 1-line data selector/multiplexer, inverting outputs
2484	REAR PARTS AREA	Shelf 2 – Column B	74LS259	8-bit bit addressable input latch with clr
2485	REAR PARTS AREA	Shelf 2 – Column B	DP8304BN 8 bit BIXCVR	8 bit BIXCVR
2486	REAR PARTS AREA	Shelf 2 – Column B	7497	synchronous 6-bit binary rate multiplier
2487	REAR PARTS AREA	Shelf 2 – Column C	74260	dual 5-input NOR gate
2488	REAR PARTS AREA	Shelf 2 – Column C	74265	quad complementary output elements
2489	REAR PARTS AREA	Shelf 2 – Column C	74LS266	quad 2-input XNOR gate
2490	REAR PARTS AREA	Shelf 2 – Column C	74LS273	8-bit register, asynchronous clear
2491	REAR PARTS AREA	Shelf 2 – Column C	74LS279	quad set-reset latch
2492	REAR PARTS AREA	Shelf 2 – Column C	74280	9-bit odd/even parity bit generator/checker
2493	REAR PARTS AREA	Shelf 2 – Column C	74283	4-bit binary full adder (has carry in function)
2494	REAR PARTS AREA	Shelf 2 – Column C	74284	4-bit by 4-bit parallel binary multiplier (high order 4 bits of product)
2495	REAR PARTS AREA	Shelf 2 – Column C	74285	4-bit by 4-bit parallel binary multiplier (low order 4 bits of product)
2496	REAR PARTS AREA	Shelf 2 – Column C	74287	1024-bit PROM (256x4)
2497	REAR PARTS AREA	Shelf 2 – Column C	74293 4 b binary counter	4-bit binary counter (separate divide-by-2 and divide-by-8 sections)
2498	REAR PARTS AREA	Shelf 2 – Column C	74LS298 Quad 2-input mux w/storage	quad 2-input multiplexer, storage
2499	REAR PARTS AREA	Shelf 2 – Column C	74367	hex buffer, non-inverting outputs
2500	REAR PARTS AREA	Shelf 2 – Column C	74LS368	hex buffer, inverting outputs
2501	REAR PARTS AREA	Shelf 2 – Column C	74LS373	octal transparent latch
2502	REAR PARTS AREA	Shelf 2 – Column C	74LS374 octal register	octal register
2503	REAR PARTS AREA	Shelf 2 – Column C	74LS377 8b register with clock enable	8-bit register, clock enable
2504	REAR PARTS AREA	Shelf 2 – Column C	74LS379	4-bit register, clock enable and complementary outputs
2505	REAR PARTS AREA	Shelf 2 – Column C	74LS390 and 74LS393	dual 4-bit binary counter, asynchronous clear; Dual 4-Bit Decade Counters
2506	REAR PARTS AREA	Shelf 2 – Column C	74500	6-bit flash analog-to-digital converter (ADC)
2507	REAR PARTS AREA	Shelf 2 – Column C	74573	octal D-type transparent latch
2508	REAR PARTS AREA	Shelf 2 – Column C	74HC595N shift register; TPIC6B595 high power shift register	8-bit shift registers, serial-in, parallel-out, output latches, output enable
2509	REAR PARTS AREA	Shelf 2 – Column C	74LS670	16-bit register file (4x4)
2510	REAR PARTS AREA	Shelf 2 – Column C	4001	
2511	REAR PARTS AREA	Shelf 2 – Column C	4008	
2512	REAR PARTS AREA	Shelf 2 – Column C	4011	
2513	REAR PARTS AREA	Shelf 2 – Column C	4012	

2514	REAR PARTS AREA	Shelf 2 – Column C	4013/4014	
2515	REAR PARTS AREA	Shelf 2 – Column C	4014	
2516	REAR PARTS AREA	Shelf 2 – Column C	4016	
2517	REAR PARTS AREA	Shelf 2 – Column C	4017	
2518	REAR PARTS AREA	Shelf 2 – Column C	4023	
2519	REAR PARTS AREA	Shelf 2 – Column C	4024	
2520	REAR PARTS AREA	Shelf 2 – Column C	4028	
2521	REAR PARTS AREA	Shelf 2 – Column C	4041	
2522	REAR PARTS AREA	Shelf 2 – Column C	4049	
2523	REAR PARTS AREA	Shelf 2 – Column C	4069	
2524	REAR PARTS AREA	Shelf 2 – Column C	4066	
2525	REAR PARTS AREA	Shelf 2 – Column C	4081	
2526	REAR PARTS AREA	Shelf 2 – Column C	4093	
2527	REAR PARTS AREA	Shelf 2 – Column C	ULN2003A 7 Channel Darlington	
2528	REAR PARTS AREA	Shelf 2 – Column C	CD4070BE	
2529	REAR PARTS AREA	Shelf 2 – Column C	CD40107BE	
2530	REAR PARTS AREA	Shelf 2 – Column C	4027	
2531	REAR PARTS AREA	Shelf 2 – Column C	TL780-12CKC 12V regulator TO-220	
2532	REAR PARTS AREA	Shelf 2 – Column C	DSA2-16A-ND – diode avalanche 1600V 7A axial	
2533	REAR PARTS AREA	Shelf 2 – Column C	74LS624 voltage controlled oscillator	
2534	REAR PARTS AREA	Shelf 2 – Column D	NJM7912FA-ND -12V Regulator TO-220	
2535	REAR PARTS AREA	Shelf 2 – Column D	7905 -5V linear voltage regulator	
2536	REAR PARTS AREA	Shelf 2 – Column D	LM7805-TO-92 +5V linear voltage regulator	
2537	REAR PARTS AREA	Shelf 2 – Column D	LM7915 -15V linear voltage regulator	
2538	REAR PARTS AREA	Shelf 2 – Column D	LM7815 +15V linear voltage regulator	
2539	REAR PARTS AREA	Shelf 2 – Column D	74LS125 – LM7909 -9V 1A regulator	
2540	REAR PARTS AREA	Shelf 2 – Column D	74LS169	
2541	REAR PARTS AREA	Shelf 2 – Column D	7447-74LS114	
2542	REAR PARTS AREA	Shelf 2 – Column D	74244	
2543	REAR PARTS AREA	Shelf 2 – Column D	7440	
2544	REAR PARTS AREA	Shelf 2 – Column D	74160	
2545	REAR PARTS AREA	Shelf 2 – Column D	74122	
2546	REAR PARTS AREA	Shelf 2 – Column D	2206CP function gen – 2207CP voltage control oscillator	
2547	REAR PARTS AREA	Shelf 2 – Column D	7412	
2548	REAR PARTS AREA	Shelf 2 – Column D	UA775-LF353	
2549	REAR PARTS AREA	Shelf 2 – Column D	V7805-1000 DC-DC 5V 5W – LM381	
2550	REAR PARTS AREA	Shelf 2 – Column D	LM566 – LM723	
2551	REAR PARTS AREA	Shelf 2 – Column D	TL083CN-TL080	
2552	REAR PARTS AREA	Shelf 2 – Column D	UA308-LM301	
2553	REAR PARTS AREA	Shelf 2 – Column D	LF347 – LF351N	
2554	REAR PARTS AREA	Shelf 2 – Column D	2N3494 PNP Small signal transistor	
2555	REAR PARTS AREA	Shelf 2 – Column D	SMP50N06 N-Channel MOSFET; LM567 phase lock loop	
2556	REAR PARTS AREA	Shelf 2 – Column D	2N5769	
2557	REAR PARTS AREA	Shelf 2 – Column D	LM336 2.5V reference source	
2558	REAR PARTS AREA	Shelf 2 – Column D	LM339 Quad voltage comparator	
2559	REAR PARTS AREA	Shelf 2 – Column D	LM380N audio power amplifier	
2560	REAR PARTS AREA	Shelf 2 – Column D	LM393 Low offset voltage dual comparators	
2561	REAR PARTS AREA	Shelf 2 – Column D	CP567 phase locked loop	
2562	REAR PARTS AREA	Shelf 2 – Column D	LM3914 dot bar display driver	
2563	REAR PARTS AREA	Shelf 2 – Column D	TIP30 PNP 1 Amp Darlington power transistor	
2564	REAR PARTS AREA	Shelf 2 – Column D	6.3V trans voltage clamp	
2565	REAR PARTS AREA	Shelf 2 – Column D	330uH inductors	
2566	REAR PARTS AREA	Shelf 2 – Column D	1Kx6 resistor network	
2567	REAR PARTS AREA	Shelf 2 – Column D	330 Ohm x 10 resistor network	
2568	REAR PARTS AREA	Shelf 2 – Column D	X9C102P Digital potentiometer	
2569	REAR PARTS AREA	Shelf 2 – Column D	Random resistor nets; various values	
2570	REAR PARTS AREA	Shelf 2 – Column D	APQ2369	
2571	REAR PARTS AREA	Shelf 2 – Column D	MPQ2369	
2572	REAR PARTS AREA	Shelf 2 – Column D	LTC1062	
2573	REAR PARTS AREA	Shelf 2 – Column D	MC14514B	
2574	REAR PARTS AREA	Shelf 2 – Column D	AIR0-02-151K 150uH inductor	
2575	REAR PARTS AREA	Shelf 2 – Column D	MUR3020	
2576	REAR PARTS AREA	Shelf 2 – Column D	MT8888	
2577	REAR PARTS AREA	Shelf 2 – Column D	LF442CN JFET Amp	
2578	REAR PARTS AREA	Shelf 2 – Column D	TL084CN	
2579	REAR PARTS AREA	Shelf 2 – TOP	Dupont connector kits	
2580	REAR PARTS AREA	Shelf 2 – TOP	Resistor kits, various	
2581	REAR PARTS AREA	Shelf 2 – Column D – TOP	Polyswitch resettable fuses (in case)	
2582	REAR PARTS AREA	Shelf 2	TTL Data book, Texas Instruments	
2583	REAR PARTS AREA	Shelf 2	TTL data sheets, assorted	
2584	REAR PARTS AREA	Shelf 2 – Column E	IRLB8721PBF MOSFET 30V 62A 9mOhm	R1 C1
2585	REAR PARTS AREA	Shelf 2 – Column E	GP1U501QS IR Detector	R1 C2
2586	REAR PARTS AREA	Shelf 2 – Column E	Rectifier Bridge 1.5A 50V	R1 C3
2587	REAR PARTS AREA	Shelf 2 – Column E	100V 4 Amp full bridge rectifier	R1 C4
2588	REAR PARTS AREA	Shelf 2 – Column E	EMPTY	R1 C5
2589	REAR PARTS AREA	Shelf 2 – Column E	LM311N comparator	R1 C6
2590	REAR PARTS AREA	Shelf 2 – Column E	LM393P dual comparators	R1 C7
2591	REAR PARTS AREA	Shelf 2 – Column E	LM339N quad comparators	R1 C8
2592	REAR PARTS AREA	Shelf 2 – Column E	ATTINY13A	R2 C1
2593	REAR PARTS AREA	Shelf 2 – Column E	ATMEGA8-16	R2 C2
2594	REAR PARTS AREA	Shelf 2 – Column E	ATMEGA16	R2 C3
2595	REAR PARTS AREA	Shelf 2 – Column E	SI-3240G 24V 1.5A regulator	R2 C4
2596	REAR PARTS AREA	Shelf 2 – Column E	TL082CP FET Op amp	R2 C5
2597	REAR PARTS AREA	Shelf 2 – Column E	LM6361N high speed op amp 50 MHz	R2 C6
2598	REAR PARTS AREA	Shelf 2 – Column E	8L01-05-001 Reed relay 0.5A 5V	R2 C7
2599	REAR PARTS AREA	Shelf 2 – Column E	MOC3023 Triac photocoupler	R2 C8
2600	REAR PARTS AREA	Shelf 2 – Column E	TL494IN PWM controller	R3 C1
2601	REAR PARTS AREA	Shelf 2 – Column E	78L18 Linear regulator +18V	R3 C2
2602	REAR PARTS AREA	Shelf 2 – Column E	DF10M bridge rectifier 1kV 1A	R3 C3
2603	REAR PARTS AREA	Shelf 2 – Column E	DF02M bridge rectifier 200V 1A	R3 C4
2604	REAR PARTS AREA	Shelf 2 – Column E	MF4CN-50 low pass filter	R3 C5
2605	REAR PARTS AREA	Shelf 2 – Column E	ZNRV10431U Varistor	R3 C6
2606	REAR PARTS AREA	Shelf 2 – Column E	TLV2462CP dual op amp	R3 C7
2607	REAR PARTS AREA	Shelf 2 – Column E	TV2462AQDRQ1 dual op amp	R3 C8
2608	REAR PARTS AREA	Shelf 2 – Column E	TK4436-ND inductor 10 uH	R4 C1
2609	REAR PARTS AREA	Shelf 2 – Column E	L298N dual full bridge driver	R4 C2
2610	REAR PARTS AREA	Shelf 2 – Column E	TK40E6N1.S1X MOSFET N-ch 60V 40A	R4 C3
2611	REAR PARTS AREA	Shelf 2 – Column E	1.5KE150CA DICT-ND TVS diode 1500W 150V	R4 C4
2612	REAR PARTS AREA	Shelf 2 – Column E	STGW30N120KD IGBT 30A 1200V	R4 C5
2613	REAR PARTS AREA	Shelf 2 – Column E	LF156H JFET op amp	R4 C6
2614	REAR PARTS AREA	Shelf 2 – Column E	QSE156 photosensor	R4 C7
2615	REAR PARTS AREA	Shelf 2 – Column E	INA122PA instrumentation op amp	R4 C8
2616	REAR PARTS AREA	Shelf 2 – Column E	BD-A515R1 7 segment dual digit display; ATMEGA8515L	R5 C1
2617	REAR PARTS AREA	Shelf 2 – Column E	FQP30N06L 60V Power MOSFET	R5 C2

2618	REAR PARTS AREA	Shelf 2 – Column E	50V 4 Amp full bridge rectifier	R5 C2
2619	REAR PARTS AREA	Shelf 2 – Column E	1N4007 diode	R5 C3
2620	REAR PARTS AREA	Shelf 2 – Column E	1 Mohm 0.1% precision resistor	R5 C4
2621	REAR PARTS AREA	Shelf 2 – Column E	IRFP150 Power MOSFET; L6203 full IC bridge	R6 C1
2622	REAR PARTS AREA	Shelf 2 – Column E	Phototransistors	R6 C2
2623	REAR PARTS AREA	Shelf 2 – Column E	GAL16V8-25LNC general array logic; TMS62256 TI SRAM 32K x 8 bit	R6 C3
2624	REAR PARTS AREA	Shelf 2 – Column E	Single Female Headers 40 pin	R6 C4
2625	REAR PARTS AREA	Shelf 2 – Column E	4 digit 7 segment display	R7 C1
2626	REAR PARTS AREA	Shelf 2 – Column E	4 digit 7 segment display	R7 C2
2627	REAR PARTS AREA	Shelf 2 – Column E	1N4004 diode	R7 C3
2628	REAR PARTS AREA	Shelf 2 – Column E	Assorted diodes	R7 C4
2629	REAR PARTS AREA	Shelf 2 – Column E – TOP	Dupont connectors	
2630	REAR PARTS AREA	Shelf 2 – Column E – TOP	Dupont connectors 2	
2631	REAR PARTS AREA	Shelf 2 – Column F	<=10MHz crystals	
2632	REAR PARTS AREA	Shelf 2 – Column F	10 MHz crystals	
2633	REAR PARTS AREA	Shelf 2 – Column F	16 MHz crystals	
2634	REAR PARTS AREA	Shelf 2 – Column F	20 MHz oscillators	
2635	REAR PARTS AREA	Shelf 2 – Column F	40 MHz oscillators, CMOS and TTL	
2636	REAR PARTS AREA	Shelf 2 – Column F	JUMPERS (0.1" for board)	
2637	REAR PARTS AREA	Shelf 2 – Column F	32.768 kHz crystals	
2638	REAR PARTS AREA	Shelf 2 – Column F	16 MHz resonators	
2639	REAR PARTS AREA	Shelf 2 – Column F	18 MHz crystals	
2640	REAR PARTS AREA	Shelf 2 – Column F	20 MHz crystals	
2641	REAR PARTS AREA	Shelf 2 – Column F	2N3819 RF JFET	
2642	REAR PARTS AREA	Shelf 2 – Column F	Arduino stack kits	
2643	REAR PARTS AREA	Shelf 2 – Column F	50 MHz crystals	
2644	REAR PARTS AREA	Shelf 2 – Column F	48 MHz crystals	
2645	REAR PARTS AREA	Shelf 2 – Column F	55.8 Mhz crystals; 55.125 MHz crystals	
2646	REAR PARTS AREA	Shelf 2 – Column F	16 pin (2x8) sockets	
2647	REAR PARTS AREA	Shelf 2 – Column F	NE565A phase lock loop – 2N3441 BJT NPN 140V 3A	
2648	REAR PARTS AREA	Shelf 2 – Column F	6 pin stackable (Arduino, 2x3)	
2649	REAR PARTS AREA	Shelf 2 – Column F	32.000 MHz crystals	
2650	REAR PARTS AREA	Shelf 2 – Column F	IRF740 IRL7833	
2651	REAR PARTS AREA	Shelf 2 – Column F	LMC6001 current amp	
2652	REAR PARTS AREA	Shelf 2 – Column F	TL071 op amps	
2653	REAR PARTS AREA	Shelf 2 – Column F	ICL7660 voltage converters	
2654	REAR PARTS AREA	Shelf 2 – Column F	8 pin stackable (Arduino, 1x8)	
2655	REAR PARTS AREA	Shelf 2 – Column F	0.1 Ohm 2W 1% resistor, 0.2 Ohm 1% resistor	
2656	REAR PARTS AREA	Shelf 2 – Column F	7905 -5V 1A regulator	
2657	REAR PARTS AREA	Shelf 2 – Column F	LH0002CN unity gain buffer	
2658	REAR PARTS AREA	Shelf 2 – Column F	Dual stackable 0.1" headers (special)	
2659	REAR PARTS AREA	Shelf 2 – Column F	Dual stackable 0.1" headers (female)	
2660	REAR PARTS AREA	Shelf 2 – Column F	10 pin stackable (Arduino, 1x10)	
2661	REAR PARTS AREA	Shelf 2 – Column F	MOSFETS NDP7050L-IRF710-IRF510-2N7000-IRLB8721	
2662	REAR PARTS AREA	Shelf 2 – Column F	IRF610	
2663	REAR PARTS AREA	Shelf 2 – Column F	16 MHz crystals	
2664	REAR PARTS AREA	Shelf 2 – Column F	1 MHz crystals	
2665	REAR PARTS AREA	Shelf 2 – Column F	1 MHz crystals	
2666	REAR PARTS AREA	Shelf 2 – Column F	Single female headers, 0.1" <40pin	
2667	REAR PARTS AREA	Shelf 2 – Column F	Long male headers, 0.1"	
2668	REAR PARTS AREA	Shelf 2 – Column F	Single male headers, 0.1"	
2669	REAR PARTS AREA	Shelf 2 – Column F	Single male headers, 0.1"	
2670	REAR PARTS AREA	Shelf 2 – Column F	Double female headers, 0.1"	
2671	REAR PARTS AREA	Shelf 2 – Column F	Double male headers, 0.1"	
2672	REAR PARTS AREA	Shelf 2 – Column G	LM350T, LM342P	
2673	REAR PARTS AREA	Shelf 2 – Column G	LMC64442 op amp	
2674	REAR PARTS AREA	Shelf 2 – Column G	TL084 op amp	
2675	REAR PARTS AREA	Shelf 2 – Column G	LF356 JFET op amp	
2676	REAR PARTS AREA	Shelf 2 – Column G	NE5532 dual op amp	
2677	REAR PARTS AREA	Shelf 2 – Column G	G201E1 5V-5V converter, R-78E5.0-1.0 5V supply	
2678	REAR PARTS AREA	Shelf 2 – Column G	2N6027 PUT 40V	
2679	REAR PARTS AREA	Shelf 2 – Column G	ZTX658 NPN Hi V Trans	
2680	REAR PARTS AREA	Shelf 2 – Column G	LM329DZ 6.9V precision reference	
2681	REAR PARTS AREA	Shelf 2 – Column G	LM385 voltage regulator	
2682	REAR PARTS AREA	Shelf 2 – Column G	MIC29310 LDO 3.3V	
2683	REAR PARTS AREA	Shelf 2 – Column G	Old transistors	
2684	REAR PARTS AREA	Shelf 2 – Column G	MAX483 RS485/422 transceiver 7812 12V 1A regulator	
2685	REAR PARTS AREA	Shelf 2 – Column G	LM337	
2686	REAR PARTS AREA	Shelf 2 – Column G	2N4410 NPN 80V 0.2A	
2687	REAR PARTS AREA	Shelf 2 – Column G	Schottky diode 30V 200 mA	
2688	REAR PARTS AREA	Shelf 2 – Column G	LM395T transistor	
2689	REAR PARTS AREA	Shelf 2 – Column G	KY5050 voltage regulator	
2690	REAR PARTS AREA	Shelf 2 – Column G	LT1529 variable voltage regulator	
2691	REAR PARTS AREA	Shelf 2 – Column G	MAX726 switch voltage regulator	
2692	REAR PARTS AREA	Shelf 2 – Column G	LM317 adjustable voltage regulator	
2693	REAR PARTS AREA	Shelf 2 – Column G	LM334 current source	
2694	REAR PARTS AREA	Shelf 2 – Column G	IRFS3806 power MOSFET	
2695	REAR PARTS AREA	Shelf 2 – Column G	LD29300V80 3A LDO 8V regulator	
2696	REAR PARTS AREA	Shelf 2 – Column G	MAX600 voltage inverter/doubler	
2697	REAR PARTS AREA	Shelf 2 – Column G	2N2907A transistors; PN2907A	
2698	REAR PARTS AREA	Shelf 2 – Column G	TS922 op amp	
2699	REAR PARTS AREA	Shelf 2 – Column G	NJM2396F33 3.3V LDO voltage regulator	
2700	REAR PARTS AREA	Shelf 2 – Column G	LM1086CT-5.0 voltage regulator 1.5A	
2701	REAR PARTS AREA	Shelf 2 – Column G	7815 CT 15V 1A voltage regulator	
2702	REAR PARTS AREA	Shelf 2 – Column G	AS1114 low pass filter	
2703	REAR PARTS AREA	Shelf 2 – Column G	LM2902-MAX232N	
2704	REAR PARTS AREA	Shelf 2 – Column G	TIP3055 NPN Transistor; 2N3055 NPN 60V	
2705	REAR PARTS AREA	Shelf 2 – Column G	IRF1404	
2706	REAR PARTS AREA	Shelf 2 – Column G	2N2221, 2N2222A, 2N2222; 164 04 Transistor	
2707	REAR PARTS AREA	Shelf 2 – Column G	Photodiodes	
2708	REAR PARTS AREA	Shelf 2 – Column G	LM3914-LM3915 LED Bar displays	
2709	REAR PARTS AREA	Shelf 2 – Column G	PCB HD ribbon cable	
2710	REAR PARTS AREA	Shelf 2 – Column G	IR LEDs	
2711	REAR PARTS AREA	Shelf 2 – Column G – TOP	LED case – red, green, yellow, orange, IR, UV (?)	
2712	REAR PARTS AREA	Shelf 2 – Column H	MBR745 7.5A Schottky	
2713	REAR PARTS AREA	Shelf 2 – Column H	TIP120 Darlington	
2714	REAR PARTS AREA	Shelf 2 – Column H	2N2907-2N3906-2N4403 PNP	
2715	REAR PARTS AREA	Shelf 2 – Column H	IXGP20N50 MOSFET 50 Amps 200V 0.06 Rds	
2716	REAR PARTS AREA	Shelf 2 – Column H	20N60 MOSFET	
2717	REAR PARTS AREA	Shelf 2 – Column H	Motorola WW-62 NPN	
2718	REAR PARTS AREA	Shelf 2 – Column H	2N5089 NPN	
2719	REAR PARTS AREA	Shelf 2 – Column H	2N3904	
2720	REAR PARTS AREA	Shelf 2 – Column H	NTE262 PNP – NTE184 NPN – NTE66 MOSFET power N-ch	
2721	REAR PARTS AREA	Shelf 2 – Column H	MPF102	

2722	REAR PARTS AREA	Shelf 2 – Column H	A92 PNP 0.5A	
2723	REAR PARTS AREA	Shelf 2 – Column H	Z5CT555	
2724	REAR PARTS AREA	Shelf 2 – Column H	2N4403 PNP – PN2907 PNP 800mA	
2725	REAR PARTS AREA	Shelf 2 – Column H	2N3019	
2726	REAR PARTS AREA	Shelf 2 – Column H	2N3906	
2727	REAR PARTS AREA	Shelf 2 – Column H	NTE197 PNP	
2728	REAR PARTS AREA	Shelf 2 – Column H	2N6028 300mW 40V SCR	
2729	REAR PARTS AREA	Shelf 2 – Column H	NE555N, NE5534	
2730	REAR PARTS AREA	Shelf 2 – Column H	2N4401 NPN	
2731	REAR PARTS AREA	Shelf 2 – Column H	PN2907 PNP	
2732	REAR PARTS AREA	Shelf 2 – Column H	BC546 NPN 65V 0.1A	
2733	REAR PARTS AREA	Shelf 2 – Column H	TIP112 NPN Darlington	
2734	REAR PARTS AREA	Shelf 2 – Column H	TIP32A NPN	
2735	REAR PARTS AREA	Shelf 2 – Column H	LM555	
2736	REAR PARTS AREA	Shelf 2 – Column H	2N5484 JFET	
2737	REAR PARTS AREA	Shelf 2 – Column H	BC337-BC557-BD139-BD140 NPN PNP	
2738	REAR PARTS AREA	Shelf 2 – Column H	2N5485	
2739	REAR PARTS AREA	Shelf 2 – Column H	2N5485 N JFET	
2740	REAR PARTS AREA	Shelf 2 – Column H	1N4250	
2741	REAR PARTS AREA	Shelf 2 – Column H	556 Timers	
2742	REAR PARTS AREA	Shelf 2 – Column H	2N2219A-A92-2N3904-2N2222-2N5551-2N3906	
2743	REAR PARTS AREA	Shelf 2 – Column H	S8850-S8050-S9012-S9013-S9014-S9015-S9018	
2744	REAR PARTS AREA	Shelf 2 – Column H	A42-A733-A1015-C945-C1815-2N5401	
2745	REAR PARTS AREA	Shelf 2 – Column H	BDX34A PNP 60V, 2N3019 80V 1A	
2746	REAR PARTS AREA	Shelf 2 – Column H	ZIF Headers	
2747	REAR PARTS AREA	Shelf 2 – Column H	0.0047uF 50V	
2748	REAR PARTS AREA	Shelf 2 – Column H	Precision thermistors; MM5369 stage oscillator/divider (generate precise reference from crystals)	
2749	REAR PARTS AREA	Shelf 2 – Column H	W172DIP-7 12V Reed Relay	
2750	REAR PARTS AREA	Shelf 2 – Column H	Transistors, TO-220	
2751	REAR PARTS AREA	Shelf 2 – Column H	Transistors, TO-92	
2752	REAR PARTS AREA	Shelf 2 – Column H	TDA2003V Audio amp	
2753	BAKER RACK A – TOP	Column A	LED 5mm 470nm blue clear LED	R1 C1
2754	BAKER RACK A – TOP	Column A	Photointerruptor PCB optic slot 10mm	R1 C2
2755	BAKER RACK A – TOP	Column A	Hamamatsu S6560 dual photodiode	R1 C3
2756	BAKER RACK A – TOP	Column A	Wire wrap templates	R1 C4
2757	BAKER RACK A – TOP	Column A	SB560-E3/54 Diode Schottky 60V 5A DO201AD	R1 C5
2758	BAKER RACK A – TOP	Column A	DC/DC Converter 12V 6W	R1 C6
2759	BAKER RACK A – TOP	Column A	Rect bridge GPP 600V 35A GBPC	R1 C7
2760	BAKER RACK A – TOP	Column A	VBE17-12N07 – rect bridge	R1 C8
2761	BAKER RACK A – TOP	Column A	747250-4 9 pin D-sub right angle	R2 C1
2762	BAKER RACK A – TOP	Column A	747321-4 9 pin male plastic D-sub	R2 C2
2763	BAKER RACK A – TOP	Column A	CWR-180-09-0003 DB9 male connector	R2 C3
2764	BAKER RACK A – TOP	Column A	banana plugs/posts	R2 C4
2765	BAKER RACK A – TOP	Column A	dual banana plugs	R2 C5
2766	BAKER RACK A – TOP	Column A	banana plugs orange/yellow	R2 C6
2767	BAKER RACK A – TOP	Column A	BNC jacks PCB mount	R2 C7
2768	BAKER RACK A – TOP	Column A	gray mini socket	R2 C8
2769	BAKER RACK A – TOP	Column A	banana jacks green/blue	R3 C1
2770	BAKER RACK A – TOP	Column A	banana jacks – black	R3 C2
2771	BAKER RACK A – TOP	Column A	banana jacks – white	R3 C3
2772	BAKER RACK A – TOP	Column A	banana jacks – black/red	R3 C4
2773	BAKER RACK A – TOP	Column A	banana jacks – violet/brown	R3 C5
2774	BAKER RACK A – TOP	Column A	banana jacks – orange/yellow	R3 C6
2775	BAKER RACK A – TOP	Column A	banana plugs – red	R3 C7
2776	BAKER RACK A – TOP	Column A	banana plugs – green/blue	R3 C8
2777	BAKER RACK A – TOP	Column A	QILE44P-410TB 44 pin socket PLCC	R4 C1
2778	BAKER RACK A – TOP	Column A	940-00-044-24-000000 44 pin socket PLCC	R4 C2
2779	BAKER RACK A – TOP	Column A	44 pin PLCC IC socket	R4 C3
2780	BAKER RACK A – TOP	Column A	QILE44P-410T – 44 pin PLCC through hole	R4 C4
2781	BAKER RACK A – TOP	Column A	QILE44P-410T – 44 pin PLCC through hole	R4 C5
2782	BAKER RACK A – TOP	Column A	499252-5 – strain relief 10 pin socket	R4 C6
2783	BAKER RACK A – TOP	Column A	Banana plug parts – various	R4 C7
2784	BAKER RACK A – TOP	Column A	Banana plugs – all metal	R4 C8
2785	BAKER RACK A – TOP	Column A	18 pin IC socket	R5 C1
2786	BAKER RACK A – TOP	Column A	20 pin IC socket	R5 C2
2787	BAKER RACK A – TOP	Column A	28 pin IC socket	R5 C3
2788	BAKER RACK A – TOP	Column A	28 pin IC socket	R5 C4
2789	BAKER RACK A – TOP	Column A	28 pin IC socket (0.3" wide)	R5 C5
2790	BAKER RACK A – TOP	Column A	40 pin IC socket (0.3" wide)	R5 C6
2791	BAKER RACK A – TOP	Column A	24 pin IC socket (0.3" wide)	R5 C7
2792	BAKER RACK A – TOP	Column A	6-pin DIN	R5 C8
2793	BAKER RACK A – TOP	Column A	313-1427-008 – ¼" aluminum spacer	R6 C1
2794	BAKER RACK A – TOP	Column A	WM1114 – 22-30 AWG pins	R6 C2
2795	BAKER RACK A – TOP	Column A	BA2032SM – eject coin cell holder	R6 C3
2796	BAKER RACK A – TOP	Column A	Misc USB – A to A and B to B	R6 C4
2797	BAKER RACK A – TOP	Column A	414337-1 connector SMB right angle	R6 C5
2798	BAKER RACK A – TOP	Column A	Safety type binding post (banana plug) 10A 250VAC RS 274-0009	R6 C6
2799	BAKER RACK A – TOP	Column A	24 PIN IC socket	R6 C7
2800	BAKER RACK A – TOP	Column A	0030-001 replacement blade for PTS-30	R6 C8
2801	BAKER RACK A – TOP	Column A	110-99-316-41-001 – 16 pin DIP socket	R7 C1
2802	BAKER RACK A – TOP	Column A	CWR-181-09-0003 – DB9 female tin plastic shell	R7 C2
2803	BAKER RACK A – TOP	Column A	1033310-1 10 POS R/A AU Header	R7 C3
2804	BAKER RACK A – TOP	Column A	28 pin IC socket (0.3" wide)	R7 C4
2805	BAKER RACK A – TOP	Column A	Tadiran battery (3.7V) Lithium Ion	R7 C5
2806	BAKER RACK A – TOP	Column A	Lithium coin cells	R7 C6
2807	BAKER RACK A – TOP	Column A	AR16-HZL 16 pin IC socket	R7 C7
2808	BAKER RACK A – TOP	Column A	958-BR insulator, red (for banana plug socket)	R7 C8
2809	BAKER RACK A – TOP	Column A	BR1225 Lithium coin cell	R8 C1
2810	BAKER RACK A – TOP	Column A	500 PC coin cell battery holder 12 mm	R8 C2
2811	BAKER RACK A – TOP	Column A	S20425-3 Conn MOD Jack 6-6 Vert PCB	R8 C3
2812	BAKER RACK A – TOP	Column A	banana plug sockets – various colors	R8 C4
2813	BAKER RACK A – TOP	Column A	818-S-0-UT-2.2G headless reduced 4P	R8 C5
2814	BAKER RACK A – TOP	Column A	H9066-ND 3x6 6-6PC Jack	R8 C6
2815	BAKER RACK A – TOP	Column A	0.01uH, 0.2 Ohm inductors	R8 C7
2816	BAKER RACK A – TOP	Column A	02-06-1103 Female term connector 18-24 AWG WM1001	R8 C8
2817	BAKER RACK A – TOP	Column B	A6277SA serial LED driver	R1 C1
2818	BAKER RACK A – TOP	Column B	LU70031-ND red diffuse 3mm LED	R1 C2
2819	BAKER RACK A – TOP	Column B	EFR5366X – 5mm LED red clear high bright	R1 C3
2820	BAKER RACK A – TOP	Column B	CMD3450 LED ultrabright green	R1 C4
2821	BAKER RACK A – TOP	Column B	LTL-2F3VEKNT LED Red AlInGaP 632nm 5mm	R1 C5
2822	BAKER RACK A – TOP	Column B	MV5491A LED red/green white diffuse T-1 ¼	R1 C6
2823	BAKER RACK A – TOP	Column B	LED 5mm 592nm amber water clear	R1 C7
2824	BAKER RACK A – TOP	Column B	T5SAL6200 17 degree 40mW Vishay IR LED	R1 C8

2825	BAKER RACK A – TOP	Column B	LTST-C170TBKT LED blue clear	R2 C1
2826	BAKER RACK A – TOP	Column B	EFA5366X – LED Orange clear high bright	R2 C2
2827	BAKER RACK A – TOP	Column B	MM8505I – micro laser module 850nm 5mW	R2 C3
2828	BAKER RACK A – TOP	Column B	LTL-2F3VFKNT LED 611nm yellow-orange AlInGaP 5 mm	R2 C4
2829	BAKER RACK A – TOP	Column B	SSL-LX5083HT LED hi-eff red transparent 5mm	R2 C5
2830	BAKER RACK A – TOP	Column B	LTL42EKEKN – LED 632nm red clear 5mm	R2 C6
2831	BAKER RACK A – TOP	Column B	LTL-2F3VFKNT LED Red AlInGaP 632nm 5mm	R2 C7
2832	BAKER RACK A – TOP	Column B	TSAL6400 LED IR 5mm	R2 C8
2833	BAKER RACK A – TOP	Column B	LN81RPH LED orange diff round 5mm	R3 C1
2834	BAKER RACK A – TOP	Column B	LED green PC mount	R3 C2
2835	BAKER RACK A – TOP	Column B	SSL-LX5083SUV – LED 380nm violet water clear 5mm	R3 C3
2836	BAKER RACK A – TOP	Column B	LTL-4203 LED red diff 5mm	R3 C4
2837	BAKER RACK A – TOP	Column B	LED Red diff T1-3/4	R3 C5
2838	BAKER RACK A – TOP	Column B	5306H1 LED Red PC mount 5mm	R3 C6
2839	BAKER RACK A – TOP	Column B	5306H3 LED Amber PC mount 5mm	R3 C7
2840	BAKER RACK A – TOP	Column B	LED yellow diffuse T 1-3/4	R3 C8
2841	BAKER RACK A – TOP	Column B	516-1377-ND LED 5mm 635nm red water clear	R4 C1
2842	BAKER RACK A – TOP	Column B	CMD3350 – LED ultrabright yellow T1-3/4	R4 C2
2843	BAKER RACK A – TOP	Column B	5306H7 LED yellow PC mount 5mm	R4 C3
2844	BAKER RACK A – TOP	Column B	SSA-LXB10HW-GF/LP LED 10x25mm 10 segment red diff	R4 C4
2845	BAKER RACK A – TOP	Column B	LED bicolor diffuse T1-3/4	R4 C5
2846	BAKER RACK A – TOP	Column B	HMLP-CM28-W2000 LED crazy bright green LED	R4 C6
2847	BAKER RACK A – TOP	Column B	SSL-LX5083UVLC LED violet clear 410 nm 5mm	R4 C7
2848	BAKER RACK A – TOP	Column B	530MW04C 30deg warm white LED 5mm	R4 C8
2849	BAKER RACK A – TOP	Column B	560V2C 60 deg pure green LED 5mm	R5 C1
2850	BAKER RACK A – TOP	Column B	05W580B8C 80 deg blue 100mA 5mm	R5 C2
2851	BAKER RACK A – TOP	Column B	05W580CYC 80 deg yellow amber 100mA 5mm	R5 C3
2852	BAKER RACK A – TOP	Column B	05W580EGC 80 deg green 100mA 5mm	R5 C4
2853	BAKER RACK A – TOP	Column B	05W580EWC 80 deg white 100mA 5mm	R5 C5
2854	BAKER RACK A – TOP	Column B	05W580EWC 80 deg warm white 100mA 5mm	R5 C6
2855	BAKER RACK A – TOP	Column B	540JPKC 40 deg pink LED 5mm	R5 C7
2856	BAKER RACK A – TOP	Column B	TSAL7200 17 deg IRED LED 5mm	R5 C8
2857	BAKER RACK A – TOP	Column B	560VWC 60 deg white LED 5mm	R6 C1
2858	BAKER RACK A – TOP	Column B	1N4001	R6 C2
2859	BAKER RACK A – TOP	Column B	1N4002/1N4003	R6 C3
2860	BAKER RACK A – TOP	Column B	1N4004/1N4005	R6 C4
2861	BAKER RACK A – TOP	Column B	1N4007T 1A 1000V rect diode	R6 C5
2862	BAKER RACK A – TOP	Column B	1N4148 0.15A 75V diode	R6 C6
2863	BAKER RACK A – TOP	Column B	P6KE24CA – diode TVS 24V 600W bi directional	R6 C7
2864	BAKER RACK A – TOP	Column B	1N4936T – 1A 400V	R6 C8
2865	BAKER RACK A – TOP	Column B	LTL-4252N LED yellow clear 3mm transparent	R7 C1
2866	BAKER RACK A – TOP	Column B	LTL-16KY LED T-1 DBL yellow diff flange	R7 C2
2867	BAKER RACK A – TOP	Column B	LTL-16KE LED T-1 DBL hieff red diff flange	R7 C3
2868	BAKER RACK A – TOP	Column B	LTL-42EKEKN LED – read clear AlInGaP 632nm	R7 C4
2869	BAKER RACK A – TOP	Column B	LTL-16KG LED T-1 DBL Green diff flange 3mm T-1	R7 C5
2870	BAKER RACK A – TOP	Column B	LTL-16AG LED Green diff T 1-3/4	R7 C6
2871	BAKER RACK A – TOP	Column B	LED holders T1-3/4	R7 C7
2872	BAKER RACK A – TOP	Column B	High output IR LED T1-3/4	R7 C8
2873	BAKER RACK A – TOP	Column B	MCP6294-F/P Quad 10 Mhz op amp	R8 C1
2874	BAKER RACK A – TOP	Column B	TSL261R-LF light to voltage	R8 C2
2875	BAKER RACK A – TOP	Column B	TSL267R-LF light to voltage	R8 C3
2876	BAKER RACK A – TOP	Column B	MCP6292-E/P – IC op amp GP 2 circuit 8 DIP	R8 C4
2877	BAKER RACK A – TOP	Column B	ZTX758 trans PNP 400V 1A	R8 C5
2878	BAKER RACK A – TOP	Column B	ZTX658 Trans 400V 0.5A NPN high voltage	R8 C6
2879	BAKER RACK A – TOP	Column B	MPS751 Trans PNP TO-92	R8 C7
2880	BAKER RACK A – TOP	Column B	67-1001-ND diode IR emitter 5mm IR clear LED	R8 C8
2881	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	Power Trends P76302R 5V step down	R1 C1
2882	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	74AC299	R1 C2
2883	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	Power Trends 78HT265HC – 6.5V step down	R1 C3
2884	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	PT5101A – non-isolated 5V 1A step down	R1 C4
2885	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	NMR100 5V converter (4.5 to 5.5 V input)	R1 C5
2886	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	GAL16V8D/GAL20V8B	R1 C6
2887	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	LF444ACN	R1 C7
2888	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	AM26C32CN	R1 C8
2889	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	OPA137P	R2 C1
2890	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	PS05021 4	R2 C2
2891	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	CD74HC125E	R2 C3
2892	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	74AC299PC – shift register	R2 C4
2893	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	CLC425	R2 C5
2894	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	PT6302R	R2 C6
2895	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	16 BIT A/D	R2 C7
2896	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	LMC6484AIN	R2 C8
2897	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	ISO124P	R3 C1
2898	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	8L02 05 41	R3 C2
2899	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	Reed relay 5V 250mA 8L41-05-111	R3 C3
2900	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	CA3262AE	R3 C4
2901	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	PS0502 4	R3 C5
2902	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	PS2502 4	R3 C6
2903	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	SSM2142	R3 C7
2904	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	Diode FD40H100SFP GK0Y0 V5 100V 40A 0.45V drop	R3 C8
2905	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	HCPL 2631	R4 C1
2906	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	OPA37 GP	R4 C2
2907	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	SSM2141P	R4 C3
2908	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	OPA27 GP	R4 C4
2909	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	TL431CP	R4 C5
2910	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	SN75437 ANE	R4 C6
2911	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	PC2501 4	R4 C7
2912	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	CA3262 AE	R4 C8
2913	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	MC74HC137	R5 C1
2914	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	AD7890AN 2	R5 C2
2915	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	LT1013 Dual Op Amp	R5 C3
2916	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	LT1014 Quad Op Amp	R5 C4
2917	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	TLCC252BCP Op Amp	R5 C5
2918	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	TC9402CPD	R5 C6
2919	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	AQW214	R5 C7
2920	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	LMC6482AIN	R5 C8
2921	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	MM74HC540N	R6 C1
2922	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	MCP6002; MCP6004 op amps	R6 C2
2923	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	MC74AC541N	R6 C3
2924	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	LT1055 CN8	R6 C4
2925	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	694 3 R20KA	R6 C5
2926	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	DLG403G Analog Switch	R6 C6
2927	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	74HC646N	R6 C7
2928	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	TL16C550CN UART CHIP	R6 C8

2929	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	16 pin DIP to WIRE	R7 C1
2930	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	16 pin DIP to WIRE	R7 C2
2931	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	AD536AJQ	R7 C3
2932	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	74AC646SPC	R7 C4
2933	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	ADM707AN	R7 C5
2934	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	LINFINIT SG3526N	R7 C6
2935	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	AD7890AM 10	R7 C7
2936	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	AD78803AM	R7 C8
2937	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	CD4066BCN	R8 C1
2938	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	IRL244NPBF – MOSFET N-CH 55V 47A TO-220AB	R8 C2
2939	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	CD4053BCN	R8 C3
2940	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	CD4053BCN	R8 C4
2941	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	Transistor NPN TIP50 – 500V 1A TO-220	R8 C5
2942	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	LN1251CTR – LED Red J-Type SMD NO HDR/TRLR	R8 C6
2943	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	LM78L12AZ – 12V 100mA (like 7812)	R8 C7
2944	BAKER RACK A	Shelf 3 – 8x8 drawer unit LEFT	TL431CP PREC REF 2.5V TO 36V	R8 C8
2945	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	4700 pF 500V ceramic disk	R1 C1
2946	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	100 pF 500V ceramic disk	R1 C2
2947	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	5.2-30pF 100V ceramic trim cap	R1 C3
2948	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	100V 47uF	R1 C4
2949	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	1.2uF 16V	R1 C5
2950	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	470nF 100V	R1 C6
2951	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	22nF ceramic	R1 C7
2952	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	4.7uF tantalum capacitor 10% 10V radial	R1 C8
2953	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	1.5uF 25VDC tantalum	R2 C1
2954	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	10uF 16VDC tantalum	R2 C2
2955	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	47uF 25V aluminum	R2 C3
2956	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	1uF 50V ceramic	R2 C4
2957	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	50V 0.1uF	R2 C5
2958	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	0.1uF 25V	R2 C6
2959	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	0.1uF 100V ceramic	R2 C7
2960	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	330uF 10V electrolytic	R2 C8
2961	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	Axial ferrite bead	R3 C1
2962	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	Axial ferrite bead	R3 C2
2963	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	1000pF 500V ceramic disk	R3 C3
2964	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	33pF 100V	R3 C4
2965	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	100V 1uF	R3 C5
2966	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	100uF 50V aluminum electrolytic	R3 C6
2967	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	47uF 63V	R3 C7
2968	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	100V 4.7uF	R3 C8
2969	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	Misc disk capacitors	R4 C1
2970	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	0.01uF 400V	R4 C2
2971	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	10000pF 50V	R4 C3
2972	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	100pF 50V	R4 C4
2973	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	22pF 50V	R4 C5
2974	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	15pF 100V	R4 C6
2975	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	1000pF 50V	R4 C7
2976	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	1pF 50V	R4 C8
2977	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	10uF 25V	R5 C1
2978	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	10uF 100V	R5 C2
2979	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	33uF 100V	R5 C3
2980	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	220uF 10V	R5 C4
2981	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	TVS Diode 9V 15.4V DO204ACSA9.0CA-E3/54	R5 C5
2982	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	10uF 50V	R5 C6
2983	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	10uF 50V axial	R5 C7
2984	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	1uF 50V non-polarized RS 272-996	R5 C8
2985	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	0.1uF 50V	R6 C1
2986	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	0.1uF 50V	R6 C2
2987	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	0.01uF 50V	R6 C3
2988	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	Thermostat 160C 317-1056-ND normally closed	R6 C4
2989	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	100uF 100V	R6 C5
2990	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	100uF 100V	R6 C6
2991	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	IRFP9240; IRFP240	R6 C7
2992	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	0.1uF 250V	R6 C8
2993	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	IRL520 N-CH 100V 9.2A	R7 C1
2994	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	IRL2703 – HEX/MOS N-CH	R7 C2
2995	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	VASD1-s5-d5-SIP DC DC 5V 1W	R7 C3
2996	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	EMPTY	R7 C4
2997	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	EMPTY	R7 C5
2998	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	EMPTY	R7 C6
2999	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	EMPTY	R7 C7
3000	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	ZVN4306AV MOSFET N-CH Avalanche 60V 1.1A	R7 C8
3001	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	12VDC regulator switch 0.4A SIP linear regulator (15V-36V input range)	R8 C1
3002	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	MJH11020G Darlington NPN 15A 200V	R8 C2
3003	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	SD103A 40V Schottky 400mW DO-35; SB140E-G DO-41 40V 1A	R8 C3
3004	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	1.5KE400CA 1500W 400V transient voltage suppressor	R8 C4
3005	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	MPF102 Amp N-Ch RF SS transistor	R8 C5
3006	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	STP80PF55 MOSFET P-CH 55V 80A TO-220A	R8 C6
3007	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	IRL1592 controller ballast dimming	R8 C7
3008	BAKER RACK A	Shelf 3 – 8x8 drawer unit RIGHT	IRF510PBF MOSFET N-CH 100V 5.6A	R8 C8
3009	BAKER RACK B – TOP	Column A	PR26MF21NSZ – opto relay SSR 280VAC 0.6A zero crossing	R1 C1
3010	BAKER RACK B – TOP	Column A	MCP9700 – temperature analog voltage TO-92	R1 C2
3011	BAKER RACK B – TOP	Column A	IS471F – OPIC light detector 940nm	R1 C3
3012	BAKER RACK B – TOP	Column A	IR phototransistor T1-3/4	R1 C4
3013	BAKER RACK B – TOP	Column A	IS489 OPIC light detector 900nm	R1 C5
3014	BAKER RACK B – TOP	Column A	136047 CdS cells (photoresistor)	R1 C6
3015	BAKER RACK B – TOP	Column A	PNA4603H – photo IC for brightness control 540nm	R1 C7
3016	BAKER RACK B – TOP	Column A	LTM-97DT-40 RCVR module 49kHz Top-Look	R1 C8
3017	BAKER RACK B – TOP	Column A	TSLA16100 – 10 degree 40mW Vishay IR Emitter	R2 C1
3018	BAKER RACK B – TOP	Column A	PS9601 – photocoupler hi speed digital	R2 C2
3019	BAKER RACK B – TOP	Column A	6N136 – optoisolator transistor output	R2 C3
3020	BAKER RACK B – TOP	Column A	6N138 – split Darlington optoisolator; TIL196 opto isolator	R2 C4
3021	BAKER RACK B – TOP	Column A	TEMP3700 Vishay semiconductor IR detector	R2 C5
3022	BAKER RACK B – TOP	Column A	TSL14S – Taos light to voltage	R2 C6
3023	BAKER RACK B – TOP	Column A	TSL12S – Taos light to voltage	R2 C7
3024	BAKER RACK B – TOP	Column A	IS456 – OPIC light detector 680nm	R2 C8
3025	BAKER RACK B – TOP	Column A	IF-D91 – fiber optic plastic photodiode 890nm	R3 C1
3026	BAKER RACK B – TOP	Column A	IF-D92 – fiber optic phototransistor 870nm	R3 C2
3027	BAKER RACK B – TOP	Column A	IF-D93 – fiber optic photodarlington	R3 C3
3028	BAKER RACK B – TOP	Column A	IF-D95T – photologic detector TTL/CMOS	R3 C4
3029	BAKER RACK B – TOP	Column A	IF-D91A FLCS IR LED	R3 C5
3030	BAKER RACK B – TOP	Column A	TSHF5400 – high speed IR emitting diode 870nm	R3 C6
3031	BAKER RACK B – TOP	Column A	GP2Y0D02YK – 80 cm distance sensor	R3 C7
3032	BAKER RACK B – TOP	Column A	IRU101533 - 1.5A LOW DROPOUT POSITIVE REGULATOR 3.3V	R3 C8

3033	BAKER RACK B – TOP	Column A	GP2540 – reflect photointerruptor 6.5mm PC mount	R4 C1
3034	BAKER RACK B – TOP	Column A	67-1097-ND – SSL-LX5093AD – LED 5mm amber diffused	R4 C2
3035	BAKER RACK B – TOP	Column A	GP1UD26XK – control top remote receiver 40kHz	R4 C3
3036	BAKER RACK B – TOP	Column A	TSOP1838 – Vishay IR mod 38kHz	R4 C4
3037	BAKER RACK B – TOP	Column A	P373-ND – LN81RPH – LED orange diffused round	R4 C5
3038	BAKER RACK B – TOP	Column A	BS120 – blue sens 1.5mm SQ photodiode	R4 C6
3039	BAKER RACK B – TOP	Column A	425-1161-ND Sharp GP2D12 10-80 cm distance measuring analog out	R4 C7
3040	BAKER RACK B – TOP	Column A	GP2Y0A02YK – Sharp 150cm distance sensor analog out	R4 C8
3041	BAKER RACK B – TOP	Column A	MV5353-ND LED SS Yellow diffused wide 5mm	R5 C1
3042	BAKER RACK B – TOP	Column A	TSHA6203 – high speed IR emitting diode 870nm	R5 C2
3043	BAKER RACK B – TOP	Column A	BPV11F – Vishay IR detector 150mW	R5 C3
3044	BAKER RACK B – TOP	Column A	BPW34 215mW Vishay IR detector	R5 C4
3045	BAKER RACK B – TOP	Column A	PNZ164 – NPN phototransistor	R5 C5
3046	BAKER RACK B – TOP	Column A	BS520 – blue square 5.3mm photodiode	R5 C6
3047	BAKER RACK B – TOP	Column A	PN1215-R phototransistor NPN 800nm	R5 C7
3048	BAKER RACK B – TOP	Column A	PD100MF0MP – side look IR photodiode 850nm	R5 C8
3049	BAKER RACK B – TOP	Column A	67-1612-ND/SSL-LX5093SRC/E – LED 5mm 2800mcd super bright	R6 C1
3050	BAKER RACK B – TOP	Column A	VAOL-5GUV8T4 UV LED – 385nm 80mcd 30 deg	R6 C2
3051	BAKER RACK B – TOP	Column A	MV64531-ND – LED SS HE green diffuse LP 5mm	R6 C3
3052	BAKER RACK B – TOP	Column A	Random LEDs	R6 C4
3053	BAKER RACK B – TOP	Column A	QSE114 – IC phototransistor IR 880nm side looking	R6 C5
3054	BAKER RACK B – TOP	Column A	PCB17XJ0000F – photocoupler tran out 4-DIP	R6 C6
3055	BAKER RACK B – TOP	Column A	PNA4613M00XD – IR photo 40kHz with holder	R6 C7
3056	BAKER RACK B – TOP	Column A	PS2501-1 1 channel optocoupler trans	R6 C8
3057	BAKER RACK B – TOP	Column A	H211TI – slotted photoswitch	R7 C1
3058	BAKER RACK B – TOP	Column A	3900 uH 0.4A inductor	R7 C2
3059	BAKER RACK B – TOP	Column A	ZTX651 transistor NPN 2A 60V	R7 C3
3060	BAKER RACK B – TOP	Column A	2N3904DI – transistor 40V NPN	R7 C4
3061	BAKER RACK B – TOP	Column A	ZTX1149A – transistor PNP 25V 3A	R7 C5
3062	BAKER RACK B – TOP	Column A	ZTX1049A – transistor NPN 30V 4000mA/4A	R7 C6
3063	BAKER RACK B – TOP	Column A	ZTX751 – transistor PNP 2A 60V	R7 C7
3064	BAKER RACK B – TOP	Column A	V7812-1000 converter DC/DC 12V 1A	R7 C8
3065	BAKER RACK B – TOP	Column A	60APU02 – diode 60A 200V	R8 C1
3066	BAKER RACK B – TOP	Column A	RE200B – IR temperature sensor	R8 C2
3067	BAKER RACK B – TOP	Column A	2N3906 PNP small signal general purpose amp TO-92	R8 C3
3068	BAKER RACK B – TOP	Column A	PN2222A – NPN transistor 600mA 40V TO-92	R8 C4
3069	BAKER RACK B – TOP	Column A	2N3904 transistor NPN high speed 200mA 40V TO-92	R8 C5
3070	BAKER RACK B – TOP	Column A	SCS210AG 600V 10A Schottky barrier diode	R8 C6
3071	BAKER RACK B – TOP	Column A	104JG1F – thermistor NTC 100K	R8 C7
3072	BAKER RACK B – TOP	Column A	104LAF – thermistor NTC 100K	R8 C8
3073	BAKER RACK B – TOP	Column B	100pF 50V	R1 C1
3074	BAKER RACK B – TOP	Column B	220pF 50V	R1 C2
3075	BAKER RACK B – TOP	Column B	330pF 50V	R1 C3
3076	BAKER RACK B – TOP	Column B	47pF 50V	R1 C4
3077	BAKER RACK B – TOP	Column B	4700pF 50V	R1 C5
3078	BAKER RACK B – TOP	Column B	0.056uF 50V	R1 C6
3079	BAKER RACK B – TOP	Column B	0.047uF 50V	R1 C7
3080	BAKER RACK B – TOP	Column B	0.022uF 50V	R1 C8
3081	BAKER RACK B – TOP	Column B	0.22uF 50V	R2 C1
3082	BAKER RACK B – TOP	Column B	0.33uF 50V	R2 C2
3083	BAKER RACK B – TOP	Column B	0.1uF 50V	R2 C3
3084	BAKER RACK B – TOP	Column B	820pF 50V	R2 C4
3085	BAKER RACK B – TOP	Column B	100nF 50V	R2 C5
3086	BAKER RACK B – TOP	Column B	47pF 500V; 100pF 500V	R2 C6
3087	BAKER RACK B – TOP	Column B	150pF 500V; 220pF 500V	R2 C7
3088	BAKER RACK B – TOP	Column B	330pF 500V; 470pF 500V	R2 C8
3089	BAKER RACK B – TOP	Column B	680pF 500V; 1500pF 50V	R3 C1
3090	BAKER RACK B – TOP	Column B	2200pF 50V; 3300pF 50V	R3 C2
3091	BAKER RACK B – TOP	Column B	4700pF 50V; 6800pF 50V	R3 C3
3092	BAKER RACK B – TOP	Column B	0.033uF 25V; 0.047uF 25V	R3 C4
3093	BAKER RACK B – TOP	Column B	0.022uF 25V	R3 C5
3094	BAKER RACK B – TOP	Column B	TSL220 light to frequency; DS0026 Dual high speed MOSFET driver	R3 C6
3095	BAKER RACK B – TOP	Column B	MAX7219CNG IC driver 7 segment 8 digit; MAX242EPN ICTransceiver full RS232	R3 C7
3096	BAKER RACK B – TOP	Column B	CNY17F-3 photocoupler/optoisolator	R3 C8
3097	BAKER RACK B – TOP	Column B	SN75453BP; TL7702ACP	R4 C1
3098	BAKER RACK B – TOP	Column B	UC3635N;L292V motor driver	R4 C2
3099	BAKER RACK B – TOP	Column B	A2232 optocoupler; AMP30G low noise amp	R4 C3
3100	BAKER RACK B – TOP	Column B	LM3524N PWM controller; 4N37 optoisolator	R4 C4
3101	BAKER RACK B – TOP	Column B	PN2222 NPN general	R4 C5
3102	BAKER RACK B – TOP	Column B	MPSA13 NPN	R4 C6
3103	BAKER RACK B – TOP	Column B	TIP41A NPN 60V general; TIP31A NPN 60V	R4 C7
3104	BAKER RACK B – TOP	Column B	8550 general purpose; 2N5457 N-channel	R4 C8
3105	BAKER RACK B – TOP	Column B	AM26LV32 LOW V HS QUAD receiver; 6 pin socket	R5 C1
3106	BAKER RACK B – TOP	Column B	8 pin socket; 14 pin socket	R5 C2
3107	BAKER RACK B – TOP	Column B	16 pin socket; 20 pin socket	R5 C3
3108	BAKER RACK B – TOP	Column B	220pF 50V; NMV1212SA 12V-12V DC-DC isolators	R5 C4
3109	BAKER RACK B – TOP	Column B	Diodes Silicon: 1N4001,1N4004,1N4007,1N5404,1N5408,6A01,6A08; Zener: 1N751,1N4733,1N4735,1N4742; Switching: 1N4150; 1N4148,1N914; Bridge Rectifier: W01; W02; Germanium 1N60; 1N34A; SECOND KIT: rectifier diodes 1N4001,1N4004,1N4007,RL207,1N5404,1N5406,1N5408,switching diodes 1N4148; fast recovery diodes UF4007; FR107; FR207; Schottky diodes 1N5817,1N5819,1N5822	R6 C1
3110	BAKER RACK B – TOP	Column B	Capacitors – 10pF; 22pF;47pF (disc); 100pF (101); 220pF (220); 470pF(471) disc; 0.001uF, 0.022uF,0.047uF; 0.01uF; 0.022uF; 0.1uF; 0.22uF Mylar;1uF;4.7uF;10uF;22uF;47uF;100uF;470uF;1000uF electrolytic (35V)	R6 C2
3111	BAKER RACK B – TOP	Column B	24 pin socket; 28 pin socket and 32 pin socket	R6 C3
3112	BAKER RACK B – TOP	Column B	LT1101 voltage comparator – AD976AAN 16 bit A/D converter	R6 C4
3113	BAKER RACK B – TOP	Column B	2N3904 – large number	R7
3114	BAKER RACK B – TOP	Column B	NDY2415 3W 18-36V IN 15V OUT – PT6302N 9-38V IN 5V OUT; AD293 isolation amplifier	R7
3115	BAKER RACK B – TOP	Column B	NML05055 5V-5V voltage converter	R7
3116	BAKER RACK B – TOP	Column B	AD8803A Octal 8 Bit DAC	R7
3117	BAKER RACK B – TOP	Column B	ECG5687 600V 25A Triac; ECG5483 200V 8A SCR	R7
3118	BAKER RACK B	Shelf 2	0.03uF 500V	R1 C1
3119	BAKER RACK B	Shelf 2	0.01uF 1000V	R1 C2
3120	BAKER RACK B	Shelf 2	0.005uF 1000V	R1 C3
3121	BAKER RACK B	Shelf 2	Varistor 130V	R1 C4
3122	BAKER RACK B	Shelf 2	Varistor 387V; Varistor 430V	R1 C5
3123	BAKER RACK B	Shelf 2	68pF 100V/300V	R1 C6
3124	BAKER RACK B	Shelf 2	1F 5.5V Ultracapacitor	R1 C7
3125	BAKER RACK B	Shelf 2	0.05uF 8000V	R1 C8
3126	BAKER RACK B	Shelf 2	4.0uF 600V	R2 C1
3127	BAKER RACK B	Shelf 2	0.001uF 1000V	R2 C2
3128	BAKER RACK B	Shelf 2	0.68uF 400V	R2 C3
3129	BAKER RACK B	Shelf 2	25uF 500V	R2 C4
3130	BAKER RACK B	Shelf 2	0.0001uF 1000V	R2 C5
3131	BAKER RACK B	Shelf 2	50uF 500V	R2 C6

3132	BAKER RACK B	Shelf 2	3.3F 5.5V Ultracapacitor	R2 C7
3133	BAKER RACK B	Shelf 2	0.005uF 8000V	R2 C8
3134	BAKER RACK B	Shelf 2	33uF 10V	R3 C1
3135	BAKER RACK B	Shelf 2	10uF 15V	R3 C2
3136	BAKER RACK B	Shelf 2	22uF 16V	R3 C3
3137	BAKER RACK B	Shelf 2	47uF 16V	R3 C4
3138	BAKER RACK B	Shelf 2	0.01uF 25V	R3 C5
3139	BAKER RACK B	Shelf 2	15uF 50V	R3 C6
3140	BAKER RACK B	Shelf 2	100uF 63V	R3 C7
3141	BAKER RACK B	Shelf 2	3300uF 63V	R3 C8
3142	BAKER RACK B	Shelf 2	47uF 10V	R4 C1
3143	BAKER RACK B	Shelf 2	0.047uF 80V/0.01uF 80V	R4 C2
3144	BAKER RACK B	Shelf 2	0.022uF 100V	R4 C3
3145	BAKER RACK B	Shelf 2	1uF 100V	R4 C4
3146	BAKER RACK B	Shelf 2	2.2uF 100V	R4 C5
3147	BAKER RACK B	Shelf 2	33uF 100V	R4 C6
3148	BAKER RACK B	Shelf 2	47uF 100V	R4 C7
3149	BAKER RACK B	Shelf 2	22uF 250V	R4 C8
3150	BAKER RACK B	Shelf 2	47uF 35V	R5 C1
3151	BAKER RACK B	Shelf 2	100uF 63V; 100uF 350V	R5 C2
3152	BAKER RACK B	Shelf 2	100uF 63V (second bin); 80uF 330V	R5 C3
3153	BAKER RACK B	Shelf 2	0.08uF 300V	R5 C4
3154	BAKER RACK B	Shelf 2	3uF 400V	R6 C1
3155	BAKER RACK B	Shelf 2	UNSORTED ASSORTED <100uF capacitors	R6 C2
3156	BAKER RACK B	Shelf 2	7.5uF 450V	R6 C3
3157	BAKER RACK B	Shelf 2	10uF 450V; 10uF 200V	R6 C4
3158	BAKER RACK B	Shelf 2	1uF 50V	R7 C1
3159	BAKER RACK B	Shelf 2	47uF 35V	R7 C2
3160	BAKER RACK B	Shelf 2	1uF 50V	R7 C3
3161	BAKER RACK B	Shelf 2	1uF 50V metal film	R7 C4
3162	BAKER RACK B	Shelf 2	Perf boards, SMT to PTH converters	
3163	BAKER RACK B	Shelf 2	Battery holders AAAA, C, and D	
3164	BAKER RACK B	Shelf 2	SMT tooling	
3165	BAKER RACK B	Shelf 2	SMT and PTH LEDs	
3166	BAKER RACK B	Shelf 2	SMT crystals	
3167	BAKER RACK B	Shelf 2	SMT and PTH LEDs (sample books)	
3168	BAKER RACK B	Shelf 1	Flash bulbs; Large heat sinks; rotary switches 1; rotary switches 2	
3169	BAKER RACK B	Shelf 1	Odd connectors	
3170	BAKER RACK B	Shelf 1	Breadboard parts	
3171	BAKER RACK B	Shelf 1	Third hand parts	
3172	BAKER RACK B	Shelf 1	IC sockets with long leads	
3173	BAKER RACK B	Shelf 1	Extra fuses - <1A, 1A-10A, >10A, 50A, fuse holders, inline fuse holders	